

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333714-840

Luminaire Tested: **S125RDIW-S1090D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333714-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1340U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9684.3 lumens
Efficiency: N/A
Efficacy: 138.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	38
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	1.8
10°-20°	474.3	4.9
20°-30°	687.8	7.1
30°-40°	783.9	8.1
40°-50°	764.1	7.9
50°-60°	643.2	6.6
60°-70°	450.9	4.7
70°-80°	231.8	2.4
80°-90°	62.2	0.6
90°-100°	64.1	0.7
100°-110°	395.0	4.1
110°-120°	716.5	7.4
120°-130°	919.5	9.5
130°-140°	989.0	10.2
140°-150°	928.3	9.6
150°-160°	750.9	7.8
160°-170°	485.7	5.0
170°-180°	167.5	1.7
0°-30°	1331.9	13.8
0°-40°	2115.8	21.8
0°-60°	3523.1	36.4
0°-90°	4267.9	44.1
90°-120°	1175.6	12.1
90°-150°	4012.4	41.4
90°-180°	5416.0	55.9
0°-180°	9684.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	12	21	27	31	7
95°	74	68	21	27	28	95
105°	384	389	390	390	388	408
115°	722	728	730	724	716	715
125°	1026	1035	1036	1030	1026	916
135°	1280	1287	1285	1282	1275	986
145°	1484	1486	1487	1487	1480	928
155°	1634	1627	1629	1632	1623	753
165°	1725	1717	1718	1725	1716	487
175°	1764	1757	1757	1767	1756	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.3	24.1	22.9	21.6	20.4	19.9	20.1	20.2	20.4	20.5	20.8
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4
92.5°	20.1	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4
95°	74.5	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4
97.5°	155.6	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1
100°	218.3	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2
102.5°	282.2	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1
105°	384.5	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2
110°	559.7	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	624.5	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0
115°	721.8	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4
117.5°	822.4	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7
120°	885.1	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3
122.5°	940.6	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8
125°	1026.4	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4
127.5°	1108.2	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4
130°	1158.4	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5
132.5°	1208.7	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3
135°	1280.1	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8
137.5°	1345.7	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3
140°	1388.6	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5
142.5°	1427.2	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8
145°	1484.0	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9
147.5°	1533.7	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1
150°	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7
152.5°	1595.4	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9
155°	1634.4	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0
157.5°	1664.5	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9
160°	1685.4	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0
162.5°	1702.1	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2
165°	1724.6	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8
167.5°	1741.3	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7
170°	1750.8	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2
172.5°	1757.1	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3
175°	1763.8	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6
177.5°	1767.0	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	21.1	21.4	21.7	21.8	21.7	21.7	21.6	21.5
90°	23.8	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	23.8	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	23.8	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	48.0	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	140.9	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	273.9	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.3	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	560.5	559.7	558.8	558.5	558.8	559.1	559.4	559.7



TEST NUMBER: P333714-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	626.9	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	727.3	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	824.2	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.7	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	946.2	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1033.2	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.8	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1164.6	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1213.0	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1284.1	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.4	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.1	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1430.9	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.2	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.5	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.3	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1593.5	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1630.9	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1661.9	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1681.2	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1698.8	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1721.5	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1738.8	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1747.6	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1754.4	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1761.9	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1765.0	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)