

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333716

Luminaire Tested: **S125RDIW-S1090D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333716
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10500.0 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35																				
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26																				
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22																				
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																				
6	62	50	43	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17																				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14																				
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12																				
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.5
10°-20°	462.1	4.4
20°-30°	732.6	7.0
30°-40°	883.5	8.4
40°-50°	789.0	7.5
50°-60°	605.0	5.8
60°-70°	393.2	3.7
70°-80°	191.2	1.8
80°-90°	49.9	0.5
90°-100°	73.8	0.7
100°-110°	454.8	4.3
110°-120°	824.9	7.9
120°-130°	1058.6	10.1
130°-140°	1138.6	10.8
140°-150°	1068.8	10.2
150°-160°	864.5	8.2
160°-170°	559.1	5.3
170°-180°	192.9	1.8
0°-30°	1352.3	12.9
0°-40°	2235.8	21.3
0°-60°	3629.8	34.6
0°-90°	4264.0	40.6
90°-120°	1353.5	12.9
90°-150°	4619.5	44.0
90°-180°	6236.0	59.4
0°-180°	10500.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	37
90°	36	2	36	2	36	17
95°	32	86	32	86	32	26
105°	447	443	447	443	447	404
115°	825	831	825	831	825	819
125°	1182	1182	1182	1182	1182	1051
135°	1468	1474	1468	1474	1468	1133
145°	1704	1709	1704	1709	1704	1064
155°	1868	1882	1868	1882	1868	861
165°	1975	1986	1975	1986	1975	557
175°	2022	2031	2022	2031	2022	192
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	19.1	18.4	17.6	17.4	17.8	18.6	17.7	16.8	16.5	16.2	16.2
90°	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4	25.8	24.1	21.7
92.5°	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4	25.8	24.1	22.0
95°	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4	25.8	24.1	36.8
97.5°	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2	64.6	74.1	99.2
100°	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2	212.1	261.9	260.6
102.5°	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3	324.8	334.2	333.4
105°	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0	567.9	567.8	567.2
110°	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3	646.3	647.3	646.6



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8	723.1	724.4	724.0
115°	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3	838.6	840.0	839.7
117.5°	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8	950.5	952.3	951.0
120°	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8	1021.5	1022.1	1021.1
122.5°	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4	1090.1	1090.8	1090.3
125°	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6	1190.9	1192.2	1192.2
127.5°	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1	1281.8	1282.6	1282.8
130°	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8	1341.8	1342.8	1342.4
132.5°	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6	1396.8	1397.0	1397.7
135°	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4	1479.1	1479.8	1480.4
137.5°	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7	1554.6	1554.4	1555.0
140°	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5	1600.9	1600.2	1600.5
142.5°	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4	1647.3	1647.2	1646.7
145°	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3	1711.9	1711.6	1711.6
147.5°	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8	1767.4	1767.0	1766.6
150°	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2	1802.6	1801.9	1801.2
152.5°	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6	1833.9	1833.2	1832.6
155°	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7	1876.7	1875.7	1875.0
157.5°	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3	1912.3	1911.2	1911.1
160°	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5	1934.2	1932.9	1932.5
162.5°	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9	1954.0	1952.1	1951.8
165°	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0	1980.0	1978.0	1977.7
167.5°	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8	1999.4	1997.0	1996.7
170°	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0	2009.3	2006.6	2006.3
172.5°	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9	2017.5	2015.1	2014.5
175°	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5	2025.9	2023.2	2022.9
177.5°	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1	2030.2	2028.3	2028.0
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	16.3	15.8	15.9	15.4	14.3	16.5	17.6	17.6	17.0	16.5	15.9
90°	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5	4.2	6.9	9.5
92.5°	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2	21.3	19.4	17.6
95°	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8	84.8	83.8	82.8
97.5°	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1	180.9	182.7	184.6
100°	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4	252.4	253.4	254.4
102.5°	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9	326.1	327.4	328.7
105°	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6	443.9	445.3	446.6
107.5°	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
110°	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3	644.3	644.3	644.3



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0	719.8	720.6	721.4
115°	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0	832.6	834.3	836.0
117.5°	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9	946.8	946.7	946.7
120°	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1	1018.8	1018.5	1018.1
122.5°	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0	1084.2	1085.5	1086.8
125°	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7	1184.0	1186.4	1188.7
127.5°	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9	1277.6	1279.3	1281.0
130°	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7	1335.4	1337.1	1338.8
132.5°	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5	1393.5	1395.4	1397.4
135°	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7	1475.7	1477.8	1479.8
137.5°	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3	1551.0	1552.8	1554.5
140°	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7	1599.4	1600.0	1600.7
142.5°	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2	1643.6	1644.0	1644.4
145°	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6	1709.2	1709.9	1710.6
147.5°	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8	1765.6	1765.5	1765.4
150°	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1801.2	1800.6	1799.9
152.5°	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8	1835.4	1833.9	1832.4
155°	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7	1879.7	1877.7	1875.7
157.5°	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3	1915.1	1913.9	1912.7
160°	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4	1938.4	1936.4	1934.4
162.5°	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7	1957.7	1955.7	1953.6
165°	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6	1983.6	1981.5	1979.5
167.5°	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8	2002.8	2000.7	1998.6
170°	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7	2013.3	2011.0	2008.6
172.5°	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9	2020.6	2018.2	2015.9
175°	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7	2028.7	2026.7	2024.7
177.5°	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3	2032.7	2031.1	2029.5
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	15.9	16.4	16.4	17.9	16.8	17.8	18.1	17.9	18.2	18.6	18.3
90°	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4	29.1	30.8	32.1
92.5°	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4	29.1	30.8	31.8
95°	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4	29.1	30.8	31.6
97.5°	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2	45.8	36.3	31.6
100°	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2	112.4	62.6	37.0
102.5°	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3	305.9	296.5	280.4
105°	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.4
107.5°	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0	568.0	568.1	567.6
110°	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3	644.3	643.3	643.0



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8	720.6	719.3	718.4
115°	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3	836.0	834.6	833.0
117.5°	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8	947.1	945.3	944.0
120°	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8	1020.1	1019.5	1018.3
122.5°	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4	1088.8	1088.1	1086.8
125°	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6	1188.2	1186.9	1185.7
127.5°	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1	1280.4	1279.6	1278.0
130°	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8	1339.8	1338.8	1337.4
132.5°	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6	1396.4	1396.2	1395.2
135°	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4	1477.8	1477.1	1475.7
137.5°	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7	1554.8	1555.0	1554.2
140°	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5	1602.2	1602.9	1602.2
142.5°	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4	1647.6	1647.7	1646.8
145°	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3	1712.6	1712.9	1712.1
147.5°	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8	1768.2	1768.6	1767.6
150°	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2	1803.9	1804.6	1803.6
152.5°	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6	1835.2	1835.9	1835.0
155°	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7	1878.7	1879.7	1878.8
157.5°	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3	1914.4	1915.5	1914.7
160°	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5	1936.9	1938.2	1937.6
162.5°	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9	1957.8	1959.6	1959.1
165°	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0	1984.1	1986.1	1985.7
167.5°	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8	2004.2	2006.6	2006.3
170°	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0	2014.7	2017.3	2017.2
172.5°	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9	2022.3	2024.7	2024.4
175°	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5	2031.2	2033.9	2033.7
177.5°	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1	2033.9	2035.8	2035.7
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	19.0	18.7	18.9	19.1	18.9	18.7	19.0	18.3	18.6	18.2	17.9
90°	33.1	34.1	35.1	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4
92.5°	32.3	32.8	33.3	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4
95°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4
97.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2
100°	35.6	34.3	33.0	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2
102.5°	257.6	234.9	212.1	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3
105°	448.1	447.8	447.4	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6
107.5°	566.6	565.6	564.6	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0
110°	643.3	643.6	644.0	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	718.0	717.5	717.0	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8
115°	831.0	828.9	826.9	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3
117.5°	943.2	942.3	941.4	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8
120°	1016.6	1014.9	1013.3	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8
122.5°	1084.9	1082.9	1081.0	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4
125°	1184.7	1183.7	1182.7	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6
127.5°	1275.5	1273.1	1270.6	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1
130°	1335.8	1334.1	1332.4	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8
132.5°	1393.6	1391.9	1390.2	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6
135°	1473.7	1471.7	1469.7	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4
137.5°	1552.4	1550.7	1548.9	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7
140°	1600.2	1598.2	1596.2	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5
142.5°	1644.7	1642.7	1640.7	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4
145°	1710.1	1708.1	1706.1	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3
147.5°	1765.2	1762.8	1760.4	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8
150°	1800.9	1798.2	1795.6	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2
152.5°	1832.6	1830.2	1827.8	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6
155°	1876.2	1873.5	1870.8	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7
157.5°	1912.0	1909.3	1906.6	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3
160°	1934.9	1932.2	1929.5	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5
162.5°	1956.2	1953.2	1950.3	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9
165°	1983.1	1980.4	1977.7	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0
167.5°	2003.3	2000.3	1997.3	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8
170°	2014.2	2011.2	2008.1	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0
172.5°	2021.4	2018.4	2015.4	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9
175°	2030.7	2027.7	2024.7	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5
177.5°	2033.5	2031.4	2029.2	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	18.1	17.8	16.8	17.9	16.4	16.4	15.9	15.9	16.5	17.0	17.6
90°	25.8	24.1	21.7	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5
92.5°	25.8	24.1	22.0	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2
95°	25.8	24.1	36.8	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8
97.5°	64.6	74.1	99.2	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1
100°	212.1	261.9	260.6	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4
102.5°	324.8	334.2	333.4	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9
105°	448.6	448.6	448.6	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6
107.5°	567.9	567.8	567.2	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8
110°	646.3	647.3	646.6	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	723.1	724.4	724.0	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0
115°	838.6	840.0	839.7	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0
117.5°	950.5	952.3	951.0	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9
120°	1021.5	1022.1	1021.1	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1
122.5°	1090.1	1090.8	1090.3	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0
125°	1190.9	1192.2	1192.2	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7
127.5°	1281.8	1282.6	1282.8	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9
130°	1341.8	1342.8	1342.4	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7
132.5°	1396.8	1397.0	1397.7	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5
135°	1479.1	1479.8	1480.4	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7
137.5°	1554.6	1554.4	1555.0	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3
140°	1600.9	1600.2	1600.5	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7
142.5°	1647.3	1647.2	1646.7	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2
145°	1711.9	1711.6	1711.6	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6
147.5°	1767.4	1767.0	1766.6	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8
150°	1802.6	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9
152.5°	1833.9	1833.2	1832.6	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8
155°	1876.7	1875.7	1875.0	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7
157.5°	1912.3	1911.2	1911.1	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3
160°	1934.2	1932.9	1932.5	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4
162.5°	1954.0	1952.1	1951.8	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7
165°	1980.0	1978.0	1977.7	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6
167.5°	1999.4	1997.0	1996.7	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8
170°	2009.3	2006.6	2006.3	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7
172.5°	2017.5	2015.1	2014.5	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9
175°	2025.9	2023.2	2022.9	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7
177.5°	2030.2	2028.3	2028.0	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.6	16.5	14.3	15.4	15.9	15.8	16.3	16.2	16.2	16.5	16.8
90°	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4
92.5°	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4
95°	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4
97.5°	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2
100°	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2
102.5°	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3
105°	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0
110°	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8
115°	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3
117.5°	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8
120°	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8
122.5°	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4
125°	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6
127.5°	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1
130°	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8
132.5°	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6
135°	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4
137.5°	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7
140°	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5
142.5°	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4
145°	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3
147.5°	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8
150°	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2
152.5°	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6
155°	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7
157.5°	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3
160°	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5
162.5°	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9
165°	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0
167.5°	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8
170°	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0
172.5°	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9
175°	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5
177.5°	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	17.7	18.6	17.8	17.4	17.6	18.4	19.1
90°	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333716

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)