

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333715-840

Luminaire Tested: **S125RDIW-S1090D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333715-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8965.0 lumens  
Efficiency: N/A  
Efficacy: 128.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.7	1.9
10°-20°	474.3	5.3
20°-30°	687.8	7.7
30°-40°	783.9	8.7
40°-50°	764.1	8.5
50°-60°	643.2	7.2
60°-70°	450.9	5.0
70°-80°	231.8	2.6
80°-90°	62.2	0.7
90°-100°	112.7	1.3
100°-110°	332.9	3.7
110°-120°	563.9	6.3
120°-130°	742.1	8.3
130°-140°	831.6	9.3
140°-150°	815.0	9.1
150°-160°	684.5	7.6
160°-170°	455.0	5.1
170°-180°	159.2	1.8
0°-30°	1331.9	14.9
0°-40°	2115.8	23.6
0°-60°	3523.1	39.3
0°-90°	4267.9	47.6
90°-120°	1009.6	11.3
90°-150°	3398.3	37.9
90°-180°	4697.0	52.4
0°-180°	8965.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	12	21	27	31	8
95°	85	88	101	110	113	91
105°	299	305	313	321	325	319
115°	565	570	572	571	570	558
125°	824	831	833	831	829	738
135°	1072	1079	1081	1080	1076	826
145°	1298	1303	1307	1307	1303	811
155°	1486	1486	1487	1491	1486	684
165°	1615	1613	1614	1618	1611	455
175°	1679	1674	1674	1681	1673	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.3	24.1	22.9	21.6	20.4	19.9	20.1	20.2	20.4	20.6	20.8
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4
92.5°	31.7	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2
95°	85.1	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9
97.5°	141.5	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5
100°	183.4	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1
102.5°	228.4	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2
105°	298.7	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9
107.5°	376.2	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7
110°	429.7	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0



TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.1	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9
115°	564.6	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2
117.5°	645.3	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3
120°	695.6	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5
122.5°	750.1	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6
125°	823.9	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5
127.5°	902.5	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3
130°	949.7	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6
132.5°	996.8	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8
135°	1071.6	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8
137.5°	1141.8	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6
140°	1186.8	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9
142.5°	1231.9	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7
145°	1298.2	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4
147.5°	1359.5	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2
150°	1400.4	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3
152.5°	1433.9	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6
155°	1485.5	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9
157.5°	1531.6	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2
160°	1558.8	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4
162.5°	1583.0	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8
165°	1615.2	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1
167.5°	1642.4	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9
170°	1657.1	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7
172.5°	1667.6	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1
175°	1679.4	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9
177.5°	1685.4	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	21.1	21.4	21.7	21.8	21.7	21.7	21.6	21.5
90°	23.8	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	54.1	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	104.9	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	164.4	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	205.7	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	248.0	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	316.6	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	390.5	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	441.9	442.7	443.6	443.9	443.6	443.3	443.0	442.7





TEST NUMBER: P333715-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.3	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.9	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.5	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.4	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.9	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	908.0	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.3	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.5	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.0	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1198.5	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.0	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1366.9	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.2	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1489.1	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1532.4	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1558.5	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1583.2	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1616.2	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1640.7	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1655.4	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1665.9	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1677.6	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1682.9	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)