

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333719

Luminaire Tested: **S125RDIW-S1090D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333719  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9634.6 lumens  
Efficiency: N/A  
Efficacy: 125.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.1	1.7
10°-20°	469.7	4.9
20°-30°	681.1	7.1
30°-40°	776.2	8.1
40°-50°	756.6	7.9
50°-60°	636.9	6.6
60°-70°	446.5	4.6
70°-80°	229.5	2.4
80°-90°	62.2	0.6
90°-100°	129.8	1.3
100°-110°	383.3	4.0
110°-120°	649.2	6.7
120°-130°	854.4	8.9
130°-140°	957.4	9.9
140°-150°	938.3	9.7
150°-160°	788.1	8.2
160°-170°	523.9	5.4
170°-180°	183.3	1.9
0°-30°	1318.9	13.7
0°-40°	2095.1	21.7
0°-60°	3488.6	36.2
0°-90°	4226.8	43.9
90°-120°	1162.3	12.1
90°-150°	3912.5	40.6
90°-180°	5408.0	56.1
0°-180°	9634.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	2	13	24	32	36	9
95°	98	102	116	126	130	105
105°	344	352	360	369	374	367
115°	650	656	659	658	656	643
125°	949	957	959	956	955	849
135°	1234	1242	1244	1244	1238	951
145°	1495	1501	1505	1505	1501	934
155°	1710	1710	1712	1717	1710	787
165°	1860	1857	1858	1863	1855	524
175°	1934	1928	1927	1935	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.1	24.0	22.9	21.7	20.6	20.1	20.3	20.6	20.8	21.0	21.4
90°	1.5	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8
92.5°	36.5	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1
95°	98.0	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5
97.5°	162.9	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1
100°	211.1	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8
102.5°	263.0	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3
105°	343.9	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5
107.5°	433.1	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6
110°	494.7	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7



TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	557.4	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5
115°	650.0	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7
117.5°	742.9	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6
120°	800.8	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9
122.5°	863.6	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9
125°	948.6	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5
127.5°	1039.1	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7
130°	1093.4	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6
132.5°	1147.7	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1
135°	1233.7	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2
137.5°	1314.5	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0
140°	1366.4	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1
142.5°	1418.3	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7
145°	1494.6	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1
147.5°	1565.2	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9
150°	1612.2	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8
152.5°	1650.8	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2
155°	1710.3	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1
157.5°	1763.3	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9
160°	1794.7	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0
162.5°	1822.5	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1
165°	1859.6	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4
167.5°	1890.9	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9
170°	1907.8	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8
172.5°	1919.9	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9
175°	1933.5	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4
177.5°	1940.4	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	21.7	22.0	22.4	22.5	22.5	22.4	22.4	22.4
90°	27.5	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	62.3	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	120.8	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	189.3	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	236.8	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	285.6	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	364.5	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	449.6	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	508.8	509.8	510.8	511.1	510.8	510.4	510.1	509.8





TEST NUMBER: P333719

CATALOG NUMBER: S125RDIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.0	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.4	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	748.9	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.7	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.9	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.4	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.3	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.8	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.4	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1379.8	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.1	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1573.7	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.0	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1714.4	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1764.2	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1794.4	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1822.7	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1860.7	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1888.9	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1905.8	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1917.9	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1931.5	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1937.6	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)