

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333719-840

Luminaire Tested: **S125RDIW-S1090D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333719-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9729.6 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20								20		
RC	80					70						30								10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	106	106	106	106		97	97	97	97		80	80	80		65	65	65		50	50	50	44
1	97	92	89	85		88	85	81	79		70	68	66		57	56	54		45	44	43	37
2	88	81	75	70		80	74	69	65		62	58	55		50	48	45		40	38	36	32
3	80	71	64	58		73	65	59	54		55	50	46		45	41	39		35	33	31	27
4	74	63	55	49		67	58	51	46		49	44	40		40	36	33		32	29	27	23
5	68	56	48	42		62	52	45	40		44	38	34		36	32	29		29	26	24	20
6	62	50	43	37		57	47	40	34		39	34	30		32	28	25		26	23	21	18
7	58	46	38	32		53	42	35	30		36	30	26		30	25	22		24	21	19	16
8	53	41	34	29		49	38	32	27		32	27	23		27	23	20		22	19	17	14
9	50	38	30	25		46	35	28	24		30	25	21		25	21	18		20	17	15	13
10	46	35	28	23		43	32	26	21		27	22	19		23	19	16		19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	1.7
10°-20°	474.3	4.9
20°-30°	687.8	7.1
30°-40°	783.9	8.1
40°-50°	764.1	7.9
50°-60°	643.2	6.6
60°-70°	450.9	4.6
70°-80°	231.8	2.4
80°-90°	62.8	0.6
90°-100°	131.1	1.3
100°-110°	387.1	4.0
110°-120°	655.6	6.7
120°-130°	862.9	8.9
130°-140°	966.8	9.9
140°-150°	947.6	9.7
150°-160°	795.9	8.2
160°-170°	529.1	5.4
170°-180°	185.2	1.9
0°-30°	1331.9	13.7
0°-40°	2115.8	21.7
0°-60°	3523.1	36.2
0°-90°	4268.5	43.9
90°-120°	1173.8	12.1
90°-150°	3951.1	40.6
90°-180°	5461.0	56.1
0°-180°	9729.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	2	14	24	32	37	9
95°	99	103	117	128	131	106
105°	347	355	364	373	378	371
115°	656	662	666	664	663	649
125°	958	967	969	966	964	858
135°	1246	1255	1256	1256	1250	960
145°	1509	1515	1520	1520	1515	943
155°	1727	1727	1729	1734	1727	795
165°	1878	1875	1876	1882	1873	530
175°	1953	1947	1946	1954	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.3	24.2	23.1	21.9	20.8	20.3	20.5	20.8	21.0	21.2	21.6
90°	1.5	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1
92.5°	36.9	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7
95°	99.0	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7
97.5°	164.5	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9
100°	213.2	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1
102.5°	265.6	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1
105°	347.3	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1
107.5°	437.4	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0
110°	499.6	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.9	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1
115°	656.4	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2
117.5°	750.2	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0
120°	808.7	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9
122.5°	872.1	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5
125°	958.0	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0
127.5°	1049.4	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0
130°	1104.2	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5
132.5°	1159.0	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5
135°	1245.9	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5
137.5°	1327.5	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1
140°	1379.9	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7
142.5°	1432.3	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8
145°	1509.3	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9
147.5°	1580.6	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4
150°	1628.1	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7
152.5°	1667.1	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5
155°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0
157.5°	1780.7	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3
160°	1812.4	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7
162.5°	1840.5	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1
165°	1877.9	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7
167.5°	1909.6	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5
170°	1926.6	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6
172.5°	1938.8	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8
175°	1952.6	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4
177.5°	1959.5	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	21.9	22.2	22.6	22.7	22.7	22.6	22.6	22.6
90°	27.8	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	62.9	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	122.0	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	191.2	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	239.1	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	288.4	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	368.1	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	454.0	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	513.8	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333719-840

CATALOG NUMBER: S125RDIW-S1090D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	573.6	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.9	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.3	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.3	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	967.3	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.7	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1114.2	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1170.2	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.5	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1393.4	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.2	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1589.2	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1673.3	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1731.3	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1781.6	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1812.1	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1840.7	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1879.1	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1907.5	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1924.6	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1936.8	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1950.6	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1956.7	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)