

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333668

Luminaire Tested: **S125RDIW-S610D1050U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333668  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1050U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6590.0 lumens  
Efficiency: N/A  
Efficacy: 145.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	29	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	1.3
10°-20°	260.1	3.9
20°-30°	412.3	6.3
30°-40°	497.2	7.5
40°-50°	444.0	6.7
50°-60°	340.5	5.2
60°-70°	221.3	3.4
70°-80°	107.6	1.6
80°-90°	28.5	0.4
90°-100°	49.6	0.8
100°-110°	305.6	4.6
110°-120°	554.2	8.4
120°-130°	711.2	10.8
130°-140°	765.0	11.6
140°-150°	718.0	10.9
150°-160°	580.8	8.8
160°-170°	375.7	5.7
170°-180°	129.6	2.0
0°-30°	761.1	11.5
0°-40°	1258.3	19.1
0°-60°	2042.9	31.0
0°-90°	2400.3	36.4
90°-120°	909.3	13.8
90°-150°	3103.6	47.1
90°-180°	4190.0	63.6
0°-180°	6590.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	21
90°	24	1	24	1	24	11
95°	21	58	21	58	21	18
105°	300	297	300	297	300	272
115°	554	558	554	558	554	550
125°	794	794	794	794	794	706
135°	986	990	986	990	986	761
145°	1145	1148	1145	1148	1145	715
155°	1255	1264	1255	1264	1255	578
165°	1327	1334	1327	1334	1327	374
175°	1358	1364	1358	1364	1358	129
180°	1364	1364	1364	1364	1364	



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	11.5	11.1	10.7	10.5	10.7	11.1	10.6	10.1	9.8	9.6	9.6
90°	24.3	23.6	22.9	22.3	21.6	20.7	19.6	18.4	17.3	16.2	14.6
92.5°	22.7	22.3	22.0	21.7	21.4	20.7	19.6	18.4	17.3	16.2	14.8
95°	21.2	21.2	21.2	21.2	21.2	20.7	19.6	18.4	17.3	16.2	24.7
97.5°	21.2	21.2	21.2	21.2	21.2	24.4	30.7	37.1	43.4	49.8	66.7
100°	21.2	22.1	23.0	23.9	24.8	42.0	75.5	109.0	142.5	176.0	175.1
102.5°	127.2	142.5	157.8	173.1	188.4	199.2	205.5	211.8	218.2	224.5	224.0
105°	300.4	300.6	300.8	301.1	301.3	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	378.7	379.3	380.0	380.7	381.4	381.7	381.6	381.6	381.5	381.5	381.0
110°	432.9	432.6	432.4	432.2	432.0	432.2	432.9	433.5	434.2	434.9	434.4



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.4	481.7	482.0	482.4	482.7	483.3	484.1	485.0	485.8	486.7	486.4
115°	554.2	555.6	556.9	558.3	559.6	560.7	561.6	562.5	563.4	564.3	564.1
117.5°	631.9	632.5	633.1	633.7	634.2	635.1	636.3	637.5	638.6	639.8	638.9
120°	679.6	680.8	681.9	683.0	684.1	684.9	685.4	685.8	686.3	686.7	686.0
122.5°	725.0	726.3	727.6	728.9	730.2	731.0	731.5	731.9	732.4	732.8	732.5
125°	793.9	794.6	795.3	796.0	796.6	797.4	798.3	799.2	800.1	801.0	801.0
127.5°	852.0	853.6	855.3	857.0	858.6	859.7	860.2	860.7	861.2	861.7	861.8
130°	894.1	895.2	896.3	897.4	898.5	899.4	900.1	900.8	901.5	902.1	901.9
132.5°	932.9	934.0	935.1	936.3	937.4	938.0	938.1	938.3	938.4	938.6	939.0
135°	986.1	987.4	988.8	990.1	991.5	992.4	992.8	993.3	993.7	994.2	994.6
137.5°	1039.5	1040.7	1041.8	1043.0	1044.2	1044.7	1044.6	1044.5	1044.4	1044.3	1044.7
140°	1071.0	1072.4	1073.7	1075.1	1076.4	1076.9	1076.4	1076.0	1075.5	1075.1	1075.3
142.5°	1101.0	1102.3	1103.7	1105.0	1106.4	1107.0	1106.9	1106.8	1106.7	1106.6	1106.3
145°	1144.9	1146.2	1147.6	1148.9	1150.3	1150.8	1150.6	1150.4	1150.2	1149.9	1149.9
147.5°	1181.1	1182.7	1184.3	1185.9	1187.6	1188.2	1188.0	1187.7	1187.4	1187.1	1186.9
150°	1204.5	1206.3	1208.1	1209.9	1211.7	1212.4	1212.0	1211.5	1211.1	1210.6	1210.2
152.5°	1226.4	1228.0	1229.6	1231.2	1232.9	1233.4	1233.0	1232.5	1232.1	1231.6	1231.2
155°	1255.1	1256.9	1258.7	1260.5	1262.3	1262.9	1262.2	1261.5	1260.8	1260.2	1259.7
157.5°	1279.2	1281.0	1282.8	1284.6	1286.4	1286.9	1286.2	1285.5	1284.8	1284.0	1284.0
160°	1294.6	1296.4	1298.2	1300.0	1301.7	1302.2	1301.3	1300.4	1299.5	1298.6	1298.4
162.5°	1308.3	1310.3	1312.3	1314.2	1316.2	1316.6	1315.3	1314.1	1312.8	1311.5	1311.3
165°	1326.9	1328.7	1330.5	1332.3	1334.1	1334.3	1333.0	1331.6	1330.3	1328.9	1328.7
167.5°	1339.9	1341.9	1343.9	1345.9	1348.0	1348.2	1346.5	1344.9	1343.3	1341.7	1341.5
170°	1347.1	1349.2	1351.2	1353.2	1355.2	1355.4	1353.6	1351.8	1350.0	1348.2	1347.9
172.5°	1352.0	1354.0	1356.0	1358.1	1360.1	1360.3	1358.7	1357.1	1355.4	1353.8	1353.4
175°	1358.3	1360.3	1362.3	1364.3	1366.4	1366.5	1364.7	1362.9	1361.1	1359.3	1359.1
177.5°	1361.9	1363.4	1364.8	1366.2	1367.7	1367.8	1366.5	1365.2	1364.0	1362.7	1362.5
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	9.6	9.3	9.3	8.9	8.3	9.4	10.0	9.9	9.7	9.4	9.2
90°	13.0	11.5	9.9	8.2	6.4	4.6	2.8	1.0	2.8	4.6	6.4
92.5°	13.4	12.0	10.6	10.5	11.8	13.1	14.3	15.6	14.3	13.1	11.8
95°	33.3	41.8	50.3	55.0	55.6	56.3	57.0	57.6	57.0	56.3	55.6
97.5°	83.6	100.5	117.4	125.2	124.0	122.8	121.6	120.4	121.6	122.8	124.0
100°	174.2	173.3	172.4	171.6	170.9	170.2	169.6	168.9	169.6	170.2	170.9
102.5°	223.4	222.9	222.4	221.7	220.8	220.0	219.1	218.3	219.1	220.0	220.8
105°	301.4	301.4	301.4	300.9	300.0	299.1	298.2	297.3	298.2	299.1	300.0
107.5°	380.6	380.1	379.7	379.5	379.5	379.5	379.5	379.5	379.5	379.5	379.5
110°	434.0	433.5	433.1	432.9	432.9	432.9	432.9	432.9	432.9	432.9	432.9





TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	486.1	485.9	485.6	485.2	484.6	484.1	483.6	483.0	483.6	484.1	484.6
115°	563.9	563.7	563.4	562.8	561.6	560.5	559.4	558.3	559.4	560.5	561.6
117.5°	638.1	637.2	636.4	636.0	636.0	636.1	636.1	636.2	636.1	636.1	636.0
120°	685.4	684.7	684.0	683.8	684.0	684.2	684.5	684.7	684.5	684.2	684.0
122.5°	732.2	731.9	731.6	731.0	730.1	729.3	728.4	727.6	728.4	729.3	730.1
125°	801.0	801.0	801.0	800.2	798.6	797.1	795.5	793.9	795.5	797.1	798.6
127.5°	862.0	862.1	862.2	861.7	860.6	859.5	858.4	857.2	858.4	859.5	860.6
130°	901.7	901.5	901.2	900.6	899.4	898.3	897.2	896.1	897.2	898.3	899.4
132.5°	939.5	940.0	940.5	940.1	938.8	937.5	936.2	934.9	936.2	937.5	938.8
135°	995.1	995.5	996.0	995.5	994.2	992.8	991.5	990.1	991.5	992.8	994.2
137.5°	1045.2	1045.6	1046.0	1045.6	1044.4	1043.2	1042.1	1040.9	1042.1	1043.2	1044.4
140°	1075.5	1075.8	1076.0	1075.9	1075.4	1075.0	1074.5	1074.1	1074.5	1075.0	1075.4
142.5°	1106.0	1105.7	1105.4	1105.1	1104.8	1104.6	1104.3	1104.0	1104.3	1104.6	1104.8
145°	1149.9	1149.9	1149.9	1149.7	1149.3	1148.8	1148.4	1147.9	1148.4	1148.8	1149.3
147.5°	1186.6	1186.3	1186.1	1186.0	1186.1	1186.2	1186.3	1186.3	1186.3	1186.2	1186.1
150°	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1210.2	1209.7	1209.3
152.5°	1230.8	1230.3	1229.9	1230.1	1231.1	1232.1	1233.1	1234.1	1233.1	1232.1	1231.1
155°	1259.3	1258.8	1258.4	1258.8	1260.2	1261.5	1262.9	1264.2	1262.9	1261.5	1260.2
157.5°	1283.9	1283.9	1283.9	1284.2	1285.1	1285.9	1286.7	1287.5	1286.7	1285.9	1285.1
160°	1298.2	1297.9	1297.7	1298.3	1299.6	1301.0	1302.3	1303.7	1302.3	1301.0	1299.6
162.5°	1311.1	1310.9	1310.6	1311.2	1312.6	1313.9	1315.3	1316.6	1315.3	1313.9	1312.6
165°	1328.5	1328.3	1328.0	1328.6	1330.0	1331.3	1332.7	1334.0	1332.7	1331.3	1330.0
167.5°	1341.2	1341.0	1340.8	1341.4	1342.8	1344.2	1345.6	1346.9	1345.6	1344.2	1342.8
170°	1347.7	1347.5	1347.3	1347.9	1349.5	1351.1	1352.7	1354.2	1352.7	1351.1	1349.5
172.5°	1353.0	1352.6	1352.2	1352.8	1354.4	1355.9	1357.5	1359.1	1357.5	1355.9	1354.4
175°	1358.8	1358.6	1358.4	1358.9	1360.3	1361.6	1363.0	1364.3	1363.0	1361.6	1360.3
177.5°	1362.4	1362.2	1362.0	1362.5	1363.5	1364.6	1365.7	1366.8	1365.7	1364.6	1363.5
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	9.2	9.6	9.6	10.5	9.9	10.5	10.8	10.7	10.9	11.1	11.0
90°	8.2	9.9	11.5	13.0	14.6	16.2	17.3	18.4	19.6	20.7	21.6
92.5°	10.5	10.6	12.0	13.4	14.8	16.2	17.3	18.4	19.6	20.7	21.4
95°	55.0	50.3	41.8	33.3	24.7	16.2	17.3	18.4	19.6	20.7	21.2
97.5°	125.2	117.4	100.5	83.6	66.7	49.8	43.4	37.1	30.7	24.4	21.2
100°	171.6	172.4	173.3	174.2	175.1	176.0	142.5	109.0	75.5	42.0	24.8
102.5°	221.7	222.4	222.9	223.4	224.0	224.5	218.2	211.8	205.5	199.2	188.4
105°	300.9	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.3
107.5°	379.5	379.7	380.1	380.6	381.0	381.5	381.5	381.6	381.6	381.7	381.4
110°	432.9	433.1	433.5	434.0	434.4	434.9	434.2	433.5	432.9	432.2	432.0



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	485.2	485.6	485.9	486.1	486.4	486.7	485.8	485.0	484.1	483.3	482.7
115°	562.8	563.4	563.7	563.9	564.1	564.3	563.4	562.5	561.6	560.7	559.6
117.5°	636.0	636.4	637.2	638.1	638.9	639.8	638.6	637.5	636.3	635.1	634.2
120°	683.8	684.0	684.7	685.4	686.0	686.7	686.3	685.8	685.4	684.9	684.1
122.5°	731.0	731.6	731.9	732.2	732.5	732.8	732.4	731.9	731.5	731.0	730.2
125°	800.2	801.0	801.0	801.0	801.0	801.0	800.1	799.2	798.3	797.4	796.6
127.5°	861.7	862.2	862.1	862.0	861.8	861.7	861.2	860.7	860.2	859.7	858.6
130°	900.6	901.2	901.5	901.7	901.9	902.1	901.5	900.8	900.1	899.4	898.5
132.5°	940.1	940.5	940.0	939.5	939.0	938.6	938.4	938.3	938.1	938.0	937.4
135°	995.5	996.0	995.5	995.1	994.6	994.2	993.7	993.3	992.8	992.4	991.5
137.5°	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4	1044.5	1044.6	1044.7	1044.2
140°	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5	1076.0	1076.4	1076.9	1076.4
142.5°	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7	1106.8	1106.9	1107.0	1106.4
145°	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2	1150.4	1150.6	1150.8	1150.3
147.5°	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4	1187.7	1188.0	1188.2	1187.6
150°	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1	1211.5	1212.0	1212.4	1211.7
152.5°	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1	1232.5	1233.0	1233.4	1232.9
155°	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8	1261.5	1262.2	1262.9	1262.3
157.5°	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8	1285.5	1286.2	1286.9	1286.4
160°	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5	1300.4	1301.3	1302.2	1301.7
162.5°	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8	1314.1	1315.3	1316.6	1316.2
165°	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3	1331.6	1333.0	1334.3	1334.1
167.5°	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3	1344.9	1346.5	1348.2	1348.0
170°	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0	1351.8	1353.6	1355.4	1355.2
172.5°	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4	1357.1	1358.7	1360.3	1360.1
175°	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1	1362.9	1364.7	1366.5	1366.4
177.5°	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0	1365.2	1366.5	1367.8	1367.7
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	11.4	11.3	11.4	11.5	11.4	11.3	11.4	11.0	11.1	10.9	10.7
90°	22.3	22.9	23.6	24.3	23.6	22.9	22.3	21.6	20.7	19.6	18.4
92.5°	21.7	22.0	22.3	22.7	22.3	22.0	21.7	21.4	20.7	19.6	18.4
95°	21.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2	20.7	19.6	18.4
97.5°	21.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2	24.4	30.7	37.1
100°	23.9	23.0	22.1	21.2	22.1	23.0	23.9	24.8	42.0	75.5	109.0
102.5°	173.1	157.8	142.5	127.2	142.5	157.8	173.1	188.4	199.2	205.5	211.8
105°	301.1	300.8	300.6	300.4	300.6	300.8	301.1	301.3	301.4	301.4	301.4
107.5°	380.7	380.0	379.3	378.7	379.3	380.0	380.7	381.4	381.7	381.6	381.6
110°	432.2	432.4	432.6	432.9	432.6	432.4	432.2	432.0	432.2	432.9	433.5



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.4	482.0	481.7	481.4	481.7	482.0	482.4	482.7	483.3	484.1	485.0
115°	558.3	556.9	555.6	554.2	555.6	556.9	558.3	559.6	560.7	561.6	562.5
117.5°	633.7	633.1	632.5	631.9	632.5	633.1	633.7	634.2	635.1	636.3	637.5
120°	683.0	681.9	680.8	679.6	680.8	681.9	683.0	684.1	684.9	685.4	685.8
122.5°	728.9	727.6	726.3	725.0	726.3	727.6	728.9	730.2	731.0	731.5	731.9
125°	796.0	795.3	794.6	793.9	794.6	795.3	796.0	796.6	797.4	798.3	799.2
127.5°	857.0	855.3	853.6	852.0	853.6	855.3	857.0	858.6	859.7	860.2	860.7
130°	897.4	896.3	895.2	894.1	895.2	896.3	897.4	898.5	899.4	900.1	900.8
132.5°	936.3	935.1	934.0	932.9	934.0	935.1	936.3	937.4	938.0	938.1	938.3
135°	990.1	988.8	987.4	986.1	987.4	988.8	990.1	991.5	992.4	992.8	993.3
137.5°	1043.0	1041.8	1040.7	1039.5	1040.7	1041.8	1043.0	1044.2	1044.7	1044.6	1044.5
140°	1075.1	1073.7	1072.4	1071.0	1072.4	1073.7	1075.1	1076.4	1076.9	1076.4	1076.0
142.5°	1105.0	1103.7	1102.3	1101.0	1102.3	1103.7	1105.0	1106.4	1107.0	1106.9	1106.8
145°	1148.9	1147.6	1146.2	1144.9	1146.2	1147.6	1148.9	1150.3	1150.8	1150.6	1150.4
147.5°	1185.9	1184.3	1182.7	1181.1	1182.7	1184.3	1185.9	1187.6	1188.2	1188.0	1187.7
150°	1209.9	1208.1	1206.3	1204.5	1206.3	1208.1	1209.9	1211.7	1212.4	1212.0	1211.5
152.5°	1231.2	1229.6	1228.0	1226.4	1228.0	1229.6	1231.2	1232.9	1233.4	1233.0	1232.5
155°	1260.5	1258.7	1256.9	1255.1	1256.9	1258.7	1260.5	1262.3	1262.9	1262.2	1261.5
157.5°	1284.6	1282.8	1281.0	1279.2	1281.0	1282.8	1284.6	1286.4	1286.9	1286.2	1285.5
160°	1300.0	1298.2	1296.4	1294.6	1296.4	1298.2	1300.0	1301.7	1302.2	1301.3	1300.4
162.5°	1314.2	1312.3	1310.3	1308.3	1310.3	1312.3	1314.2	1316.2	1316.6	1315.3	1314.1
165°	1332.3	1330.5	1328.7	1326.9	1328.7	1330.5	1332.3	1334.1	1334.3	1333.0	1331.6
167.5°	1345.9	1343.9	1341.9	1339.9	1341.9	1343.9	1345.9	1348.0	1348.2	1346.5	1344.9
170°	1353.2	1351.2	1349.2	1347.1	1349.2	1351.2	1353.2	1355.2	1355.4	1353.6	1351.8
172.5°	1358.1	1356.0	1354.0	1352.0	1354.0	1356.0	1358.1	1360.1	1360.3	1358.7	1357.1
175°	1364.3	1362.3	1360.3	1358.3	1360.3	1362.3	1364.3	1366.4	1366.5	1364.7	1362.9
177.5°	1366.2	1364.8	1363.4	1361.9	1363.4	1364.8	1366.2	1367.7	1367.8	1366.5	1365.2
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	10.8	10.5	9.9	10.5	9.6	9.6	9.2	9.2	9.4	9.7	9.9
90°	17.3	16.2	14.6	13.0	11.5	9.9	8.2	6.4	4.6	2.8	1.0
92.5°	17.3	16.2	14.8	13.4	12.0	10.6	10.5	11.8	13.1	14.3	15.6
95°	17.3	16.2	24.7	33.3	41.8	50.3	55.0	55.6	56.3	57.0	57.6
97.5°	43.4	49.8	66.7	83.6	100.5	117.4	125.2	124.0	122.8	121.6	120.4
100°	142.5	176.0	175.1	174.2	173.3	172.4	171.6	170.9	170.2	169.6	168.9
102.5°	218.2	224.5	224.0	223.4	222.9	222.4	221.7	220.8	220.0	219.1	218.3
105°	301.4	301.4	301.4	301.4	301.4	301.4	300.9	300.0	299.1	298.2	297.3
107.5°	381.5	381.5	381.0	380.6	380.1	379.7	379.5	379.5	379.5	379.5	379.5
110°	434.2	434.9	434.4	434.0	433.5	433.1	432.9	432.9	432.9	432.9	432.9



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	485.8	486.7	486.4	486.1	485.9	485.6	485.2	484.6	484.1	483.6	483.0
115°	563.4	564.3	564.1	563.9	563.7	563.4	562.8	561.6	560.5	559.4	558.3
117.5°	638.6	639.8	638.9	638.1	637.2	636.4	636.0	636.0	636.1	636.1	636.2
120°	686.3	686.7	686.0	685.4	684.7	684.0	683.8	684.0	684.2	684.5	684.7
122.5°	732.4	732.8	732.5	732.2	731.9	731.6	731.0	730.1	729.3	728.4	727.6
125°	800.1	801.0	801.0	801.0	801.0	801.0	800.2	798.6	797.1	795.5	793.9
127.5°	861.2	861.7	861.8	862.0	862.1	862.2	861.7	860.6	859.5	858.4	857.2
130°	901.5	902.1	901.9	901.7	901.5	901.2	900.6	899.4	898.3	897.2	896.1
132.5°	938.4	938.6	939.0	939.5	940.0	940.5	940.1	938.8	937.5	936.2	934.9
135°	993.7	994.2	994.6	995.1	995.5	996.0	995.5	994.2	992.8	991.5	990.1
137.5°	1044.4	1044.3	1044.7	1045.2	1045.6	1046.0	1045.6	1044.4	1043.2	1042.1	1040.9
140°	1075.5	1075.1	1075.3	1075.5	1075.8	1076.0	1075.9	1075.4	1075.0	1074.5	1074.1
142.5°	1106.7	1106.6	1106.3	1106.0	1105.7	1105.4	1105.1	1104.8	1104.6	1104.3	1104.0
145°	1150.2	1149.9	1149.9	1149.9	1149.9	1149.9	1149.7	1149.3	1148.8	1148.4	1147.9
147.5°	1187.4	1187.1	1186.9	1186.6	1186.3	1186.1	1186.0	1186.1	1186.2	1186.3	1186.3
150°	1211.1	1210.6	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6
152.5°	1232.1	1231.6	1231.2	1230.8	1230.3	1229.9	1230.1	1231.1	1232.1	1233.1	1234.1
155°	1260.8	1260.2	1259.7	1259.3	1258.8	1258.4	1258.8	1260.2	1261.5	1262.9	1264.2
157.5°	1284.8	1284.0	1284.0	1283.9	1283.9	1283.9	1284.2	1285.1	1285.9	1286.7	1287.5
160°	1299.5	1298.6	1298.4	1298.2	1297.9	1297.7	1298.3	1299.6	1301.0	1302.3	1303.7
162.5°	1312.8	1311.5	1311.3	1311.1	1310.9	1310.6	1311.2	1312.6	1313.9	1315.3	1316.6
165°	1330.3	1328.9	1328.7	1328.5	1328.3	1328.0	1328.6	1330.0	1331.3	1332.7	1334.0
167.5°	1343.3	1341.7	1341.5	1341.2	1341.0	1340.8	1341.4	1342.8	1344.2	1345.6	1346.9
170°	1350.0	1348.2	1347.9	1347.7	1347.5	1347.3	1347.9	1349.5	1351.1	1352.7	1354.2
172.5°	1355.4	1353.8	1353.4	1353.0	1352.6	1352.2	1352.8	1354.4	1355.9	1357.5	1359.1
175°	1361.1	1359.3	1359.1	1358.8	1358.6	1358.4	1358.9	1360.3	1361.6	1363.0	1364.3
177.5°	1364.0	1362.7	1362.5	1362.4	1362.2	1362.0	1362.5	1363.5	1364.6	1365.7	1366.8
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	10.0	9.4	8.3	8.9	9.3	9.3	9.6	9.6	9.6	9.8	10.1
90°	2.8	4.6	6.4	8.2	9.9	11.5	13.0	14.6	16.2	17.3	18.4
92.5°	14.3	13.1	11.8	10.5	10.6	12.0	13.4	14.8	16.2	17.3	18.4
95°	57.0	56.3	55.6	55.0	50.3	41.8	33.3	24.7	16.2	17.3	18.4
97.5°	121.6	122.8	124.0	125.2	117.4	100.5	83.6	66.7	49.8	43.4	37.1
100°	169.6	170.2	170.9	171.6	172.4	173.3	174.2	175.1	176.0	142.5	109.0
102.5°	219.1	220.0	220.8	221.7	222.4	222.9	223.4	224.0	224.5	218.2	211.8
105°	298.2	299.1	300.0	300.9	301.4	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	379.5	379.5	379.5	379.5	379.7	380.1	380.6	381.0	381.5	381.5	381.6
110°	432.9	432.9	432.9	432.9	433.1	433.5	434.0	434.4	434.9	434.2	433.5





TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.6	484.1	484.6	485.2	485.6	485.9	486.1	486.4	486.7	485.8	485.0
115°	559.4	560.5	561.6	562.8	563.4	563.7	563.9	564.1	564.3	563.4	562.5
117.5°	636.1	636.1	636.0	636.0	636.4	637.2	638.1	638.9	639.8	638.6	637.5
120°	684.5	684.2	684.0	683.8	684.0	684.7	685.4	686.0	686.7	686.3	685.8
122.5°	728.4	729.3	730.1	731.0	731.6	731.9	732.2	732.5	732.8	732.4	731.9
125°	795.5	797.1	798.6	800.2	801.0	801.0	801.0	801.0	801.0	800.1	799.2
127.5°	858.4	859.5	860.6	861.7	862.2	862.1	862.0	861.8	861.7	861.2	860.7
130°	897.2	898.3	899.4	900.6	901.2	901.5	901.7	901.9	902.1	901.5	900.8
132.5°	936.2	937.5	938.8	940.1	940.5	940.0	939.5	939.0	938.6	938.4	938.3
135°	991.5	992.8	994.2	995.5	996.0	995.5	995.1	994.6	994.2	993.7	993.3
137.5°	1042.1	1043.2	1044.4	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4	1044.5
140°	1074.5	1075.0	1075.4	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5	1076.0
142.5°	1104.3	1104.6	1104.8	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7	1106.8
145°	1148.4	1148.8	1149.3	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2	1150.4
147.5°	1186.3	1186.2	1186.1	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4	1187.7
150°	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1	1211.5
152.5°	1233.1	1232.1	1231.1	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1	1232.5
155°	1262.9	1261.5	1260.2	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8	1261.5
157.5°	1286.7	1285.9	1285.1	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8	1285.5
160°	1302.3	1301.0	1299.6	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5	1300.4
162.5°	1315.3	1313.9	1312.6	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8	1314.1
165°	1332.7	1331.3	1330.0	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3	1331.6
167.5°	1345.6	1344.2	1342.8	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3	1344.9
170°	1352.7	1351.1	1349.5	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0	1351.8
172.5°	1357.5	1355.9	1354.4	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4	1357.1
175°	1363.0	1361.6	1360.3	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1	1362.9
177.5°	1365.7	1364.6	1363.5	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0	1365.2
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	10.6	11.1	10.7	10.5	10.7	11.1	11.5
90°	19.6	20.7	21.6	22.3	22.9	23.6	24.3
92.5°	19.6	20.7	21.4	21.7	22.0	22.3	22.7
95°	19.6	20.7	21.2	21.2	21.2	21.2	21.2
97.5°	30.7	24.4	21.2	21.2	21.2	21.2	21.2
100°	75.5	42.0	24.8	23.9	23.0	22.1	21.2
102.5°	205.5	199.2	188.4	173.1	157.8	142.5	127.2
105°	301.4	301.4	301.3	301.1	300.8	300.6	300.4
107.5°	381.6	381.7	381.4	380.7	380.0	379.3	378.7
110°	432.9	432.2	432.0	432.2	432.4	432.6	432.9



TEST NUMBER: P333668

CATALOG NUMBER: S125RDIW-S610D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	484.1	483.3	482.7	482.4	482.0	481.7	481.4
115°	561.6	560.7	559.6	558.3	556.9	555.6	554.2
117.5°	636.3	635.1	634.2	633.7	633.1	632.5	631.9
120°	685.4	684.9	684.1	683.0	681.9	680.8	679.6
122.5°	731.5	731.0	730.2	728.9	727.6	726.3	725.0
125°	798.3	797.4	796.6	796.0	795.3	794.6	793.9
127.5°	860.2	859.7	858.6	857.0	855.3	853.6	852.0
130°	900.1	899.4	898.5	897.4	896.3	895.2	894.1
132.5°	938.1	938.0	937.4	936.3	935.1	934.0	932.9
135°	992.8	992.4	991.5	990.1	988.8	987.4	986.1
137.5°	1044.6	1044.7	1044.2	1043.0	1041.8	1040.7	1039.5
140°	1076.4	1076.9	1076.4	1075.1	1073.7	1072.4	1071.0
142.5°	1106.9	1107.0	1106.4	1105.0	1103.7	1102.3	1101.0
145°	1150.6	1150.8	1150.3	1148.9	1147.6	1146.2	1144.9
147.5°	1188.0	1188.2	1187.6	1185.9	1184.3	1182.7	1181.1
150°	1212.0	1212.4	1211.7	1209.9	1208.1	1206.3	1204.5
152.5°	1233.0	1233.4	1232.9	1231.2	1229.6	1228.0	1226.4
155°	1262.2	1262.9	1262.3	1260.5	1258.7	1256.9	1255.1
157.5°	1286.2	1286.9	1286.4	1284.6	1282.8	1281.0	1279.2
160°	1301.3	1302.2	1301.7	1300.0	1298.2	1296.4	1294.6
162.5°	1315.3	1316.6	1316.2	1314.2	1312.3	1310.3	1308.3
165°	1333.0	1334.3	1334.1	1332.3	1330.5	1328.7	1326.9
167.5°	1346.5	1348.2	1348.0	1345.9	1343.9	1341.9	1339.9
170°	1353.6	1355.4	1355.2	1353.2	1351.2	1349.2	1347.1
172.5°	1358.7	1360.3	1360.1	1358.1	1356.0	1354.0	1352.0
175°	1364.7	1366.5	1366.4	1364.3	1362.3	1360.3	1358.3
177.5°	1366.5	1367.8	1367.7	1366.2	1364.8	1363.4	1361.9
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3

(END OF REPORT)