

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333730-840

Luminaire Tested: **S125RDIW-S1270D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333730-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1050U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9158.7 lumens  
Efficiency: N/A  
Efficacy: 135.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	108	108	108	108		100	100	100	100		85	85	85		72	72	72		60	60	60	54	
1	99	95	91	87		92	88	85	82		75	73	71		64	62	60		53	52	51	46	
2	90	83	77	72		83	77	72	67		66	62	59		56	53	51		47	45	43	39	
3	82	73	66	60		76	68	62	57		59	54	50		50	46	43		42	39	37	33	
4	76	65	57	51		70	60	53	48		52	47	43		45	41	37		37	34	32	29	
5	69	58	50	44		64	54	47	41		47	41	37		40	36	32		34	31	28	25	
6	64	52	44	38		59	49	41	36		42	37	32		36	32	28		31	27	25	22	
7	59	47	39	34		55	44	37	32		38	33	29		33	29	25		28	25	22	20	
8	55	43	35	30		51	40	33	28		35	29	25		30	26	23		26	22	20	18	
9	51	39	32	27		48	37	30	25		32	27	23		28	24	20		24	21	18	16	
10	48	36	29	24		45	34	27	23		30	24	21		26	22	18		22	19	16	14	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.0	2.1
10°-20°	547.8	6.0
20°-30°	794.4	8.7
30°-40°	905.3	9.9
40°-50°	882.5	9.6
50°-60°	742.8	8.1
60°-70°	520.7	5.7
70°-80°	267.7	2.9
80°-90°	70.5	0.8
90°-100°	50.1	0.5
100°-110°	308.6	3.4
110°-120°	559.7	6.1
120°-130°	718.2	7.8
130°-140°	772.5	8.4
140°-150°	725.1	7.9
150°-160°	586.6	6.4
160°-170°	379.4	4.1
170°-180°	130.8	1.4
0°-30°	1538.2	16.8
0°-40°	2443.5	26.7
0°-60°	4068.9	44.4
0°-90°	4927.7	53.8
90°-120°	918.3	10.0
90°-150°	3134.2	34.2
90°-180°	4231.0	46.2
0°-180°	9158.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	9	16	21	24	6
95°	58	53	16	21	21	74
105°	300	304	304	304	303	318
115°	564	569	570	566	560	559
125°	802	808	809	805	802	716
135°	1000	1006	1004	1002	996	770
145°	1159	1161	1161	1162	1156	725
155°	1277	1271	1273	1275	1268	588
165°	1347	1341	1342	1347	1340	380
175°	1378	1372	1373	1380	1372	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.2	27.6	26.0	24.3	22.8	22.0	22.0	22.1	22.1	22.1	22.4
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.1	14.7	16.4	17.5
92.5°	15.8	14.4	13.2	11.9	10.6	10.7	12.1	13.5	14.9	16.4	17.5
95°	58.2	57.6	56.9	56.1	55.5	50.8	42.2	33.6	24.9	16.4	17.5
97.5°	121.6	122.8	124.0	125.2	126.4	118.6	101.5	84.4	67.4	50.3	43.8
100°	170.6	171.3	171.9	172.6	173.3	174.1	175.0	175.9	176.8	177.7	143.9
102.5°	220.5	221.3	222.2	223.0	223.9	224.6	225.1	225.6	226.2	226.7	220.4
105°	300.2	301.1	302.1	303.0	303.9	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	383.2	383.2	383.2	383.2	383.2	383.4	383.8	384.4	384.8	385.3	385.3
110°	437.2	437.2	437.2	437.2	437.2	437.4	437.8	438.3	438.7	439.2	438.5



TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.4	488.9	489.4	490.0	490.4	490.7	490.9	491.2	491.5	490.6
115°	563.8	564.9	566.0	567.1	568.4	569.0	569.3	569.5	569.7	569.9	569.0
117.5°	642.5	642.4	642.4	642.3	642.3	642.7	643.5	644.4	645.2	646.1	644.9
120°	691.5	691.3	690.9	690.7	690.5	690.7	691.5	692.2	692.8	693.5	693.1
122.5°	734.8	735.6	736.5	737.3	738.2	738.8	739.1	739.4	739.7	740.0	739.6
125°	801.7	803.3	805.0	806.5	808.1	808.9	808.9	808.9	808.9	808.9	808.0
127.5°	865.7	866.9	868.0	869.1	870.2	870.7	870.6	870.5	870.3	870.2	869.7
130°	904.9	906.1	907.2	908.3	909.5	910.1	910.4	910.6	910.8	911.0	910.4
132.5°	944.1	945.4	946.7	948.1	949.4	949.8	949.3	948.8	948.3	947.9	947.7
135°	999.9	1001.3	1002.6	1004.0	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5
137.5°	1051.2	1052.4	1053.5	1054.7	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7
140°	1084.7	1085.1	1085.6	1086.0	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1
142.5°	1114.9	1115.2	1115.5	1115.7	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6
145°	1159.2	1159.7	1160.1	1160.6	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5
147.5°	1198.0	1198.0	1197.9	1197.8	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1
150°	1222.5	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0
152.5°	1246.3	1245.3	1244.3	1243.2	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3
155°	1276.7	1275.4	1273.9	1272.6	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2
157.5°	1300.2	1299.4	1298.6	1297.8	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5
160°	1316.6	1315.1	1313.8	1312.4	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3
162.5°	1329.6	1328.3	1326.9	1325.5	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8
165°	1347.2	1345.8	1344.4	1343.1	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4
167.5°	1360.2	1358.9	1357.5	1356.0	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6
170°	1367.6	1366.0	1364.4	1362.8	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3
172.5°	1372.5	1370.9	1369.3	1367.8	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8
175°	1377.8	1376.4	1375.0	1373.7	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5
177.5°	1380.3	1379.2	1378.1	1377.0	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	22.6	22.8	23.0	23.1	22.9	22.8	22.7	22.5
90°	18.6	19.8	20.9	21.8	22.5	23.1	23.8	24.5
92.5°	18.6	19.8	20.9	21.6	21.9	22.2	22.5	22.9
95°	18.6	19.8	20.9	21.4	21.4	21.4	21.4	21.4
97.5°	37.5	31.0	24.6	21.4	21.4	21.4	21.4	21.4
100°	110.1	76.2	42.4	25.0	24.1	23.2	22.3	21.4
102.5°	213.9	207.5	201.2	190.3	174.8	159.4	143.9	128.5
105°	304.4	304.4	304.4	304.3	304.1	303.8	303.6	303.4
107.5°	385.4	385.4	385.5	385.2	384.5	383.7	383.0	382.4
110°	437.8	437.2	436.5	436.3	436.5	436.7	436.9	437.2





TEST NUMBER: P333730-840

CATALOG NUMBER: S125RDIW-S1270D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.8	488.9	488.1	487.5	487.2	486.8	486.5	486.1
115°	568.0	567.1	566.2	565.1	563.8	562.4	561.1	559.7
117.5°	643.8	642.6	641.4	640.5	640.0	639.3	638.7	638.1
120°	692.6	692.2	691.7	690.8	689.7	688.6	687.5	686.3
122.5°	739.1	738.7	738.2	737.4	736.1	734.8	733.5	732.2
125°	807.1	806.2	805.3	804.5	803.9	803.1	802.4	801.7
127.5°	869.2	868.7	868.2	867.1	865.5	863.7	862.0	860.4
130°	909.7	909.0	908.3	907.4	906.3	905.1	904.0	902.9
132.5°	947.6	947.4	947.3	946.6	945.5	944.3	943.2	942.1
135°	1003.1	1002.6	1002.2	1001.3	999.9	998.6	997.1	995.8
137.5°	1054.8	1054.9	1055.0	1054.5	1053.3	1052.1	1051.0	1049.8
140°	1086.6	1087.0	1087.5	1087.0	1085.7	1084.3	1083.0	1081.6
142.5°	1117.7	1117.8	1117.9	1117.3	1115.9	1114.6	1113.2	1111.9
145°	1161.7	1162.0	1162.2	1161.6	1160.2	1158.9	1157.5	1156.2
147.5°	1199.4	1199.7	1199.9	1199.3	1197.6	1196.0	1194.4	1192.8
150°	1223.5	1224.0	1224.4	1223.7	1221.8	1220.0	1218.2	1216.4
152.5°	1244.7	1245.2	1245.6	1245.1	1243.3	1241.7	1240.1	1238.5
155°	1273.9	1274.7	1275.4	1274.8	1272.9	1271.1	1269.3	1267.5
157.5°	1298.2	1298.9	1299.6	1299.1	1297.3	1295.5	1293.6	1291.8
160°	1313.2	1314.1	1315.0	1314.5	1312.8	1311.0	1309.2	1307.4
162.5°	1327.1	1328.3	1329.6	1329.2	1327.2	1325.2	1323.2	1321.2
165°	1344.7	1346.2	1347.5	1347.3	1345.4	1343.6	1341.8	1340.0
167.5°	1358.2	1359.8	1361.5	1361.3	1359.2	1357.2	1355.1	1353.1
170°	1365.1	1367.0	1368.8	1368.6	1366.5	1364.5	1362.5	1360.4
172.5°	1370.5	1372.1	1373.7	1373.5	1371.5	1369.4	1367.4	1365.3
175°	1376.3	1378.2	1380.0	1379.9	1377.8	1375.7	1373.7	1371.7
177.5°	1378.7	1380.0	1381.3	1381.2	1379.7	1378.3	1376.8	1375.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8

(END OF REPORT)