

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333733-840

Luminaire Tested: **S125RDIW-S1270D1340U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333733-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9669.1 lumens  
Efficiency: N/A  
Efficacy: 126.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12385	12385	12385	12385
5°	14249	12401	10952	12401
10°	16344	12338	9664	12338
15°	17653	12211	8590	12211
20°	19467	12065	7932	12065
25°	22528	11870	7360	11870
30°	24515	11665	6986	11665
35°	20679	11427	6641	11427
40°	14441	10997	6345	10997
45°	10714	10418	6054	10418
50°	8542	9815	5805	9815
55°	7250	9067	5584	9067
60°	6263	8400	5227	8400
65°	5582	7674	4499	7674
70°	4904	7030	4101	7030
75°	4245	6089	3850	6089
80°	3217	5121	3217	5121
85°	2690	4024	3031	4024



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.9	1.9
10°-20°	538.9	5.6
20°-30°	854.5	8.8
30°-40°	1030.4	10.7
40°-50°	920.2	9.5
50°-60°	705.7	7.3
60°-70°	458.6	4.7
70°-80°	223.0	2.3
80°-90°	56.9	0.6
90°-100°	112.7	1.2
100°-110°	332.9	3.4
110°-120°	563.9	5.8
120°-130°	742.1	7.7
130°-140°	831.6	8.6
140°-150°	815.0	8.4
150°-160°	684.5	7.1
160°-170°	455.0	4.7
170°-180°	159.2	1.6
0°-30°	1577.3	16.3
0°-40°	2607.7	27.0
0°-60°	4233.5	43.8
0°-90°	4971.9	51.4
90°-120°	1009.6	10.4
90°-150°	3398.3	35.1
90°-180°	4697.0	48.6
0°-180°	9669.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1918	1918	1918	1918	1918	
5°	2198	1913	1689	1913	2198	220
15°	2640	1826	1285	1826	2640	757
25°	3161	1666	1033	1666	3161	1452
35°	2623	1449	842	1449	2623	1584
45°	1173	1141	663	1141	1173	936
55°	644	805	496	805	644	584
65°	365	502	294	502	365	363
75°	170	244	154	244	170	181
85°	36	54	41	54	36	42
90°	31	1	31	1	31	20
95°	113	85	113	85	113	115
105°	325	299	325	299	325	344
115°	570	565	570	565	570	564
125°	829	824	829	824	829	740
135°	1076	1072	1076	1072	1076	830
145°	1303	1298	1303	1298	1303	814
155°	1486	1486	1486	1486	1486	684
165°	1611	1615	1611	1615	1611	454
175°	1673	1679	1673	1679	1673	159
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2017.1	2015.9	2018.4	2011.4	2012.1	2001.4	2001.4	1993.2	1982.5	1974.3	1970.5
5°	2197.9	2199.5	2196.3	2184.4	2176.7	2164.8	2151.4	2127.8	2108.1	2089.2	2074.3
7.5°	2384.0	2385.1	2374.7	2371.1	2351.2	2336.7	2306.9	2274.8	2246.3	2210.2	2182.4
10°	2492.2	2491.5	2480.4	2471.8	2454.5	2432.5	2403.4	2365.5	2330.2	2290.8	2253.0
12.5°	2555.3	2553.2	2549.7	2539.2	2523.1	2503.7	2478.9	2441.8	2398.1	2355.0	2310.9
15°	2640.3	2634.7	2624.5	2611.1	2588.3	2565.5	2537.9	2504.9	2463.2	2414.4	2373.4
17.5°	2745.4	2745.6	2729.9	2711.3	2680.3	2640.0	2597.5	2544.1	2487.4	2433.7	2390.1
20°	2832.4	2829.9	2814.3	2778.0	2742.6	2692.2	2643.4	2578.1	2508.8	2438.7	2384.4
22.5°	2957.1	2950.9	2934.6	2887.0	2832.1	2767.1	2692.5	2612.7	2529.0	2449.4	2378.1
25°	3161.4	3156.6	3124.4	3069.3	2992.1	2892.2	2794.6	2685.1	2564.8	2460.0	2373.4
27.5°	3301.2	3296.0	3272.1	3226.3	3155.1	3049.9	2917.8	2771.6	2621.2	2477.2	2352.3
30°	3287.3	3299.1	3296.0	3274.8	3221.3	3126.7	3004.8	2840.2	2661.5	2492.2	2343.5
32.5°	3089.6	3100.2	3127.9	3169.6	3172.7	3134.9	3043.8	2891.8	2706.8	2514.4	2336.5
35°	2622.9	2637.2	2690.7	2774.9	2885.1	2977.2	2996.1	2914.3	2748.1	2541.1	2326.2
37.5°	2016.5	2094.0	2139.0	2227.7	2394.2	2563.6	2726.5	2786.5	2715.8	2530.1	2309.4
40°	1712.9	1731.8	1812.1	1912.1	2052.2	2228.6	2460.8	2628.5	2633.9	2504.9	2282.9
42.5°	1466.1	1490.1	1545.1	1625.0	1744.9	1921.3	2161.0	2382.3	2484.8	2435.6	2248.3
45°	1173.0	1191.0	1231.2	1292.6	1384.7	1530.3	1736.6	1992.4	2195.5	2275.0	2155.4
47.5°	963.5	973.3	1008.2	1055.0	1123.2	1229.3	1389.0	1611.0	1854.6	2025.5	2008.6
50°	850.2	861.2	888.0	923.4	980.9	1070.6	1198.1	1383.1	1634.3	1842.8	1884.6
52.5°	762.0	771.1	787.8	821.3	868.8	937.8	1040.7	1208.0	1434.0	1655.8	1752.3
55°	643.9	650.3	663.6	682.5	720.3	769.9	858.8	974.5	1157.2	1380.8	1522.5
57.5°	546.6	549.8	558.3	575.7	601.9	638.1	702.4	800.4	931.4	1132.8	1289.1
60°	484.9	488.1	499.1	510.9	531.4	564.4	614.8	683.3	809.2	975.3	1133.6
62.5°	435.8	437.7	442.4	454.2	472.2	497.7	537.3	593.2	693.4	839.3	988.8
65°	365.3	366.1	367.6	377.1	388.1	407.0	432.9	472.3	547.9	658.1	790.3
67.5°	297.6	298.6	304.2	307.5	319.0	328.9	344.2	374.3	427.5	501.8	604.6
70°	259.7	259.0	264.5	268.4	272.4	284.2	294.4	318.8	351.8	408.6	494.3
72.5°	224.5	222.5	224.8	226.2	231.5	239.4	249.7	264.7	290.1	329.2	394.9
75°	170.1	170.9	170.9	172.4	176.3	179.5	182.6	190.5	204.7	230.7	266.1
77.5°	119.4	118.1	121.4	121.9	124.2	127.6	130.4	133.5	139.4	150.1	168.3
80°	86.5	86.5	87.4	89.8	89.0	90.5	94.4	97.7	104.7	111.0	117.2
82.5°	66.4	65.8	66.6	67.1	67.0	68.5	69.9	70.5	73.2	76.3	80.8
85°	36.3	36.3	37.0	37.0	37.8	37.8	38.6	38.6	38.6	39.4	40.2
87.5°	20.1	19.3	18.6	18.4	18.8	19.8	18.9	18.0	17.7	17.4	17.7
90°	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8	22.4	21.0	18.9
92.5°	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1	52.2	50.3	47.8
95°	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9	102.9	100.9	98.0
97.5°	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4	162.5	160.6	156.6
100°	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7	203.1	200.5	196.6
102.5°	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0	245.2	242.4	240.4
105°	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6	314.9	313.1	311.3
107.5°	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5	389.7	388.8	387.5
110°	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9	441.0	440.1	439.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3	492.9	492.5	491.4
115°	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9	572.2	572.5	571.9
117.5°	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5	650.3	650.1	649.4
120°	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5	703.5	703.5	703.2
122.5°	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4	755.6	755.9	755.1
125°	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9	832.5	833.1	832.8
127.5°	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0	908.3	908.6	908.3
130°	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3	958.6	958.9	958.3
132.5°	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5	1006.8	1007.1	1007.2
135°	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8	1080.8	1080.8	1080.5
137.5°	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0	1152.6	1152.3	1151.7
140°	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5	1197.9	1197.3	1196.4
142.5°	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0	1242.7	1242.3	1241.2
145°	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4	1307.4	1307.4	1306.5
147.5°	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9	1366.2	1365.5	1364.8
150°	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3	1404.3	1404.3	1403.1
152.5°	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2	1438.6	1437.8	1437.3
155°	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1	1487.9	1486.8	1486.5
157.5°	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4	1531.2	1530.0	1529.7
160°	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5	1557.4	1556.2	1555.9
162.5°	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2	1581.8	1580.3	1580.2
165°	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2	1615.1	1613.9	1613.6
167.5°	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7	1638.9	1637.2	1637.2
170°	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4	1653.7	1651.8	1651.8
172.5°	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9	1664.1	1662.3	1662.3
175°	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6	1675.9	1674.2	1674.2
177.5°	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9	1681.5	1680.1	1680.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1970.5	1966.1	1957.9	1950.4	1941.0	1932.8	1927.0	1920.2	1911.4	1900.7	1891.8
5°	2057.7	2040.4	2017.6	1997.9	1972.8	1953.1	1932.6	1912.9	1893.2	1868.0	1846.0
7.5°	2154.4	2118.7	2083.9	2040.1	2000.4	1965.0	1931.0	1896.5	1862.8	1827.0	1792.6
10°	2213.6	2170.3	2122.3	2067.2	2016.8	1968.8	1924.7	1881.4	1835.7	1795.6	1752.3
12.5°	2269.1	2213.1	2158.2	2088.6	2028.1	1969.4	1913.4	1859.4	1810.6	1758.5	1712.0
15°	2319.1	2264.0	2202.6	2117.6	2033.4	1962.5	1896.3	1826.3	1765.6	1707.5	1655.5
17.5°	2338.4	2280.7	2209.4	2127.7	2035.6	1946.4	1861.3	1784.4	1713.1	1645.3	1586.8
20°	2330.9	2275.0	2201.8	2123.8	2025.5	1932.6	1840.5	1755.4	1676.0	1604.3	1542.2
22.5°	2312.7	2254.8	2184.1	2101.8	2008.4	1910.0	1811.5	1720.8	1637.5	1563.4	1495.5
25°	2285.2	2206.6	2134.1	2053.8	1964.9	1867.2	1765.6	1665.7	1576.8	1501.2	1427.2
27.5°	2256.7	2158.5	2066.4	1986.6	1892.6	1805.5	1707.6	1605.1	1511.6	1434.6	1358.7
30°	2230.9	2120.7	2019.1	1928.6	1839.7	1757.1	1664.2	1564.2	1468.1	1388.7	1311.5
32.5°	2198.8	2081.6	1970.0	1865.6	1779.9	1697.9	1613.8	1518.2	1424.7	1342.6	1264.3
35°	2158.5	2008.9	1887.7	1776.8	1681.4	1601.9	1526.4	1449.3	1355.5	1270.5	1194.2
37.5°	2105.6	1935.9	1795.6	1674.7	1574.3	1494.4	1434.7	1364.2	1278.7	1197.3	1126.5
40°	2073.5	1883.0	1729.5	1609.8	1504.3	1420.1	1364.2	1304.4	1226.5	1150.1	1079.2
42.5°	2030.6	1834.5	1662.7	1538.0	1431.9	1350.8	1294.3	1242.0	1176.7	1104.8	1028.9
45°	1946.7	1740.5	1560.2	1426.4	1319.4	1239.8	1187.1	1140.6	1091.1	1024.9	958.8
47.5°	1837.4	1642.4	1453.8	1307.7	1202.9	1129.0	1077.8	1041.2	1005.7	949.5	885.2
50°	1750.0	1561.9	1377.6	1235.9	1124.1	1054.1	1006.0	976.9	944.6	893.4	839.9
52.5°	1646.7	1478.6	1298.3	1153.4	1047.9	982.3	936.1	907.1	880.4	838.7	787.7
55°	1483.9	1336.7	1171.3	1039.9	943.1	877.0	832.8	805.3	789.6	754.2	714.0
57.5°	1296.1	1190.5	1044.8	918.1	832.4	767.1	734.8	711.3	693.6	668.5	640.2
60°	1165.1	1091.1	960.4	839.9	761.2	699.0	669.9	650.3	633.7	612.5	590.4
62.5°	1032.2	978.4	864.6	761.2	688.8	636.7	609.5	591.7	572.6	558.3	536.8
65°	854.1	806.1	727.4	646.3	579.4	537.7	518.0	502.2	490.4	474.6	459.7
67.5°	664.4	644.9	590.6	534.6	486.7	449.5	432.5	421.5	407.3	397.9	387.6
70°	547.9	538.5	499.9	462.9	418.0	392.8	377.1	372.3	355.1	345.6	338.5
72.5°	444.6	440.2	418.0	392.3	360.7	338.6	324.2	318.8	307.8	300.2	295.7
75°	304.7	306.2	302.3	285.8	274.0	259.7	247.2	244.0	236.2	229.8	225.9
77.5°	192.7	200.8	201.1	200.3	195.5	186.9	181.7	179.4	171.6	169.3	168.3
80°	132.3	140.9	148.8	147.9	146.4	144.1	140.2	137.7	133.8	131.5	129.9
82.5°	88.2	96.2	102.8	107.0	106.7	104.4	101.7	100.6	99.8	98.1	97.8
85°	41.7	43.3	45.6	51.2	55.1	55.8	55.1	54.3	51.9	52.7	53.5
87.5°	17.9	17.5	17.7	17.3	16.2	18.8	20.3	20.4	19.6	18.8	18.1
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7	33.3	34.9	36.6
95°	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1	85.7	86.3	86.8
97.5°	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5	141.7	142.0	142.2
100°	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4
102.5°	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4	229.6	230.8	232.0
105°	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7	300.1	301.5	303.1
107.5°	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2	377.7	379.1	380.6
110°	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7	431.1	432.6	434.0





TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1	484.9	485.6	486.5
115°	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6	565.7	566.9	568.0
117.5°	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3	645.8	646.3	646.8
120°	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6	697.0	698.5	699.9
122.5°	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6
125°	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9	825.7	827.5	829.2
127.5°	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5	903.5	904.5	905.5
130°	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7	951.2	952.6	954.1
132.5°	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8	999.3	1001.7	1004.0
135°	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6	1073.3	1075.0	1076.8
137.5°	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8	1143.5	1145.2	1146.8
140°	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8	1188.3	1189.7	1191.2
142.5°	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9	1233.1	1234.4	1235.6
145°	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2	1299.3	1300.5	1301.6
147.5°	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5	1360.1	1360.8	1361.4
150°	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4	1400.1	1399.8	1399.5
152.5°	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9	1434.3	1434.7	1435.1
155°	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6	1531.0	1530.3	1529.6
160°	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8	1558.0	1557.1	1556.2
162.5°	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0	1582.4	1581.7	1581.0
165°	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2	1614.6	1614.0	1613.5
167.5°	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4	1641.2	1640.1	1638.9
170°	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1	1656.0	1654.8	1653.7
172.5°	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6	1666.4	1665.3	1664.1
175°	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4	1678.2	1677.1	1675.9
177.5°	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4	1684.5	1683.5	1682.6
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1885.5	1876.7	1870.4	1857.7	1849.0	1845.2	1838.3	1836.3	1843.3	1838.3	1837.7
5°	1829.5	1806.6	1788.6	1770.4	1750.7	1738.2	1719.3	1716.1	1711.4	1704.2	1702.7
7.5°	1762.2	1732.5	1709.2	1679.3	1653.3	1632.3	1608.7	1597.5	1591.4	1582.3	1570.0
10°	1716.9	1681.4	1650.0	1620.0	1587.8	1561.9	1538.2	1520.0	1508.2	1497.2	1492.6
12.5°	1672.1	1636.1	1595.8	1559.6	1523.6	1494.4	1468.2	1456.5	1443.4	1430.5	1419.5
15°	1602.8	1554.7	1510.7	1468.9	1438.2	1406.7	1381.5	1364.2	1344.5	1339.1	1317.8
17.5°	1529.0	1482.0	1430.4	1386.4	1350.8	1316.2	1288.5	1268.8	1254.1	1233.8	1224.0
20°	1483.1	1427.2	1376.8	1336.7	1297.3	1256.4	1228.0	1211.5	1197.3	1180.8	1173.0
22.5°	1434.0	1379.4	1327.7	1280.6	1240.6	1200.3	1180.1	1163.1	1146.9	1131.7	1121.3
25°	1361.9	1306.8	1252.4	1203.7	1162.0	1132.8	1109.1	1089.4	1080.9	1065.9	1054.8
27.5°	1290.5	1231.9	1175.6	1126.9	1094.2	1065.4	1046.0	1030.5	1014.8	1001.8	992.2
30°	1244.6	1184.8	1123.4	1084.8	1050.2	1022.6	1001.3	986.3	974.5	962.7	955.6
32.5°	1198.6	1136.9	1082.4	1040.7	1007.9	984.1	962.3	948.0	935.5	922.4	914.1
35°	1124.9	1062.0	1017.8	976.9	944.6	922.6	907.7	887.2	877.0	867.5	858.8
37.5°	1056.4	997.8	950.2	914.2	886.3	864.3	845.0	833.9	821.3	812.8	805.7
40°	1006.0	952.5	909.2	871.4	851.0	826.6	808.5	794.3	784.9	773.9	766.0
42.5°	960.7	911.0	868.9	835.0	809.4	788.8	771.3	757.1	745.2	737.3	730.6
45°	896.7	847.1	806.1	774.6	751.0	731.3	713.2	706.1	690.3	681.0	677.8
47.5°	830.3	786.0	746.4	717.4	693.2	674.6	657.6	643.2	634.5	625.2	620.2
50°	785.7	743.2	706.1	677.8	654.2	633.7	617.9	608.5	596.7	588.0	581.8
52.5°	740.9	701.6	664.6	637.4	617.0	596.5	579.0	569.5	558.3	552.8	548.4
55°	677.0	635.3	603.8	577.0	555.7	536.8	520.4	510.9	503.8	498.3	496.8
57.5°	604.6	571.5	542.2	518.2	496.0	478.3	463.8	454.8	448.6	447.8	443.0
60°	557.3	527.5	500.7	474.6	455.8	439.3	426.7	416.5	410.1	409.3	407.8
62.5°	510.1	481.4	456.6	433.7	416.8	400.8	388.9	377.4	373.7	369.7	366.2
65°	440.0	414.0	393.6	375.5	357.4	344.0	332.2	325.1	316.5	311.7	303.1
67.5°	371.2	351.1	331.4	316.2	301.9	289.2	279.4	268.9	263.1	259.3	253.0
70°	325.9	310.1	290.4	274.0	263.0	252.7	244.8	233.0	229.0	225.9	222.8
72.5°	283.1	269.2	252.7	239.3	228.3	218.6	209.5	204.0	200.2	196.9	195.1
75°	222.8	209.4	195.2	185.8	177.9	170.1	165.3	161.4	159.8	159.1	155.8
77.5°	163.6	156.5	145.1	137.6	132.4	129.3	125.0	123.0	122.8	119.4	118.3
80°	125.1	121.2	111.8	108.7	104.7	101.6	99.2	95.2	91.3	89.8	87.4
82.5°	93.0	89.1	85.3	80.3	77.0	75.1	72.7	71.3	71.8	69.6	68.5
85°	49.6	45.6	44.1	43.3	41.7	43.3	42.5	41.7	40.9	40.2	40.9
87.5°	17.9	18.3	18.1	19.8	18.3	19.3	19.6	19.3	19.6	19.8	19.5
90°	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8	25.3	26.8	28.0
92.5°	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1	56.0	58.0	59.3
95°	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9	106.9	109.1	110.3
97.5°	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4	166.3	168.2	169.5
100°	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7	208.2	210.9	212.5
102.5°	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0	250.9	253.8	255.6
105°	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6	318.3	320.0	321.3
107.5°	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5	391.4	392.3	392.7
110°	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9	442.7	443.6	443.9



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3	493.7	494.1	494.1
115°	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9	571.6	571.3	571.0
117.5°	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5	650.7	651.0	650.5
120°	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5	703.5	703.5	702.9
122.5°	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4	755.2	754.9	754.4
125°	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9	831.4	830.8	830.4
127.5°	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0	907.7	907.5	907.0
130°	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3	958.1	957.8	957.3
132.5°	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5	1006.2	1005.9	1005.4
135°	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8	1080.8	1080.8	1080.2
137.5°	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0	1153.3	1153.7	1153.1
140°	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5	1199.0	1199.6	1199.2
142.5°	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0	1243.4	1243.7	1243.2
145°	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4	1307.4	1307.4	1306.9
147.5°	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9	1367.6	1368.3	1367.7
150°	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3	1404.3	1404.3	1404.0
152.5°	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2	1439.9	1440.6	1440.5
155°	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1	1490.3	1491.5	1491.3
157.5°	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4	1533.5	1534.7	1534.3
160°	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5	1559.7	1560.8	1560.7
162.5°	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2	1584.5	1585.9	1585.8
165°	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2	1617.4	1618.5	1618.2
167.5°	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7	1642.4	1644.2	1644.2
170°	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4	1657.1	1658.8	1658.7
172.5°	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9	1667.6	1669.3	1669.3
175°	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6	1679.4	1681.1	1680.9
177.5°	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9	1684.4	1685.8	1685.7
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1837.0	1830.1	1828.2	1830.7	1828.2	1830.1	1837.0	1837.7	1838.3	1843.3	1836.3
5°	1694.9	1687.0	1690.9	1689.3	1690.9	1687.0	1694.9	1702.7	1704.2	1711.4	1716.1
7.5°	1569.8	1560.0	1549.6	1553.0	1549.6	1560.0	1569.8	1570.0	1582.3	1591.4	1597.5
10°	1482.3	1474.4	1469.7	1473.6	1469.7	1474.4	1482.3	1492.6	1497.2	1508.2	1520.0
12.5°	1408.7	1403.9	1399.8	1398.1	1399.8	1403.9	1408.7	1419.5	1430.5	1443.4	1456.5
15°	1308.3	1298.9	1294.9	1284.8	1294.9	1298.9	1308.3	1317.8	1339.1	1344.5	1364.2
17.5°	1215.9	1212.7	1202.5	1198.1	1202.5	1212.7	1215.9	1224.0	1233.8	1254.1	1268.8
20°	1161.1	1158.0	1147.7	1154.1	1147.7	1158.0	1161.1	1173.0	1180.8	1197.3	1211.5
22.5°	1115.8	1108.8	1105.5	1103.7	1105.5	1108.8	1115.8	1121.3	1131.7	1146.9	1163.1
25°	1051.7	1041.5	1037.5	1032.8	1037.5	1041.5	1051.7	1054.8	1065.9	1080.9	1089.4
27.5°	987.7	982.3	977.0	975.8	977.0	982.3	987.7	992.2	1001.8	1014.8	1030.5
30°	946.2	940.7	936.8	936.8	936.8	940.7	946.2	955.6	962.7	974.5	986.3
32.5°	909.1	904.8	900.9	900.3	900.9	904.8	909.1	914.1	922.4	935.5	948.0
35°	855.0	848.6	847.1	842.3	847.1	848.6	855.0	858.8	867.5	877.0	887.2
37.5°	798.7	793.5	793.3	792.8	793.3	793.5	798.7	805.7	812.8	821.3	833.9
40°	762.8	758.8	758.1	752.6	758.1	758.8	762.8	766.0	773.9	784.9	794.3
42.5°	724.4	722.4	719.6	717.3	719.6	722.4	724.4	730.6	737.3	745.2	757.1
45°	672.3	666.7	666.7	662.8	666.7	666.7	672.3	677.8	681.0	690.3	706.1
47.5°	618.4	614.2	614.6	610.6	614.6	614.2	618.4	620.2	625.2	634.5	643.2
50°	582.5	580.2	579.4	577.8	579.4	580.2	582.5	581.8	588.0	596.7	608.5
52.5°	546.6	545.5	548.6	545.0	548.6	545.5	546.6	548.4	552.8	558.3	569.5
55°	498.3	495.9	500.7	495.9	500.7	495.9	498.3	496.8	498.3	503.8	510.9
57.5°	442.7	440.5	444.7	442.4	444.7	440.5	442.7	443.0	447.8	448.6	454.8
60°	406.2	401.5	403.8	404.7	403.8	401.5	406.2	407.8	409.3	410.1	416.5
62.5°	362.7	359.9	361.6	358.0	361.6	359.9	362.7	366.2	369.7	373.7	377.4
65°	301.5	299.1	296.0	294.4	296.0	299.1	301.5	303.1	311.7	316.5	325.1
67.5°	253.3	247.6	247.5	248.7	247.5	247.6	253.3	253.0	259.3	263.1	268.9
70°	218.0	218.0	217.2	217.2	217.2	218.0	218.0	222.8	225.9	229.0	233.0
72.5°	193.5	192.9	191.5	190.9	191.5	192.9	193.5	195.1	196.9	200.2	204.0
75°	155.8	156.6	155.1	154.3	155.1	156.6	155.8	155.8	159.1	159.8	161.4
77.5°	115.1	111.8	113.5	111.8	113.5	111.8	115.1	118.3	119.4	122.8	123.0
80°	87.4	86.5	89.0	86.5	89.0	86.5	87.4	87.4	89.8	91.3	95.2
82.5°	69.1	68.4	69.5	67.7	69.5	68.4	69.1	68.5	69.6	71.8	71.3
85°	41.7	40.9	40.2	40.9	40.2	40.9	41.7	40.9	40.2	40.9	41.7
87.5°	20.3	19.8	20.0	20.1	20.0	19.8	20.3	19.5	19.8	19.6	19.3
90°	28.8	29.7	30.6	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8
92.5°	59.9	60.6	61.2	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1
95°	110.9	111.5	112.1	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9
97.5°	169.8	170.2	170.5	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4
100°	213.1	213.7	214.3	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7
102.5°	256.4	257.2	258.0	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0
105°	322.2	323.2	324.0	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6
107.5°	392.6	392.5	392.5	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5
110°	443.6	443.3	443.0	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	493.6	493.1	492.5	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3
115°	570.7	570.4	570.2	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9
117.5°	649.3	648.1	647.0	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5
120°	701.7	700.5	699.3	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5
122.5°	753.4	752.5	751.5	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4
125°	830.1	829.8	829.5	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9
127.5°	906.5	905.8	905.2	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0
130°	956.7	956.1	955.5	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3
132.5°	1004.6	1003.7	1002.9	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5
135°	1078.9	1077.8	1076.6	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8
137.5°	1151.7	1150.1	1148.7	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0
140°	1197.7	1196.3	1194.9	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5
142.5°	1241.7	1240.3	1238.8	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0
145°	1306.1	1305.1	1304.2	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4
147.5°	1365.6	1363.7	1361.7	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9
150°	1403.4	1402.8	1402.2	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3
152.5°	1439.4	1438.4	1437.2	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2
155°	1489.9	1488.4	1486.9	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1
157.5°	1532.4	1530.5	1528.5	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4
160°	1559.3	1557.8	1556.4	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5
162.5°	1584.1	1582.4	1580.7	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2
165°	1616.5	1614.8	1613.0	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2
167.5°	1642.3	1640.5	1638.7	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7
170°	1656.7	1654.7	1652.5	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4
172.5°	1667.5	1665.7	1663.9	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9
175°	1678.9	1676.9	1674.9	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6
177.5°	1683.9	1682.3	1680.7	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1838.3	1845.2	1849.0	1857.7	1870.4	1876.7	1885.5	1891.8	1900.7	1911.4	1920.2
5°	1719.3	1738.2	1750.7	1770.4	1788.6	1806.6	1829.5	1846.0	1868.0	1893.2	1912.9
7.5°	1608.7	1632.3	1653.3	1679.3	1709.2	1732.5	1762.2	1792.6	1827.0	1862.8	1896.5
10°	1538.2	1561.9	1587.8	1620.0	1650.0	1681.4	1716.9	1752.3	1795.6	1835.7	1881.4
12.5°	1468.2	1494.4	1523.6	1559.6	1595.8	1636.1	1672.1	1712.0	1758.5	1810.6	1859.4
15°	1381.5	1406.7	1438.2	1468.9	1510.7	1554.7	1602.8	1655.5	1707.5	1765.6	1826.3
17.5°	1288.5	1316.2	1350.8	1386.4	1430.4	1482.0	1529.0	1586.8	1645.3	1713.1	1784.4
20°	1228.0	1256.4	1297.3	1336.7	1376.8	1427.2	1483.1	1542.2	1604.3	1676.0	1755.4
22.5°	1180.1	1200.3	1240.6	1280.6	1327.7	1379.4	1434.0	1495.5	1563.4	1637.5	1720.8
25°	1109.1	1132.8	1162.0	1203.7	1252.4	1306.8	1361.9	1427.2	1501.2	1576.8	1665.7
27.5°	1046.0	1065.4	1094.2	1126.9	1175.6	1231.9	1290.5	1358.7	1434.6	1511.6	1605.1
30°	1001.3	1022.6	1050.2	1084.8	1123.4	1184.8	1244.6	1311.5	1388.7	1468.1	1564.2
32.5°	962.3	984.1	1007.9	1040.7	1082.4	1136.9	1198.6	1264.3	1342.6	1424.7	1518.2
35°	907.7	922.6	944.6	976.9	1017.8	1062.0	1124.9	1194.2	1270.5	1355.5	1449.3
37.5°	845.0	864.3	886.3	914.2	950.2	997.8	1056.4	1126.5	1197.3	1278.7	1364.2
40°	808.5	826.6	851.0	871.4	909.2	952.5	1006.0	1079.2	1150.1	1226.5	1304.4
42.5°	771.3	788.8	809.4	835.0	868.9	911.0	960.7	1028.9	1104.8	1176.7	1242.0
45°	713.2	731.3	751.0	774.6	806.1	847.1	896.7	958.8	1024.9	1091.1	1140.6
47.5°	657.6	674.6	693.2	717.4	746.4	786.0	830.3	885.2	949.5	1005.7	1041.2
50°	617.9	633.7	654.2	677.8	706.1	743.2	785.7	839.9	893.4	944.6	976.9
52.5°	579.0	596.5	617.0	637.4	664.6	701.6	740.9	787.7	838.7	880.4	907.1
55°	520.4	536.8	555.7	577.0	603.8	635.3	677.0	714.0	754.2	789.6	805.3
57.5°	463.8	478.3	496.0	518.2	542.2	571.5	604.6	640.2	668.5	693.6	711.3
60°	426.7	439.3	455.8	474.6	500.7	527.5	557.3	590.4	612.5	633.7	650.3
62.5°	388.9	400.8	416.8	433.7	456.6	481.4	510.1	536.8	558.3	572.6	591.7
65°	332.2	344.0	357.4	375.5	393.6	414.0	440.0	459.7	474.6	490.4	502.2
67.5°	279.4	289.2	301.9	316.2	331.4	351.1	371.2	387.6	397.9	407.3	421.5
70°	244.8	252.7	263.0	274.0	290.4	310.1	325.9	338.5	345.6	355.1	372.3
72.5°	209.5	218.6	228.3	239.3	252.7	269.2	283.1	295.7	300.2	307.8	318.8
75°	165.3	170.1	177.9	185.8	195.2	209.4	222.8	225.9	229.8	236.2	244.0
77.5°	125.0	129.3	132.4	137.6	145.1	156.5	163.6	168.3	169.3	171.6	179.4
80°	99.2	101.6	104.7	108.7	111.8	121.2	125.1	129.9	131.5	133.8	137.7
82.5°	72.7	75.1	77.0	80.3	85.3	89.1	93.0	97.8	98.1	99.8	100.6
85°	42.5	43.3	41.7	43.3	44.1	45.6	49.6	53.5	52.7	51.9	54.3
87.5°	19.6	19.3	18.3	19.8	18.1	18.3	17.9	18.1	18.8	19.6	20.4
90°	22.4	21.0	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	52.2	50.3	47.8	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7
95°	102.9	100.9	98.0	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1
97.5°	162.5	160.6	156.6	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5
100°	203.1	200.5	196.6	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4
102.5°	245.2	242.4	240.4	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4
105°	314.9	313.1	311.3	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7
107.5°	389.7	388.8	387.5	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2
110°	441.0	440.1	439.3	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.9	492.5	491.4	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1
115°	572.2	572.5	571.9	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6
117.5°	650.3	650.1	649.4	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3
120°	703.5	703.5	703.2	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6
122.5°	755.6	755.9	755.1	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1
125°	832.5	833.1	832.8	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9
127.5°	908.3	908.6	908.3	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5
130°	958.6	958.9	958.3	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7
132.5°	1006.8	1007.1	1007.2	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8
135°	1080.8	1080.8	1080.5	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6
137.5°	1152.6	1152.3	1151.7	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8
140°	1197.9	1197.3	1196.4	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8
142.5°	1242.7	1242.3	1241.2	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9
145°	1307.4	1307.4	1306.5	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2
147.5°	1366.2	1365.5	1364.8	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5
150°	1404.3	1404.3	1403.1	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4
152.5°	1438.6	1437.8	1437.3	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9
155°	1487.9	1486.8	1486.5	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1531.2	1530.0	1529.7	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6
160°	1557.4	1556.2	1555.9	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8
162.5°	1581.8	1580.3	1580.2	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0
165°	1615.1	1613.9	1613.6	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2
167.5°	1638.9	1637.2	1637.2	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4
170°	1653.7	1651.8	1651.8	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1
172.5°	1664.1	1662.3	1662.3	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6
175°	1675.9	1674.2	1674.2	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4
177.5°	1681.5	1680.1	1680.4	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1927.0	1932.8	1941.0	1950.4	1957.9	1966.1	1970.5	1970.5	1974.3	1982.5	1993.2
5°	1932.6	1953.1	1972.8	1997.9	2017.6	2040.4	2057.7	2074.3	2089.2	2108.1	2127.8
7.5°	1931.0	1965.0	2000.4	2040.1	2083.9	2118.7	2154.4	2182.4	2210.2	2246.3	2274.8
10°	1924.7	1968.8	2016.8	2067.2	2122.3	2170.3	2213.6	2253.0	2290.8	2330.2	2365.5
12.5°	1913.4	1969.4	2028.1	2088.6	2158.2	2213.1	2269.1	2310.9	2355.0	2398.1	2441.8
15°	1896.3	1962.5	2033.4	2117.6	2202.6	2264.0	2319.1	2373.4	2414.4	2463.2	2504.9
17.5°	1861.3	1946.4	2035.6	2127.7	2209.4	2280.7	2338.4	2390.1	2433.7	2487.4	2544.1
20°	1840.5	1932.6	2025.5	2123.8	2201.8	2275.0	2330.9	2384.4	2438.7	2508.8	2578.1
22.5°	1811.5	1910.0	2008.4	2101.8	2184.1	2254.8	2312.7	2378.1	2449.4	2529.0	2612.7
25°	1765.6	1867.2	1964.9	2053.8	2134.1	2206.6	2285.2	2373.4	2460.0	2564.8	2685.1
27.5°	1707.6	1805.5	1892.6	1986.6	2066.4	2158.5	2256.7	2352.3	2477.2	2621.2	2771.6
30°	1664.2	1757.1	1839.7	1928.6	2019.1	2120.7	2230.9	2343.5	2492.2	2661.5	2840.2
32.5°	1613.8	1697.9	1779.9	1865.6	1970.0	2081.6	2198.8	2336.5	2514.4	2706.8	2891.8
35°	1526.4	1601.9	1681.4	1776.8	1887.7	2008.9	2158.5	2326.2	2541.1	2748.1	2914.3
37.5°	1434.7	1494.4	1574.3	1674.7	1795.6	1935.9	2105.6	2309.4	2530.1	2715.8	2786.5
40°	1364.2	1420.1	1504.3	1609.8	1729.5	1883.0	2073.5	2282.9	2504.9	2633.9	2628.5
42.5°	1294.3	1350.8	1431.9	1538.0	1662.7	1834.5	2030.6	2248.3	2435.6	2484.8	2382.3
45°	1187.1	1239.8	1319.4	1426.4	1560.2	1740.5	1946.7	2155.4	2275.0	2195.5	1992.4
47.5°	1077.8	1129.0	1202.9	1307.7	1453.8	1642.4	1837.4	2008.6	2025.5	1854.6	1611.0
50°	1006.0	1054.1	1124.1	1235.9	1377.6	1561.9	1750.0	1884.6	1842.8	1634.3	1383.1
52.5°	936.1	982.3	1047.9	1153.4	1298.3	1478.6	1646.7	1752.3	1655.8	1434.0	1208.0
55°	832.8	877.0	943.1	1039.9	1171.3	1336.7	1483.9	1522.5	1380.8	1157.2	974.5
57.5°	734.8	767.1	832.4	918.1	1044.8	1190.5	1296.1	1289.1	1132.8	931.4	800.4
60°	669.9	699.0	761.2	839.9	960.4	1091.1	1165.1	1133.6	975.3	809.2	683.3
62.5°	609.5	636.7	688.8	761.2	864.6	978.4	1032.2	988.8	839.3	693.4	593.2
65°	518.0	537.7	579.4	646.3	727.4	806.1	854.1	790.3	658.1	547.9	472.3
67.5°	432.5	449.5	486.7	534.6	590.6	644.9	664.4	604.6	501.8	427.5	374.3
70°	377.1	392.8	418.0	462.9	499.9	538.5	547.9	494.3	408.6	351.8	318.8
72.5°	324.2	338.6	360.7	392.3	418.0	440.2	444.6	394.9	329.2	290.1	264.7
75°	247.2	259.7	274.0	285.8	302.3	306.2	304.7	266.1	230.7	204.7	190.5
77.5°	181.7	186.9	195.5	200.3	201.1	200.8	192.7	168.3	150.1	139.4	133.5
80°	140.2	144.1	146.4	147.9	148.8	140.9	132.3	117.2	111.0	104.7	97.7
82.5°	101.7	104.4	106.7	107.0	102.8	96.2	88.2	80.8	76.3	73.2	70.5
85°	55.1	55.8	55.1	51.2	45.6	43.3	41.7	40.2	39.4	38.6	38.6
87.5°	20.3	18.8	16.2	17.3	17.7	17.5	17.9	17.7	17.4	17.7	18.0
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8
92.5°	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1
95°	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9
97.5°	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4
100°	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7
102.5°	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0
105°	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6
107.5°	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5
110°	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9





TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3
115°	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9
117.5°	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5
120°	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5
122.5°	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4
125°	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9
127.5°	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0
130°	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3
132.5°	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5
135°	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8
137.5°	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0
140°	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5
142.5°	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0
145°	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4
147.5°	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9
150°	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3
152.5°	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2
155°	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1
157.5°	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4
160°	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5
162.5°	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2
165°	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2
167.5°	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7
170°	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4
172.5°	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9
175°	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6
177.5°	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2001.4	2001.4	2012.1	2011.4	2018.4	2015.9	2017.1
5°	2151.4	2164.8	2176.7	2184.4	2196.3	2199.5	2197.9
7.5°	2306.9	2336.7	2351.2	2371.1	2374.7	2385.1	2384.0
10°	2403.4	2432.5	2454.5	2471.8	2480.4	2491.5	2492.2
12.5°	2478.9	2503.7	2523.1	2539.2	2549.7	2553.2	2555.3
15°	2537.9	2565.5	2588.3	2611.1	2624.5	2634.7	2640.3
17.5°	2597.5	2640.0	2680.3	2711.3	2729.9	2745.6	2745.4
20°	2643.4	2692.2	2742.6	2778.0	2814.3	2829.9	2832.4
22.5°	2692.5	2767.1	2832.1	2887.0	2934.6	2950.9	2957.1
25°	2794.6	2892.2	2992.1	3069.3	3124.4	3156.6	3161.4
27.5°	2917.8	3049.9	3155.1	3226.3	3272.1	3296.0	3301.2
30°	3004.8	3126.7	3221.3	3274.8	3296.0	3299.1	3287.3
32.5°	3043.8	3134.9	3172.7	3169.6	3127.9	3100.2	3089.6
35°	2996.1	2977.2	2885.1	2774.9	2690.7	2637.2	2622.9
37.5°	2726.5	2563.6	2394.2	2227.7	2139.0	2094.0	2016.5
40°	2460.8	2228.6	2052.2	1912.1	1812.1	1731.8	1712.9
42.5°	2161.0	1921.3	1744.9	1625.0	1545.1	1490.1	1466.1
45°	1736.6	1530.3	1384.7	1292.6	1231.2	1191.0	1173.0
47.5°	1389.0	1229.3	1123.2	1055.0	1008.2	973.3	963.5
50°	1198.1	1070.6	980.9	923.4	888.0	861.2	850.2
52.5°	1040.7	937.8	868.8	821.3	787.8	771.1	762.0
55°	858.8	769.9	720.3	682.5	663.6	650.3	643.9
57.5°	702.4	638.1	601.9	575.7	558.3	549.8	546.6
60°	614.8	564.4	531.4	510.9	499.1	488.1	484.9
62.5°	537.3	497.7	472.2	454.2	442.4	437.7	435.8
65°	432.9	407.0	388.1	377.1	367.6	366.1	365.3
67.5°	344.2	328.9	319.0	307.5	304.2	298.6	297.6
70°	294.4	284.2	272.4	268.4	264.5	259.0	259.7
72.5°	249.7	239.4	231.5	226.2	224.8	222.5	224.5
75°	182.6	179.5	176.3	172.4	170.9	170.9	170.1
77.5°	130.4	127.6	124.2	121.9	121.4	118.1	119.4
80°	94.4	90.5	89.0	89.8	87.4	86.5	86.5
82.5°	69.9	68.5	67.0	67.1	66.6	65.8	66.4
85°	38.6	37.8	37.8	37.0	37.0	36.3	36.3
87.5°	18.9	19.8	18.8	18.4	18.6	19.3	20.1
90°	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	442.7	443.6	443.9	443.6	443.3	443.0	442.7



TEST NUMBER: P333733-840

CATALOG NUMBER: S125RDIW-S1270D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)