

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333696

Luminaire Tested: **S125RDIW-S850D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333696  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1560U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9517.4 lumens  
Efficiency: N/A  
Efficacy: 139.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34				
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	37	36	30				
2	86	79	73	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	26	22				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16				
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10				
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	1.3
10°-20°	355.5	3.7
20°-30°	563.6	5.9
30°-40°	679.7	7.1
40°-50°	607.0	6.4
50°-60°	465.5	4.9
60°-70°	302.5	3.2
70°-80°	147.1	1.5
80°-90°	39.3	0.4
90°-100°	73.8	0.8
100°-110°	454.8	4.8
110°-120°	824.9	8.7
120°-130°	1058.6	11.1
130°-140°	1138.6	12.0
140°-150°	1068.8	11.2
150°-160°	864.5	9.1
160°-170°	559.1	5.9
170°-180°	192.9	2.0
0°-30°	1040.4	10.9
0°-40°	1720.1	18.1
0°-60°	2792.5	29.3
0°-90°	3281.4	34.5
90°-120°	1353.5	14.2
90°-150°	4619.5	48.5
90°-180°	6236.0	65.5
0°-180°	9517.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	36	2	36	2	36	17
95°	32	86	32	86	32	26
105°	447	443	447	443	447	404
115°	825	831	825	831	825	819
125°	1182	1182	1182	1182	1182	1051
135°	1468	1474	1468	1474	1468	1133
145°	1704	1709	1704	1709	1704	1064
155°	1868	1882	1868	1882	1868	861
165°	1975	1986	1975	1986	1975	557
175°	2022	2031	2022	2031	2022	192
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	16.4	15.7	15.1	14.9	15.1	15.7	15.0	14.2	13.9	13.5	13.5
90°	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4	25.8	24.1	21.7
92.5°	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4	25.8	24.1	22.0
95°	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4	25.8	24.1	36.8
97.5°	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2	64.6	74.1	99.2
100°	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2	212.1	261.9	260.6
102.5°	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3	324.8	334.2	333.4
105°	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0	567.9	567.8	567.2
110°	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3	646.3	647.3	646.6



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8	723.1	724.4	724.0
115°	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3	838.6	840.0	839.7
117.5°	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8	950.5	952.3	951.0
120°	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8	1021.5	1022.1	1021.1
122.5°	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4	1090.1	1090.8	1090.3
125°	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6	1190.9	1192.2	1192.2
127.5°	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1	1281.8	1282.6	1282.8
130°	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8	1341.8	1342.8	1342.4
132.5°	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6	1396.8	1397.0	1397.7
135°	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4	1479.1	1479.8	1480.4
137.5°	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7	1554.6	1554.4	1555.0
140°	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5	1600.9	1600.2	1600.5
142.5°	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4	1647.3	1647.2	1646.7
145°	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3	1711.9	1711.6	1711.6
147.5°	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8	1767.4	1767.0	1766.6
150°	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2	1802.6	1801.9	1801.2
152.5°	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6	1833.9	1833.2	1832.6
155°	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7	1876.7	1875.7	1875.0
157.5°	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3	1912.3	1911.2	1911.1
160°	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5	1934.2	1932.9	1932.5
162.5°	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9	1954.0	1952.1	1951.8
165°	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0	1980.0	1978.0	1977.7
167.5°	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8	1999.4	1997.0	1996.7
170°	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0	2009.3	2006.6	2006.3
172.5°	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9	2017.5	2015.1	2014.5
175°	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5	2025.9	2023.2	2022.9
177.5°	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1	2030.2	2028.3	2028.0
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	13.4	13.0	12.9	12.4	11.5	13.0	13.7	13.6	13.3	13.0	12.7
90°	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5	4.2	6.9	9.5
92.5°	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2	21.3	19.4	17.6
95°	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8	84.8	83.8	82.8
97.5°	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1	180.9	182.7	184.6
100°	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4	252.4	253.4	254.4
102.5°	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9	326.1	327.4	328.7
105°	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6	443.9	445.3	446.6
107.5°	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
110°	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3	644.3	644.3	644.3





TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0	719.8	720.6	721.4
115°	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0	832.6	834.3	836.0
117.5°	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9	946.8	946.7	946.7
120°	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1	1018.8	1018.5	1018.1
122.5°	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0	1084.2	1085.5	1086.8
125°	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7	1184.0	1186.4	1188.7
127.5°	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9	1277.6	1279.3	1281.0
130°	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7	1335.4	1337.1	1338.8
132.5°	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5	1393.5	1395.4	1397.4
135°	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7	1475.7	1477.8	1479.8
137.5°	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3	1551.0	1552.8	1554.5
140°	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7	1599.4	1600.0	1600.7
142.5°	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2	1643.6	1644.0	1644.4
145°	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6	1709.2	1709.9	1710.6
147.5°	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8	1765.6	1765.5	1765.4
150°	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1801.2	1800.6	1799.9
152.5°	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8	1835.4	1833.9	1832.4
155°	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7	1879.7	1877.7	1875.7
157.5°	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3	1915.1	1913.9	1912.7
160°	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4	1938.4	1936.4	1934.4
162.5°	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7	1957.7	1955.7	1953.6
165°	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6	1983.6	1981.5	1979.5
167.5°	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8	2002.8	2000.7	1998.6
170°	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7	2013.3	2011.0	2008.6
172.5°	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9	2020.6	2018.2	2015.9
175°	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7	2028.7	2026.7	2024.7
177.5°	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3	2032.7	2031.1	2029.5
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	12.8	13.3	13.4	14.7	13.9	14.8	15.1	15.0	15.4	15.7	15.6
90°	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4	29.1	30.8	32.1
92.5°	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4	29.1	30.8	31.8
95°	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4	29.1	30.8	31.6
97.5°	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2	45.8	36.3	31.6
100°	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2	112.4	62.6	37.0
102.5°	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3	305.9	296.5	280.4
105°	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.4
107.5°	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0	568.0	568.1	567.6
110°	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3	644.3	643.3	643.0



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8	720.6	719.3	718.4
115°	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3	836.0	834.6	833.0
117.5°	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8	947.1	945.3	944.0
120°	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8	1020.1	1019.5	1018.3
122.5°	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4	1088.8	1088.1	1086.8
125°	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6	1188.2	1186.9	1185.7
127.5°	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1	1280.4	1279.6	1278.0
130°	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8	1339.8	1338.8	1337.4
132.5°	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6	1396.4	1396.2	1395.2
135°	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4	1477.8	1477.1	1475.7
137.5°	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7	1554.8	1555.0	1554.2
140°	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5	1602.2	1602.9	1602.2
142.5°	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4	1647.6	1647.7	1646.8
145°	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3	1712.6	1712.9	1712.1
147.5°	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8	1768.2	1768.6	1767.6
150°	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2	1803.9	1804.6	1803.6
152.5°	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6	1835.2	1835.9	1835.0
155°	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7	1878.7	1879.7	1878.8
157.5°	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3	1914.4	1915.5	1914.7
160°	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5	1936.9	1938.2	1937.6
162.5°	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9	1957.8	1959.6	1959.1
165°	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0	1984.1	1986.1	1985.7
167.5°	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8	2004.2	2006.6	2006.3
170°	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0	2014.7	2017.3	2017.2
172.5°	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9	2022.3	2024.7	2024.4
175°	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5	2031.2	2033.9	2033.7
177.5°	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1	2033.9	2035.8	2035.7
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	16.2	16.0	16.2	16.4	16.2	16.0	16.2	15.6	15.7	15.4	15.0
90°	33.1	34.1	35.1	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4
92.5°	32.3	32.8	33.3	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4
95°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4
97.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2
100°	35.6	34.3	33.0	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2
102.5°	257.6	234.9	212.1	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3
105°	448.1	447.8	447.4	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6
107.5°	566.6	565.6	564.6	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0
110°	643.3	643.6	644.0	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	718.0	717.5	717.0	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8
115°	831.0	828.9	826.9	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3
117.5°	943.2	942.3	941.4	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8
120°	1016.6	1014.9	1013.3	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8
122.5°	1084.9	1082.9	1081.0	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4
125°	1184.7	1183.7	1182.7	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6
127.5°	1275.5	1273.1	1270.6	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1
130°	1335.8	1334.1	1332.4	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8
132.5°	1393.6	1391.9	1390.2	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6
135°	1473.7	1471.7	1469.7	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4
137.5°	1552.4	1550.7	1548.9	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7
140°	1600.2	1598.2	1596.2	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5
142.5°	1644.7	1642.7	1640.7	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4
145°	1710.1	1708.1	1706.1	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3
147.5°	1765.2	1762.8	1760.4	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8
150°	1800.9	1798.2	1795.6	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2
152.5°	1832.6	1830.2	1827.8	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6
155°	1876.2	1873.5	1870.8	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7
157.5°	1912.0	1909.3	1906.6	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3
160°	1934.9	1932.2	1929.5	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5
162.5°	1956.2	1953.2	1950.3	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9
165°	1983.1	1980.4	1977.7	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0
167.5°	2003.3	2000.3	1997.3	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8
170°	2014.2	2011.2	2008.1	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0
172.5°	2021.4	2018.4	2015.4	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9
175°	2030.7	2027.7	2024.7	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5
177.5°	2033.5	2031.4	2029.2	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	15.1	14.8	13.9	14.7	13.4	13.3	12.8	12.7	13.0	13.3	13.6
90°	25.8	24.1	21.7	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5
92.5°	25.8	24.1	22.0	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2
95°	25.8	24.1	36.8	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8
97.5°	64.6	74.1	99.2	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1
100°	212.1	261.9	260.6	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4
102.5°	324.8	334.2	333.4	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9
105°	448.6	448.6	448.6	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6
107.5°	567.9	567.8	567.2	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8
110°	646.3	647.3	646.6	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	723.1	724.4	724.0	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0
115°	838.6	840.0	839.7	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0
117.5°	950.5	952.3	951.0	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9
120°	1021.5	1022.1	1021.1	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1
122.5°	1090.1	1090.8	1090.3	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0
125°	1190.9	1192.2	1192.2	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7
127.5°	1281.8	1282.6	1282.8	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9
130°	1341.8	1342.8	1342.4	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7
132.5°	1396.8	1397.0	1397.7	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5
135°	1479.1	1479.8	1480.4	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7
137.5°	1554.6	1554.4	1555.0	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3
140°	1600.9	1600.2	1600.5	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7
142.5°	1647.3	1647.2	1646.7	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2
145°	1711.9	1711.6	1711.6	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6
147.5°	1767.4	1767.0	1766.6	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8
150°	1802.6	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9
152.5°	1833.9	1833.2	1832.6	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8
155°	1876.7	1875.7	1875.0	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7
157.5°	1912.3	1911.2	1911.1	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3
160°	1934.2	1932.9	1932.5	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4
162.5°	1954.0	1952.1	1951.8	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7
165°	1980.0	1978.0	1977.7	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6
167.5°	1999.4	1997.0	1996.7	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8
170°	2009.3	2006.6	2006.3	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7
172.5°	2017.5	2015.1	2014.5	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9
175°	2025.9	2023.2	2022.9	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7
177.5°	2030.2	2028.3	2028.0	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.7	13.0	11.5	12.4	12.9	13.0	13.4	13.5	13.5	13.9	14.2
90°	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4
92.5°	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4
95°	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4
97.5°	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2
100°	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2
102.5°	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3
105°	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0
110°	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3





TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8
115°	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3
117.5°	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8
120°	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8
122.5°	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4
125°	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6
127.5°	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1
130°	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8
132.5°	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6
135°	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4
137.5°	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7
140°	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5
142.5°	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4
145°	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3
147.5°	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8
150°	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2
152.5°	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6
155°	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7
157.5°	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3
160°	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5
162.5°	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9
165°	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0
167.5°	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8
170°	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0
172.5°	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9
175°	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5
177.5°	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	15.0	15.7	15.1	14.9	15.1	15.7	16.4
90°	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333696

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)