

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333642-840

Luminaire Tested: **S125RDIW-S375D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333642-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3353.6 lumens
Efficiency: N/A
Efficacy: 145.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.7
10°-20°	162.4	4.8
20°-30°	235.5	7.0
30°-40°	268.4	8.0
40°-50°	261.6	7.8
50°-60°	220.2	6.6
60°-70°	154.3	4.6
70°-80°	79.3	2.4
80°-90°	21.3	0.6
90°-100°	22.4	0.7
100°-110°	138.0	4.1
110°-120°	250.3	7.5
120°-130°	321.3	9.6
130°-140°	345.6	10.3
140°-150°	324.4	9.7
150°-160°	262.4	7.8
160°-170°	169.7	5.1
170°-180°	58.5	1.7
0°-30°	456.0	13.6
0°-40°	724.3	21.6
0°-60°	1206.1	36.0
0°-90°	1461.1	43.6
90°-120°	410.7	12.2
90°-150°	1401.9	41.8
90°-180°	1893.0	56.4
0°-180°	3353.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	0	4	7	10	11	2
95°	26	24	7	9	10	33
105°	134	136	136	136	136	142
115°	252	254	255	253	250	250
125°	359	362	362	360	359	320
135°	447	450	449	448	446	345
145°	519	519	520	520	517	324
155°	571	569	569	570	567	263
165°	603	600	600	603	599	170
175°	616	614	614	617	614	59
180°	616	616	616	616	616	



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.7	8.3	7.9	7.5	7.0	6.9	6.9	7.0	7.0	7.1	7.2
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.3	7.8
92.5°	7.1	6.5	5.9	5.4	4.7	4.7	5.5	6.1	6.7	7.3	7.8
95°	26.1	25.8	25.4	25.1	24.8	22.7	18.9	15.0	11.2	7.3	7.8
97.5°	54.3	54.9	55.4	56.0	56.6	53.0	45.3	37.8	30.1	22.5	19.6
100°	76.2	76.6	77.0	77.3	77.6	77.9	78.3	78.7	79.1	79.5	64.3
102.5°	98.6	99.0	99.4	99.8	100.2	100.5	100.7	100.9	101.2	101.4	98.6
105°	134.3	134.7	135.1	135.5	135.9	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.4	171.4	171.4	171.4	171.5	171.7	171.9	172.1	172.3	172.4
110°	195.5	195.5	195.5	195.5	195.5	195.6	195.8	196.0	196.2	196.4	196.1



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.4	218.6	218.9	219.1	219.3	219.4	219.6	219.7	219.8	219.4
115°	252.2	252.7	253.2	253.7	254.2	254.5	254.6	254.7	254.8	254.9	254.5
117.5°	287.4	287.3	287.3	287.3	287.3	287.5	287.8	288.2	288.6	289.0	288.5
120°	309.3	309.2	309.1	309.0	308.9	309.0	309.3	309.6	309.9	310.2	310.0
122.5°	328.7	329.0	329.4	329.8	330.2	330.4	330.6	330.7	330.9	331.0	330.8
125°	358.6	359.3	360.0	360.7	361.4	361.8	361.8	361.8	361.8	361.8	361.4
127.5°	387.2	387.8	388.3	388.8	389.3	389.5	389.4	389.4	389.3	389.2	389.0
130°	404.8	405.3	405.8	406.3	406.8	407.1	407.2	407.3	407.4	407.5	407.2
132.5°	422.3	422.9	423.5	424.0	424.6	424.9	424.6	424.4	424.1	423.9	423.9
135°	447.3	447.9	448.5	449.1	449.7	449.9	449.7	449.5	449.3	449.1	448.9
137.5°	470.2	470.7	471.2	471.8	472.3	472.5	472.3	472.1	471.9	471.7	471.8
140°	485.1	485.3	485.5	485.7	485.9	486.0	485.9	485.8	485.7	485.6	485.8
142.5°	498.7	498.9	499.0	499.1	499.2	499.3	499.5	499.6	499.8	499.9	499.9
145°	518.6	518.8	519.0	519.2	519.4	519.5	519.5	519.5	519.5	519.5	519.6
147.5°	535.9	535.8	535.8	535.7	535.7	535.7	535.9	536.0	536.1	536.2	536.3
150°	546.8	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	547.0
152.5°	557.4	557.0	556.5	556.1	555.6	555.5	555.7	555.9	556.1	556.3	556.5
155°	571.1	570.5	569.9	569.3	568.7	568.5	568.7	568.9	569.1	569.3	569.6
157.5°	581.6	581.2	580.9	580.5	580.1	580.0	580.0	580.0	580.0	580.1	580.4
160°	588.9	588.2	587.6	587.0	586.4	586.2	586.3	586.4	586.5	586.6	587.0
162.5°	594.7	594.1	593.5	592.9	592.3	592.1	592.2	592.3	592.4	592.5	593.0
165°	602.6	602.0	601.4	600.8	600.2	599.9	600.0	600.1	600.2	600.3	600.9
167.5°	608.4	607.8	607.2	606.5	605.9	605.6	605.7	605.8	605.9	606.0	606.8
170°	611.8	611.1	610.3	609.6	608.8	608.5	608.6	608.7	608.8	608.9	609.8
172.5°	613.9	613.2	612.5	611.8	611.1	610.9	611.0	611.2	611.4	611.6	612.3
175°	616.3	615.7	615.1	614.5	613.9	613.6	613.7	613.8	613.9	614.0	614.8
177.5°	617.4	616.9	616.4	615.9	615.4	615.2	615.3	615.4	615.5	615.6	616.1
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	7.3	7.4	7.5	7.5	7.5	7.5	7.5	7.4
90°	8.3	8.8	9.3	9.8	10.1	10.4	10.7	11.0
92.5°	8.3	8.8	9.3	9.7	9.8	10.0	10.1	10.2
95°	8.3	8.8	9.3	9.6	9.6	9.6	9.6	9.6
97.5°	16.8	13.9	11.0	9.6	9.6	9.6	9.6	9.6
100°	49.3	34.1	19.0	11.2	10.8	10.4	10.0	9.6
102.5°	95.7	92.8	90.0	85.1	78.2	71.3	64.3	57.5
105°	136.1	136.1	136.1	136.1	136.0	135.9	135.8	135.7
107.5°	172.4	172.4	172.4	172.3	172.0	171.7	171.4	171.1
110°	195.8	195.5	195.2	195.1	195.2	195.3	195.4	195.5



TEST NUMBER: P333642-840

CATALOG NUMBER: S125RDIW-S375D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	219.0	218.6	218.3	218.0	217.9	217.7	217.6	217.4
115°	254.1	253.7	253.3	252.8	252.2	251.6	251.0	250.3
117.5°	287.9	287.4	286.9	286.5	286.2	286.0	285.7	285.5
120°	309.8	309.6	309.4	309.0	308.5	308.0	307.5	307.0
122.5°	330.6	330.4	330.2	329.8	329.2	328.6	328.1	327.5
125°	361.0	360.6	360.2	359.8	359.5	359.2	358.9	358.6
127.5°	388.8	388.6	388.4	387.9	387.1	386.4	385.6	384.9
130°	406.9	406.6	406.3	405.9	405.4	404.9	404.3	403.8
132.5°	423.8	423.7	423.7	423.4	422.9	422.4	421.9	421.4
135°	448.7	448.5	448.3	447.9	447.3	446.7	446.1	445.5
137.5°	471.8	471.9	471.9	471.7	471.1	470.6	470.1	469.6
140°	486.0	486.3	486.5	486.3	485.6	485.0	484.4	483.8
142.5°	500.0	500.0	500.1	499.8	499.2	498.6	498.0	497.4
145°	519.7	519.8	519.9	519.6	519.0	518.4	517.8	517.2
147.5°	536.5	536.6	536.7	536.4	535.7	535.0	534.2	533.5
150°	547.2	547.4	547.6	547.3	546.5	545.7	544.9	544.1
152.5°	556.7	556.9	557.1	556.9	556.1	555.4	554.7	554.0
155°	569.9	570.2	570.5	570.2	569.4	568.6	567.7	566.9
157.5°	580.7	581.0	581.3	581.1	580.3	579.5	578.7	577.8
160°	587.4	587.8	588.2	588.0	587.2	586.4	585.6	584.8
162.5°	593.6	594.2	594.7	594.6	593.7	592.8	591.9	591.0
165°	601.6	602.2	602.8	602.7	601.9	601.0	600.2	599.4
167.5°	607.5	608.2	608.9	608.9	607.9	607.0	606.1	605.2
170°	610.6	611.5	612.3	612.2	611.3	610.4	609.5	608.5
172.5°	613.0	613.7	614.5	614.4	613.5	612.6	611.7	610.8
175°	615.6	616.4	617.2	617.2	616.3	615.4	614.5	613.6
177.5°	616.7	617.2	617.8	617.8	617.1	616.5	615.8	615.2
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3

(END OF REPORT)