

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333698

Luminaire Tested: **S125RDIW-S850D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333698
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9488.7 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	58	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	1.4
10°-20°	361.3	3.8
20°-30°	524.0	5.5
30°-40°	597.2	6.3
40°-50°	582.1	6.1
50°-60°	490.0	5.2
60°-70°	343.5	3.6
70°-80°	176.6	1.9
80°-90°	48.8	0.5
90°-100°	73.8	0.8
100°-110°	454.8	4.8
110°-120°	824.9	8.7
120°-130°	1058.6	11.2
130°-140°	1138.6	12.0
140°-150°	1068.8	11.3
150°-160°	864.5	9.1
160°-170°	559.1	5.9
170°-180°	192.9	2.0
0°-30°	1014.6	10.7
0°-40°	1611.8	17.0
0°-60°	2683.9	28.3
0°-90°	3252.7	34.3
90°-120°	1353.5	14.3
90°-150°	4619.5	48.7
90°-180°	6236.0	65.7
0°-180°	9488.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	2	13	24	31	36	6
95°	86	78	24	31	32	109
105°	443	448	449	448	447	469
115°	831	838	840	834	825	823
125°	1182	1192	1192	1186	1182	1055
135°	1474	1482	1480	1476	1468	1136
145°	1709	1711	1712	1712	1704	1068
155°	1882	1873	1876	1879	1868	867
165°	1986	1977	1978	1986	1975	561
175°	2031	2022	2023	2034	2022	193
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.4	18.7	17.9	17.1	16.4	16.1	16.4	16.7	17.0	17.3	17.6
90°	1.5	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8
92.5°	23.2	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8
95°	85.8	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8
97.5°	179.1	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6
100°	251.4	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1
102.5°	324.9	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8
105°	442.6	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9
110°	644.3	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	719.0	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1
115°	831.0	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6
117.5°	946.9	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5
120°	1019.1	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5
122.5°	1083.0	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1
125°	1181.7	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9
127.5°	1275.9	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8
130°	1333.7	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8
132.5°	1391.5	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8
135°	1473.7	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1
137.5°	1549.3	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6
140°	1598.7	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9
142.5°	1643.2	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3
145°	1708.6	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9
147.5°	1765.8	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4
150°	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6
152.5°	1836.8	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9
155°	1881.7	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7
157.5°	1916.3	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3
160°	1940.4	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2
162.5°	1959.7	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0
165°	1985.6	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0
167.5°	2004.8	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4
170°	2015.7	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3
172.5°	2022.9	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5
175°	2030.7	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9
177.5°	2034.3	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	17.9	18.3	18.6	18.8	18.8	18.8	18.8	18.9
90°	27.4	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	27.4	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	27.4	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	55.2	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	162.2	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	315.3	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	645.3	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333698

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.8	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	837.3	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	948.8	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.8	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1089.4	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1189.6	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1281.1	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1340.8	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.6	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1478.4	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.7	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1601.5	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.4	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.3	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1767.8	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.2	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1834.6	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1877.7	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1913.3	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1935.5	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1955.9	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1982.0	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2001.8	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2012.0	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2019.9	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2028.5	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2032.1	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)