

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333678-840

Luminaire Tested: **S125RDIW-S610D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333678-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1560U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8701.8 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30	24
2	85	78	72	67	75	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.1
10°-20°	267.0	3.1
20°-30°	387.1	4.4
30°-40°	441.2	5.1
40°-50°	430.0	4.9
50°-60°	362.0	4.2
60°-70°	253.8	2.9
70°-80°	130.4	1.5
80°-90°	37.2	0.4
90°-100°	74.5	0.9
100°-110°	459.3	5.3
110°-120°	833.0	9.6
120°-130°	1069.1	12.3
130°-140°	1149.9	13.2
140°-150°	1079.3	12.4
150°-160°	873.1	10.0
160°-170°	564.7	6.5
170°-180°	194.8	2.2
0°-30°	749.6	8.6
0°-40°	1190.8	13.7
0°-60°	1982.8	22.8
0°-90°	2404.2	27.6
90°-120°	1366.8	15.7
90°-150°	4665.0	53.6
90°-180°	6298.0	72.4
0°-180°	8701.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	2	14	24	32	36	6
95°	87	79	24	32	32	110
105°	447	453	453	453	452	474
115°	839	846	848	842	833	832
125°	1193	1203	1204	1198	1193	1065
135°	1488	1497	1494	1491	1482	1147
145°	1726	1728	1728	1729	1721	1079
155°	1900	1892	1894	1898	1886	875
165°	2005	1997	1998	2006	1994	566
175°	2051	2042	2043	2054	2042	195
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.4	14.0	13.6	13.2	12.7	12.7	13.0	13.4	13.7	14.0	14.4
90°	1.5	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1
92.5°	23.4	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1
95°	86.6	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1
97.5°	180.9	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2
100°	253.9	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2
102.5°	328.1	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0
105°	447.0	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5
110°	650.7	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	726.1	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2
115°	839.2	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9
117.5°	956.2	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9
120°	1029.2	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6
122.5°	1093.7	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9
125°	1193.4	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6
127.5°	1288.5	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4
130°	1346.9	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0
132.5°	1405.2	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6
135°	1488.2	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7
137.5°	1564.6	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9
140°	1614.5	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7
142.5°	1659.4	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6
145°	1725.5	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8
147.5°	1783.2	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8
150°	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4
152.5°	1854.9	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0
155°	1900.3	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2
157.5°	1935.2	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2
160°	1959.5	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3
162.5°	1979.0	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3
165°	2005.2	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5
167.5°	2024.6	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1
170°	2035.6	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1
172.5°	2042.9	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4
175°	2050.7	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9
177.5°	2054.4	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	14.7	15.0	15.5	15.7	15.7	15.8	15.9	15.9
90°	27.7	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	27.7	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	55.7	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	163.8	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	318.4	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	651.7	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333678-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	728.9	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	845.6	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	958.2	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.9	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1100.1	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1201.3	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.7	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1354.0	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.4	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1493.0	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.0	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1617.3	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.7	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.2	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.2	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.0	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1852.7	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1896.2	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1932.2	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1954.6	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1975.2	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2001.6	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2021.5	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2031.8	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2039.8	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2048.5	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2052.1	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)