

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333663-840

Luminaire Tested: **S125RDIW-S610D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333663-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D470U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4042.5 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	38	35	31
5	70	59	51	45	66	55	48	42	49	43	38	43	38	34	37	33	30	27
6	65	53	45	39	61	50	42	37	44	38	34	39	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	29	25	46	35	28	24	31	25	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	2.4
10°-20°	267.0	6.6
20°-30°	387.1	9.6
30°-40°	441.2	10.9
40°-50°	430.0	10.6
50°-60°	362.0	9.0
60°-70°	253.8	6.3
70°-80°	130.4	3.2
80°-90°	34.2	0.8
90°-100°	39.4	1.0
100°-110°	116.3	2.9
110°-120°	197.1	4.9
120°-130°	259.3	6.4
130°-140°	290.6	7.2
140°-150°	284.8	7.0
150°-160°	239.2	5.9
160°-170°	159.0	3.9
170°-180°	55.6	1.4
0°-30°	749.6	18.5
0°-40°	1190.8	29.5
0°-60°	1982.8	49.0
0°-90°	2401.3	59.4
90°-120°	352.8	8.7
90°-150°	1187.4	29.4
90°-180°	1641.0	40.6
0°-180°	4042.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	0	4	7	10	11	4
95°	30	31	35	38	39	32
105°	104	107	109	112	114	111
115°	197	199	200	200	199	195
125°	288	290	291	290	290	258
135°	374	377	378	378	376	288
145°	454	455	457	457	455	283
155°	519	519	520	521	519	239
165°	564	564	564	565	563	159
175°	587	585	585	587	584	56
180°	588	588	588	588	588	



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.4	12.6	11.8	11.0	10.6	10.7	10.7	10.7	10.7	10.8
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.4	7.9
92.5°	11.1	11.6	12.2	12.8	13.3	14.0	14.9	15.9	16.7	17.6	18.3
95°	29.8	30.0	30.2	30.4	30.6	31.2	32.2	33.2	34.2	35.2	36.0
97.5°	49.4	49.5	49.6	49.7	49.8	50.5	51.9	53.3	54.7	56.1	56.8
100°	64.1	64.1	64.1	64.1	64.1	64.7	66.0	67.4	68.7	70.0	71.0
102.5°	79.8	80.2	80.7	81.1	81.5	82.0	82.7	83.3	84.0	84.6	85.6
105°	104.3	104.8	105.3	105.8	106.4	106.9	107.6	108.2	108.8	109.4	110.0
107.5°	131.5	132.0	132.5	133.0	133.5	134.0	134.4	134.9	135.4	135.8	136.1
110°	150.2	150.7	151.2	151.7	152.2	152.6	152.9	153.2	153.5	153.8	154.1



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.2	169.5	169.7	170.0	170.3	170.6	171.0	171.4	171.7	172.1	172.3
115°	197.2	197.6	198.1	198.5	198.9	199.2	199.4	199.7	199.9	200.1	200.0
117.5°	225.5	225.6	225.8	226.0	226.2	226.4	226.6	226.7	226.9	227.1	227.2
120°	243.1	243.6	244.1	244.6	245.1	245.4	245.5	245.6	245.7	245.8	245.8
122.5°	262.1	262.3	262.5	262.7	262.8	263.1	263.3	263.6	263.9	264.1	264.0
125°	287.9	288.5	289.1	289.7	290.3	290.7	290.8	290.9	291.0	291.1	290.9
127.5°	315.4	315.7	316.1	316.4	316.8	317.0	317.1	317.2	317.3	317.5	317.4
130°	331.8	332.3	332.9	333.4	333.9	334.3	334.5	334.7	334.9	335.1	335.0
132.5°	348.3	349.1	350.0	350.8	351.6	352.0	352.0	351.9	351.9	351.8	351.7
135°	374.4	375.1	375.7	376.3	376.9	377.2	377.3	377.4	377.5	377.6	377.6
137.5°	398.9	399.5	400.1	400.7	401.3	401.7	401.9	402.1	402.3	402.6	402.7
140°	414.7	415.2	415.7	416.2	416.7	417.2	417.5	417.8	418.1	418.4	418.6
142.5°	430.4	430.8	431.3	431.7	432.1	432.5	432.9	433.3	433.7	434.1	434.2
145°	453.6	454.0	454.4	454.8	455.2	455.6	455.9	456.2	456.5	456.8	456.8
147.5°	475.0	475.2	475.4	475.6	475.9	476.2	476.4	476.7	476.9	477.2	477.4
150°	489.3	489.2	489.1	489.0	488.9	489.1	489.5	489.9	490.3	490.7	490.7
152.5°	501.0	501.2	501.3	501.4	501.6	501.7	501.9	502.1	502.2	502.4	502.6
155°	519.1	519.1	519.1	519.1	519.1	519.1	519.2	519.3	519.4	519.5	519.9
157.5°	535.1	534.9	534.7	534.5	534.2	534.2	534.3	534.4	534.5	534.6	535.0
160°	544.7	544.4	544.0	543.7	543.4	543.3	543.4	543.5	543.6	543.7	544.2
162.5°	553.1	552.9	552.7	552.4	552.2	552.1	552.1	552.1	552.2	552.2	552.7
165°	564.3	564.1	563.9	563.7	563.5	563.5	563.6	563.7	563.8	563.9	564.3
167.5°	573.9	573.5	573.1	572.7	572.3	572.1	572.1	572.1	572.1	572.1	572.7
170°	579.0	578.6	578.1	577.7	577.3	577.1	577.1	577.1	577.1	577.1	577.7
172.5°	582.7	582.3	581.9	581.5	581.1	580.9	580.9	580.9	580.9	580.9	581.5
175°	586.8	586.3	585.9	585.5	585.1	584.9	584.9	584.9	584.9	584.9	585.5
177.5°	588.9	588.5	588.2	587.9	587.5	587.3	587.3	587.2	587.1	587.0	587.5
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	10.9	11.0	11.1	11.1	11.0	10.9	10.9	10.8
90°	8.4	8.9	9.4	9.8	10.1	10.4	10.7	11.0
92.5°	18.9	19.6	20.3	20.7	20.9	21.1	21.4	21.6
95°	36.7	37.4	38.1	38.6	38.8	39.0	39.2	39.4
97.5°	57.5	58.2	58.8	59.2	59.3	59.5	59.6	59.7
100°	71.9	72.8	73.7	74.2	74.4	74.6	74.8	75.0
102.5°	86.6	87.7	88.7	89.3	89.6	89.9	90.2	90.5
105°	110.6	111.2	111.8	112.3	112.6	112.9	113.2	113.5
107.5°	136.4	136.7	137.0	137.2	137.2	137.1	137.1	137.1
110°	154.4	154.7	155.0	155.1	155.0	154.9	154.8	154.7



TEST NUMBER: P333663-840

CATALOG NUMBER: S125RDIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.4	172.5	172.7	172.7	172.5	172.3	172.1	171.9
115°	199.9	199.8	199.7	199.5	199.4	199.3	199.2	199.1
117.5°	227.3	227.3	227.4	227.3	226.9	226.5	226.0	225.6
120°	245.8	245.8	245.8	245.6	245.2	244.8	244.4	244.0
122.5°	264.0	263.9	263.8	263.6	263.3	263.0	262.6	262.3
125°	290.7	290.5	290.3	290.1	290.0	289.9	289.8	289.7
127.5°	317.3	317.2	317.1	316.9	316.7	316.5	316.3	316.1
130°	334.9	334.8	334.7	334.5	334.3	334.1	333.9	333.7
132.5°	351.6	351.5	351.4	351.3	351.0	350.7	350.4	350.1
135°	377.6	377.6	377.6	377.4	377.0	376.6	376.2	375.8
137.5°	402.8	402.9	403.1	402.9	402.4	401.9	401.3	400.8
140°	418.8	419.0	419.2	419.0	418.5	418.0	417.5	417.0
142.5°	434.3	434.4	434.5	434.3	433.8	433.3	432.8	432.3
145°	456.8	456.8	456.8	456.7	456.4	456.1	455.8	455.4
147.5°	477.6	477.9	478.1	477.9	477.2	476.5	475.7	475.1
150°	490.7	490.7	490.7	490.6	490.4	490.2	490.0	489.8
152.5°	502.9	503.1	503.3	503.3	502.9	502.6	502.2	501.8
155°	520.3	520.7	521.1	521.1	520.6	520.1	519.6	519.1
157.5°	535.4	535.8	536.2	536.1	535.4	534.7	534.1	533.4
160°	544.6	545.0	545.4	545.3	544.8	544.3	543.8	543.3
162.5°	553.2	553.6	554.1	554.1	553.5	552.9	552.3	551.7
165°	564.7	565.1	565.5	565.4	564.8	564.2	563.6	563.0
167.5°	573.3	573.9	574.5	574.5	573.8	573.2	572.6	572.0
170°	578.3	579.0	579.7	579.6	578.9	578.1	577.4	576.7
172.5°	582.1	582.7	583.3	583.3	582.6	582.0	581.4	580.8
175°	586.1	586.8	587.4	587.3	586.6	585.9	585.2	584.5
177.5°	588.0	588.5	589.1	589.0	588.4	587.8	587.2	586.7
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1

(END OF REPORT)