

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333436-935

Luminaire Tested: **S125DIW-S1090D770U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333436-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6508.1 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8843	8843	8843	8843
5°	10240	8873	7769	8873
10°	11913	8826	6807	8826
15°	13188	8762	6279	8762
20°	14762	8659	5856	8659
25°	17293	8543	5648	8543
30°	18678	8429	5469	8429
35°	15358	8215	5351	8215
40°	10916	7917	5223	7917
45°	8386	7516	5149	7516
50°	7159	7018	5138	7018
55°	6373	6531	5183	6531
60°	5749	5997	5315	5997
65°	5310	5462	5453	5462
70°	4828	4906	5531	4906
75°	4262	4319	5480	4319
80°	3585	3522	5013	3522
85°	2838	2542	4046	2542



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	2.0
10°-20°	392.4	6.0
20°-30°	637.2	9.8
30°-40°	777.3	11.9
40°-50°	707.1	10.9
50°-60°	563.2	8.7
60°-70°	392.3	6.0
70°-80°	209.2	3.2
80°-90°	54.6	0.8
90°-100°	31.3	0.5
100°-110°	192.7	3.0
110°-120°	349.6	5.4
120°-130°	448.6	6.9
130°-140°	482.6	7.4
140°-150°	452.9	7.0
150°-160°	366.4	5.6
160°-170°	237.0	3.6
170°-180°	81.7	1.3
0°-30°	1161.5	17.8
0°-40°	1938.8	29.8
0°-60°	3209.2	49.3
0°-90°	3865.3	59.4
90°-120°	573.6	8.8
90°-150°	1957.7	30.1
90°-180°	2643.0	40.6
0°-180°	6508.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1580	1369	1198	1369	1580	159
15°	1972	1310	939	1310	1972	565
25°	2427	1199	793	1199	2427	1108
35°	1948	1042	679	1042	1948	1192
45°	918	823	564	823	918	735
55°	566	580	460	580	566	510
65°	348	357	357	357	348	345
75°	171	173	220	173	171	184
85°	38	34	55	34	38	45
90°	15	1	15	1	15	8
95°	13	36	13	36	13	11
105°	190	188	190	188	190	171
115°	350	352	350	352	350	347
125°	501	501	501	501	501	446
135°	622	625	622	625	622	480
145°	722	724	722	724	722	451
155°	792	798	792	798	792	365
165°	837	842	837	842	837	236
175°	857	861	857	861	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1448.2	1446.3	1444.5	1440.7	1443.6	1435.6	1431.9	1425.4	1417.5	1414.7	1411.4
5°	1579.5	1582.4	1585.4	1573.1	1574.3	1566.2	1547.6	1532.4	1520.3	1504.5	1493.5
7.5°	1737.6	1730.7	1730.2	1722.3	1708.7	1697.7	1678.2	1653.3	1629.3	1601.8	1579.2
10°	1816.6	1817.2	1812.0	1802.7	1788.1	1777.7	1752.1	1727.7	1698.1	1663.2	1638.2
12.5°	1876.1	1878.5	1872.0	1859.4	1852.3	1828.9	1808.9	1779.8	1744.6	1716.7	1678.7
15°	1972.4	1966.0	1961.4	1945.6	1933.5	1909.0	1877.1	1846.8	1808.4	1773.1	1737.6
17.5°	2065.1	2070.2	2061.5	2047.2	2009.3	1980.8	1937.9	1896.6	1848.8	1801.3	1758.9
20°	2147.9	2152.5	2139.2	2114.2	2068.8	2040.4	1984.0	1930.5	1875.3	1814.3	1767.8
22.5°	2251.1	2247.4	2229.3	2191.3	2152.1	2099.4	2038.4	1973.3	1904.1	1835.2	1773.4
25°	2426.8	2402.4	2391.3	2344.3	2292.6	2215.3	2131.6	2036.3	1950.3	1859.1	1780.0
27.5°	2524.2	2516.5	2504.2	2471.4	2417.1	2334.4	2235.8	2119.6	1998.3	1883.1	1779.7
30°	2504.6	2505.9	2507.0	2496.6	2461.7	2399.5	2301.3	2176.3	2032.2	1902.6	1782.9
32.5°	2331.8	2352.9	2373.1	2397.0	2406.8	2394.9	2333.4	2220.5	2072.2	1924.9	1781.1
35°	1947.9	1954.4	2020.0	2085.1	2173.4	2242.0	2287.9	2237.9	2113.0	1943.9	1778.8
37.5°	1518.9	1550.2	1595.7	1669.2	1796.7	1910.9	2057.7	2125.2	2084.9	1950.1	1774.8
40°	1294.8	1323.8	1353.5	1428.4	1535.9	1674.2	1841.0	1983.4	2016.5	1930.5	1760.8
42.5°	1121.8	1144.9	1177.8	1234.1	1324.0	1446.5	1605.8	1791.8	1906.3	1873.8	1731.6
45°	918.2	932.7	958.3	1003.1	1068.2	1164.0	1304.7	1508.0	1685.3	1744.0	1662.1
47.5°	785.9	785.8	805.7	836.6	883.6	965.0	1069.0	1228.4	1417.7	1557.8	1551.3
50°	712.5	709.6	725.2	752.0	789.2	843.3	942.6	1069.9	1251.7	1410.4	1454.6
52.5°	649.3	649.6	659.3	679.0	710.2	756.3	830.5	945.3	1100.7	1263.5	1346.7
55°	566.0	563.7	574.7	588.1	610.8	641.0	694.5	782.2	908.3	1068.7	1176.8
57.5°	489.7	496.2	500.6	509.9	528.7	549.0	594.0	658.4	758.5	896.1	1010.4
60°	445.1	451.5	455.0	464.3	479.4	496.9	531.8	584.0	668.3	786.9	900.2
62.5°	405.2	410.2	411.3	419.7	432.0	449.0	476.4	520.4	586.9	690.6	801.6
65°	347.5	347.5	349.8	358.5	364.4	379.4	400.4	432.4	485.9	566.6	661.3
67.5°	292.0	294.7	294.2	298.0	303.3	315.1	330.1	356.5	396.1	455.0	530.8
70°	255.7	258.0	257.4	260.4	266.1	273.7	285.9	310.9	339.4	389.9	455.0
72.5°	223.2	224.1	222.6	226.4	229.9	236.5	250.1	263.5	290.1	332.8	386.2
75°	170.8	172.0	173.1	175.5	179.0	182.4	189.4	202.9	220.2	252.2	286.5
77.5°	128.1	125.9	128.6	128.3	130.3	132.9	139.1	146.2	160.5	180.7	207.2
80°	96.4	97.0	97.0	97.6	100.6	102.3	107.5	112.7	123.8	138.9	157.5
82.5°	70.4	72.0	71.0	72.1	74.5	75.8	78.7	83.0	89.4	101.3	114.7
85°	38.3	35.5	36.6	37.8	37.8	38.3	40.6	42.4	45.9	50.5	55.8
87.5°	14.2	15.1	15.4	15.3	15.8	15.6	17.3	17.2	18.4	19.7	21.4
90°	15.3	14.9	14.5	14.0	13.6	13.0	12.3	11.6	10.9	10.2	9.2
92.5°	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.6	10.9	10.2	9.3
95°	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.6	10.9	10.2	15.6
97.5°	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4	27.4	31.4	42.0
100°	13.4	13.9	14.6	15.1	15.7	26.5	47.6	68.8	89.9	111.0	110.5
102.5°	80.2	89.9	99.5	109.2	118.8	125.6	129.7	133.6	137.7	141.6	141.3
105°	189.5	189.6	189.8	189.9	190.0	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	238.8	239.3	239.7	240.1	240.6	240.7	240.7	240.7	240.6	240.6	240.4
110°	273.0	272.9	272.8	272.6	272.5	272.6	273.0	273.5	273.9	274.3	274.1



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	303.7	303.8	304.1	304.3	304.4	304.8	305.4	305.9	306.4	307.0	306.9
115°	349.6	350.4	351.3	352.1	353.0	353.7	354.3	354.8	355.4	356.0	355.9
117.5°	398.6	399.0	399.3	399.7	400.1	400.6	401.4	402.1	402.9	403.6	403.0
120°	428.7	429.5	430.2	430.8	431.5	432.0	432.3	432.7	432.9	433.2	432.7
122.5°	457.3	458.1	458.9	459.8	460.5	461.2	461.4	461.7	462.0	462.3	462.1
125°	500.8	501.3	501.6	502.0	502.5	503.0	503.6	504.1	504.7	505.2	505.2
127.5°	537.4	538.5	539.5	540.5	541.7	542.3	542.6	542.9	543.2	543.5	543.6
130°	564.0	564.6	565.4	566.1	566.8	567.4	567.8	568.3	568.6	569.0	568.9
132.5°	588.5	589.2	589.9	590.6	591.3	591.7	591.8	591.9	591.9	592.0	592.4
135°	622.0	622.8	623.7	624.6	625.4	626.0	626.3	626.5	626.8	627.2	627.4
137.5°	655.7	656.4	657.2	657.9	658.7	659.0	658.9	658.9	658.8	658.8	659.0
140°	675.6	676.5	677.3	678.1	679.0	679.3	679.0	678.7	678.5	678.1	678.3
142.5°	694.5	695.3	696.2	697.1	697.9	698.3	698.3	698.2	698.1	698.1	697.8
145°	722.2	723.1	723.8	724.7	725.6	725.9	725.8	725.7	725.5	725.4	725.4
147.5°	745.0	746.1	747.1	748.1	749.1	749.5	749.3	749.2	749.0	748.8	748.6
150°	759.8	761.0	762.1	763.2	764.4	764.8	764.5	764.2	764.0	763.6	763.4
152.5°	773.6	774.6	775.7	776.6	777.7	778.1	777.7	777.5	777.2	776.9	776.6
155°	791.7	792.9	794.0	795.1	796.3	796.6	796.2	795.7	795.3	794.9	794.6
157.5°	806.9	808.0	809.2	810.3	811.4	811.8	811.3	810.9	810.5	809.9	809.9
160°	816.6	817.8	818.9	820.0	821.1	821.4	820.9	820.3	819.8	819.2	819.0
162.5°	825.3	826.6	827.8	829.1	830.3	830.5	829.7	828.9	828.1	827.3	827.2
165°	837.0	838.2	839.3	840.4	841.5	841.7	840.9	840.0	839.1	838.3	838.2
167.5°	845.2	846.4	847.7	849.0	850.3	850.4	849.4	848.3	847.3	846.4	846.2
170°	849.8	851.0	852.3	853.6	854.9	855.0	853.9	852.6	851.5	850.4	850.2
172.5°	852.8	854.1	855.4	856.7	857.9	858.1	857.0	856.0	855.0	854.0	853.8
175°	856.8	858.1	859.4	860.7	861.9	861.9	860.8	859.7	858.6	857.5	857.3
177.5°	859.1	860.0	860.9	861.8	862.7	862.8	861.9	861.2	860.4	859.6	859.5
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1408.7	1405.4	1401.7	1395.2	1387.2	1383.1	1376.6	1372.4	1364.0	1357.0	1349.6
5°	1480.1	1465.1	1451.1	1433.0	1413.3	1400.5	1385.4	1368.6	1351.2	1333.1	1313.4
7.5°	1554.2	1527.4	1498.4	1467.1	1436.6	1408.4	1381.6	1355.2	1330.6	1300.8	1275.6
10°	1604.0	1570.2	1534.2	1491.8	1450.5	1414.5	1377.9	1345.9	1313.4	1278.5	1247.7
12.5°	1653.6	1608.8	1557.9	1511.3	1461.6	1418.2	1375.1	1334.3	1293.4	1254.8	1218.8
15°	1688.8	1649.2	1602.1	1535.9	1480.1	1420.3	1363.3	1310.4	1261.0	1218.1	1172.8
17.5°	1711.9	1661.0	1610.4	1546.9	1473.8	1406.8	1342.3	1281.8	1226.1	1171.6	1127.8
20°	1716.1	1663.8	1610.9	1548.7	1473.8	1397.1	1332.6	1259.9	1200.1	1143.7	1090.2
22.5°	1714.7	1655.4	1597.8	1533.9	1460.8	1390.1	1312.1	1238.0	1173.1	1117.7	1061.9
25°	1701.6	1638.2	1566.2	1501.7	1429.6	1354.6	1275.6	1198.9	1132.6	1069.3	1014.1
27.5°	1690.7	1608.4	1526.9	1451.6	1382.1	1313.4	1237.7	1159.2	1085.6	1021.5	969.5
30°	1677.1	1587.1	1495.2	1416.8	1345.3	1278.5	1207.0	1130.3	1053.6	990.8	935.0
32.5°	1665.1	1560.1	1463.2	1377.8	1302.1	1237.1	1171.2	1098.2	1022.9	959.2	903.4
35°	1641.7	1520.3	1409.3	1312.8	1232.0	1165.2	1110.0	1042.0	972.8	911.2	857.7
37.5°	1612.1	1467.9	1348.8	1247.7	1159.2	1088.7	1037.3	985.2	918.8	859.4	811.1
40°	1588.8	1430.7	1304.7	1201.2	1109.4	1036.1	988.5	939.1	883.9	828.7	777.6
42.5°	1559.5	1397.3	1260.0	1148.7	1057.7	986.4	936.4	894.5	845.8	794.3	746.8
45°	1505.7	1336.6	1187.8	1068.2	976.3	905.9	854.3	822.9	786.3	737.4	697.3
47.5°	1426.6	1263.7	1109.8	986.3	891.6	826.4	777.9	747.8	722.0	685.7	649.4
50°	1356.3	1209.4	1053.6	931.0	836.3	770.6	725.8	698.5	676.4	648.5	617.8
52.5°	1277.8	1141.0	998.2	877.0	783.3	718.5	674.7	650.7	632.2	612.3	581.9
55°	1153.0	1036.7	904.2	789.2	702.6	639.2	600.9	580.0	564.9	549.7	531.2
57.5°	1015.5	924.5	807.2	702.0	622.2	564.6	528.8	508.5	496.7	489.0	478.0
60°	918.8	840.9	739.8	643.9	566.0	514.9	480.0	464.3	454.4	448.1	439.9
62.5°	829.1	765.1	671.4	583.9	515.8	467.4	436.4	421.1	411.6	408.5	401.8
65°	696.8	647.4	570.1	497.5	439.4	398.0	372.0	357.4	351.5	348.1	348.7
67.5°	566.5	536.4	474.3	412.3	366.0	331.4	310.5	299.3	296.4	291.7	291.6
70°	487.0	464.3	412.0	358.0	316.7	290.0	271.4	259.8	256.8	254.5	254.0
72.5°	416.8	396.9	351.5	308.2	271.1	247.7	232.3	225.3	220.6	219.2	219.1
75°	313.2	302.2	266.1	231.9	206.3	190.0	179.6	173.1	169.7	169.1	169.7
77.5°	222.7	213.0	190.1	165.8	149.7	137.4	128.5	126.3	122.3	122.5	121.9
80°	167.4	161.0	146.5	127.3	113.9	103.4	98.8	94.7	93.6	91.8	93.6
82.5°	121.3	114.5	104.6	92.4	81.4	75.1	70.4	69.1	68.4	67.7	68.0
85°	59.8	60.4	54.6	45.3	40.6	37.2	34.3	34.3	33.7	33.1	33.7
87.5°	22.1	21.0	18.9	17.3	14.7	13.2	12.5	12.7	11.5	11.3	12.0
90°	8.3	7.2	6.2	5.2	4.0	2.9	1.8	0.6	1.8	2.9	4.0
92.5°	8.4	7.6	6.7	6.6	7.4	8.3	9.0	9.8	9.0	8.3	7.4
95°	21.0	26.3	31.8	34.7	35.1	35.5	35.9	36.3	35.9	35.5	35.1
97.5°	52.7	63.4	74.0	79.0	78.2	77.5	76.7	75.9	76.7	77.5	78.2
100°	109.9	109.3	108.7	108.2	107.8	107.4	106.9	106.5	106.9	107.4	107.8
102.5°	140.9	140.6	140.3	139.8	139.3	138.8	138.2	137.7	138.2	138.8	139.3
105°	190.1	190.1	190.1	189.9	189.2	188.7	188.1	187.5	188.1	188.7	189.2
107.5°	240.0	239.8	239.5	239.4	239.4	239.4	239.4	239.4	239.4	239.4	239.4
110°	273.8	273.5	273.2	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.7	306.5	306.3	306.1	305.7	305.4	305.1	304.7	305.1	305.4	305.7
115°	355.7	355.6	355.4	355.0	354.3	353.6	352.8	352.1	352.8	353.6	354.3
117.5°	402.5	402.0	401.4	401.1	401.2	401.2	401.2	401.3	401.2	401.2	401.2
120°	432.3	431.9	431.4	431.4	431.4	431.6	431.8	431.9	431.8	431.6	431.4
122.5°	461.8	461.7	461.5	461.2	460.5	460.0	459.5	458.9	459.5	460.0	460.5
125°	505.2	505.2	505.2	504.8	503.8	502.8	501.8	500.8	501.8	502.8	503.8
127.5°	543.7	543.8	543.9	543.5	542.9	542.2	541.5	540.7	541.5	542.2	542.9
130°	568.8	568.6	568.5	568.1	567.4	566.6	565.9	565.2	565.9	566.6	567.4
132.5°	592.6	593.0	593.3	593.1	592.2	591.4	590.6	589.7	590.6	591.4	592.2
135°	627.7	628.0	628.3	628.0	627.2	626.3	625.4	624.6	625.4	626.3	627.2
137.5°	659.3	659.5	659.8	659.5	658.8	658.1	657.4	656.6	657.4	658.1	658.8
140°	678.5	678.6	678.7	678.6	678.4	678.1	677.8	677.5	677.8	678.1	678.4
142.5°	697.7	697.5	697.2	697.1	696.9	696.7	696.5	696.4	696.5	696.7	696.9
145°	725.4	725.4	725.4	725.2	725.0	724.7	724.4	724.1	724.4	724.7	725.0
147.5°	748.5	748.4	748.2	748.1	748.2	748.2	748.3	748.4	748.3	748.2	748.2
150°	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	763.4	763.1	762.8
152.5°	776.4	776.1	775.8	775.9	776.6	777.2	777.8	778.4	777.8	777.2	776.6
155°	794.4	794.1	793.8	794.1	794.9	795.7	796.6	797.5	796.6	795.7	794.9
157.5°	809.9	809.9	809.9	810.1	810.6	811.1	811.7	812.1	811.7	811.1	810.6
160°	818.9	818.7	818.6	819.0	819.8	820.6	821.5	822.3	821.5	820.6	819.8
162.5°	827.1	826.9	826.7	827.1	827.9	828.8	829.7	830.5	829.7	828.8	827.9
165°	838.0	837.8	837.8	838.1	839.0	839.8	840.6	841.5	840.6	839.8	839.0
167.5°	846.0	845.9	845.8	846.1	847.1	847.9	848.8	849.6	848.8	847.9	847.1
170°	850.2	850.0	849.8	850.2	851.3	852.2	853.3	854.3	853.3	852.2	851.3
172.5°	853.5	853.3	853.0	853.3	854.3	855.3	856.4	857.3	856.4	855.3	854.3
175°	857.1	857.0	856.9	857.2	858.1	858.9	859.8	860.7	859.8	858.9	858.1
177.5°	859.4	859.3	859.1	859.5	860.1	860.8	861.4	862.1	861.4	860.8	860.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1345.4	1340.3	1336.1	1326.8	1321.7	1314.7	1309.2	1315.2	1308.7	1311.5	1307.3
5°	1303.5	1287.2	1275.6	1258.7	1244.2	1230.8	1221.0	1219.2	1214.5	1212.2	1205.2
7.5°	1253.0	1232.7	1212.7	1190.6	1172.0	1153.1	1141.0	1131.0	1124.4	1115.7	1109.7
10°	1223.3	1195.9	1172.8	1146.0	1122.7	1102.4	1086.2	1078.0	1070.5	1059.4	1055.3
12.5°	1186.5	1158.3	1130.0	1101.4	1079.0	1056.4	1042.4	1030.1	1024.8	1012.4	1011.2
15°	1142.5	1100.1	1072.2	1043.1	1012.4	993.8	982.1	968.7	962.9	954.2	947.8
17.5°	1089.9	1052.1	1017.2	987.1	960.7	945.0	930.7	921.4	911.5	905.8	895.3
20°	1051.9	1015.8	980.9	949.0	928.7	910.6	899.0	890.3	879.9	876.9	866.5
22.5°	1019.8	980.0	946.6	919.7	897.5	877.2	864.6	858.7	851.4	842.5	840.4
25°	967.6	926.3	897.9	871.2	851.4	832.8	824.1	816.5	809.5	803.1	800.8
27.5°	922.5	885.6	851.8	827.7	810.5	793.5	785.8	776.6	771.5	766.4	760.1
30°	890.9	853.1	823.5	800.2	781.6	766.5	758.4	752.0	747.3	742.7	739.2
32.5°	858.3	823.4	794.6	771.9	753.3	741.8	734.7	730.1	725.0	719.5	715.1
35°	815.4	777.0	749.1	729.4	714.8	706.1	697.9	693.9	688.0	688.0	683.4
37.5°	766.9	733.7	709.1	691.1	678.0	670.3	661.4	658.7	655.0	652.5	650.8
40°	738.0	707.2	684.0	666.0	652.0	645.7	638.7	634.0	631.7	628.8	627.6
42.5°	708.3	678.9	656.6	640.0	627.8	622.4	615.9	612.6	608.0	604.2	603.5
45°	663.1	634.6	614.2	600.9	590.4	584.0	580.0	573.0	570.7	566.0	565.4
47.5°	620.2	592.9	572.9	562.0	552.8	547.5	541.1	534.2	531.5	529.2	528.9
50°	588.1	563.1	544.5	534.1	525.4	517.8	511.4	506.8	505.0	505.0	506.2
52.5°	555.6	534.3	518.5	505.7	497.5	489.4	483.5	480.7	478.0	480.9	482.9
55°	507.9	486.4	474.8	462.6	454.4	445.1	442.2	441.1	439.4	444.0	446.3
57.5°	457.4	442.4	428.8	416.6	409.3	404.0	400.0	399.3	402.6	404.8	412.3
60°	425.4	407.9	395.7	386.4	377.7	374.3	373.1	372.0	374.3	380.6	390.5
62.5°	390.0	375.9	362.7	355.8	349.4	343.5	343.4	344.1	348.7	356.0	365.8
65°	338.2	326.0	317.3	309.2	303.9	300.4	301.6	303.9	309.2	319.0	330.1
67.5°	285.6	277.2	269.4	262.8	257.8	257.8	259.0	262.4	268.6	280.0	290.1
70°	251.7	242.4	235.9	233.1	228.9	226.6	230.1	235.9	241.2	251.7	260.4
72.5°	217.7	209.8	204.8	202.9	201.0	199.2	200.4	206.6	213.7	224.2	234.3
75°	167.4	164.5	161.0	158.7	156.9	158.1	159.2	165.1	170.8	181.9	193.6
77.5°	122.2	119.2	117.0	116.5	115.5	116.1	119.3	123.6	129.3	137.4	146.2
80°	92.4	91.3	90.1	89.5	89.5	90.1	94.7	97.6	102.9	110.4	117.4
82.5°	67.3	66.6	66.4	66.2	66.7	66.8	69.7	73.4	77.7	83.4	89.5
85°	35.5	34.3	36.0	36.6	35.5	37.2	38.3	40.6	42.4	45.3	48.2
87.5°	12.7	13.8	13.5	14.2	14.4	15.5	15.2	17.2	18.3	19.4	19.0
90°	5.2	6.2	7.2	8.3	9.2	10.2	10.9	11.6	12.3	13.0	13.6
92.5°	6.6	6.7	7.6	8.4	9.3	10.2	10.9	11.6	12.3	13.0	13.5
95°	34.7	31.8	26.3	21.0	15.6	10.2	10.9	11.6	12.3	13.0	13.4
97.5°	79.0	74.0	63.4	52.7	42.0	31.4	27.4	23.4	19.4	15.4	13.4
100°	108.2	108.7	109.3	109.9	110.5	111.0	89.9	68.8	47.6	26.5	15.7
102.5°	139.8	140.3	140.6	140.9	141.3	141.6	137.7	133.6	129.7	125.6	118.8
105°	189.9	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.0
107.5°	239.4	239.5	239.8	240.0	240.4	240.6	240.6	240.7	240.7	240.7	240.6
110°	273.0	273.2	273.5	273.8	274.1	274.3	273.9	273.5	273.0	272.6	272.5



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	306.1	306.3	306.5	306.7	306.9	307.0	306.4	305.9	305.4	304.8	304.4
115°	355.0	355.4	355.6	355.7	355.9	356.0	355.4	354.8	354.3	353.7	353.0
117.5°	401.1	401.4	402.0	402.5	403.0	403.6	402.9	402.1	401.4	400.6	400.1
120°	431.4	431.4	431.9	432.3	432.7	433.2	432.9	432.7	432.3	432.0	431.5
122.5°	461.2	461.5	461.7	461.8	462.1	462.3	462.0	461.7	461.4	461.2	460.5
125°	504.8	505.2	505.2	505.2	505.2	505.2	504.7	504.1	503.6	503.0	502.5
127.5°	543.5	543.9	543.8	543.7	543.6	543.5	543.2	542.9	542.6	542.3	541.7
130°	568.1	568.5	568.6	568.8	568.9	569.0	568.6	568.3	567.8	567.4	566.8
132.5°	593.1	593.3	593.0	592.6	592.4	592.0	591.9	591.9	591.8	591.7	591.3
135°	628.0	628.3	628.0	627.7	627.4	627.2	626.8	626.5	626.3	626.0	625.4
137.5°	659.5	659.8	659.5	659.3	659.0	658.8	658.8	658.9	658.9	659.0	658.7
140°	678.6	678.7	678.6	678.5	678.3	678.1	678.5	678.7	679.0	679.3	679.0
142.5°	697.1	697.2	697.5	697.7	697.8	698.1	698.1	698.2	698.3	698.3	697.9
145°	725.2	725.4	725.4	725.4	725.4	725.4	725.5	725.7	725.8	725.9	725.6
147.5°	748.1	748.2	748.4	748.5	748.6	748.8	749.0	749.2	749.3	749.5	749.1
150°	762.5	762.5	762.8	763.1	763.4	763.6	764.0	764.2	764.5	764.8	764.4
152.5°	775.9	775.8	776.1	776.4	776.6	776.9	777.2	777.5	777.7	778.1	777.7
155°	794.1	793.8	794.1	794.4	794.6	794.9	795.3	795.7	796.2	796.6	796.3
157.5°	810.1	809.9	809.9	809.9	809.9	809.9	810.5	810.9	811.3	811.8	811.4
160°	819.0	818.6	818.7	818.9	819.0	819.2	819.8	820.3	820.9	821.4	821.1
162.5°	827.1	826.7	826.9	827.1	827.2	827.3	828.1	828.9	829.7	830.5	830.3
165°	838.1	837.8	837.8	838.0	838.2	838.3	839.1	840.0	840.9	841.7	841.5
167.5°	846.1	845.8	845.9	846.0	846.2	846.4	847.3	848.3	849.4	850.4	850.3
170°	850.2	849.8	850.0	850.2	850.2	850.4	851.5	852.6	853.9	855.0	854.9
172.5°	853.3	853.0	853.3	853.5	853.8	854.0	855.0	856.0	857.0	858.1	857.9
175°	857.2	856.9	857.0	857.1	857.3	857.5	858.6	859.7	860.8	861.9	861.9
177.5°	859.5	859.1	859.3	859.4	859.5	859.6	860.4	861.2	861.9	862.8	862.7
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1304.5	1307.8	1305.0	1308.7	1305.0	1307.8	1304.5	1307.3	1311.5	1308.7	1315.2
5°	1202.4	1197.1	1200.6	1198.3	1200.6	1197.1	1202.4	1205.2	1212.2	1214.5	1219.2
7.5°	1108.0	1103.0	1097.3	1094.6	1097.3	1103.0	1108.0	1109.7	1115.7	1124.4	1131.0
10°	1049.0	1042.6	1042.0	1037.9	1042.0	1042.6	1049.0	1055.3	1059.4	1070.5	1078.0
12.5°	1005.7	999.8	993.2	991.4	993.2	999.8	1005.7	1011.2	1012.4	1024.8	1030.1
15°	944.3	939.7	935.6	939.1	935.6	939.7	944.3	947.8	954.2	962.9	968.7
17.5°	893.3	889.5	888.8	884.5	888.8	889.5	893.3	895.3	905.8	911.5	921.4
20°	861.3	858.3	859.5	852.0	859.5	858.3	861.3	866.5	876.9	879.9	890.3
22.5°	835.7	830.0	829.3	827.8	829.3	830.0	835.7	840.4	842.5	851.4	858.7
25°	795.6	792.6	789.8	792.6	789.8	792.6	795.6	800.8	803.1	809.5	816.5
27.5°	760.6	757.1	756.3	756.6	756.3	757.1	760.6	760.1	766.4	771.5	776.6
30°	739.2	733.4	734.0	733.4	734.0	733.4	739.2	739.2	742.7	747.3	752.0
32.5°	715.9	712.0	711.2	710.2	711.2	712.0	715.9	715.1	719.5	725.0	730.1
35°	681.7	681.7	678.7	678.7	678.7	681.7	681.7	683.4	688.0	688.0	693.9
37.5°	649.5	648.8	647.1	647.4	647.1	648.8	649.5	650.8	652.5	655.0	658.7
40°	625.3	624.7	622.9	619.5	622.9	624.7	625.3	627.6	628.8	631.7	634.0
42.5°	602.0	600.1	599.3	598.1	599.3	600.1	602.0	603.5	604.2	608.0	612.6
45°	565.4	565.4	564.3	563.7	564.3	565.4	565.4	565.4	566.0	570.7	573.0
47.5°	529.9	530.9	533.1	532.8	533.1	530.9	529.9	528.9	529.2	531.5	534.2
50°	508.5	509.1	510.8	511.4	510.8	509.1	508.5	506.2	505.0	505.0	506.8
52.5°	484.7	488.2	490.3	490.0	490.3	488.2	484.7	482.9	480.9	478.0	480.7
55°	451.5	455.6	459.7	460.3	459.7	455.6	451.5	446.3	444.0	439.4	441.1
57.5°	418.6	424.3	428.6	430.1	428.6	424.3	418.6	412.3	404.8	402.6	399.3
60°	396.3	403.9	409.1	411.5	409.1	403.9	396.3	390.5	380.6	374.3	372.0
62.5°	375.0	383.4	388.7	389.1	388.7	383.4	375.0	365.8	356.0	348.7	344.1
65°	339.9	348.7	353.4	356.8	353.4	348.7	339.9	330.1	319.0	309.2	303.9
67.5°	302.3	311.0	316.2	318.9	316.2	311.0	302.3	290.1	280.0	268.6	262.4
70°	274.9	283.6	290.6	292.9	290.6	283.6	274.9	260.4	251.7	241.2	235.9
72.5°	247.9	255.7	261.3	264.1	261.3	255.7	247.9	234.3	224.2	213.7	206.6
75°	201.0	211.5	216.8	219.6	216.8	211.5	201.0	193.6	181.9	170.8	165.1
77.5°	155.1	164.5	167.7	169.2	167.7	164.5	155.1	146.2	137.4	129.3	123.6
80°	124.3	130.2	134.2	134.8	134.2	130.2	124.3	117.4	110.4	102.9	97.6
82.5°	95.6	100.4	101.7	103.2	101.7	100.4	95.6	89.5	83.4	77.7	73.4
85°	52.3	54.6	55.2	54.6	55.2	54.6	52.3	48.2	45.3	42.4	40.6
87.5°	20.0	19.6	19.7	20.8	19.7	19.6	20.0	19.0	19.4	18.3	17.2
90°	14.0	14.5	14.9	15.3	14.9	14.5	14.0	13.6	13.0	12.3	11.6
92.5°	13.7	13.9	14.1	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.6
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.6
97.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4
100°	15.1	14.6	13.9	13.4	13.9	14.6	15.1	15.7	26.5	47.6	68.8
102.5°	109.2	99.5	89.9	80.2	89.9	99.5	109.2	118.8	125.6	129.7	133.6
105°	189.9	189.8	189.6	189.5	189.6	189.8	189.9	190.0	190.1	190.1	190.1
107.5°	240.1	239.7	239.3	238.8	239.3	239.7	240.1	240.6	240.7	240.7	240.7
110°	272.6	272.8	272.9	273.0	272.9	272.8	272.6	272.5	272.6	273.0	273.5



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	304.3	304.1	303.8	303.7	303.8	304.1	304.3	304.4	304.8	305.4	305.9
115°	352.1	351.3	350.4	349.6	350.4	351.3	352.1	353.0	353.7	354.3	354.8
117.5°	399.7	399.3	399.0	398.6	399.0	399.3	399.7	400.1	400.6	401.4	402.1
120°	430.8	430.2	429.5	428.7	429.5	430.2	430.8	431.5	432.0	432.3	432.7
122.5°	459.8	458.9	458.1	457.3	458.1	458.9	459.8	460.5	461.2	461.4	461.7
125°	502.0	501.6	501.3	500.8	501.3	501.6	502.0	502.5	503.0	503.6	504.1
127.5°	540.5	539.5	538.5	537.4	538.5	539.5	540.5	541.7	542.3	542.6	542.9
130°	566.1	565.4	564.6	564.0	564.6	565.4	566.1	566.8	567.4	567.8	568.3
132.5°	590.6	589.9	589.2	588.5	589.2	589.9	590.6	591.3	591.7	591.8	591.9
135°	624.6	623.7	622.8	622.0	622.8	623.7	624.6	625.4	626.0	626.3	626.5
137.5°	657.9	657.2	656.4	655.7	656.4	657.2	657.9	658.7	659.0	658.9	658.9
140°	678.1	677.3	676.5	675.6	676.5	677.3	678.1	679.0	679.3	679.0	678.7
142.5°	697.1	696.2	695.3	694.5	695.3	696.2	697.1	697.9	698.3	698.3	698.2
145°	724.7	723.8	723.1	722.2	723.1	723.8	724.7	725.6	725.9	725.8	725.7
147.5°	748.1	747.1	746.1	745.0	746.1	747.1	748.1	749.1	749.5	749.3	749.2
150°	763.2	762.1	761.0	759.8	761.0	762.1	763.2	764.4	764.8	764.5	764.2
152.5°	776.6	775.7	774.6	773.6	774.6	775.7	776.6	777.7	778.1	777.7	777.5
155°	795.1	794.0	792.9	791.7	792.9	794.0	795.1	796.3	796.6	796.2	795.7
157.5°	810.3	809.2	808.0	806.9	808.0	809.2	810.3	811.4	811.8	811.3	810.9
160°	820.0	818.9	817.8	816.6	817.8	818.9	820.0	821.1	821.4	820.9	820.3
162.5°	829.1	827.8	826.6	825.3	826.6	827.8	829.1	830.3	830.5	829.7	828.9
165°	840.4	839.3	838.2	837.0	838.2	839.3	840.4	841.5	841.7	840.9	840.0
167.5°	849.0	847.7	846.4	845.2	846.4	847.7	849.0	850.3	850.4	849.4	848.3
170°	853.6	852.3	851.0	849.8	851.0	852.3	853.6	854.9	855.0	853.9	852.6
172.5°	856.7	855.4	854.1	852.8	854.1	855.4	856.7	857.9	858.1	857.0	856.0
175°	860.7	859.4	858.1	856.8	858.1	859.4	860.7	861.9	861.9	860.8	859.7
177.5°	861.8	860.9	860.0	859.1	860.0	860.9	861.8	862.7	862.8	861.9	861.2
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1309.2	1314.7	1321.7	1326.8	1336.1	1340.3	1345.4	1349.6	1357.0	1364.0	1372.4
5°	1221.0	1230.8	1244.2	1258.7	1275.6	1287.2	1303.5	1313.4	1333.1	1351.2	1368.6
7.5°	1141.0	1153.1	1172.0	1190.6	1212.7	1232.7	1253.0	1275.6	1300.8	1330.6	1355.2
10°	1086.2	1102.4	1122.7	1146.0	1172.8	1195.9	1223.3	1247.7	1278.5	1313.4	1345.9
12.5°	1042.4	1056.4	1079.0	1101.4	1130.0	1158.3	1186.5	1218.8	1254.8	1293.4	1334.3
15°	982.1	993.8	1012.4	1043.1	1072.2	1100.1	1142.5	1172.8	1218.1	1261.0	1310.4
17.5°	930.7	945.0	960.7	987.1	1017.2	1052.1	1089.9	1127.8	1171.6	1226.1	1281.8
20°	899.0	910.6	928.7	949.0	980.9	1015.8	1051.9	1090.2	1143.7	1200.1	1259.9
22.5°	864.6	877.2	897.5	919.7	946.6	980.0	1019.8	1061.9	1117.7	1173.1	1238.0
25°	824.1	832.8	851.4	871.2	897.9	926.3	967.6	1014.1	1069.3	1132.6	1198.9
27.5°	785.8	793.5	810.5	827.7	851.8	885.6	922.5	969.5	1021.5	1085.6	1159.2
30°	758.4	766.5	781.6	800.2	823.5	853.1	890.9	935.0	990.8	1053.6	1130.3
32.5°	734.7	741.8	753.3	771.9	794.6	823.4	858.3	903.4	959.2	1022.9	1098.2
35°	697.9	706.1	714.8	729.4	749.1	777.0	815.4	857.7	911.2	972.8	1042.0
37.5°	661.4	670.3	678.0	691.1	709.1	733.7	766.9	811.1	859.4	918.8	985.2
40°	638.7	645.7	652.0	666.0	684.0	707.2	738.0	777.6	828.7	883.9	939.1
42.5°	615.9	622.4	627.8	640.0	656.6	678.9	708.3	746.8	794.3	845.8	894.5
45°	580.0	584.0	590.4	600.9	614.2	634.6	663.1	697.3	737.4	786.3	822.9
47.5°	541.1	547.5	552.8	562.0	572.9	592.9	620.2	649.4	685.7	722.0	747.8
50°	511.4	517.8	525.4	534.1	544.5	563.1	588.1	617.8	648.5	676.4	698.5
52.5°	483.5	489.4	497.5	505.7	518.5	534.3	555.6	581.9	612.3	632.2	650.7
55°	442.2	445.1	454.4	462.6	474.8	486.4	507.9	531.2	549.7	564.9	580.0
57.5°	400.0	404.0	409.3	416.6	428.8	442.4	457.4	478.0	489.0	496.7	508.5
60°	373.1	374.3	377.7	386.4	395.7	407.9	425.4	439.9	448.1	454.4	464.3
62.5°	343.4	343.5	349.4	355.8	362.7	375.9	390.0	401.8	408.5	411.6	421.1
65°	301.6	300.4	303.9	309.2	317.3	326.0	338.2	348.7	348.1	351.5	357.4
67.5°	259.0	257.8	257.8	262.8	269.4	277.2	285.6	291.6	291.7	296.4	299.3
70°	230.1	226.6	228.9	233.1	235.9	242.4	251.7	254.0	254.5	256.8	259.8
72.5°	200.4	199.2	201.0	202.9	204.8	209.8	217.7	219.1	219.2	220.6	225.3
75°	159.2	158.1	156.9	158.7	161.0	164.5	167.4	169.7	169.1	169.7	173.1
77.5°	119.3	116.1	115.5	116.5	117.0	119.2	122.2	121.9	122.5	122.3	126.3
80°	94.7	90.1	89.5	89.5	90.1	91.3	92.4	93.6	91.8	93.6	94.7
82.5°	69.7	66.8	66.7	66.2	66.4	66.6	67.3	68.0	67.7	68.4	69.1
85°	38.3	37.2	35.5	36.6	36.0	34.3	35.5	33.7	33.1	33.7	34.3
87.5°	15.2	15.5	14.4	14.2	13.5	13.8	12.7	12.0	11.3	11.5	12.7
90°	10.9	10.2	9.2	8.3	7.2	6.2	5.2	4.0	2.9	1.8	0.6
92.5°	10.9	10.2	9.3	8.4	7.6	6.7	6.6	7.4	8.3	9.0	9.8
95°	10.9	10.2	15.6	21.0	26.3	31.8	34.7	35.1	35.5	35.9	36.3
97.5°	27.4	31.4	42.0	52.7	63.4	74.0	79.0	78.2	77.5	76.7	75.9
100°	89.9	111.0	110.5	109.9	109.3	108.7	108.2	107.8	107.4	106.9	106.5
102.5°	137.7	141.6	141.3	140.9	140.6	140.3	139.8	139.3	138.8	138.2	137.7
105°	190.1	190.1	190.1	190.1	190.1	190.1	189.9	189.2	188.7	188.1	187.5
107.5°	240.6	240.6	240.4	240.0	239.8	239.5	239.4	239.4	239.4	239.4	239.4
110°	273.9	274.3	274.1	273.8	273.5	273.2	273.0	273.0	273.0	273.0	273.0



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	306.4	307.0	306.9	306.7	306.5	306.3	306.1	305.7	305.4	305.1	304.7
115°	355.4	356.0	355.9	355.7	355.6	355.4	355.0	354.3	353.6	352.8	352.1
117.5°	402.9	403.6	403.0	402.5	402.0	401.4	401.1	401.2	401.2	401.2	401.3
120°	432.9	433.2	432.7	432.3	431.9	431.4	431.4	431.4	431.6	431.8	431.9
122.5°	462.0	462.3	462.1	461.8	461.7	461.5	461.2	460.5	460.0	459.5	458.9
125°	504.7	505.2	505.2	505.2	505.2	505.2	504.8	503.8	502.8	501.8	500.8
127.5°	543.2	543.5	543.6	543.7	543.8	543.9	543.5	542.9	542.2	541.5	540.7
130°	568.6	569.0	568.9	568.8	568.6	568.5	568.1	567.4	566.6	565.9	565.2
132.5°	591.9	592.0	592.4	592.6	593.0	593.3	593.1	592.2	591.4	590.6	589.7
135°	626.8	627.2	627.4	627.7	628.0	628.3	628.0	627.2	626.3	625.4	624.6
137.5°	658.8	658.8	659.0	659.3	659.5	659.8	659.5	658.8	658.1	657.4	656.6
140°	678.5	678.1	678.3	678.5	678.6	678.7	678.6	678.4	678.1	677.8	677.5
142.5°	698.1	698.1	697.8	697.7	697.5	697.2	697.1	696.9	696.7	696.5	696.4
145°	725.5	725.4	725.4	725.4	725.4	725.4	725.2	725.0	724.7	724.4	724.1
147.5°	749.0	748.8	748.6	748.5	748.4	748.2	748.1	748.2	748.2	748.3	748.4
150°	764.0	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6
152.5°	777.2	776.9	776.6	776.4	776.1	775.8	775.9	776.6	777.2	777.8	778.4
155°	795.3	794.9	794.6	794.4	794.1	793.8	794.1	794.9	795.7	796.6	797.5
157.5°	810.5	809.9	809.9	809.9	809.9	809.9	810.1	810.6	811.1	811.7	812.1
160°	819.8	819.2	819.0	818.9	818.7	818.6	819.0	819.8	820.6	821.5	822.3
162.5°	828.1	827.3	827.2	827.1	826.9	826.7	827.1	827.9	828.8	829.7	830.5
165°	839.1	838.3	838.2	838.0	837.8	837.8	838.1	839.0	839.8	840.6	841.5
167.5°	847.3	846.4	846.2	846.0	845.9	845.8	846.1	847.1	847.9	848.8	849.6
170°	851.5	850.4	850.2	850.2	850.0	849.8	850.2	851.3	852.2	853.3	854.3
172.5°	855.0	854.0	853.8	853.5	853.3	853.0	853.3	854.3	855.3	856.4	857.3
175°	858.6	857.5	857.3	857.1	857.0	856.9	857.2	858.1	858.9	859.8	860.7
177.5°	860.4	859.6	859.5	859.4	859.3	859.1	859.5	860.1	860.8	861.4	862.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1376.6	1383.1	1387.2	1395.2	1401.7	1405.4	1408.7	1411.4	1414.7	1417.5	1425.4
5°	1385.4	1400.5	1413.3	1433.0	1451.1	1465.1	1480.1	1493.5	1504.5	1520.3	1532.4
7.5°	1381.6	1408.4	1436.6	1467.1	1498.4	1527.4	1554.2	1579.2	1601.8	1629.3	1653.3
10°	1377.9	1414.5	1450.5	1491.8	1534.2	1570.2	1604.0	1638.2	1663.2	1698.1	1727.7
12.5°	1375.1	1418.2	1461.6	1511.3	1557.9	1608.8	1653.6	1678.7	1716.7	1744.6	1779.8
15°	1363.3	1420.3	1480.1	1535.9	1602.1	1649.2	1688.8	1737.6	1773.1	1808.4	1846.8
17.5°	1342.3	1406.8	1473.8	1546.9	1610.4	1661.0	1711.9	1758.9	1801.3	1848.8	1896.6
20°	1332.6	1397.1	1473.8	1548.7	1610.9	1663.8	1716.1	1767.8	1814.3	1875.3	1930.5
22.5°	1312.1	1390.1	1460.8	1533.9	1597.8	1655.4	1714.7	1773.4	1835.2	1904.1	1973.3
25°	1275.6	1354.6	1429.6	1501.7	1566.2	1638.2	1701.6	1780.0	1859.1	1950.3	2036.3
27.5°	1237.7	1313.4	1382.1	1451.6	1526.9	1608.4	1690.7	1779.7	1883.1	1998.3	2119.6
30°	1207.0	1278.5	1345.3	1416.8	1495.2	1587.1	1677.1	1782.9	1902.6	2032.2	2176.3
32.5°	1171.2	1237.1	1302.1	1377.8	1463.2	1560.1	1665.1	1781.1	1924.9	2072.2	2220.5
35°	1110.0	1165.2	1232.0	1312.8	1409.3	1520.3	1641.7	1778.8	1943.9	2113.0	2237.9
37.5°	1037.3	1088.7	1159.2	1247.7	1348.8	1467.9	1612.1	1774.8	1950.1	2084.9	2125.2
40°	988.5	1036.1	1109.4	1201.2	1304.7	1430.7	1588.8	1760.8	1930.5	2016.5	1983.4
42.5°	936.4	986.4	1057.7	1148.7	1260.0	1397.3	1559.5	1731.6	1873.8	1906.3	1791.8
45°	854.3	905.9	976.3	1068.2	1187.8	1336.6	1505.7	1662.1	1744.0	1685.3	1508.0
47.5°	777.9	826.4	891.6	986.3	1109.8	1263.7	1426.6	1551.3	1557.8	1417.7	1228.4
50°	725.8	770.6	836.3	931.0	1053.6	1209.4	1356.3	1454.6	1410.4	1251.7	1069.9
52.5°	674.7	718.5	783.3	877.0	998.2	1141.0	1277.8	1346.7	1263.5	1100.7	945.3
55°	600.9	639.2	702.6	789.2	904.2	1036.7	1153.0	1176.8	1068.7	908.3	782.2
57.5°	528.8	564.6	622.2	702.0	807.2	924.5	1015.5	1010.4	896.1	758.5	658.4
60°	480.0	514.9	566.0	643.9	739.8	840.9	918.8	900.2	786.9	668.3	584.0
62.5°	436.4	467.4	515.8	583.9	671.4	765.1	829.1	801.6	690.6	586.9	520.4
65°	372.0	398.0	439.4	497.5	570.1	647.4	696.8	661.3	566.6	485.9	432.4
67.5°	310.5	331.4	366.0	412.3	474.3	536.4	566.5	530.8	455.0	396.1	356.5
70°	271.4	290.0	316.7	358.0	412.0	464.3	487.0	455.0	389.9	339.4	310.9
72.5°	232.3	247.7	271.1	308.2	351.5	396.9	416.8	386.2	332.8	290.1	263.5
75°	179.6	190.0	206.3	231.9	266.1	302.2	313.2	286.5	252.2	220.2	202.9
77.5°	128.5	137.4	149.7	165.8	190.1	213.0	222.7	207.2	180.7	160.5	146.2
80°	98.8	103.4	113.9	127.3	146.5	161.0	167.4	157.5	138.9	123.8	112.7
82.5°	70.4	75.1	81.4	92.4	104.6	114.5	121.3	114.7	101.3	89.4	83.0
85°	34.3	37.2	40.6	45.3	54.6	60.4	59.8	55.8	50.5	45.9	42.4
87.5°	12.5	13.2	14.7	17.3	18.9	21.0	22.1	21.4	19.7	18.4	17.2
90°	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9	11.6
92.5°	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9	11.6
95°	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9	11.6
97.5°	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4	23.4
100°	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9	68.8
102.5°	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7	133.6
105°	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6	240.7
110°	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9	273.5



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4	305.9
115°	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4	354.8
117.5°	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9	402.1
120°	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9	432.7
122.5°	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0	461.7
125°	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7	504.1
127.5°	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2	542.9
130°	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6	568.3
132.5°	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9	591.9
135°	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8	626.5
137.5°	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8	658.9
140°	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5	678.7
142.5°	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1	698.2
145°	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5	725.7
147.5°	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0	749.2
150°	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0	764.2
152.5°	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2	777.5
155°	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3	795.7
157.5°	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5	810.9
160°	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8	820.3
162.5°	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1	828.9
165°	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1	840.0
167.5°	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3	848.3
170°	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5	852.6
172.5°	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0	856.0
175°	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6	859.7
177.5°	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4	861.2
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1431.9	1435.6	1443.6	1440.7	1444.5	1446.3	1448.2
5°	1547.6	1566.2	1574.3	1573.1	1585.4	1582.4	1579.5
7.5°	1678.2	1697.7	1708.7	1722.3	1730.2	1730.7	1737.6
10°	1752.1	1777.7	1788.1	1802.7	1812.0	1817.2	1816.6
12.5°	1808.9	1828.9	1852.3	1859.4	1872.0	1878.5	1876.1
15°	1877.1	1909.0	1933.5	1945.6	1961.4	1966.0	1972.4
17.5°	1937.9	1980.8	2009.3	2047.2	2061.5	2070.2	2065.1
20°	1984.0	2040.4	2068.8	2114.2	2139.2	2152.5	2147.9
22.5°	2038.4	2099.4	2152.1	2191.3	2229.3	2247.4	2251.1
25°	2131.6	2215.3	2292.6	2344.3	2391.3	2402.4	2426.8
27.5°	2235.8	2334.4	2417.1	2471.4	2504.2	2516.5	2524.2
30°	2301.3	2399.5	2461.7	2496.6	2507.0	2505.9	2504.6
32.5°	2333.4	2394.9	2406.8	2397.0	2373.1	2352.9	2331.8
35°	2287.9	2242.0	2173.4	2085.1	2020.0	1954.4	1947.9
37.5°	2057.7	1910.9	1796.7	1669.2	1595.7	1550.2	1518.9
40°	1841.0	1674.2	1535.9	1428.4	1353.5	1323.8	1294.8
42.5°	1605.8	1446.5	1324.0	1234.1	1177.8	1144.9	1121.8
45°	1304.7	1164.0	1068.2	1003.1	958.3	932.7	918.2
47.5°	1069.0	965.0	883.6	836.6	805.7	785.8	785.9
50°	942.6	843.3	789.2	752.0	725.2	709.6	712.5
52.5°	830.5	756.3	710.2	679.0	659.3	649.6	649.3
55°	694.5	641.0	610.8	588.1	574.7	563.7	566.0
57.5°	594.0	549.0	528.7	509.9	500.6	496.2	489.7
60°	531.8	496.9	479.4	464.3	455.0	451.5	445.1
62.5°	476.4	449.0	432.0	419.7	411.3	410.2	405.2
65°	400.4	379.4	364.4	358.5	349.8	347.5	347.5
67.5°	330.1	315.1	303.3	298.0	294.2	294.7	292.0
70°	285.9	273.7	266.1	260.4	257.4	258.0	255.7
72.5°	250.1	236.5	229.9	226.4	222.6	224.1	223.2
75°	189.4	182.4	179.0	175.5	173.1	172.0	170.8
77.5°	139.1	132.9	130.3	128.3	128.6	125.9	128.1
80°	107.5	102.3	100.6	97.6	97.0	97.0	96.4
82.5°	78.7	75.8	74.5	72.1	71.0	72.0	70.4
85°	40.6	38.3	37.8	37.8	36.6	35.5	38.3
87.5°	17.3	15.6	15.8	15.3	15.4	15.1	14.2
90°	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.0	272.6	272.5	272.6	272.8	272.9	273.0



TEST NUMBER: P333436-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)