

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333440-935

Luminaire Tested: **S125DIW-S1090D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333440-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6467.6 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	33	30
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9489	9489	9489
5°	9510	9419	9479
10°	9452	9353	9406
15°	9349	9240	9279
20°	9203	9082	9099
25°	9045	8896	8888
30°	8850	8694	8651
35°	8642	8476	8358
40°	8427	8241	8123
45°	8195	8026	7867
50°	7941	7766	7533
55°	7696	7473	7264
60°	7401	7177	6921
65°	7051	6820	6589
70°	6717	6409	6190
75°	6119	5916	5712
80°	5449	5359	5229
85°	4735	4824	4565



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.5	2.1
10°-20°	391.3	6.1
20°-30°	577.8	8.9
30°-40°	674.2	10.4
40°-50°	677.1	10.5
50°-60°	594.4	9.2
60°-70°	442.9	6.8
70°-80°	253.2	3.9
80°-90°	75.5	1.2
90°-100°	31.3	0.5
100°-110°	192.7	3.0
110°-120°	349.6	5.4
120°-130°	448.6	6.9
130°-140°	482.6	7.5
140°-150°	452.9	7.0
150°-160°	366.4	5.7
160°-170°	237.0	3.7
170°-180°	81.7	1.3
0°-30°	1107.6	17.1
0°-40°	1781.8	27.5
0°-60°	3053.3	47.2
0°-90°	3824.8	59.1
90°-120°	573.6	8.9
90°-150°	1957.7	30.3
90°-180°	2643.0	40.9
0°-180°	6467.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1469	1469	1469	1469	1469	
5°	1467	1464	1453	1463	1462	139
15°	1398	1394	1382	1388	1388	394
25°	1269	1263	1248	1250	1247	584
35°	1096	1091	1075	1069	1060	685
45°	897	892	879	865	861	691
55°	684	679	664	653	645	610
65°	461	458	446	436	431	458
75°	245	243	237	234	229	261
85°	64	65	65	64	62	71
90°	1	6	10	13	15	5
95°	36	33	10	13	13	46
105°	188	190	190	190	190	199
115°	352	355	356	353	350	349
125°	501	505	505	503	501	447
135°	625	628	627	626	622	481
145°	724	725	725	726	722	453
155°	798	794	795	796	792	367
165°	842	838	838	842	837	238
175°	861	857	858	862	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1472.9	1472.3	1471.6	1471.0	1470.4	1469.0	1467.0	1464.9	1462.8	1460.8	1462.8
5°	1466.9	1466.4	1465.9	1465.3	1464.8	1463.3	1460.7	1458.1	1455.5	1452.9	1455.3
7.5°	1453.4	1452.9	1452.3	1451.8	1451.3	1449.6	1446.7	1443.9	1441.1	1438.2	1440.5
10°	1441.3	1440.8	1440.3	1439.8	1439.2	1437.5	1434.7	1431.8	1429.0	1426.2	1428.2
12.5°	1426.4	1425.5	1424.5	1423.6	1422.7	1420.9	1418.2	1415.7	1413.0	1410.3	1412.0
15°	1398.3	1397.5	1396.7	1395.9	1395.2	1393.4	1390.5	1387.7	1384.8	1382.0	1383.3
17.5°	1366.0	1364.9	1363.7	1362.5	1361.4	1359.3	1356.4	1353.5	1350.6	1347.6	1349.2
20°	1339.0	1338.5	1338.0	1337.5	1337.0	1335.0	1331.6	1328.3	1324.9	1321.5	1323.4
22.5°	1312.0	1311.1	1310.2	1309.2	1308.3	1306.2	1303.1	1299.9	1296.8	1293.7	1294.9
25°	1269.3	1268.0	1266.7	1265.4	1264.1	1261.8	1258.4	1255.1	1251.7	1248.4	1248.9
27.5°	1219.3	1218.5	1217.7	1216.9	1216.2	1214.1	1210.6	1207.1	1203.7	1200.2	1200.3
30°	1186.7	1185.9	1185.2	1184.4	1183.6	1181.3	1177.4	1173.5	1169.7	1165.8	1165.3
32.5°	1151.4	1150.2	1149.0	1147.8	1146.7	1144.4	1140.8	1137.4	1133.9	1130.5	1129.5
35°	1096.1	1095.0	1094.0	1093.0	1091.9	1089.6	1086.0	1082.4	1078.7	1075.1	1073.8
37.5°	1038.6	1037.3	1036.0	1034.7	1033.5	1031.1	1027.7	1024.3	1020.9	1017.5	1015.5
40°	999.6	998.3	997.0	995.7	994.5	992.0	988.3	984.7	981.1	977.5	975.2
42.5°	957.8	956.7	955.6	954.5	953.4	951.1	947.4	943.8	940.2	936.6	934.4
45°	897.3	896.3	895.3	894.2	893.2	891.1	888.0	884.9	881.8	878.7	875.6
47.5°	832.2	832.2	832.3	832.4	832.4	830.6	826.9	823.1	819.4	815.7	812.5
50°	790.4	789.6	788.8	788.1	787.3	785.3	782.2	779.1	776.0	772.9	769.6
52.5°	747.6	747.0	746.5	745.9	745.4	743.4	740.1	736.8	733.5	730.1	727.2
55°	683.5	682.7	681.9	681.1	680.4	678.1	674.5	670.9	667.3	663.7	661.3
57.5°	615.8	615.4	615.0	614.6	614.2	612.4	609.3	606.3	603.3	600.2	597.2
60°	573.0	572.0	570.9	569.9	568.9	567.0	564.1	561.3	558.4	555.6	553.0
62.5°	528.4	527.5	526.8	525.9	525.1	523.5	521.0	518.6	516.2	513.8	510.9
65°	461.4	460.9	460.4	459.9	459.3	457.7	454.9	452.0	449.2	446.3	444.0
67.5°	396.6	395.5	394.4	393.3	392.3	390.6	388.5	386.4	384.3	382.2	380.2
70°	355.7	354.4	353.1	351.8	350.5	348.7	346.4	344.1	341.7	339.4	337.9
72.5°	311.1	310.1	309.3	308.4	307.5	306.3	304.9	303.3	301.9	300.3	298.6
75°	245.2	244.7	244.2	243.7	243.1	242.3	241.0	239.7	238.4	237.1	236.3
77.5°	184.6	184.3	184.2	184.0	183.7	183.3	182.5	181.8	181.2	180.4	179.9
80°	146.5	146.5	146.5	146.5	146.5	146.2	145.7	145.2	144.6	144.1	143.9
82.5°	113.0	112.5	112.2	111.8	111.3	111.1	111.0	110.9	110.7	110.6	110.2
85°	63.9	64.1	64.4	64.7	64.9	65.1	65.1	65.1	65.1	65.1	64.8
87.5°	25.2	25.5	25.7	25.9	26.2	26.3	26.3	26.3	26.3	26.3	26.3
90°	0.6	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9
92.5°	9.8	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9
95°	36.3	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9
97.5°	75.9	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4
100°	106.5	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9
102.5°	137.7	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7
105°	187.5	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6
110°	273.0	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.7	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4
115°	352.1	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4
117.5°	401.3	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9
120°	431.9	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9
122.5°	458.9	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0
125°	500.8	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7
127.5°	540.7	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2
130°	565.2	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6
132.5°	589.7	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9
135°	624.6	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8
137.5°	656.6	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8
140°	677.5	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5
142.5°	696.4	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1
145°	724.1	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5
147.5°	748.4	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0
150°	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0
152.5°	778.4	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2
155°	797.5	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3
157.5°	812.1	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5
160°	822.3	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8
162.5°	830.5	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1
165°	841.5	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1
167.5°	849.6	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3
170°	854.3	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5
172.5°	857.3	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0
175°	860.7	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6
177.5°	862.1	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1464.9	1467.0	1469.0	1470.0	1469.8	1469.6	1469.4	1469.2
5°	1457.6	1459.9	1462.2	1463.3	1463.0	1462.8	1462.5	1462.2
7.5°	1442.8	1445.1	1447.3	1448.4	1448.1	1447.9	1447.6	1447.3
10°	1430.3	1432.4	1434.4	1435.4	1435.1	1434.9	1434.6	1434.3
12.5°	1413.7	1415.3	1416.9	1417.8	1417.7	1417.6	1417.6	1417.6
15°	1384.6	1385.9	1387.2	1387.8	1387.8	1387.8	1387.8	1387.8
17.5°	1350.8	1352.4	1354.0	1354.2	1352.9	1351.6	1350.3	1349.0
20°	1325.2	1327.0	1328.8	1329.0	1327.7	1326.5	1325.2	1323.9
22.5°	1296.1	1297.3	1298.4	1298.6	1297.7	1296.8	1296.0	1295.0
25°	1249.4	1249.9	1250.4	1250.3	1249.5	1248.7	1247.9	1247.2
27.5°	1200.4	1200.5	1200.7	1200.3	1199.5	1198.8	1198.0	1197.2
30°	1164.8	1164.2	1163.7	1163.1	1162.4	1161.6	1160.8	1160.0
32.5°	1128.6	1127.7	1126.8	1125.6	1124.2	1122.8	1121.4	1120.0
35°	1072.5	1071.3	1070.0	1068.3	1066.3	1064.2	1062.1	1060.1
37.5°	1013.7	1011.8	1009.9	1008.3	1007.1	1005.9	1004.7	1003.6
40°	972.8	970.5	968.2	966.6	965.9	965.1	964.3	963.5
42.5°	932.4	930.2	928.2	926.4	925.3	924.1	922.9	921.7
45°	872.5	869.4	866.3	864.4	863.6	862.8	862.0	861.3
47.5°	809.4	806.2	803.1	800.6	798.8	797.0	795.2	793.4
50°	766.2	762.8	759.5	756.9	755.1	753.3	751.5	749.7
52.5°	724.3	721.3	718.4	715.9	713.9	711.9	709.9	707.8
55°	659.0	656.7	654.4	652.3	650.5	648.7	646.9	645.1
57.5°	594.3	591.2	588.2	586.3	585.3	584.3	583.3	582.3
60°	550.4	547.9	545.3	543.0	541.2	539.4	537.6	535.8
62.5°	508.2	505.4	502.6	500.5	499.1	497.7	496.3	494.9
65°	441.7	439.4	437.0	435.3	434.3	433.3	432.2	431.2
67.5°	378.2	376.3	374.3	373.0	372.4	371.8	371.2	370.6
70°	336.3	334.8	333.2	331.9	330.9	329.8	328.8	327.8
72.5°	296.9	295.1	293.3	292.0	290.9	289.9	288.9	287.8
75°	235.6	234.8	234.0	233.1	232.0	231.0	230.0	228.9
77.5°	179.4	179.0	178.6	178.0	177.2	176.5	175.7	175.0
80°	143.6	143.4	143.1	142.7	142.2	141.6	141.1	140.6
82.5°	109.7	109.3	108.8	108.5	108.4	108.3	108.2	108.1
85°	64.6	64.3	64.1	63.6	63.1	62.6	62.1	61.6
87.5°	26.5	26.6	26.8	26.7	26.3	26.0	25.7	25.4
90°	11.6	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	11.6	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	11.6	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	23.4	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	68.8	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	133.6	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.5	273.0	272.6	272.5	272.6	272.8	272.9	273.0



TEST NUMBER: P333440-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	305.9	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.8	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	402.1	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.7	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.7	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	504.1	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.9	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	568.3	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.9	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.5	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	678.7	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.2	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.7	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.2	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.2	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.5	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	795.7	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	810.9	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.3	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	828.9	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.0	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	848.3	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	852.6	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	856.0	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	859.7	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.2	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)