

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333667-840

Luminaire Tested: **S125RDIW-S610D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333667-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5090.1 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.9
10°-20°	267.0	5.2
20°-30°	387.1	7.6
30°-40°	441.2	8.7
40°-50°	430.0	8.4
50°-60°	362.0	7.1
60°-70°	253.8	5.0
70°-80°	130.4	2.6
80°-90°	35.0	0.7
90°-100°	64.5	1.3
100°-110°	190.5	3.7
110°-120°	322.7	6.3
120°-130°	424.7	8.3
130°-140°	475.9	9.3
140°-150°	466.4	9.2
150°-160°	391.7	7.7
160°-170°	260.4	5.1
170°-180°	91.1	1.8
0°-30°	749.6	14.7
0°-40°	1190.8	23.4
0°-60°	1982.8	39.0
0°-90°	2402.1	47.2
90°-120°	577.8	11.4
90°-150°	1944.8	38.2
90°-180°	2688.0	52.8
0°-180°	5090.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	7	12	16	18	5
95°	49	51	58	63	64	52
105°	171	175	179	184	186	183
115°	323	326	328	327	326	319
125°	472	476	477	475	474	422
135°	613	618	618	618	616	472
145°	743	746	748	748	746	464
155°	850	850	851	853	850	391
165°	924	923	924	926	922	261
175°	961	958	958	962	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.5	12.9	12.2	11.5	11.2	11.3	11.4	11.5	11.6	11.8
90°	0.7	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8
92.5°	18.2	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9
95°	48.8	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9
97.5°	81.0	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0
100°	104.9	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2
102.5°	130.8	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4
105°	171.0	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2
107.5°	215.3	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0
110°	245.9	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.1	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2
115°	323.2	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4
117.5°	369.3	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1
120°	398.1	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5
122.5°	429.3	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4
125°	471.5	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5
127.5°	516.5	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8
130°	543.5	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6
132.5°	570.5	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2
135°	613.2	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4
137.5°	653.4	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6
140°	679.2	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5
142.5°	705.0	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1
145°	743.0	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2
147.5°	778.0	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8
150°	801.4	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7
152.5°	820.6	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2
155°	850.1	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5
157.5°	876.6	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3
160°	892.1	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3
162.5°	905.9	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2
165°	924.3	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2
167.5°	940.0	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0
170°	948.4	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3
172.5°	954.3	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3
175°	961.1	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1
177.5°	964.5	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	11.9	12.1	12.3	12.3	12.3	12.2	12.2	12.2
90°	13.6	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	31.0	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	60.1	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	94.1	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	117.6	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	142.0	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	181.2	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	223.5	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	252.9	253.4	253.9	254.1	253.9	253.7	253.6	253.4



TEST NUMBER: P333667-840

CATALOG NUMBER: S125RDIW-S610D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.4	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.3	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.2	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.3	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	476.2	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.7	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.5	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	576.0	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	659.8	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	685.9	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.3	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.2	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	823.6	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.2	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.0	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	891.9	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.1	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	924.9	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	939.0	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	947.4	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	953.3	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	960.1	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.1	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)