

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333691-840

Luminaire Tested: **S125RDIW-S850D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333691-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1050U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6952.5 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.9
10°-20°	364.9	5.2
20°-30°	529.2	7.6
30°-40°	603.1	8.7
40°-50°	587.8	8.5
50°-60°	494.8	7.1
60°-70°	346.9	5.0
70°-80°	178.3	2.6
80°-90°	47.9	0.7
90°-100°	88.1	1.3
100°-110°	260.1	3.7
110°-120°	440.5	6.3
120°-130°	579.7	8.3
130°-140°	649.6	9.3
140°-150°	636.6	9.2
150°-160°	534.7	7.7
160°-170°	355.4	5.1
170°-180°	124.4	1.8
0°-30°	1024.6	14.7
0°-40°	1627.7	23.4
0°-60°	2710.4	39.0
0°-90°	3283.4	47.2
90°-120°	788.6	11.3
90°-150°	2654.6	38.2
90°-180°	3669.0	52.8
0°-180°	6952.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	9	16	21	24	6
95°	67	69	79	86	88	71
105°	233	238	245	251	254	249
115°	441	445	447	446	445	436
125°	644	649	651	649	648	576
135°	837	843	844	844	840	645
145°	1014	1018	1021	1021	1018	634
155°	1160	1160	1161	1165	1160	534
165°	1262	1260	1261	1264	1259	356
175°	1312	1308	1308	1313	1307	125
180°	1315	1315	1315	1315	1315	



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.6	17.6	16.7	15.8	15.3	15.5	15.6	15.8	15.9	16.1
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.2	14.7	16.4	17.5
92.5°	24.7	26.1	27.3	28.6	29.9	31.5	33.4	35.3	37.4	39.3	40.8
95°	66.6	67.0	67.5	67.9	68.4	69.7	72.0	74.2	76.5	78.8	80.4
97.5°	110.5	110.7	110.9	111.1	111.3	112.9	116.0	119.2	122.3	125.4	126.9
100°	143.3	143.3	143.3	143.3	143.3	144.7	147.6	150.7	153.6	156.5	158.6
102.5°	178.4	179.4	180.3	181.2	182.1	183.3	184.8	186.3	187.8	189.3	191.6
105°	233.3	234.4	235.6	236.7	237.8	239.1	240.4	241.9	243.2	244.6	245.9
107.5°	293.9	295.0	296.2	297.3	298.4	299.5	300.5	301.6	302.7	303.7	304.4
110°	335.6	336.8	337.9	339.0	340.2	341.1	341.7	342.4	343.2	343.9	344.5



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.2	378.8	379.4	380.0	380.5	381.3	382.1	383.0	383.8	384.8	385.1
115°	441.0	441.9	442.8	443.7	444.6	445.4	445.8	446.3	446.7	447.2	447.0
117.5°	504.0	504.4	504.8	505.2	505.7	506.1	506.5	507.0	507.4	507.8	508.0
120°	543.3	544.5	545.6	546.7	547.9	548.6	548.8	549.1	549.3	549.5	549.5
122.5°	585.9	586.3	586.7	587.1	587.5	588.0	588.7	589.3	589.9	590.5	590.3
125°	643.6	645.0	646.3	647.7	649.0	649.8	650.2	650.4	650.6	650.8	650.4
127.5°	705.0	705.8	706.6	707.3	708.1	708.6	708.9	709.2	709.4	709.7	709.5
130°	741.8	743.0	744.2	745.3	746.4	747.2	747.7	748.1	748.6	749.0	748.8
132.5°	778.7	780.5	782.4	784.3	786.2	787.1	787.0	786.9	786.8	786.7	786.5
135°	837.0	838.4	839.7	841.1	842.5	843.2	843.5	843.7	843.9	844.1	844.1
137.5°	891.9	893.2	894.5	895.9	897.2	898.1	898.6	899.1	899.6	900.1	900.3
140°	927.1	928.2	929.4	930.5	931.6	932.5	933.2	933.9	934.5	935.2	935.7
142.5°	962.3	963.2	964.2	965.1	966.1	967.0	967.9	968.8	969.6	970.5	970.7
145°	1014.0	1014.9	1015.8	1016.7	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2
147.5°	1062.0	1062.5	1063.0	1063.4	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2
150°	1093.9	1093.7	1093.4	1093.2	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9
152.5°	1120.0	1120.3	1120.6	1121.1	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7
155°	1160.3	1160.3	1160.3	1160.3	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4
157.5°	1196.4	1195.9	1195.4	1194.9	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1
160°	1217.7	1217.0	1216.3	1215.7	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6
162.5°	1236.5	1236.0	1235.5	1235.0	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6
165°	1261.7	1261.2	1260.7	1260.3	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5
167.5°	1282.9	1282.0	1281.1	1280.2	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2
170°	1294.4	1293.5	1292.6	1291.7	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7
172.5°	1302.6	1301.7	1300.8	1299.9	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9
175°	1311.8	1310.9	1310.0	1309.1	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1
177.5°	1316.6	1315.8	1315.0	1314.3	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	16.4	16.6	16.8	16.9	16.8	16.8	16.7	16.7
90°	18.7	19.8	20.9	21.8	22.5	23.2	23.8	24.5
92.5°	42.3	43.8	45.3	46.3	46.8	47.3	47.8	48.3
95°	82.0	83.5	85.1	86.1	86.6	87.1	87.6	88.0
97.5°	128.5	130.0	131.5	132.3	132.6	132.9	133.2	133.4
100°	160.7	162.7	164.7	166.0	166.4	166.9	167.3	167.8
102.5°	193.8	196.0	198.2	199.7	200.3	201.0	201.6	202.2
105°	247.3	248.6	250.0	251.1	251.8	252.4	253.1	253.8
107.5°	305.1	305.8	306.4	306.8	306.7	306.7	306.6	306.6
110°	345.2	345.9	346.6	346.8	346.6	346.3	346.1	345.9



TEST NUMBER: P333691-840

CATALOG NUMBER: S125RDIW-S850D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.7	386.0	386.0	385.6	385.2	384.8	384.4
115°	446.7	446.5	446.3	446.1	445.8	445.6	445.4	445.1
117.5°	508.1	508.3	508.5	508.1	507.2	506.2	505.3	504.4
120°	549.5	549.5	549.5	549.1	548.2	547.2	546.3	545.4
122.5°	590.1	589.9	589.7	589.3	588.5	587.7	587.0	586.3
125°	649.8	649.4	648.9	648.6	648.4	648.1	647.9	647.7
127.5°	709.2	709.0	708.8	708.5	708.0	707.6	707.1	706.7
130°	748.6	748.3	748.1	747.8	747.3	746.9	746.4	746.0
132.5°	786.2	786.0	785.8	785.4	784.7	784.1	783.5	782.7
135°	844.1	844.1	844.1	843.7	842.8	841.9	841.0	840.1
137.5°	900.6	900.9	901.1	900.7	899.6	898.5	897.3	896.2
140°	936.1	936.6	937.1	936.8	935.6	934.4	933.3	932.2
142.5°	971.0	971.3	971.6	971.1	970.0	968.9	967.8	966.5
145°	1021.2	1021.2	1021.2	1020.9	1020.2	1019.5	1018.9	1018.1
147.5°	1067.7	1068.2	1068.8	1068.3	1066.8	1065.2	1063.7	1062.2
150°	1096.9	1096.9	1096.9	1096.7	1096.2	1095.8	1095.3	1094.9
152.5°	1124.2	1124.8	1125.3	1125.2	1124.4	1123.6	1122.7	1121.9
155°	1163.3	1164.2	1165.1	1164.9	1163.8	1162.7	1161.5	1160.3
157.5°	1197.0	1197.9	1198.8	1198.5	1197.0	1195.5	1194.0	1192.5
160°	1217.5	1218.4	1219.3	1219.1	1218.0	1216.9	1215.8	1214.6
162.5°	1236.7	1237.7	1238.8	1238.7	1237.4	1236.1	1234.8	1233.4
165°	1262.4	1263.3	1264.3	1264.0	1262.7	1261.3	1260.0	1258.6
167.5°	1281.6	1282.9	1284.3	1284.3	1282.9	1281.5	1280.1	1278.7
170°	1293.0	1294.4	1295.8	1295.7	1294.0	1292.5	1290.9	1289.3
172.5°	1301.2	1302.6	1303.9	1303.9	1302.5	1301.1	1299.7	1298.3
175°	1310.4	1311.8	1313.2	1313.0	1311.5	1309.9	1308.3	1306.7
177.5°	1314.6	1315.8	1316.8	1316.7	1315.5	1314.1	1312.9	1311.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8

(END OF REPORT)