

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333488-935

Luminaire Tested: **S125DIW-S1270D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333488-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9788.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	1.6
10°-20°	451.9	4.6
20°-30°	667.3	6.8
30°-40°	778.6	8.0
40°-50°	782.0	8.0
50°-60°	686.5	7.0
60°-70°	511.5	5.2
70°-80°	292.5	3.0
80°-90°	88.7	0.9
90°-100°	63.5	0.6
100°-110°	391.6	4.0
110°-120°	710.2	7.3
120°-130°	911.5	9.3
130°-140°	980.4	10.0
140°-150°	920.2	9.4
150°-160°	744.4	7.6
160°-170°	481.4	4.9
170°-180°	166.0	1.7
0°-30°	1279.2	13.1
0°-40°	2057.8	21.0
0°-60°	3526.3	36.0
0°-90°	4419.0	45.1
90°-120°	1165.3	11.9
90°-150°	3977.4	40.6
90°-180°	5369.0	54.9
0°-180°	9788.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	83
90°	1	12	21	27	31	7
95°	74	67	21	27	27	94
105°	381	386	386	386	385	404
115°	716	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1269	1276	1274	1271	1264	978
145°	1471	1474	1474	1474	1467	920
155°	1620	1613	1615	1618	1608	746
165°	1710	1702	1703	1710	1700	483
175°	1748	1741	1742	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.3	29.7	30.1	30.7	31.1	31.4	31.6	31.8	31.9	32.0	32.4
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2
92.5°	20.0	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2
95°	73.9	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2
97.5°	154.2	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6
100°	216.5	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6
102.5°	279.7	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7
105°	381.1	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0
110°	554.7	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	619.1	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6
115°	715.5	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0
117.5°	815.3	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4
120°	877.4	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5
122.5°	932.5	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6
125°	1017.4	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4
127.5°	1098.5	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6
130°	1148.3	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3
132.5°	1198.1	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6
135°	1268.9	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5
137.5°	1333.9	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5
140°	1376.5	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4
142.5°	1414.8	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3
145°	1471.1	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9
147.5°	1520.4	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7
150°	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0
152.5°	1581.5	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0
155°	1620.1	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8
157.5°	1649.9	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5
160°	1670.7	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3
162.5°	1687.3	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4
165°	1709.6	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8
167.5°	1726.1	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5
170°	1735.5	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0
172.5°	1741.7	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1
175°	1748.4	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3
177.5°	1751.5	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	32.6	33.0	33.2	33.2	32.9	32.6	32.3	32.0
90°	23.6	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	23.6	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	23.6	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	139.7	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	271.5	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	555.6	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333488-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	621.5	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	720.9	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	816.9	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.9	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	938.0	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1024.2	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1103.0	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1154.4	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.5	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.9	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.6	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1378.9	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.4	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.3	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.1	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1552.6	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1579.6	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1616.7	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1647.4	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1666.5	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1684.0	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1706.5	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1723.5	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1732.3	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1739.1	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1746.5	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1749.6	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)