

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333694-840

Luminaire Tested: **S125RDIW-S850D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333694-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1340U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8700.7 lumens  
Efficiency: N/A  
Efficacy: 141.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77		60	60	60		45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63		53	52	50		40	39	38	32
2	87	80	74	69	79	72	67	63	59	56	52		47	44	42		35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44		41	38	36		31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38		37	34	31		28	26	24	20
5	67	55	47	42	60	51	44	39	42	36	33		33	30	27		25	23	21	17
6	61	50	42	36	55	45	38	33	37	32	28		30	26	23		23	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25		27	23	21		21	18	16	14
8	52	41	33	28	48	37	31	26	31	26	22		25	21	18		19	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20		23	19	17		18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18		21	18	15		17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.6	1.5
10°-20°	364.9	4.2
20°-30°	529.2	6.1
30°-40°	603.1	6.9
40°-50°	587.8	6.8
50°-60°	494.8	5.7
60°-70°	346.9	4.0
70°-80°	178.3	2.0
80°-90°	48.7	0.6
90°-100°	64.1	0.7
100°-110°	395.0	4.5
110°-120°	716.5	8.2
120°-130°	919.5	10.6
130°-140°	989.0	11.4
140°-150°	928.3	10.7
150°-160°	750.9	8.6
160°-170°	485.7	5.6
170°-180°	167.5	1.9
0°-30°	1024.6	11.8
0°-40°	1627.7	18.7
0°-60°	2710.4	31.2
0°-90°	3284.2	37.7
90°-120°	1175.6	13.5
90°-150°	4012.4	46.1
90°-180°	5416.0	62.2
0°-180°	8700.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	12	21	27	31	6
95°	74	68	21	27	28	95
105°	384	389	390	390	388	408
115°	722	728	730	724	716	715
125°	1026	1035	1036	1030	1026	916
135°	1280	1287	1285	1282	1275	986
145°	1484	1486	1487	1487	1480	928
155°	1634	1627	1629	1632	1623	753
165°	1725	1717	1718	1725	1716	487
175°	1764	1757	1757	1767	1756	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.6	18.7	17.9	17.1	16.2	15.9	16.2	16.4	16.6	16.8	17.1
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4
92.5°	20.1	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4
95°	74.5	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4
97.5°	155.6	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1
100°	218.3	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2
102.5°	282.2	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1
105°	384.5	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2
110°	559.7	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4



TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	624.5	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0
115°	721.8	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4
117.5°	822.4	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7
120°	885.1	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3
122.5°	940.6	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8
125°	1026.4	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4
127.5°	1108.2	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4
130°	1158.4	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5
132.5°	1208.7	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3
135°	1280.1	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8
137.5°	1345.7	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3
140°	1388.6	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5
142.5°	1427.2	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8
145°	1484.0	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9
147.5°	1533.7	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1
150°	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7
152.5°	1595.4	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9
155°	1634.4	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0
157.5°	1664.5	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9
160°	1685.4	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0
162.5°	1702.1	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2
165°	1724.6	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8
167.5°	1741.3	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7
170°	1750.8	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2
172.5°	1757.1	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3
175°	1763.8	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6
177.5°	1767.0	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	17.4	17.7	18.0	18.1	18.1	18.1	18.1	18.0
90°	23.8	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	23.8	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	23.8	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	48.0	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	140.9	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	273.9	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.3	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	560.5	559.7	558.8	558.5	558.8	559.1	559.4	559.7





TEST NUMBER: P333694-840

CATALOG NUMBER: S125RDIW-S850D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	626.9	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	727.3	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	824.2	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.7	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	946.2	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1033.2	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.8	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1164.6	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1213.0	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1284.1	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.4	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.1	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1430.9	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.2	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.5	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.3	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1593.5	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1630.9	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1661.9	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1681.2	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1698.8	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1721.5	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1738.8	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1747.6	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1754.4	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1761.9	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1765.0	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)