

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333489-935

Luminaire Tested: **S125DIW-S1270D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333489-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9075.1 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	1.8
10°-20°	451.9	5.0
20°-30°	667.3	7.4
30°-40°	778.6	8.6
40°-50°	782.0	8.6
50°-60°	686.5	7.6
60°-70°	511.5	5.6
70°-80°	292.5	3.2
80°-90°	88.7	1.0
90°-100°	111.8	1.2
100°-110°	330.0	3.6
110°-120°	559.0	6.2
120°-130°	735.7	8.1
130°-140°	824.3	9.1
140°-150°	807.9	8.9
150°-160°	678.6	7.5
160°-170°	451.1	5.0
170°-180°	157.9	1.7
0°-30°	1279.2	14.1
0°-40°	2057.8	22.7
0°-60°	3526.3	38.9
0°-90°	4419.0	48.7
90°-120°	1000.8	11.0
90°-150°	3368.6	37.1
90°-180°	4656.0	51.3
0°-180°	9075.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	83
90°	1	12	21	27	31	9
95°	84	88	100	109	112	90
105°	296	303	310	318	322	316
115°	560	565	568	566	565	553
125°	817	824	826	823	822	731
135°	1062	1070	1071	1071	1066	818
145°	1287	1292	1296	1296	1292	804
155°	1473	1473	1474	1478	1473	678
165°	1601	1599	1600	1604	1597	451
175°	1665	1660	1660	1666	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.3	29.7	30.2	30.7	31.1	31.4	31.6	31.8	31.9	32.1	32.4
90°	1.3	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2
92.5°	31.4	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7
95°	84.4	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0
97.5°	140.3	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1
100°	181.8	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3
102.5°	226.4	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1
105°	296.1	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1
107.5°	372.9	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2
110°	425.9	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.9	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6
115°	559.6	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1
117.5°	639.6	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5
120°	689.5	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3
122.5°	743.6	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0
125°	816.7	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3
127.5°	894.7	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3
130°	941.4	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2
132.5°	988.2	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0
135°	1062.2	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3
137.5°	1131.8	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5
140°	1176.5	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4
142.5°	1221.2	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8
145°	1286.9	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9
147.5°	1347.6	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3
150°	1388.1	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1
152.5°	1421.3	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0
155°	1472.6	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0
157.5°	1518.2	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9
160°	1545.2	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8
162.5°	1569.2	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0
165°	1601.1	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9
167.5°	1628.1	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6
170°	1642.6	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2
172.5°	1653.0	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6
175°	1664.7	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2
177.5°	1670.7	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	32.6	33.0	33.2	33.2	32.9	32.6	32.3	32.0
90°	23.7	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	53.6	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	104.0	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	163.0	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	203.9	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	245.9	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	313.8	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	387.1	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.1	438.9	439.8	440.1	439.8	439.5	439.2	438.9



TEST NUMBER: P333489-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.0	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.9	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	644.8	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.8	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.8	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	900.1	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.9	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.7	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1142.9	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.0	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.2	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.0	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1426.7	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1476.1	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1519.0	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1545.0	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1569.3	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1602.1	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1626.3	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1640.9	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1651.3	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1663.0	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1668.3	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)