

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333467-935

Luminaire Tested: **S125DIW-S1270D770U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333467-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D770U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6755.7 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	94	90	96	92	88	85	81	79	77	72	70	68	63	62	61	56
2	93	85	79	74	87	81	75	71	72	68	64	64	60	57	56	54	51	48
3	85	75	68	62	80	71	65	59	64	58	54	56	52	49	50	47	44	41
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	45	41	38	35
5	72	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	45	40	62	51	44	38	46	40	35	41	36	32	37	33	29	27
7	61	49	40	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	23	21
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.2	2.3
10°-20°	453.2	6.7
20°-30°	736.0	10.9
30°-40°	897.7	13.3
40°-50°	816.7	12.1
50°-60°	650.5	9.6
60°-70°	453.1	6.7
70°-80°	241.6	3.6
80°-90°	62.8	0.9
90°-100°	55.0	0.8
100°-110°	162.4	2.4
110°-120°	275.1	4.1
120°-130°	362.1	5.4
130°-140°	405.7	6.0
140°-150°	397.7	5.9
150°-160°	334.0	4.9
160°-170°	222.0	3.3
170°-180°	77.7	1.2
0°-30°	1341.4	19.9
0°-40°	2239.2	33.1
0°-60°	3706.4	54.9
0°-90°	4463.9	66.1
90°-120°	492.6	7.3
90°-150°	1658.1	24.5
90°-180°	2292.0	33.9
0°-180°	6755.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	51
90°	15	1	15	1	15	10
95°	55	42	55	42	55	56
105°	158	146	158	146	158	168
115°	278	276	278	276	278	275
125°	405	402	405	402	405	361
135°	525	523	525	523	525	405
145°	636	633	636	633	636	397
155°	725	725	725	725	725	334
165°	786	788	786	788	786	222
175°	816	819	816	819	816	78
180°	821	821	821	821	821	



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	15.9	17.0	17.4	17.3	17.7	17.7	19.6	19.5	21.0	22.5	24.4
90°	15.3	14.9	14.5	14.0	13.6	13.1	12.4	11.6	10.9	10.2	9.2
92.5°	30.1	29.9	29.5	29.3	28.9	28.3	27.4	26.4	25.5	24.5	23.3
95°	54.9	54.7	54.4	54.2	53.8	53.2	52.2	51.2	50.2	49.2	47.8
97.5°	83.3	83.2	83.0	82.8	82.7	82.1	81.2	80.2	79.3	78.4	76.4
100°	104.8	104.5	104.3	104.0	103.7	102.9	101.6	100.3	99.1	97.8	95.9
102.5°	126.3	125.9	125.5	125.1	124.7	123.8	122.4	121.1	119.7	118.2	117.3
105°	158.5	158.1	157.6	157.2	156.8	156.2	155.3	154.5	153.6	152.7	151.9
107.5°	191.5	191.5	191.6	191.6	191.6	191.4	191.0	190.5	190.1	189.7	189.1
110°	216.0	216.2	216.3	216.5	216.6	216.5	216.0	215.6	215.2	214.7	214.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.0	240.3	240.6	240.8	241.1	241.1	240.9	240.7	240.6	240.3	239.8
115°	278.0	278.2	278.4	278.4	278.6	278.7	278.9	279.1	279.1	279.3	279.1
117.5°	315.1	315.6	316.2	316.8	317.4	317.6	317.5	317.4	317.3	317.2	316.9
120°	340.7	341.2	341.8	342.4	342.9	343.2	343.2	343.2	343.2	343.2	343.1
122.5°	366.3	366.7	367.1	367.6	368.1	368.3	368.4	368.6	368.7	368.8	368.4
125°	404.6	404.8	404.8	405.0	405.2	405.4	405.6	406.0	406.2	406.5	406.4
127.5°	441.4	441.7	442.0	442.3	442.6	442.7	442.9	443.1	443.2	443.3	443.2
130°	466.0	466.2	466.5	466.8	467.1	467.3	467.4	467.6	467.7	467.9	467.6
132.5°	489.0	489.4	489.7	490.2	490.5	490.9	490.9	491.1	491.3	491.4	491.5
135°	524.8	525.3	525.9	526.4	527.0	527.3	527.3	527.3	527.3	527.3	527.2
137.5°	559.7	560.5	561.2	561.9	562.6	562.9	562.7	562.6	562.4	562.2	561.9
140°	582.3	583.0	583.7	584.4	585.1	585.3	585.0	584.8	584.4	584.2	583.8
142.5°	603.7	604.4	605.2	605.9	606.6	606.8	606.7	606.5	606.3	606.1	605.6
145°	635.9	636.4	636.8	637.2	637.7	637.9	637.9	637.9	637.9	637.9	637.5
147.5°	663.5	664.4	665.4	666.3	667.3	667.6	667.3	666.9	666.6	666.2	665.9
150°	683.9	684.2	684.5	684.8	685.0	685.2	685.2	685.2	685.2	685.2	684.6
152.5°	700.8	701.3	701.8	702.3	702.8	702.9	702.6	702.2	701.9	701.5	701.3
155°	724.8	725.5	726.3	726.9	727.6	727.7	727.1	726.6	726.0	725.5	725.3
157.5°	744.9	745.8	746.7	747.7	748.6	748.8	748.2	747.7	747.1	746.6	746.4
160°	758.7	759.4	760.1	760.8	761.6	761.6	761.0	760.4	759.9	759.3	759.1
162.5°	770.4	771.3	772.1	772.9	773.8	773.8	773.1	772.5	771.8	771.1	771.0
165°	786.2	787.0	787.9	788.8	789.5	789.7	789.2	788.6	788.0	787.5	787.3
167.5°	798.7	799.6	800.5	801.3	802.2	802.2	801.4	800.6	799.7	798.8	798.8
170°	805.4	806.3	807.4	808.3	809.3	809.4	808.6	807.7	806.8	806.0	806.0
172.5°	811.0	811.8	812.7	813.6	814.5	814.5	813.6	812.8	811.9	811.1	811.1
175°	816.2	817.2	818.2	819.2	820.2	820.3	819.4	818.6	817.7	816.8	816.8
177.5°	819.2	820.1	820.9	821.7	822.4	822.5	821.8	821.1	820.4	819.8	819.9
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	25.3	24.0	21.6	19.8	16.9	15.1	14.3	14.6	13.3	12.9	13.7
90°	8.3	7.2	6.3	5.2	4.0	2.9	1.8	0.6	1.8	2.9	4.0
92.5°	22.1	20.9	19.6	18.7	17.8	17.0	16.3	15.5	16.3	17.0	17.8
95°	46.4	44.9	43.6	42.7	42.4	42.1	41.8	41.6	41.8	42.1	42.4
97.5°	74.5	72.5	70.5	69.5	69.4	69.2	69.1	69.1	69.1	69.2	69.4
100°	94.1	92.2	90.4	89.5	89.5	89.5	89.5	89.5	89.5	89.5	89.5
102.5°	116.4	115.5	114.5	113.7	113.1	112.6	112.0	111.5	112.0	112.6	113.1
105°	151.0	150.2	149.4	148.6	147.8	147.1	146.5	145.8	146.5	147.1	147.8
107.5°	188.4	187.8	187.1	186.4	185.7	185.0	184.3	183.6	184.3	185.0	185.7
110°	213.9	213.4	213.0	212.5	211.8	211.0	210.3	209.7	210.3	211.0	211.8





TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	239.3	238.7	238.2	237.7	237.4	236.9	236.6	236.3	236.6	236.9	237.4
115°	278.7	278.4	278.2	277.8	277.2	276.6	276.0	275.5	276.0	276.6	277.2
117.5°	316.7	316.4	316.2	315.9	315.6	315.4	315.1	314.9	315.1	315.4	315.6
120°	342.9	342.8	342.7	342.2	341.6	340.8	340.1	339.4	340.1	340.8	341.6
122.5°	368.1	367.6	367.3	367.0	366.8	366.5	366.3	366.0	366.3	366.5	366.8
125°	406.2	406.0	406.0	405.4	404.6	403.7	402.9	402.0	402.9	403.7	404.6
127.5°	443.0	442.8	442.6	442.3	441.9	441.3	440.8	440.4	440.8	441.3	441.9
130°	467.3	467.0	466.7	466.2	465.5	464.9	464.1	463.4	464.1	464.9	465.5
132.5°	491.5	491.5	491.6	491.0	489.9	488.7	487.6	486.4	487.6	488.7	489.9
135°	527.0	526.8	526.8	526.2	525.4	524.5	523.7	522.8	523.7	524.5	525.4
137.5°	561.5	561.3	560.9	560.4	559.6	558.7	557.9	557.1	557.9	558.7	559.6
140°	583.3	582.9	582.5	581.9	581.2	580.5	579.8	579.1	579.8	580.5	581.2
142.5°	605.1	604.6	604.0	603.5	602.9	602.3	601.7	601.1	601.7	602.3	602.9
145°	637.1	636.6	636.2	635.7	635.1	634.6	634.0	633.4	634.0	634.6	635.1
147.5°	665.6	665.2	664.9	664.6	664.3	663.9	663.7	663.3	663.7	663.9	664.3
150°	684.1	683.5	682.9	682.7	682.9	682.9	683.1	683.3	683.1	682.9	682.9
152.5°	701.1	700.9	700.6	700.4	700.3	700.0	699.8	699.6	699.8	700.0	700.3
155°	725.1	725.0	724.9	724.8	724.8	724.8	724.8	724.8	724.8	724.8	724.8
157.5°	746.2	746.1	746.0	746.1	746.4	746.7	747.0	747.3	747.0	746.7	746.4
160°	759.1	758.9	758.7	758.9	759.3	759.7	760.2	760.6	760.2	759.7	759.3
162.5°	771.0	771.0	770.9	771.1	771.5	771.7	772.1	772.4	772.1	771.7	771.5
165°	787.1	787.0	786.9	787.0	787.2	787.6	787.8	788.1	787.8	787.6	787.2
167.5°	798.8	798.8	798.8	799.1	799.7	800.2	800.8	801.4	800.8	800.2	799.7
170°	806.0	806.0	806.0	806.2	806.8	807.4	808.0	808.6	808.0	807.4	806.8
172.5°	811.1	811.1	811.1	811.4	811.9	812.5	813.0	813.6	813.0	812.5	811.9
175°	816.8	816.8	816.8	817.1	817.7	818.3	818.8	819.4	818.8	818.3	817.7
177.5°	820.0	820.1	820.3	820.5	821.0	821.4	821.9	822.3	821.9	821.4	821.0
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.5	15.8	15.4	16.2	16.4	17.7	17.2	19.5	20.8	22.0	21.5
90°	5.2	6.3	7.2	8.3	9.2	10.2	10.9	11.6	12.4	13.1	13.6
92.5°	18.7	19.6	20.9	22.1	23.3	24.5	25.5	26.4	27.4	28.3	28.9
95°	42.7	43.6	44.9	46.4	47.8	49.2	50.2	51.2	52.2	53.2	53.8
97.5°	69.5	70.5	72.5	74.5	76.4	78.4	79.3	80.2	81.2	82.1	82.7
100°	89.5	90.4	92.2	94.1	95.9	97.8	99.1	100.3	101.6	102.9	103.7
102.5°	113.7	114.5	115.5	116.4	117.3	118.2	119.7	121.1	122.4	123.8	124.7
105°	148.6	149.4	150.2	151.0	151.9	152.7	153.6	154.5	155.3	156.2	156.8
107.5°	186.4	187.1	187.8	188.4	189.1	189.7	190.1	190.5	191.0	191.4	191.6
110°	212.5	213.0	213.4	213.9	214.3	214.7	215.2	215.6	216.0	216.5	216.6



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	238.2	238.7	239.3	239.8	240.3	240.6	240.7	240.9	241.1	241.1
115°	277.8	278.2	278.4	278.7	279.1	279.3	279.1	279.1	278.9	278.7	278.6
117.5°	315.9	316.2	316.4	316.7	316.9	317.2	317.3	317.4	317.5	317.6	317.4
120°	342.2	342.7	342.8	342.9	343.1	343.2	343.2	343.2	343.2	343.2	342.9
122.5°	367.0	367.3	367.6	368.1	368.4	368.8	368.7	368.6	368.4	368.3	368.1
125°	405.4	406.0	406.0	406.2	406.4	406.5	406.2	406.0	405.6	405.4	405.2
127.5°	442.3	442.6	442.8	443.0	443.2	443.3	443.2	443.1	442.9	442.7	442.6
130°	466.2	466.7	467.0	467.3	467.6	467.9	467.7	467.6	467.4	467.3	467.1
132.5°	491.0	491.6	491.5	491.5	491.5	491.4	491.3	491.1	490.9	490.9	490.5
135°	526.2	526.8	526.8	527.0	527.2	527.3	527.3	527.3	527.3	527.3	527.0
137.5°	560.4	560.9	561.3	561.5	561.9	562.2	562.4	562.6	562.7	562.9	562.6
140°	581.9	582.5	582.9	583.3	583.8	584.2	584.4	584.8	585.0	585.3	585.1
142.5°	603.5	604.0	604.6	605.1	605.6	606.1	606.3	606.5	606.7	606.8	606.6
145°	635.7	636.2	636.6	637.1	637.5	637.9	637.9	637.9	637.9	637.9	637.7
147.5°	664.6	664.9	665.2	665.6	665.9	666.2	666.6	666.9	667.3	667.6	667.3
150°	682.7	682.9	683.5	684.1	684.6	685.2	685.2	685.2	685.2	685.2	685.0
152.5°	700.4	700.6	700.9	701.1	701.3	701.5	701.9	702.2	702.6	702.9	702.8
155°	724.8	724.9	725.0	725.1	725.3	725.5	726.0	726.6	727.1	727.7	727.6
157.5°	746.1	746.0	746.1	746.2	746.4	746.6	747.1	747.7	748.2	748.8	748.6
160°	758.9	758.7	758.9	759.1	759.1	759.3	759.9	760.4	761.0	761.6	761.6
162.5°	771.1	770.9	771.0	771.0	771.0	771.1	771.8	772.5	773.1	773.8	773.8
165°	787.0	786.9	787.0	787.1	787.3	787.5	788.0	788.6	789.2	789.7	789.5
167.5°	799.1	798.8	798.8	798.8	798.8	798.8	799.7	800.6	801.4	802.2	802.2
170°	806.2	806.0	806.0	806.0	806.0	806.0	806.8	807.7	808.6	809.4	809.3
172.5°	811.4	811.1	811.1	811.1	811.1	811.1	811.9	812.8	813.6	814.5	814.5
175°	817.1	816.8	816.8	816.8	816.8	816.8	817.7	818.6	819.4	820.3	820.2
177.5°	820.5	820.3	820.1	820.0	819.9	819.8	820.4	821.1	821.8	822.5	822.4
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	22.6	22.2	22.3	23.5	22.3	22.2	22.6	21.5	22.0	20.8	19.5
90°	14.0	14.5	14.9	15.3	14.9	14.5	14.0	13.6	13.1	12.4	11.6
92.5°	29.3	29.5	29.9	30.1	29.9	29.5	29.3	28.9	28.3	27.4	26.4
95°	54.2	54.4	54.7	54.9	54.7	54.4	54.2	53.8	53.2	52.2	51.2
97.5°	82.8	83.0	83.2	83.3	83.2	83.0	82.8	82.7	82.1	81.2	80.2
100°	104.0	104.3	104.5	104.8	104.5	104.3	104.0	103.7	102.9	101.6	100.3
102.5°	125.1	125.5	125.9	126.3	125.9	125.5	125.1	124.7	123.8	122.4	121.1
105°	157.2	157.6	158.1	158.5	158.1	157.6	157.2	156.8	156.2	155.3	154.5
107.5°	191.6	191.6	191.5	191.5	191.5	191.6	191.6	191.6	191.4	191.0	190.5
110°	216.5	216.3	216.2	216.0	216.2	216.3	216.5	216.6	216.5	216.0	215.6



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.8	240.6	240.3	240.0	240.3	240.6	240.8	241.1	241.1	240.9	240.7
115°	278.4	278.4	278.2	278.0	278.2	278.4	278.4	278.6	278.7	278.9	279.1
117.5°	316.8	316.2	315.6	315.1	315.6	316.2	316.8	317.4	317.6	317.5	317.4
120°	342.4	341.8	341.2	340.7	341.2	341.8	342.4	342.9	343.2	343.2	343.2
122.5°	367.6	367.1	366.7	366.3	366.7	367.1	367.6	368.1	368.3	368.4	368.6
125°	405.0	404.8	404.8	404.6	404.8	404.8	405.0	405.2	405.4	405.6	406.0
127.5°	442.3	442.0	441.7	441.4	441.7	442.0	442.3	442.6	442.7	442.9	443.1
130°	466.8	466.5	466.2	466.0	466.2	466.5	466.8	467.1	467.3	467.4	467.6
132.5°	490.2	489.7	489.4	489.0	489.4	489.7	490.2	490.5	490.9	490.9	491.1
135°	526.4	525.9	525.3	524.8	525.3	525.9	526.4	527.0	527.3	527.3	527.3
137.5°	561.9	561.2	560.5	559.7	560.5	561.2	561.9	562.6	562.9	562.7	562.6
140°	584.4	583.7	583.0	582.3	583.0	583.7	584.4	585.1	585.3	585.0	584.8
142.5°	605.9	605.2	604.4	603.7	604.4	605.2	605.9	606.6	606.8	606.7	606.5
145°	637.2	636.8	636.4	635.9	636.4	636.8	637.2	637.7	637.9	637.9	637.9
147.5°	666.3	665.4	664.4	663.5	664.4	665.4	666.3	667.3	667.6	667.3	666.9
150°	684.8	684.5	684.2	683.9	684.2	684.5	684.8	685.0	685.2	685.2	685.2
152.5°	702.3	701.8	701.3	700.8	701.3	701.8	702.3	702.8	702.9	702.6	702.2
155°	726.9	726.3	725.5	724.8	725.5	726.3	726.9	727.6	727.7	727.1	726.6
157.5°	747.7	746.7	745.8	744.9	745.8	746.7	747.7	748.6	748.8	748.2	747.7
160°	760.8	760.1	759.4	758.7	759.4	760.1	760.8	761.6	761.6	761.0	760.4
162.5°	772.9	772.1	771.3	770.4	771.3	772.1	772.9	773.8	773.8	773.1	772.5
165°	788.8	787.9	787.0	786.2	787.0	787.9	788.8	789.5	789.7	789.2	788.6
167.5°	801.3	800.5	799.6	798.7	799.6	800.5	801.3	802.2	802.2	801.4	800.6
170°	808.3	807.4	806.3	805.4	806.3	807.4	808.3	809.3	809.4	808.6	807.7
172.5°	813.6	812.7	811.8	811.0	811.8	812.7	813.6	814.5	814.5	813.6	812.8
175°	819.2	818.2	817.2	816.2	817.2	818.2	819.2	820.2	820.3	819.4	818.6
177.5°	821.7	820.9	820.1	819.2	820.1	820.9	821.7	822.4	822.5	821.8	821.1
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	17.2	17.7	16.4	16.2	15.4	15.8	14.5	13.7	12.9	13.3	14.6
90°	10.9	10.2	9.2	8.3	7.2	6.3	5.2	4.0	2.9	1.8	0.6
92.5°	25.5	24.5	23.3	22.1	20.9	19.6	18.7	17.8	17.0	16.3	15.5
95°	50.2	49.2	47.8	46.4	44.9	43.6	42.7	42.4	42.1	41.8	41.6
97.5°	79.3	78.4	76.4	74.5	72.5	70.5	69.5	69.4	69.2	69.1	69.1
100°	99.1	97.8	95.9	94.1	92.2	90.4	89.5	89.5	89.5	89.5	89.5
102.5°	119.7	118.2	117.3	116.4	115.5	114.5	113.7	113.1	112.6	112.0	111.5
105°	153.6	152.7	151.9	151.0	150.2	149.4	148.6	147.8	147.1	146.5	145.8
107.5°	190.1	189.7	189.1	188.4	187.8	187.1	186.4	185.7	185.0	184.3	183.6
110°	215.2	214.7	214.3	213.9	213.4	213.0	212.5	211.8	211.0	210.3	209.7



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	240.6	240.3	239.8	239.3	238.7	238.2	237.7	237.4	236.9	236.6	236.3
115°	279.1	279.3	279.1	278.7	278.4	278.2	277.8	277.2	276.6	276.0	275.5
117.5°	317.3	317.2	316.9	316.7	316.4	316.2	315.9	315.6	315.4	315.1	314.9
120°	343.2	343.2	343.1	342.9	342.8	342.7	342.2	341.6	340.8	340.1	339.4
122.5°	368.7	368.8	368.4	368.1	367.6	367.3	367.0	366.8	366.5	366.3	366.0
125°	406.2	406.5	406.4	406.2	406.0	406.0	405.4	404.6	403.7	402.9	402.0
127.5°	443.2	443.3	443.2	443.0	442.8	442.6	442.3	441.9	441.3	440.8	440.4
130°	467.7	467.9	467.6	467.3	467.0	466.7	466.2	465.5	464.9	464.1	463.4
132.5°	491.3	491.4	491.5	491.5	491.5	491.6	491.0	489.9	488.7	487.6	486.4
135°	527.3	527.3	527.2	527.0	526.8	526.8	526.2	525.4	524.5	523.7	522.8
137.5°	562.4	562.2	561.9	561.5	561.3	560.9	560.4	559.6	558.7	557.9	557.1
140°	584.4	584.2	583.8	583.3	582.9	582.5	581.9	581.2	580.5	579.8	579.1
142.5°	606.3	606.1	605.6	605.1	604.6	604.0	603.5	602.9	602.3	601.7	601.1
145°	637.9	637.9	637.5	637.1	636.6	636.2	635.7	635.1	634.6	634.0	633.4
147.5°	666.6	666.2	665.9	665.6	665.2	664.9	664.6	664.3	663.9	663.7	663.3
150°	685.2	685.2	684.6	684.1	683.5	682.9	682.7	682.9	682.9	683.1	683.3
152.5°	701.9	701.5	701.3	701.1	700.9	700.6	700.4	700.3	700.0	699.8	699.6
155°	726.0	725.5	725.3	725.1	725.0	724.9	724.8	724.8	724.8	724.8	724.8
157.5°	747.1	746.6	746.4	746.2	746.1	746.0	746.1	746.4	746.7	747.0	747.3
160°	759.9	759.3	759.1	759.1	758.9	758.7	758.9	759.3	759.7	760.2	760.6
162.5°	771.8	771.1	771.0	771.0	771.0	770.9	771.1	771.5	771.7	772.1	772.4
165°	788.0	787.5	787.3	787.1	787.0	786.9	787.0	787.2	787.6	787.8	788.1
167.5°	799.7	798.8	798.8	798.8	798.8	798.8	799.1	799.7	800.2	800.8	801.4
170°	806.8	806.0	806.0	806.0	806.0	806.0	806.2	806.8	807.4	808.0	808.6
172.5°	811.9	811.1	811.1	811.1	811.1	811.1	811.4	811.9	812.5	813.0	813.6
175°	817.7	816.8	816.8	816.8	816.8	816.8	817.1	817.7	818.3	818.8	819.4
177.5°	820.4	819.8	819.9	820.0	820.1	820.3	820.5	821.0	821.4	821.9	822.3
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.3	15.1	16.9	19.8	21.6	24.0	25.3	24.4	22.5	21.0	19.5
90°	1.8	2.9	4.0	5.2	6.3	7.2	8.3	9.2	10.2	10.9	11.6
92.5°	16.3	17.0	17.8	18.7	19.6	20.9	22.1	23.3	24.5	25.5	26.4
95°	41.8	42.1	42.4	42.7	43.6	44.9	46.4	47.8	49.2	50.2	51.2
97.5°	69.1	69.2	69.4	69.5	70.5	72.5	74.5	76.4	78.4	79.3	80.2
100°	89.5	89.5	89.5	89.5	90.4	92.2	94.1	95.9	97.8	99.1	100.3
102.5°	112.0	112.6	113.1	113.7	114.5	115.5	116.4	117.3	118.2	119.7	121.1
105°	146.5	147.1	147.8	148.6	149.4	150.2	151.0	151.9	152.7	153.6	154.5
107.5°	184.3	185.0	185.7	186.4	187.1	187.8	188.4	189.1	189.7	190.1	190.5
110°	210.3	211.0	211.8	212.5	213.0	213.4	213.9	214.3	214.7	215.2	215.6





TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	236.6	236.9	237.4	237.7	238.2	238.7	239.3	239.8	240.3	240.6	240.7
115°	276.0	276.6	277.2	277.8	278.2	278.4	278.7	279.1	279.3	279.1	279.1
117.5°	315.1	315.4	315.6	315.9	316.2	316.4	316.7	316.9	317.2	317.3	317.4
120°	340.1	340.8	341.6	342.2	342.7	342.8	342.9	343.1	343.2	343.2	343.2
122.5°	366.3	366.5	366.8	367.0	367.3	367.6	368.1	368.4	368.8	368.7	368.6
125°	402.9	403.7	404.6	405.4	406.0	406.0	406.2	406.4	406.5	406.2	406.0
127.5°	440.8	441.3	441.9	442.3	442.6	442.8	443.0	443.2	443.3	443.2	443.1
130°	464.1	464.9	465.5	466.2	466.7	467.0	467.3	467.6	467.9	467.7	467.6
132.5°	487.6	488.7	489.9	491.0	491.6	491.5	491.5	491.5	491.4	491.3	491.1
135°	523.7	524.5	525.4	526.2	526.8	526.8	527.0	527.2	527.3	527.3	527.3
137.5°	557.9	558.7	559.6	560.4	560.9	561.3	561.5	561.9	562.2	562.4	562.6
140°	579.8	580.5	581.2	581.9	582.5	582.9	583.3	583.8	584.2	584.4	584.8
142.5°	601.7	602.3	602.9	603.5	604.0	604.6	605.1	605.6	606.1	606.3	606.5
145°	634.0	634.6	635.1	635.7	636.2	636.6	637.1	637.5	637.9	637.9	637.9
147.5°	663.7	663.9	664.3	664.6	664.9	665.2	665.6	665.9	666.2	666.6	666.9
150°	683.1	682.9	682.9	682.7	682.9	683.5	684.1	684.6	685.2	685.2	685.2
152.5°	699.8	700.0	700.3	700.4	700.6	700.9	701.1	701.3	701.5	701.9	702.2
155°	724.8	724.8	724.8	724.8	724.9	725.0	725.1	725.3	725.5	726.0	726.6
157.5°	747.0	746.7	746.4	746.1	746.0	746.1	746.2	746.4	746.6	747.1	747.7
160°	760.2	759.7	759.3	758.9	758.7	758.9	759.1	759.1	759.3	759.9	760.4
162.5°	772.1	771.7	771.5	771.1	770.9	771.0	771.0	771.0	771.1	771.8	772.5
165°	787.8	787.6	787.2	787.0	786.9	787.0	787.1	787.3	787.5	788.0	788.6
167.5°	800.8	800.2	799.7	799.1	798.8	798.8	798.8	798.8	798.8	799.7	800.6
170°	808.0	807.4	806.8	806.2	806.0	806.0	806.0	806.0	806.0	806.8	807.7
172.5°	813.0	812.5	811.9	811.4	811.1	811.1	811.1	811.1	811.1	811.9	812.8
175°	818.8	818.3	817.7	817.1	816.8	816.8	816.8	816.8	816.8	817.7	818.6
177.5°	821.9	821.4	821.0	820.5	820.3	820.1	820.0	819.9	819.8	820.4	821.1
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	19.6	17.7	17.7	17.3	17.4	17.0	15.9
90°	12.4	13.1	13.6	14.0	14.5	14.9	15.3
92.5°	27.4	28.3	28.9	29.3	29.5	29.9	30.1
95°	52.2	53.2	53.8	54.2	54.4	54.7	54.9
97.5°	81.2	82.1	82.7	82.8	83.0	83.2	83.3
100°	101.6	102.9	103.7	104.0	104.3	104.5	104.8
102.5°	122.4	123.8	124.7	125.1	125.5	125.9	126.3
105°	155.3	156.2	156.8	157.2	157.6	158.1	158.5
107.5°	191.0	191.4	191.6	191.6	191.6	191.5	191.5
110°	216.0	216.5	216.6	216.5	216.3	216.2	216.0



TEST NUMBER: P333467-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	240.9	241.1	241.1	240.8	240.6	240.3	240.0
115°	278.9	278.7	278.6	278.4	278.4	278.2	278.0
117.5°	317.5	317.6	317.4	316.8	316.2	315.6	315.1
120°	343.2	343.2	342.9	342.4	341.8	341.2	340.7
122.5°	368.4	368.3	368.1	367.6	367.1	366.7	366.3
125°	405.6	405.4	405.2	405.0	404.8	404.8	404.6
127.5°	442.9	442.7	442.6	442.3	442.0	441.7	441.4
130°	467.4	467.3	467.1	466.8	466.5	466.2	466.0
132.5°	490.9	490.9	490.5	490.2	489.7	489.4	489.0
135°	527.3	527.3	527.0	526.4	525.9	525.3	524.8
137.5°	562.7	562.9	562.6	561.9	561.2	560.5	559.7
140°	585.0	585.3	585.1	584.4	583.7	583.0	582.3
142.5°	606.7	606.8	606.6	605.9	605.2	604.4	603.7
145°	637.9	637.9	637.7	637.2	636.8	636.4	635.9
147.5°	667.3	667.6	667.3	666.3	665.4	664.4	663.5
150°	685.2	685.2	685.0	684.8	684.5	684.2	683.9
152.5°	702.6	702.9	702.8	702.3	701.8	701.3	700.8
155°	727.1	727.7	727.6	726.9	726.3	725.5	724.8
157.5°	748.2	748.8	748.6	747.7	746.7	745.8	744.9
160°	761.0	761.6	761.6	760.8	760.1	759.4	758.7
162.5°	773.1	773.8	773.8	772.9	772.1	771.3	770.4
165°	789.2	789.7	789.5	788.8	787.9	787.0	786.2
167.5°	801.4	802.2	802.2	801.3	800.5	799.6	798.7
170°	808.6	809.4	809.3	808.3	807.4	806.3	805.4
172.5°	813.6	814.5	814.5	813.6	812.7	811.8	811.0
175°	819.4	820.3	820.2	819.2	818.2	817.2	816.2
177.5°	821.8	822.5	822.4	821.7	820.9	820.1	819.2
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3

(END OF REPORT)