

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333696-840

Luminaire Tested: **S125RDIW-S850D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333696-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9611.3 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	37	36	30
2	86	79	73	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	26	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8250	8250	8250	8250
5°	9491	8261	7295	8261
10°	10887	8218	6437	8218
15°	11760	8134	5722	8134
20°	12967	8036	5283	8036
25°	15007	7906	4903	7906
30°	16330	7770	4653	7770
35°	13775	7611	4424	7611
40°	9620	7325	4226	7325
45°	7136	6940	4032	6940
50°	5690	6539	3867	6539
55°	4829	6040	3719	6040
60°	4173	5594	3481	5594
65°	3718	5113	2997	5113
70°	3269	4683	2732	4683
75°	2827	4057	2565	4057
80°	2146	3414	2146	3414
85°	1786	2682	2023	2682



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.3
10°-20°	359.0	3.7
20°-30°	569.2	5.9
30°-40°	686.4	7.1
40°-50°	613.0	6.4
50°-60°	470.0	4.9
60°-70°	305.5	3.2
70°-80°	148.5	1.5
80°-90°	39.7	0.4
90°-100°	74.5	0.8
100°-110°	459.3	4.8
110°-120°	833.0	8.7
120°-130°	1069.1	11.1
130°-140°	1149.9	12.0
140°-150°	1079.3	11.2
150°-160°	873.1	9.1
160°-170°	564.7	5.9
170°-180°	194.8	2.0
0°-30°	1050.6	10.9
0°-40°	1737.0	18.1
0°-60°	2820.0	29.3
0°-90°	3313.7	34.5
90°-120°	1366.8	14.2
90°-150°	4665.0	48.5
90°-180°	6298.0	65.5
0°-180°	9611.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1277	1277	1277	1277	1277	
5°	1464	1274	1125	1274	1464	146
15°	1759	1217	856	1217	1759	504
25°	2106	1110	688	1110	2106	967
35°	1747	965	561	965	1747	1055
45°	781	760	442	760	781	623
55°	429	536	330	536	429	389
65°	243	335	196	335	243	242
75°	113	163	103	163	113	121
85°	24	36	27	36	24	29
90°	36	2	36	2	36	17
95°	32	87	32	87	32	26
105°	452	447	452	447	452	408
115°	833	839	833	839	833	827
125°	1193	1193	1193	1193	1193	1062
135°	1482	1488	1482	1488	1482	1144
145°	1721	1726	1721	1726	1721	1075
155°	1886	1900	1886	1900	1886	869
165°	1994	2005	1994	2005	1994	563
175°	2042	2051	2042	2051	2042	194
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1343.6	1342.8	1344.5	1339.9	1340.3	1333.1	1333.1	1327.7	1320.6	1315.1	1312.6
5°	1464.0	1465.1	1463.0	1455.1	1449.9	1442.0	1433.1	1417.3	1404.2	1391.7	1381.7
7.5°	1588.0	1588.7	1581.9	1579.4	1566.2	1556.5	1536.7	1515.3	1496.3	1472.2	1453.8
10°	1660.1	1659.6	1652.3	1646.5	1635.0	1620.3	1600.9	1575.7	1552.2	1525.9	1500.8
12.5°	1702.1	1700.7	1698.4	1691.4	1680.7	1667.7	1651.2	1626.5	1597.4	1568.7	1539.3
15°	1758.8	1755.0	1748.3	1739.3	1724.1	1708.9	1690.6	1668.6	1640.7	1608.2	1580.9
17.5°	1828.8	1828.9	1818.5	1806.0	1785.3	1758.6	1730.2	1694.7	1656.9	1621.1	1592.1
20°	1886.7	1885.1	1874.6	1850.5	1826.9	1793.3	1760.8	1717.3	1671.1	1624.5	1588.3
22.5°	1969.7	1965.7	1954.8	1923.1	1886.5	1843.3	1793.5	1740.4	1684.6	1631.6	1584.2
25°	2105.9	2102.7	2081.2	2044.6	1993.2	1926.5	1861.5	1788.7	1708.4	1638.7	1580.9
27.5°	2199.0	2195.5	2179.6	2149.1	2101.7	2031.6	1943.6	1846.2	1746.1	1650.1	1566.9
30°	2189.8	2197.7	2195.5	2181.4	2145.8	2082.8	2001.6	1892.0	1772.9	1660.1	1561.0
32.5°	2058.0	2065.1	2083.6	2111.3	2113.4	2088.3	2027.5	1926.3	1803.1	1674.9	1556.4
35°	1747.2	1756.7	1792.3	1848.5	1921.8	1983.2	1995.8	1941.3	1830.6	1692.6	1549.5
37.5°	1343.2	1394.8	1424.8	1483.9	1594.8	1707.7	1816.2	1856.1	1809.1	1685.4	1538.3
40°	1141.0	1153.6	1207.1	1273.7	1367.1	1484.5	1639.2	1750.9	1754.5	1668.6	1520.7
42.5°	976.5	992.5	1029.3	1082.4	1162.4	1279.8	1439.5	1586.9	1655.2	1622.4	1497.6
45°	781.3	793.3	820.1	861.0	922.4	1019.4	1156.8	1327.2	1462.5	1515.4	1435.7
47.5°	641.9	648.3	671.7	702.8	748.2	818.9	925.2	1073.2	1235.5	1349.2	1338.0
50°	566.3	573.7	591.5	615.1	653.4	713.2	798.1	921.3	1088.6	1227.6	1255.4
52.5°	507.6	513.7	524.8	547.1	578.7	624.6	693.2	804.7	955.2	1103.0	1167.2
55°	428.9	433.1	442.0	454.6	479.8	512.8	572.1	649.1	770.8	919.8	1014.1
57.5°	364.2	366.2	371.9	383.5	400.9	425.1	467.9	533.2	620.5	754.6	858.7
60°	323.1	325.1	332.4	340.3	354.0	376.0	409.5	455.1	539.1	649.6	755.1
62.5°	290.3	291.5	294.7	302.6	314.5	331.5	357.9	395.2	461.9	559.1	658.6
65°	243.3	243.9	244.9	251.2	258.5	271.1	288.4	314.6	365.0	438.4	526.4
67.5°	198.2	198.9	202.6	204.8	212.5	219.0	229.2	249.3	284.8	334.3	402.7
70°	173.1	172.5	176.2	178.8	181.5	189.2	196.1	212.4	234.4	272.2	329.3
72.5°	149.6	148.1	149.8	150.7	154.2	159.6	166.3	176.3	193.3	219.2	263.1
75°	113.3	113.8	113.8	114.8	117.4	119.6	121.7	126.9	136.3	153.6	177.2
77.5°	79.5	78.7	80.9	81.2	82.7	85.0	86.8	89.0	92.8	100.0	112.1
80°	57.7	57.7	58.2	59.8	59.3	60.3	62.9	65.0	69.8	73.9	78.2
82.5°	44.2	43.8	44.3	44.6	44.5	45.6	46.6	47.0	48.8	50.9	53.8
85°	24.1	24.1	24.6	24.6	25.1	25.1	25.7	25.7	25.7	26.3	26.8
87.5°	16.6	15.9	15.2	15.0	15.2	15.9	15.1	14.3	14.0	13.6	13.6
90°	36.5	35.4	34.4	33.4	32.4	31.1	29.4	27.7	26.1	24.3	21.9
92.5°	34.0	33.6	33.1	32.6	32.1	31.1	29.4	27.7	26.1	24.3	22.2
95°	31.9	31.9	31.9	31.9	31.9	31.1	29.4	27.7	26.1	24.3	37.2
97.5°	31.9	31.9	31.9	31.9	31.9	36.7	46.3	55.7	65.2	74.8	100.2
100°	31.9	33.3	34.6	36.0	37.4	63.2	113.5	163.8	214.2	264.5	263.2
102.5°	191.3	214.2	237.2	260.1	283.2	299.4	308.9	318.4	328.0	337.5	336.7
105°	451.5	451.8	452.2	452.5	452.8	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	569.2	570.2	571.2	572.2	573.2	573.7	573.6	573.6	573.5	573.4	572.8
110°	650.7	650.4	649.9	649.6	649.3	649.6	650.7	651.7	652.7	653.7	653.0



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	723.6	724.1	724.6	725.1	725.5	726.4	727.7	728.9	730.2	731.5	731.1
115°	833.0	835.1	837.1	839.2	841.2	842.8	844.2	845.6	846.9	848.3	848.0
117.5°	949.8	950.7	951.6	952.5	953.3	954.6	956.4	958.2	959.9	961.7	960.4
120°	1021.6	1023.3	1024.9	1026.6	1028.3	1029.6	1030.2	1030.9	1031.6	1032.2	1031.2
122.5°	1089.6	1091.7	1093.6	1095.6	1097.5	1098.8	1099.5	1100.1	1100.9	1101.6	1101.1
125°	1193.4	1194.4	1195.4	1196.4	1197.4	1198.6	1199.9	1201.3	1202.6	1204.0	1204.0
127.5°	1280.6	1283.1	1285.7	1288.1	1290.6	1292.2	1293.0	1293.7	1294.4	1295.3	1295.5
130°	1343.8	1345.5	1347.3	1349.0	1350.6	1352.0	1353.0	1354.0	1355.0	1356.0	1355.6
132.5°	1402.2	1403.9	1405.6	1407.3	1409.0	1410.0	1410.2	1410.4	1410.6	1410.8	1411.5
135°	1482.2	1484.2	1486.2	1488.2	1490.3	1491.7	1492.4	1493.0	1493.7	1494.4	1495.0
137.5°	1562.5	1564.2	1566.0	1567.7	1569.5	1570.3	1570.1	1570.0	1569.9	1569.7	1570.3
140°	1609.9	1611.9	1614.0	1616.0	1618.0	1618.7	1618.0	1617.3	1616.7	1616.0	1616.3
142.5°	1654.9	1656.9	1658.9	1660.9	1663.0	1664.0	1663.9	1663.7	1663.6	1663.4	1662.9
145°	1720.9	1722.9	1725.0	1727.0	1729.0	1729.8	1729.5	1729.2	1728.8	1728.5	1728.5
147.5°	1775.3	1777.8	1780.2	1782.6	1785.0	1786.0	1785.6	1785.2	1784.8	1784.4	1784.0
150°	1810.6	1813.3	1815.9	1818.7	1821.4	1822.4	1821.7	1821.0	1820.4	1819.7	1819.0
152.5°	1843.4	1845.8	1848.3	1850.7	1853.1	1854.0	1853.3	1852.7	1852.0	1851.3	1850.7
155°	1886.5	1889.3	1892.0	1894.7	1897.3	1898.2	1897.2	1896.2	1895.2	1894.2	1893.5
157.5°	1922.8	1925.4	1928.1	1930.9	1933.6	1934.4	1933.3	1932.2	1931.2	1930.1	1930.0
160°	1945.9	1948.5	1951.3	1954.0	1956.7	1957.3	1956.0	1954.6	1953.3	1952.0	1951.6
162.5°	1966.5	1969.5	1972.5	1975.5	1978.4	1978.9	1977.1	1975.2	1973.3	1971.4	1971.1
165°	1994.5	1997.2	1999.9	2002.7	2005.3	2005.7	2003.7	2001.6	1999.5	1997.5	1997.2
167.5°	2014.0	2017.0	2020.0	2023.1	2026.1	2026.4	2024.0	2021.5	2019.1	2016.7	2016.4
170°	2024.9	2027.9	2031.0	2034.1	2037.1	2037.2	2034.6	2031.8	2029.1	2026.4	2026.1
172.5°	2032.3	2035.3	2038.3	2041.3	2044.4	2044.7	2042.3	2039.8	2037.4	2035.0	2034.4
175°	2041.6	2044.7	2047.7	2050.7	2053.8	2054.0	2051.2	2048.5	2045.9	2043.2	2042.9
177.5°	2047.1	2049.2	2051.4	2053.6	2055.8	2055.9	2054.0	2052.1	2050.2	2048.3	2048.0
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1312.6	1309.7	1304.2	1299.2	1292.9	1287.5	1283.6	1279.1	1273.1	1266.1	1260.2
5°	1370.7	1359.2	1343.9	1330.9	1314.0	1301.0	1287.4	1274.2	1261.1	1244.4	1229.6
7.5°	1435.1	1411.3	1388.2	1359.0	1332.5	1308.9	1286.3	1263.3	1240.9	1217.1	1194.1
10°	1474.5	1445.7	1413.7	1377.0	1343.4	1311.4	1282.1	1253.2	1222.8	1196.1	1167.2
12.5°	1511.5	1474.2	1437.6	1391.3	1351.0	1311.9	1274.6	1238.6	1206.1	1171.3	1140.4
15°	1544.8	1508.1	1467.2	1410.6	1354.4	1307.3	1263.2	1216.6	1176.2	1137.4	1102.8
17.5°	1557.7	1519.2	1471.7	1417.2	1355.9	1296.6	1239.8	1188.6	1141.1	1095.9	1057.0
20°	1552.7	1515.4	1466.6	1414.7	1349.2	1287.4	1226.0	1169.3	1116.4	1068.6	1027.2
22.5°	1540.4	1502.0	1454.9	1400.1	1337.9	1272.2	1206.7	1146.3	1090.8	1041.4	996.2
25°	1522.3	1469.9	1421.6	1368.1	1308.8	1243.9	1176.2	1109.5	1050.4	1000.0	950.7
27.5°	1503.3	1437.8	1376.4	1323.3	1260.7	1202.6	1137.5	1069.1	1006.9	955.6	905.0
30°	1486.1	1412.7	1345.0	1284.8	1225.5	1170.4	1108.5	1041.9	978.0	925.0	873.6
32.5°	1464.7	1386.6	1312.3	1242.7	1185.6	1130.9	1075.0	1011.3	949.0	894.3	842.1
35°	1437.8	1338.2	1257.5	1183.5	1120.0	1067.1	1016.7	965.3	902.9	846.4	795.5
37.5°	1402.6	1289.5	1196.1	1115.6	1048.6	995.4	955.7	908.8	851.8	797.6	750.3
40°	1381.2	1254.3	1152.1	1072.4	1002.1	945.9	908.8	868.9	817.0	766.1	718.9
42.5°	1352.7	1222.0	1107.6	1024.5	953.8	899.8	862.1	827.4	783.9	735.9	685.4
45°	1296.8	1159.4	1039.4	950.2	878.9	825.9	790.7	759.8	726.8	682.8	638.6
47.5°	1224.0	1094.1	968.4	871.1	801.2	752.0	718.0	693.6	669.9	632.5	589.7
50°	1165.7	1040.4	917.7	823.2	748.8	702.2	670.1	650.8	629.2	595.1	559.5
52.5°	1096.9	985.0	864.7	768.3	698.0	654.3	623.6	604.2	586.4	558.7	524.7
55°	988.5	890.4	780.2	692.7	628.2	584.1	554.8	536.4	525.9	502.3	475.6
57.5°	863.3	793.0	695.9	611.5	554.5	511.0	489.5	473.8	462.0	445.2	426.5
60°	776.1	726.8	639.7	559.5	507.1	465.6	446.3	433.1	422.1	408.0	393.2
62.5°	687.5	651.7	575.9	507.1	458.8	424.1	406.0	394.2	381.4	371.9	357.6
65°	569.0	536.9	484.5	430.5	386.0	358.1	345.1	334.6	326.7	316.2	306.2
67.5°	442.5	429.6	393.3	356.2	324.2	299.4	288.1	280.7	271.4	265.0	258.2
70°	365.0	358.7	333.0	308.3	278.4	261.7	251.2	248.0	236.5	230.2	225.5
72.5°	296.2	293.3	278.4	261.4	240.2	225.6	215.9	212.4	205.0	200.0	196.9
75°	202.9	204.0	201.4	190.4	182.5	173.1	164.6	162.6	157.3	153.1	150.5
77.5°	128.4	133.7	133.9	133.4	130.3	124.5	121.0	119.5	114.3	112.7	112.1
80°	88.1	93.8	99.1	98.6	97.6	95.9	93.3	91.8	89.2	87.6	86.5
82.5°	58.8	64.1	68.5	71.3	71.1	69.6	67.8	67.1	66.4	65.3	65.1
85°	27.8	28.9	30.4	34.1	36.7	37.3	36.7	36.2	34.6	35.1	35.6
87.5°	13.5	13.1	13.0	12.5	11.6	13.1	13.8	13.7	13.4	13.1	12.8
90°	19.6	17.3	14.8	12.3	9.6	7.0	4.2	1.5	4.2	7.0	9.6
92.5°	20.1	18.1	16.0	15.9	17.8	19.6	21.5	23.4	21.5	19.6	17.8
95°	50.0	62.8	75.6	82.6	83.6	84.6	85.6	86.6	85.6	84.6	83.6
97.5°	125.6	151.0	176.4	188.2	186.4	184.5	182.7	180.9	182.7	184.5	186.4
100°	261.9	260.4	259.1	257.9	256.9	255.9	254.9	253.9	254.9	255.9	256.9
102.5°	335.9	335.1	334.3	333.2	331.9	330.6	329.3	328.1	329.3	330.6	331.9
105°	453.0	453.0	453.0	452.3	451.0	449.7	448.3	447.0	448.3	449.7	451.0
107.5°	572.1	571.4	570.7	570.4	570.4	570.4	570.4	570.4	570.4	570.4	570.4
110°	652.4	651.7	651.0	650.7	650.7	650.7	650.7	650.7	650.7	650.7	650.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	730.7	730.3	729.9	729.3	728.5	727.7	726.9	726.1	726.9	727.7	728.5
115°	847.6	847.3	846.9	845.9	844.2	842.5	840.8	839.2	840.8	842.5	844.2
117.5°	959.1	957.9	956.5	955.9	956.0	956.0	956.1	956.2	956.1	956.0	956.0
120°	1030.2	1029.2	1028.1	1027.8	1028.1	1028.5	1028.9	1029.2	1028.9	1028.5	1028.1
122.5°	1100.6	1100.1	1099.6	1098.7	1097.5	1096.2	1094.9	1093.7	1094.9	1096.2	1097.5
125°	1204.0	1204.0	1204.0	1202.9	1200.4	1198.1	1195.7	1193.4	1195.7	1198.1	1200.4
127.5°	1295.7	1295.9	1296.1	1295.3	1293.6	1291.9	1290.2	1288.5	1290.2	1291.9	1293.6
130°	1355.3	1355.0	1354.6	1353.6	1352.0	1350.3	1348.6	1346.9	1348.6	1350.3	1352.0
132.5°	1412.2	1413.0	1413.7	1413.1	1411.2	1409.2	1407.2	1405.2	1407.2	1409.2	1411.2
135°	1495.7	1496.4	1497.0	1496.4	1494.4	1492.4	1490.3	1488.2	1490.3	1492.4	1494.4
137.5°	1570.9	1571.6	1572.2	1571.7	1569.8	1568.1	1566.3	1564.6	1566.3	1568.1	1569.8
140°	1616.7	1617.0	1617.3	1617.2	1616.5	1615.8	1615.2	1614.5	1615.2	1615.8	1616.5
142.5°	1662.4	1662.0	1661.5	1661.0	1660.6	1660.2	1659.8	1659.4	1659.8	1660.2	1660.6
145°	1728.5	1728.5	1728.5	1728.2	1727.5	1726.8	1726.1	1725.5	1726.1	1726.8	1727.5
147.5°	1783.6	1783.2	1782.8	1782.6	1782.8	1782.9	1783.0	1783.2	1783.0	1782.9	1782.8
150°	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1819.0	1818.4	1817.7
152.5°	1850.0	1849.3	1848.6	1849.0	1850.5	1852.0	1853.5	1854.9	1853.5	1852.0	1850.5
155°	1892.8	1892.2	1891.5	1892.2	1894.2	1896.2	1898.2	1900.3	1898.2	1896.2	1894.2
157.5°	1930.0	1929.9	1929.8	1930.4	1931.6	1932.8	1934.0	1935.2	1934.0	1932.8	1931.6
160°	1951.3	1951.0	1950.6	1951.5	1953.5	1955.5	1957.5	1959.5	1957.5	1955.5	1953.5
162.5°	1970.8	1970.3	1970.0	1970.9	1972.9	1975.0	1977.0	1979.0	1977.0	1975.0	1972.9
165°	1996.9	1996.5	1996.2	1997.0	1999.0	2001.0	2003.2	2005.2	2003.2	2001.0	1999.0
167.5°	2016.0	2015.7	2015.4	2016.2	2018.3	2020.4	2022.6	2024.6	2022.6	2020.4	2018.3
170°	2025.8	2025.4	2025.1	2026.1	2028.4	2030.8	2033.2	2035.6	2033.2	2030.8	2028.4
172.5°	2033.8	2033.2	2032.6	2033.4	2035.8	2038.1	2040.5	2042.9	2040.5	2038.1	2035.8
175°	2042.5	2042.1	2041.8	2042.7	2044.7	2046.7	2048.7	2050.7	2048.7	2046.7	2044.7
177.5°	2047.8	2047.5	2047.2	2047.9	2049.5	2051.1	2052.8	2054.4	2052.8	2051.1	2049.5
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1256.0	1250.1	1245.9	1237.5	1231.6	1229.1	1224.6	1223.2	1227.9	1224.6	1224.1
5°	1218.6	1203.5	1191.3	1179.3	1166.2	1157.8	1145.2	1143.2	1139.9	1135.3	1134.2
7.5°	1173.9	1154.1	1138.5	1118.6	1101.3	1087.3	1071.6	1064.2	1060.1	1054.0	1045.8
10°	1143.7	1120.0	1099.0	1079.1	1057.6	1040.4	1024.6	1012.6	1004.7	997.3	994.2
12.5°	1113.9	1089.8	1063.0	1038.8	1014.9	995.4	978.1	970.2	961.5	952.9	945.5
15°	1067.6	1035.6	1006.2	978.5	958.1	937.1	920.3	908.8	895.6	891.9	877.8
17.5°	1018.5	987.1	952.8	923.5	899.8	876.8	858.3	845.2	835.4	821.8	815.3
20°	988.0	950.7	917.2	890.4	864.1	836.9	818.0	807.0	797.6	786.6	781.3
22.5°	955.2	918.8	884.4	853.0	826.4	799.6	786.2	774.7	764.0	753.9	746.9
25°	907.2	870.5	834.2	801.7	774.0	754.6	738.8	725.7	719.9	710.0	702.7
27.5°	859.7	820.6	783.0	750.7	728.9	709.7	696.8	686.4	676.0	667.3	661.0
30°	829.0	789.2	748.3	722.6	699.5	681.2	667.0	657.0	649.1	641.3	636.6
32.5°	798.4	757.3	721.0	693.2	671.4	655.6	641.0	631.5	623.2	614.5	608.9
35°	749.3	707.4	678.0	650.8	629.2	614.6	604.6	591.0	584.1	577.8	572.1
37.5°	703.7	664.7	632.9	609.0	590.4	575.7	562.9	555.5	547.1	541.5	536.6
40°	670.1	634.5	605.6	580.5	566.8	550.6	538.6	529.1	522.8	515.4	510.2
42.5°	640.0	606.8	578.8	556.1	539.2	525.4	513.8	504.3	496.3	491.1	486.8
45°	597.2	564.2	536.9	515.9	500.3	487.2	475.0	470.4	459.9	453.6	451.5
47.5°	553.1	523.5	497.3	477.9	461.8	449.4	438.1	428.4	422.6	416.5	413.1
50°	523.3	495.0	470.4	451.5	435.8	422.1	411.6	405.4	397.5	391.7	387.5
52.5°	493.5	467.4	442.7	424.6	411.0	397.4	385.7	379.3	371.9	368.2	365.3
55°	451.0	423.1	402.2	384.4	370.2	357.6	346.6	340.3	335.6	331.9	330.8
57.5°	402.7	380.7	361.2	345.2	330.4	318.6	308.9	303.0	298.8	298.2	295.1
60°	371.2	351.3	333.5	316.2	303.6	292.6	284.2	277.4	273.2	272.7	271.7
62.5°	339.8	320.7	304.2	288.9	277.6	267.0	259.0	251.4	248.8	246.2	244.0
65°	293.2	275.8	262.2	250.1	238.0	229.1	221.3	216.5	210.8	207.6	201.9
67.5°	247.3	233.9	220.8	210.6	201.2	192.7	186.1	179.2	175.2	172.7	168.5
70°	217.1	206.6	193.5	182.5	175.1	168.3	163.1	155.2	152.6	150.5	148.3
72.5°	188.5	179.4	168.3	159.5	152.1	145.6	139.6	135.9	133.3	131.2	130.0
75°	148.3	139.5	130.1	123.7	118.6	113.3	110.1	107.4	106.4	105.9	103.8
77.5°	109.0	104.2	96.6	91.7	88.2	86.1	83.3	81.9	81.8	79.5	78.8
80°	83.4	80.8	74.4	72.4	69.8	67.7	66.0	63.4	60.8	59.8	58.2
82.5°	62.0	59.4	56.9	53.5	51.3	50.0	48.5	47.5	47.9	46.4	45.6
85°	33.0	30.4	29.4	28.9	27.8	28.9	28.3	27.8	27.3	26.8	27.3
87.5°	12.9	13.4	13.5	14.8	14.0	14.9	15.2	15.1	15.6	15.9	15.8
90°	12.3	14.8	17.3	19.6	21.9	24.3	26.1	27.7	29.4	31.1	32.4
92.5°	15.9	16.0	18.1	20.1	22.2	24.3	26.1	27.7	29.4	31.1	32.1
95°	82.6	75.6	62.8	50.0	37.2	24.3	26.1	27.7	29.4	31.1	31.9
97.5°	188.2	176.4	151.0	125.6	100.2	74.8	65.2	55.7	46.3	36.7	31.9
100°	257.9	259.1	260.4	261.9	263.2	264.5	214.2	163.8	113.5	63.2	37.4
102.5°	333.2	334.3	335.1	335.9	336.7	337.5	328.0	318.4	308.9	299.4	283.2
105°	452.3	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0	452.8
107.5°	570.4	570.7	571.4	572.1	572.8	573.4	573.5	573.6	573.6	573.7	573.2
110°	650.7	651.0	651.7	652.4	653.0	653.7	652.7	651.7	650.7	649.6	649.3



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	729.3	729.9	730.3	730.7	731.1	731.5	730.2	728.9	727.7	726.4	725.5
115°	845.9	846.9	847.3	847.6	848.0	848.3	846.9	845.6	844.2	842.8	841.2
117.5°	955.9	956.5	957.9	959.1	960.4	961.7	959.9	958.2	956.4	954.6	953.3
120°	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6	1030.9	1030.2	1029.6	1028.3
122.5°	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9	1100.1	1099.5	1098.8	1097.5
125°	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6	1201.3	1199.9	1198.6	1197.4
127.5°	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4	1293.7	1293.0	1292.2	1290.6
130°	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0	1354.0	1353.0	1352.0	1350.6
132.5°	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6	1410.4	1410.2	1410.0	1409.0
135°	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7	1493.0	1492.4	1491.7	1490.3
137.5°	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9	1570.0	1570.1	1570.3	1569.5
140°	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7	1617.3	1618.0	1618.7	1618.0
142.5°	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6	1663.7	1663.9	1664.0	1663.0
145°	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8	1729.2	1729.5	1729.8	1729.0
147.5°	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8	1785.2	1785.6	1786.0	1785.0
150°	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4	1821.0	1821.7	1822.4	1821.4
152.5°	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0	1852.7	1853.3	1854.0	1853.1
155°	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2	1896.2	1897.2	1898.2	1897.3
157.5°	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2	1932.2	1933.3	1934.4	1933.6
160°	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3	1954.6	1956.0	1957.3	1956.7
162.5°	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3	1975.2	1977.1	1978.9	1978.4
165°	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5	2001.6	2003.7	2005.7	2005.3
167.5°	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1	2021.5	2024.0	2026.4	2026.1
170°	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1	2031.8	2034.6	2037.2	2037.1
172.5°	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4	2039.8	2042.3	2044.7	2044.4
175°	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9	2048.5	2051.2	2054.0	2053.8
177.5°	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2	2052.1	2054.0	2055.9	2055.8
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1223.7	1219.1	1217.8	1219.5	1217.8	1219.1	1223.7	1224.1	1224.6	1227.9	1223.2
5°	1128.9	1123.8	1126.3	1125.3	1126.3	1123.8	1128.9	1134.2	1135.3	1139.9	1143.2
7.5°	1045.7	1039.2	1032.3	1034.5	1032.3	1039.2	1045.7	1045.8	1054.0	1060.1	1064.2
10°	987.3	982.2	979.0	981.6	979.0	982.2	987.3	994.2	997.3	1004.7	1012.6
12.5°	938.3	935.1	932.4	931.3	932.4	935.1	938.3	945.5	952.9	961.5	970.2
15°	871.5	865.3	862.6	855.8	862.6	865.3	871.5	877.8	891.9	895.6	908.8
17.5°	809.9	807.9	801.0	798.1	801.0	807.9	809.9	815.3	821.8	835.4	845.2
20°	773.5	771.3	764.6	768.7	764.6	771.3	773.5	781.3	786.6	797.6	807.0
22.5°	743.3	738.6	736.4	735.2	736.4	738.6	743.3	746.9	753.9	764.0	774.7
25°	700.5	693.8	691.2	688.0	691.2	693.8	700.5	702.7	710.0	719.9	725.7
27.5°	658.0	654.3	650.9	650.1	650.9	654.3	658.0	661.0	667.3	676.0	686.4
30°	630.3	626.6	624.0	624.0	624.0	626.6	630.3	636.6	641.3	649.1	657.0
32.5°	605.5	602.7	600.1	599.7	600.1	602.7	605.5	608.9	614.5	623.2	631.5
35°	569.5	565.3	564.2	561.1	564.2	565.3	569.5	572.1	577.8	584.1	591.0
37.5°	532.0	528.6	528.5	528.2	528.5	528.6	532.0	536.6	541.5	547.1	555.5
40°	508.2	505.5	504.9	501.3	504.9	505.5	508.2	510.2	515.4	522.8	529.1
42.5°	482.5	481.2	479.4	477.8	479.4	481.2	482.5	486.8	491.1	496.3	504.3
45°	447.8	444.1	444.1	441.5	444.1	444.1	447.8	451.5	453.6	459.9	470.4
47.5°	411.9	409.1	409.4	406.7	409.4	409.1	411.9	413.1	416.5	422.6	428.4
50°	388.0	386.5	386.0	384.9	386.0	386.5	388.0	387.5	391.7	397.5	405.4
52.5°	364.2	363.3	365.4	363.0	365.4	363.3	364.2	365.3	368.2	371.9	379.3
55°	331.9	330.3	333.5	330.3	333.5	330.3	331.9	330.8	331.9	335.6	340.3
57.5°	294.9	293.5	296.3	294.7	296.3	293.5	294.9	295.1	298.2	298.8	303.0
60°	270.5	267.4	269.0	269.5	269.0	267.4	270.5	271.7	272.7	273.2	277.4
62.5°	241.7	239.7	240.9	238.5	240.9	239.7	241.7	244.0	246.2	248.8	251.4
65°	200.9	199.2	197.1	196.1	197.1	199.2	200.9	201.9	207.6	210.8	216.5
67.5°	168.7	165.0	164.9	165.7	164.9	165.0	168.7	168.5	172.7	175.2	179.2
70°	145.2	145.2	144.7	144.7	144.7	145.2	145.2	148.3	150.5	152.6	155.2
72.5°	128.9	128.5	127.5	127.1	127.5	128.5	128.9	130.0	131.2	133.3	135.9
75°	103.8	104.3	103.3	102.8	103.3	104.3	103.8	103.8	105.9	106.4	107.4
77.5°	76.6	74.4	75.6	74.4	75.6	74.4	76.6	78.8	79.5	81.8	81.9
80°	58.2	57.7	59.3	57.7	59.3	57.7	58.2	58.2	59.8	60.8	63.4
82.5°	46.0	45.5	46.3	45.1	46.3	45.5	46.0	45.6	46.4	47.9	47.5
85°	27.8	27.3	26.8	27.3	26.8	27.3	27.8	27.3	26.8	27.3	27.8
87.5°	16.4	16.2	16.4	16.6	16.4	16.2	16.4	15.8	15.9	15.6	15.1
90°	33.4	34.4	35.4	36.5	35.4	34.4	33.4	32.4	31.1	29.4	27.7
92.5°	32.6	33.1	33.6	34.0	33.6	33.1	32.6	32.1	31.1	29.4	27.7
95°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.1	29.4	27.7
97.5°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	36.7	46.3	55.7
100°	36.0	34.6	33.3	31.9	33.3	34.6	36.0	37.4	63.2	113.5	163.8
102.5°	260.1	237.2	214.2	191.3	214.2	237.2	260.1	283.2	299.4	308.9	318.4
105°	452.5	452.2	451.8	451.5	451.8	452.2	452.5	452.8	453.0	453.0	453.0
107.5°	572.2	571.2	570.2	569.2	570.2	571.2	572.2	573.2	573.7	573.6	573.6
110°	649.6	649.9	650.4	650.7	650.4	649.9	649.6	649.3	649.6	650.7	651.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.1	724.6	724.1	723.6	724.1	724.6	725.1	725.5	726.4	727.7	728.9
115°	839.2	837.1	835.1	833.0	835.1	837.1	839.2	841.2	842.8	844.2	845.6
117.5°	952.5	951.6	950.7	949.8	950.7	951.6	952.5	953.3	954.6	956.4	958.2
120°	1026.6	1024.9	1023.3	1021.6	1023.3	1024.9	1026.6	1028.3	1029.6	1030.2	1030.9
122.5°	1095.6	1093.6	1091.7	1089.6	1091.7	1093.6	1095.6	1097.5	1098.8	1099.5	1100.1
125°	1196.4	1195.4	1194.4	1193.4	1194.4	1195.4	1196.4	1197.4	1198.6	1199.9	1201.3
127.5°	1288.1	1285.7	1283.1	1280.6	1283.1	1285.7	1288.1	1290.6	1292.2	1293.0	1293.7
130°	1349.0	1347.3	1345.5	1343.8	1345.5	1347.3	1349.0	1350.6	1352.0	1353.0	1354.0
132.5°	1407.3	1405.6	1403.9	1402.2	1403.9	1405.6	1407.3	1409.0	1410.0	1410.2	1410.4
135°	1488.2	1486.2	1484.2	1482.2	1484.2	1486.2	1488.2	1490.3	1491.7	1492.4	1493.0
137.5°	1567.7	1566.0	1564.2	1562.5	1564.2	1566.0	1567.7	1569.5	1570.3	1570.1	1570.0
140°	1616.0	1614.0	1611.9	1609.9	1611.9	1614.0	1616.0	1618.0	1618.7	1618.0	1617.3
142.5°	1660.9	1658.9	1656.9	1654.9	1656.9	1658.9	1660.9	1663.0	1664.0	1663.9	1663.7
145°	1727.0	1725.0	1722.9	1720.9	1722.9	1725.0	1727.0	1729.0	1729.8	1729.5	1729.2
147.5°	1782.6	1780.2	1777.8	1775.3	1777.8	1780.2	1782.6	1785.0	1786.0	1785.6	1785.2
150°	1818.7	1815.9	1813.3	1810.6	1813.3	1815.9	1818.7	1821.4	1822.4	1821.7	1821.0
152.5°	1850.7	1848.3	1845.8	1843.4	1845.8	1848.3	1850.7	1853.1	1854.0	1853.3	1852.7
155°	1894.7	1892.0	1889.3	1886.5	1889.3	1892.0	1894.7	1897.3	1898.2	1897.2	1896.2
157.5°	1930.9	1928.1	1925.4	1922.8	1925.4	1928.1	1930.9	1933.6	1934.4	1933.3	1932.2
160°	1954.0	1951.3	1948.5	1945.9	1948.5	1951.3	1954.0	1956.7	1957.3	1956.0	1954.6
162.5°	1975.5	1972.5	1969.5	1966.5	1969.5	1972.5	1975.5	1978.4	1978.9	1977.1	1975.2
165°	2002.7	1999.9	1997.2	1994.5	1997.2	1999.9	2002.7	2005.3	2005.7	2003.7	2001.6
167.5°	2023.1	2020.0	2017.0	2014.0	2017.0	2020.0	2023.1	2026.1	2026.4	2024.0	2021.5
170°	2034.1	2031.0	2027.9	2024.9	2027.9	2031.0	2034.1	2037.1	2037.2	2034.6	2031.8
172.5°	2041.3	2038.3	2035.3	2032.3	2035.3	2038.3	2041.3	2044.4	2044.7	2042.3	2039.8
175°	2050.7	2047.7	2044.7	2041.6	2044.7	2047.7	2050.7	2053.8	2054.0	2051.2	2048.5
177.5°	2053.6	2051.4	2049.2	2047.1	2049.2	2051.4	2053.6	2055.8	2055.9	2054.0	2052.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1224.6	1229.1	1231.6	1237.5	1245.9	1250.1	1256.0	1260.2	1266.1	1273.1	1279.1
5°	1145.2	1157.8	1166.2	1179.3	1191.3	1203.5	1218.6	1229.6	1244.4	1261.1	1274.2
7.5°	1071.6	1087.3	1101.3	1118.6	1138.5	1154.1	1173.9	1194.1	1217.1	1240.9	1263.3
10°	1024.6	1040.4	1057.6	1079.1	1099.0	1120.0	1143.7	1167.2	1196.1	1222.8	1253.2
12.5°	978.1	995.4	1014.9	1038.8	1063.0	1089.8	1113.9	1140.4	1171.3	1206.1	1238.6
15°	920.3	937.1	958.1	978.5	1006.2	1035.6	1067.6	1102.8	1137.4	1176.2	1216.6
17.5°	858.3	876.8	899.8	923.5	952.8	987.1	1018.5	1057.0	1095.9	1141.1	1188.6
20°	818.0	836.9	864.1	890.4	917.2	950.7	988.0	1027.2	1068.6	1116.4	1169.3
22.5°	786.2	799.6	826.4	853.0	884.4	918.8	955.2	996.2	1041.4	1090.8	1146.3
25°	738.8	754.6	774.0	801.7	834.2	870.5	907.2	950.7	1000.0	1050.4	1109.5
27.5°	696.8	709.7	728.9	750.7	783.0	820.6	859.7	905.0	955.6	1006.9	1069.1
30°	667.0	681.2	699.5	722.6	748.3	789.2	829.0	873.6	925.0	978.0	1041.9
32.5°	641.0	655.6	671.4	693.2	721.0	757.3	798.4	842.1	894.3	949.0	1011.3
35°	604.6	614.6	629.2	650.8	678.0	707.4	749.3	795.5	846.4	902.9	965.3
37.5°	562.9	575.7	590.4	609.0	632.9	664.7	703.7	750.3	797.6	851.8	908.8
40°	538.6	550.6	566.8	580.5	605.6	634.5	670.1	718.9	766.1	817.0	868.9
42.5°	513.8	525.4	539.2	556.1	578.8	606.8	640.0	685.4	735.9	783.9	827.4
45°	475.0	487.2	500.3	515.9	536.9	564.2	597.2	638.6	682.8	726.8	759.8
47.5°	438.1	449.4	461.8	477.9	497.3	523.5	553.1	589.7	632.5	669.9	693.6
50°	411.6	422.1	435.8	451.5	470.4	495.0	523.3	559.5	595.1	629.2	650.8
52.5°	385.7	397.4	411.0	424.6	442.7	467.4	493.5	524.7	558.7	586.4	604.2
55°	346.6	357.6	370.2	384.4	402.2	423.1	451.0	475.6	502.3	525.9	536.4
57.5°	308.9	318.6	330.4	345.2	361.2	380.7	402.7	426.5	445.2	462.0	473.8
60°	284.2	292.6	303.6	316.2	333.5	351.3	371.2	393.2	408.0	422.1	433.1
62.5°	259.0	267.0	277.6	288.9	304.2	320.7	339.8	357.6	371.9	381.4	394.2
65°	221.3	229.1	238.0	250.1	262.2	275.8	293.2	306.2	316.2	326.7	334.6
67.5°	186.1	192.7	201.2	210.6	220.8	233.9	247.3	258.2	265.0	271.4	280.7
70°	163.1	168.3	175.1	182.5	193.5	206.6	217.1	225.5	230.2	236.5	248.0
72.5°	139.6	145.6	152.1	159.5	168.3	179.4	188.5	196.9	200.0	205.0	212.4
75°	110.1	113.3	118.6	123.7	130.1	139.5	148.3	150.5	153.1	157.3	162.6
77.5°	83.3	86.1	88.2	91.7	96.6	104.2	109.0	112.1	112.7	114.3	119.5
80°	66.0	67.7	69.8	72.4	74.4	80.8	83.4	86.5	87.6	89.2	91.8
82.5°	48.5	50.0	51.3	53.5	56.9	59.4	62.0	65.1	65.3	66.4	67.1
85°	28.3	28.9	27.8	28.9	29.4	30.4	33.0	35.6	35.1	34.6	36.2
87.5°	15.2	14.9	14.0	14.8	13.5	13.4	12.9	12.8	13.1	13.4	13.7
90°	26.1	24.3	21.9	19.6	17.3	14.8	12.3	9.6	7.0	4.2	1.5
92.5°	26.1	24.3	22.2	20.1	18.1	16.0	15.9	17.8	19.6	21.5	23.4
95°	26.1	24.3	37.2	50.0	62.8	75.6	82.6	83.6	84.6	85.6	86.6
97.5°	65.2	74.8	100.2	125.6	151.0	176.4	188.2	186.4	184.5	182.7	180.9
100°	214.2	264.5	263.2	261.9	260.4	259.1	257.9	256.9	255.9	254.9	253.9
102.5°	328.0	337.5	336.7	335.9	335.1	334.3	333.2	331.9	330.6	329.3	328.1
105°	453.0	453.0	453.0	453.0	453.0	453.0	452.3	451.0	449.7	448.3	447.0
107.5°	573.5	573.4	572.8	572.1	571.4	570.7	570.4	570.4	570.4	570.4	570.4
110°	652.7	653.7	653.0	652.4	651.7	651.0	650.7	650.7	650.7	650.7	650.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.2	731.5	731.1	730.7	730.3	729.9	729.3	728.5	727.7	726.9	726.1
115°	846.9	848.3	848.0	847.6	847.3	846.9	845.9	844.2	842.5	840.8	839.2
117.5°	959.9	961.7	960.4	959.1	957.9	956.5	955.9	956.0	956.0	956.1	956.2
120°	1031.6	1032.2	1031.2	1030.2	1029.2	1028.1	1027.8	1028.1	1028.5	1028.9	1029.2
122.5°	1100.9	1101.6	1101.1	1100.6	1100.1	1099.6	1098.7	1097.5	1096.2	1094.9	1093.7
125°	1202.6	1204.0	1204.0	1204.0	1204.0	1204.0	1202.9	1200.4	1198.1	1195.7	1193.4
127.5°	1294.4	1295.3	1295.5	1295.7	1295.9	1296.1	1295.3	1293.6	1291.9	1290.2	1288.5
130°	1355.0	1356.0	1355.6	1355.3	1355.0	1354.6	1353.6	1352.0	1350.3	1348.6	1346.9
132.5°	1410.6	1410.8	1411.5	1412.2	1413.0	1413.7	1413.1	1411.2	1409.2	1407.2	1405.2
135°	1493.7	1494.4	1495.0	1495.7	1496.4	1497.0	1496.4	1494.4	1492.4	1490.3	1488.2
137.5°	1569.9	1569.7	1570.3	1570.9	1571.6	1572.2	1571.7	1569.8	1568.1	1566.3	1564.6
140°	1616.7	1616.0	1616.3	1616.7	1617.0	1617.3	1617.2	1616.5	1615.8	1615.2	1614.5
142.5°	1663.6	1663.4	1662.9	1662.4	1662.0	1661.5	1661.0	1660.6	1660.2	1659.8	1659.4
145°	1728.8	1728.5	1728.5	1728.5	1728.5	1728.5	1728.2	1727.5	1726.8	1726.1	1725.5
147.5°	1784.8	1784.4	1784.0	1783.6	1783.2	1782.8	1782.6	1782.8	1782.9	1783.0	1783.2
150°	1820.4	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7
152.5°	1852.0	1851.3	1850.7	1850.0	1849.3	1848.6	1849.0	1850.5	1852.0	1853.5	1854.9
155°	1895.2	1894.2	1893.5	1892.8	1892.2	1891.5	1892.2	1894.2	1896.2	1898.2	1900.3
157.5°	1931.2	1930.1	1930.0	1930.0	1929.9	1929.8	1930.4	1931.6	1932.8	1934.0	1935.2
160°	1953.3	1952.0	1951.6	1951.3	1951.0	1950.6	1951.5	1953.5	1955.5	1957.5	1959.5
162.5°	1973.3	1971.4	1971.1	1970.8	1970.3	1970.0	1970.9	1972.9	1975.0	1977.0	1979.0
165°	1999.5	1997.5	1997.2	1996.9	1996.5	1996.2	1997.0	1999.0	2001.0	2003.2	2005.2
167.5°	2019.1	2016.7	2016.4	2016.0	2015.7	2015.4	2016.2	2018.3	2020.4	2022.6	2024.6
170°	2029.1	2026.4	2026.1	2025.8	2025.4	2025.1	2026.1	2028.4	2030.8	2033.2	2035.6
172.5°	2037.4	2035.0	2034.4	2033.8	2033.2	2032.6	2033.4	2035.8	2038.1	2040.5	2042.9
175°	2045.9	2043.2	2042.9	2042.5	2042.1	2041.8	2042.7	2044.7	2046.7	2048.7	2050.7
177.5°	2050.2	2048.3	2048.0	2047.8	2047.5	2047.2	2047.9	2049.5	2051.1	2052.8	2054.4
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1283.6	1287.5	1292.9	1299.2	1304.2	1309.7	1312.6	1312.6	1315.1	1320.6	1327.7
5°	1287.4	1301.0	1314.0	1330.9	1343.9	1359.2	1370.7	1381.7	1391.7	1404.2	1417.3
7.5°	1286.3	1308.9	1332.5	1359.0	1388.2	1411.3	1435.1	1453.8	1472.2	1496.3	1515.3
10°	1282.1	1311.4	1343.4	1377.0	1413.7	1445.7	1474.5	1500.8	1525.9	1552.2	1575.7
12.5°	1274.6	1311.9	1351.0	1391.3	1437.6	1474.2	1511.5	1539.3	1568.7	1597.4	1626.5
15°	1263.2	1307.3	1354.4	1410.6	1467.2	1508.1	1544.8	1580.9	1608.2	1640.7	1668.6
17.5°	1239.8	1296.6	1355.9	1417.2	1471.7	1519.2	1557.7	1592.1	1621.1	1656.9	1694.7
20°	1226.0	1287.4	1349.2	1414.7	1466.6	1515.4	1552.7	1588.3	1624.5	1671.1	1717.3
22.5°	1206.7	1272.2	1337.9	1400.1	1454.9	1502.0	1540.4	1584.2	1631.6	1684.6	1740.4
25°	1176.2	1243.9	1308.8	1368.1	1421.6	1469.9	1522.3	1580.9	1638.7	1708.4	1788.7
27.5°	1137.5	1202.6	1260.7	1323.3	1376.4	1437.8	1503.3	1566.9	1650.1	1746.1	1846.2
30°	1108.5	1170.4	1225.5	1284.8	1345.0	1412.7	1486.1	1561.0	1660.1	1772.9	1892.0
32.5°	1075.0	1130.9	1185.6	1242.7	1312.3	1386.6	1464.7	1556.4	1674.9	1803.1	1926.3
35°	1016.7	1067.1	1120.0	1183.5	1257.5	1338.2	1437.8	1549.5	1692.6	1830.6	1941.3
37.5°	955.7	995.4	1048.6	1115.6	1196.1	1289.5	1402.6	1538.3	1685.4	1809.1	1856.1
40°	908.8	945.9	1002.1	1072.4	1152.1	1254.3	1381.2	1520.7	1668.6	1754.5	1750.9
42.5°	862.1	899.8	953.8	1024.5	1107.6	1222.0	1352.7	1497.6	1622.4	1655.2	1586.9
45°	790.7	825.9	878.9	950.2	1039.4	1159.4	1296.8	1435.7	1515.4	1462.5	1327.2
47.5°	718.0	752.0	801.2	871.1	968.4	1094.1	1224.0	1338.0	1349.2	1235.5	1073.2
50°	670.1	702.2	748.8	823.2	917.7	1040.4	1165.7	1255.4	1227.6	1088.6	921.3
52.5°	623.6	654.3	698.0	768.3	864.7	985.0	1096.9	1167.2	1103.0	955.2	804.7
55°	554.8	584.1	628.2	692.7	780.2	890.4	988.5	1014.1	919.8	770.8	649.1
57.5°	489.5	511.0	554.5	611.5	695.9	793.0	863.3	858.7	754.6	620.5	533.2
60°	446.3	465.6	507.1	559.5	639.7	726.8	776.1	755.1	649.6	539.1	455.1
62.5°	406.0	424.1	458.8	507.1	575.9	651.7	687.5	658.6	559.1	461.9	395.2
65°	345.1	358.1	386.0	430.5	484.5	536.9	569.0	526.4	438.4	365.0	314.6
67.5°	288.1	299.4	324.2	356.2	393.3	429.6	442.5	402.7	334.3	284.8	249.3
70°	251.2	261.7	278.4	308.3	333.0	358.7	365.0	329.3	272.2	234.4	212.4
72.5°	215.9	225.6	240.2	261.4	278.4	293.3	296.2	263.1	219.2	193.3	176.3
75°	164.6	173.1	182.5	190.4	201.4	204.0	202.9	177.2	153.6	136.3	126.9
77.5°	121.0	124.5	130.3	133.4	133.9	133.7	128.4	112.1	100.0	92.8	89.0
80°	93.3	95.9	97.6	98.6	99.1	93.8	88.1	78.2	73.9	69.8	65.0
82.5°	67.8	69.6	71.1	71.3	68.5	64.1	58.8	53.8	50.9	48.8	47.0
85°	36.7	37.3	36.7	34.1	30.4	28.9	27.8	26.8	26.3	25.7	25.7
87.5°	13.8	13.1	11.6	12.5	13.0	13.1	13.5	13.6	13.6	14.0	14.3
90°	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1	27.7
92.5°	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1	27.7
95°	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1	27.7
97.5°	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2	55.7
100°	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2	163.8
102.5°	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0	318.4
105°	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5	573.6
110°	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7	651.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2	728.9
115°	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9	845.6
117.5°	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9	958.2
120°	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6	1030.9
122.5°	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9	1100.1
125°	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6	1201.3
127.5°	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4	1293.7
130°	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0	1354.0
132.5°	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6	1410.4
135°	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7	1493.0
137.5°	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9	1570.0
140°	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7	1617.3
142.5°	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6	1663.7
145°	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8	1729.2
147.5°	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8	1785.2
150°	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4	1821.0
152.5°	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0	1852.7
155°	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2	1896.2
157.5°	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2	1932.2
160°	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3	1954.6
162.5°	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3	1975.2
165°	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5	2001.6
167.5°	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1	2021.5
170°	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1	2031.8
172.5°	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4	2039.8
175°	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9	2048.5
177.5°	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2	2052.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1333.1	1333.1	1340.3	1339.9	1344.5	1342.8	1343.6
5°	1433.1	1442.0	1449.9	1455.1	1463.0	1465.1	1464.0
7.5°	1536.7	1556.5	1566.2	1579.4	1581.9	1588.7	1588.0
10°	1600.9	1620.3	1635.0	1646.5	1652.3	1659.6	1660.1
12.5°	1651.2	1667.7	1680.7	1691.4	1698.4	1700.7	1702.1
15°	1690.6	1708.9	1724.1	1739.3	1748.3	1755.0	1758.8
17.5°	1730.2	1758.6	1785.3	1806.0	1818.5	1828.9	1828.8
20°	1760.8	1793.3	1826.9	1850.5	1874.6	1885.1	1886.7
22.5°	1793.5	1843.3	1886.5	1923.1	1954.8	1965.7	1969.7
25°	1861.5	1926.5	1993.2	2044.6	2081.2	2102.7	2105.9
27.5°	1943.6	2031.6	2101.7	2149.1	2179.6	2195.5	2199.0
30°	2001.6	2082.8	2145.8	2181.4	2195.5	2197.7	2189.8
32.5°	2027.5	2088.3	2113.4	2111.3	2083.6	2065.1	2058.0
35°	1995.8	1983.2	1921.8	1848.5	1792.3	1756.7	1747.2
37.5°	1816.2	1707.7	1594.8	1483.9	1424.8	1394.8	1343.2
40°	1639.2	1484.5	1367.1	1273.7	1207.1	1153.6	1141.0
42.5°	1439.5	1279.8	1162.4	1082.4	1029.3	992.5	976.5
45°	1156.8	1019.4	922.4	861.0	820.1	793.3	781.3
47.5°	925.2	818.9	748.2	702.8	671.7	648.3	641.9
50°	798.1	713.2	653.4	615.1	591.5	573.7	566.3
52.5°	693.2	624.6	578.7	547.1	524.8	513.7	507.6
55°	572.1	512.8	479.8	454.6	442.0	433.1	428.9
57.5°	467.9	425.1	400.9	383.5	371.9	366.2	364.2
60°	409.5	376.0	354.0	340.3	332.4	325.1	323.1
62.5°	357.9	331.5	314.5	302.6	294.7	291.5	290.3
65°	288.4	271.1	258.5	251.2	244.9	243.9	243.3
67.5°	229.2	219.0	212.5	204.8	202.6	198.9	198.2
70°	196.1	189.2	181.5	178.8	176.2	172.5	173.1
72.5°	166.3	159.6	154.2	150.7	149.8	148.1	149.6
75°	121.7	119.6	117.4	114.8	113.8	113.8	113.3
77.5°	86.8	85.0	82.7	81.2	80.9	78.7	79.5
80°	62.9	60.3	59.3	59.8	58.2	57.7	57.7
82.5°	46.6	45.6	44.5	44.6	44.3	43.8	44.2
85°	25.7	25.1	25.1	24.6	24.6	24.1	24.1
87.5°	15.1	15.9	15.2	15.0	15.2	15.9	16.6
90°	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333696-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)