

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333359-935

Luminaire Tested: **S125DIW-S375D1340U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333359-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1340U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5330.5 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	79	76	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	45	40	57	48	41	36	37	33	29	28	24	22	19	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	0.8
10°-20°	134.4	2.5
20°-30°	218.2	4.1
30°-40°	266.1	5.0
40°-50°	242.1	4.5
50°-60°	192.8	3.6
60°-70°	134.3	2.5
70°-80°	71.6	1.3
80°-90°	21.2	0.4
90°-100°	96.1	1.8
100°-110°	283.9	5.3
110°-120°	480.8	9.0
120°-130°	632.7	11.9
130°-140°	709.0	13.3
140°-150°	694.9	13.0
150°-160°	583.6	10.9
160°-170°	388.0	7.3
170°-180°	135.8	2.5
0°-30°	397.6	7.5
0°-40°	663.7	12.5
0°-60°	1098.7	20.6
0°-90°	1325.8	24.9
90°-120°	860.8	16.1
90°-150°	2897.4	54.4
90°-180°	4005.0	75.1
0°-180°	5330.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	27	1	27	1	27	16
95°	96	73	96	73	96	98
105°	277	255	277	255	277	293
115°	486	481	486	481	486	481
125°	707	702	707	702	707	631
135°	917	914	917	914	917	707
145°	1111	1107	1111	1107	1111	694
155°	1266	1266	1266	1266	1266	583
165°	1374	1377	1374	1377	1374	387
175°	1426	1432	1426	1432	1426	136
180°	1435	1435	1435	1435	1435	



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	9.2	9.4	9.4	9.2	9.2	9.0	9.4	9.1	9.4	9.6	9.9
90°	26.8	26.1	25.3	24.5	23.8	22.8	21.6	20.3	19.1	17.9	16.1
92.5°	52.7	52.2	51.7	51.1	50.5	49.4	47.8	46.1	44.5	42.9	40.7
95°	96.1	95.6	95.1	94.5	94.0	93.0	91.2	89.5	87.7	86.0	83.5
97.5°	145.7	145.3	145.1	144.7	144.5	143.4	141.8	140.2	138.5	136.9	133.5
100°	183.1	182.7	182.2	181.7	181.2	179.8	177.5	175.4	173.1	170.9	167.6
102.5°	220.7	220.0	219.3	218.6	217.9	216.4	213.9	211.5	209.1	206.6	205.0
105°	277.0	276.2	275.5	274.7	274.0	272.9	271.4	269.9	268.5	266.9	265.4
107.5°	334.6	334.7	334.7	334.8	334.8	334.5	333.7	332.9	332.3	331.5	330.4
110°	377.5	377.7	378.0	378.2	378.5	378.2	377.5	376.8	376.0	375.2	374.5



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.5	419.9	420.4	420.9	421.3	421.3	420.9	420.6	420.3	419.9	419.0
115°	485.9	486.1	486.3	486.6	486.8	487.1	487.3	487.6	487.8	488.1	487.6
117.5°	550.6	551.6	552.6	553.6	554.6	555.0	554.7	554.6	554.4	554.2	553.7
120°	595.3	596.2	597.3	598.2	599.3	599.8	599.8	599.8	599.8	599.8	599.5
122.5°	640.0	640.8	641.5	642.3	643.2	643.6	643.9	644.0	644.2	644.5	643.8
125°	707.0	707.2	707.5	707.7	708.0	708.3	708.9	709.3	709.8	710.3	710.1
127.5°	771.3	771.8	772.3	772.8	773.3	773.7	773.9	774.1	774.4	774.6	774.4
130°	814.2	814.7	815.2	815.7	816.1	816.6	816.8	817.0	817.3	817.5	817.0
132.5°	854.4	855.1	855.7	856.5	857.2	857.6	857.9	858.2	858.4	858.7	858.8
135°	917.0	917.9	918.9	919.9	920.9	921.4	921.4	921.4	921.4	921.4	921.2
137.5°	978.2	979.4	980.6	981.9	983.1	983.6	983.3	983.0	982.7	982.4	981.9
140°	1017.4	1018.7	1019.9	1021.1	1022.4	1022.8	1022.3	1021.8	1021.3	1020.8	1020.0
142.5°	1055.0	1056.2	1057.5	1058.7	1060.0	1060.4	1060.1	1059.8	1059.5	1059.2	1058.3
145°	1111.3	1112.0	1112.8	1113.5	1114.2	1114.7	1114.7	1114.7	1114.7	1114.7	1113.9
147.5°	1159.3	1161.0	1162.7	1164.3	1166.1	1166.6	1166.0	1165.4	1164.8	1164.2	1163.6
150°	1195.1	1195.5	1196.0	1196.5	1197.0	1197.3	1197.3	1197.3	1197.3	1197.3	1196.3
152.5°	1224.5	1225.4	1226.3	1227.2	1228.1	1228.2	1227.6	1227.0	1226.5	1225.9	1225.5
155°	1266.5	1267.7	1269.0	1270.2	1271.4	1271.6	1270.6	1269.6	1268.6	1267.7	1267.4
157.5°	1301.6	1303.2	1304.8	1306.5	1308.1	1308.5	1307.4	1306.5	1305.4	1304.5	1304.2
160°	1325.7	1327.0	1328.2	1329.5	1330.7	1330.8	1329.8	1328.8	1327.8	1326.8	1326.5
162.5°	1346.3	1347.7	1349.1	1350.6	1352.0	1352.1	1350.9	1349.8	1348.6	1347.4	1347.3
165°	1373.7	1375.2	1376.7	1378.2	1379.7	1379.9	1379.0	1377.9	1377.0	1376.0	1375.7
167.5°	1395.6	1397.1	1398.7	1400.2	1401.8	1401.8	1400.3	1398.9	1397.3	1395.9	1395.9
170°	1407.2	1408.9	1410.7	1412.5	1414.2	1414.3	1412.8	1411.4	1409.9	1408.3	1408.3
172.5°	1417.0	1418.6	1420.1	1421.7	1423.2	1423.2	1421.8	1420.3	1418.8	1417.3	1417.3
175°	1426.2	1428.0	1429.7	1431.4	1433.1	1433.3	1431.8	1430.3	1428.8	1427.4	1427.4
177.5°	1431.6	1433.0	1434.3	1435.7	1437.2	1437.3	1436.1	1434.9	1433.7	1432.4	1432.7
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.9	9.2	8.3	7.4	6.2	5.3	4.7	4.6	4.5	4.6	5.3
90°	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	38.7	36.5	34.4	32.5	31.2	29.8	28.4	27.0	28.4	29.8	31.2
95°	81.0	78.5	76.1	74.6	74.0	73.6	73.1	72.6	73.1	73.6	74.0
97.5°	130.1	126.7	123.2	121.4	121.2	121.1	120.8	120.6	120.8	121.1	121.2
100°	164.5	161.2	158.0	156.4	156.4	156.4	156.4	156.4	156.4	156.4	156.4
102.5°	203.4	201.7	200.1	198.7	197.8	196.7	195.8	194.8	195.8	196.7	197.8
105°	264.0	262.4	261.0	259.6	258.4	257.1	255.9	254.7	255.9	257.1	258.4
107.5°	329.2	328.0	326.9	325.7	324.5	323.2	322.0	320.7	322.0	323.2	324.5
110°	373.8	373.1	372.3	371.3	370.1	368.9	367.6	366.4	367.6	368.9	370.1



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	418.0	417.1	416.2	415.3	414.7	414.1	413.5	412.8	413.5	414.1	414.7
115°	487.1	486.6	486.1	485.3	484.3	483.4	482.3	481.4	482.3	483.4	484.3
117.5°	553.3	552.8	552.4	552.0	551.5	551.0	550.6	550.2	550.6	551.0	551.5
120°	599.3	599.0	598.7	598.1	596.8	595.6	594.3	593.1	594.3	595.6	596.8
122.5°	643.2	642.5	641.9	641.3	640.8	640.4	640.0	639.6	640.0	640.4	640.8
125°	709.8	709.6	709.3	708.4	707.0	705.5	704.0	702.5	704.0	705.5	707.0
127.5°	774.0	773.8	773.4	772.9	772.1	771.2	770.3	769.5	770.3	771.2	772.1
130°	816.6	816.1	815.5	814.7	813.5	812.2	811.0	809.7	811.0	812.2	813.5
132.5°	858.8	858.9	859.0	858.1	856.0	854.0	852.0	849.9	852.0	854.0	856.0
135°	920.9	920.7	920.4	919.5	918.1	916.5	915.1	913.6	915.1	916.5	918.1
137.5°	981.3	980.8	980.2	979.2	977.8	976.4	974.9	973.4	974.9	976.4	977.8
140°	1019.3	1018.6	1017.8	1016.8	1015.6	1014.3	1013.1	1011.8	1013.1	1014.3	1015.6
142.5°	1057.3	1056.4	1055.4	1054.5	1053.4	1052.4	1051.4	1050.3	1051.4	1052.4	1053.4
145°	1113.1	1112.4	1111.6	1110.8	1109.7	1108.8	1107.8	1106.8	1107.8	1108.8	1109.7
147.5°	1163.0	1162.4	1161.8	1161.2	1160.7	1160.2	1159.6	1159.1	1159.6	1160.2	1160.7
150°	1195.3	1194.3	1193.3	1192.9	1193.2	1193.4	1193.7	1193.9	1193.7	1193.4	1193.2
152.5°	1225.0	1224.7	1224.3	1223.9	1223.6	1223.2	1222.9	1222.5	1222.9	1223.2	1223.6
155°	1267.1	1266.9	1266.6	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5
157.5°	1304.0	1303.7	1303.5	1303.6	1304.2	1304.8	1305.3	1305.8	1305.3	1304.8	1304.2
160°	1326.4	1326.1	1325.9	1326.1	1326.8	1327.6	1328.4	1329.0	1328.4	1327.6	1326.8
162.5°	1347.3	1347.2	1347.2	1347.5	1348.0	1348.5	1349.1	1349.6	1349.1	1348.5	1348.0
165°	1375.4	1375.2	1375.0	1375.1	1375.6	1376.1	1376.6	1377.1	1376.6	1376.1	1375.6
167.5°	1395.9	1395.9	1395.9	1396.4	1397.3	1398.4	1399.3	1400.3	1399.3	1398.4	1397.3
170°	1408.3	1408.3	1408.3	1408.9	1409.9	1410.8	1411.9	1412.8	1411.9	1410.8	1409.9
172.5°	1417.3	1417.3	1417.3	1417.8	1418.8	1419.8	1420.7	1421.8	1420.7	1419.8	1418.8
175°	1427.4	1427.4	1427.4	1427.9	1428.8	1429.9	1430.8	1431.8	1430.8	1429.9	1428.8
177.5°	1432.9	1433.0	1433.3	1433.7	1434.6	1435.4	1436.1	1436.9	1436.1	1435.4	1434.6
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.8	6.5	6.6	7.1	7.5	8.2	8.3	9.1	9.7	10.3	10.3
90°	9.0	10.9	12.7	14.4	16.1	17.9	19.1	20.3	21.6	22.8	23.8
92.5°	32.5	34.4	36.5	38.7	40.7	42.9	44.5	46.1	47.8	49.4	50.5
95°	74.6	76.1	78.5	81.0	83.5	86.0	87.7	89.5	91.2	93.0	94.0
97.5°	121.4	123.2	126.7	130.1	133.5	136.9	138.5	140.2	141.8	143.4	144.5
100°	156.4	158.0	161.2	164.5	167.6	170.9	173.1	175.4	177.5	179.8	181.2
102.5°	198.7	200.1	201.7	203.4	205.0	206.6	209.1	211.5	213.9	216.4	217.9
105°	259.6	261.0	262.4	264.0	265.4	266.9	268.5	269.9	271.4	272.9	274.0
107.5°	325.7	326.9	328.0	329.2	330.4	331.5	332.3	332.9	333.7	334.5	334.8
110°	371.3	372.3	373.1	373.8	374.5	375.2	376.0	376.8	377.5	378.2	378.5



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	415.3	416.2	417.1	418.0	419.0	419.9	420.3	420.6	420.9	421.3	421.3
115°	485.3	486.1	486.6	487.1	487.6	488.1	487.8	487.6	487.3	487.1	486.8
117.5°	552.0	552.4	552.8	553.3	553.7	554.2	554.4	554.6	554.7	555.0	554.6
120°	598.1	598.7	599.0	599.3	599.5	599.8	599.8	599.8	599.8	599.8	599.3
122.5°	641.3	641.9	642.5	643.2	643.8	644.5	644.2	644.0	643.9	643.6	643.2
125°	708.4	709.3	709.6	709.8	710.1	710.3	709.8	709.3	708.9	708.3	708.0
127.5°	772.9	773.4	773.8	774.0	774.4	774.6	774.4	774.1	773.9	773.7	773.3
130°	814.7	815.5	816.1	816.6	817.0	817.5	817.3	817.0	816.8	816.6	816.1
132.5°	858.1	859.0	858.9	858.8	858.8	858.7	858.4	858.2	857.9	857.6	857.2
135°	919.5	920.4	920.7	920.9	921.2	921.4	921.4	921.4	921.4	921.4	920.9
137.5°	979.2	980.2	980.8	981.3	981.9	982.4	982.7	983.0	983.3	983.6	983.1
140°	1016.8	1017.8	1018.6	1019.3	1020.0	1020.8	1021.3	1021.8	1022.3	1022.8	1022.4
142.5°	1054.5	1055.4	1056.4	1057.3	1058.3	1059.2	1059.5	1059.8	1060.1	1060.4	1060.0
145°	1110.8	1111.6	1112.4	1113.1	1113.9	1114.7	1114.7	1114.7	1114.7	1114.7	1114.2
147.5°	1161.2	1161.8	1162.4	1163.0	1163.6	1164.2	1164.8	1165.4	1166.0	1166.6	1166.1
150°	1192.9	1193.3	1194.3	1195.3	1196.3	1197.3	1197.3	1197.3	1197.3	1197.3	1197.0
152.5°	1223.9	1224.3	1224.7	1225.0	1225.5	1225.9	1226.5	1227.0	1227.6	1228.2	1228.1
155°	1266.5	1266.6	1266.9	1267.1	1267.4	1267.7	1268.6	1269.6	1270.6	1271.6	1271.4
157.5°	1303.6	1303.5	1303.7	1304.0	1304.2	1304.5	1305.4	1306.5	1307.4	1308.5	1308.1
160°	1326.1	1325.9	1326.1	1326.4	1326.5	1326.8	1327.8	1328.8	1329.8	1330.8	1330.7
162.5°	1347.5	1347.2	1347.2	1347.3	1347.3	1347.4	1348.6	1349.8	1350.9	1352.1	1352.0
165°	1375.1	1375.0	1375.2	1375.4	1375.7	1376.0	1377.0	1377.9	1379.0	1379.9	1379.7
167.5°	1396.4	1395.9	1395.9	1395.9	1395.9	1395.9	1397.3	1398.9	1400.3	1401.8	1401.8
170°	1408.9	1408.3	1408.3	1408.3	1408.3	1408.3	1409.9	1411.4	1412.8	1414.3	1414.2
172.5°	1417.8	1417.3	1417.3	1417.3	1417.3	1417.3	1418.8	1420.3	1421.8	1423.2	1423.2
175°	1427.9	1427.4	1427.4	1427.4	1427.4	1427.4	1428.8	1430.3	1431.8	1433.3	1433.1
177.5°	1433.7	1433.3	1433.0	1432.9	1432.7	1432.4	1433.7	1434.9	1436.1	1437.3	1437.2
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	10.8	10.8	10.9	11.5	10.9	10.8	10.8	10.3	10.3	9.7	9.1
90°	24.5	25.3	26.1	26.8	26.1	25.3	24.5	23.8	22.8	21.6	20.3
92.5°	51.1	51.7	52.2	52.7	52.2	51.7	51.1	50.5	49.4	47.8	46.1
95°	94.5	95.1	95.6	96.1	95.6	95.1	94.5	94.0	93.0	91.2	89.5
97.5°	144.7	145.1	145.3	145.7	145.3	145.1	144.7	144.5	143.4	141.8	140.2
100°	181.7	182.2	182.7	183.1	182.7	182.2	181.7	181.2	179.8	177.5	175.4
102.5°	218.6	219.3	220.0	220.7	220.0	219.3	218.6	217.9	216.4	213.9	211.5
105°	274.7	275.5	276.2	277.0	276.2	275.5	274.7	274.0	272.9	271.4	269.9
107.5°	334.8	334.7	334.7	334.6	334.7	334.7	334.8	334.8	334.5	333.7	332.9
110°	378.2	378.0	377.7	377.5	377.7	378.0	378.2	378.5	378.2	377.5	376.8



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	420.9	420.4	419.9	419.5	419.9	420.4	420.9	421.3	421.3	420.9	420.6
115°	486.6	486.3	486.1	485.9	486.1	486.3	486.6	486.8	487.1	487.3	487.6
117.5°	553.6	552.6	551.6	550.6	551.6	552.6	553.6	554.6	555.0	554.7	554.6
120°	598.2	597.3	596.2	595.3	596.2	597.3	598.2	599.3	599.8	599.8	599.8
122.5°	642.3	641.5	640.8	640.0	640.8	641.5	642.3	643.2	643.6	643.9	644.0
125°	707.7	707.5	707.2	707.0	707.2	707.5	707.7	708.0	708.3	708.9	709.3
127.5°	772.8	772.3	771.8	771.3	771.8	772.3	772.8	773.3	773.7	773.9	774.1
130°	815.7	815.2	814.7	814.2	814.7	815.2	815.7	816.1	816.6	816.8	817.0
132.5°	856.5	855.7	855.1	854.4	855.1	855.7	856.5	857.2	857.6	857.9	858.2
135°	919.9	918.9	917.9	917.0	917.9	918.9	919.9	920.9	921.4	921.4	921.4
137.5°	981.9	980.6	979.4	978.2	979.4	980.6	981.9	983.1	983.6	983.3	983.0
140°	1021.1	1019.9	1018.7	1017.4	1018.7	1019.9	1021.1	1022.4	1022.8	1022.3	1021.8
142.5°	1058.7	1057.5	1056.2	1055.0	1056.2	1057.5	1058.7	1060.0	1060.4	1060.1	1059.8
145°	1113.5	1112.8	1112.0	1111.3	1112.0	1112.8	1113.5	1114.2	1114.7	1114.7	1114.7
147.5°	1164.3	1162.7	1161.0	1159.3	1161.0	1162.7	1164.3	1166.1	1166.6	1166.0	1165.4
150°	1196.5	1196.0	1195.5	1195.1	1195.5	1196.0	1196.5	1197.0	1197.3	1197.3	1197.3
152.5°	1227.2	1226.3	1225.4	1224.5	1225.4	1226.3	1227.2	1228.1	1228.2	1227.6	1227.0
155°	1270.2	1269.0	1267.7	1266.5	1267.7	1269.0	1270.2	1271.4	1271.6	1270.6	1269.6
157.5°	1306.5	1304.8	1303.2	1301.6	1303.2	1304.8	1306.5	1308.1	1308.5	1307.4	1306.5
160°	1329.5	1328.2	1327.0	1325.7	1327.0	1328.2	1329.5	1330.7	1330.8	1329.8	1328.8
162.5°	1350.6	1349.1	1347.7	1346.3	1347.7	1349.1	1350.6	1352.0	1352.1	1350.9	1349.8
165°	1378.2	1376.7	1375.2	1373.7	1375.2	1376.7	1378.2	1379.7	1379.9	1379.0	1377.9
167.5°	1400.2	1398.7	1397.1	1395.6	1397.1	1398.7	1400.2	1401.8	1401.8	1400.3	1398.9
170°	1412.5	1410.7	1408.9	1407.2	1408.9	1410.7	1412.5	1414.2	1414.3	1412.8	1411.4
172.5°	1421.7	1420.1	1418.6	1417.0	1418.6	1420.1	1421.7	1423.2	1423.2	1421.8	1420.3
175°	1431.4	1429.7	1428.0	1426.2	1428.0	1429.7	1431.4	1433.1	1433.3	1431.8	1430.3
177.5°	1435.7	1434.3	1433.0	1431.6	1433.0	1434.3	1435.7	1437.2	1437.3	1436.1	1434.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	8.3	8.2	7.5	7.1	6.6	6.5	5.8	5.3	4.6	4.5	4.6
90°	19.1	17.9	16.1	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1
92.5°	44.5	42.9	40.7	38.7	36.5	34.4	32.5	31.2	29.8	28.4	27.0
95°	87.7	86.0	83.5	81.0	78.5	76.1	74.6	74.0	73.6	73.1	72.6
97.5°	138.5	136.9	133.5	130.1	126.7	123.2	121.4	121.2	121.1	120.8	120.6
100°	173.1	170.9	167.6	164.5	161.2	158.0	156.4	156.4	156.4	156.4	156.4
102.5°	209.1	206.6	205.0	203.4	201.7	200.1	198.7	197.8	196.7	195.8	194.8
105°	268.5	266.9	265.4	264.0	262.4	261.0	259.6	258.4	257.1	255.9	254.7
107.5°	332.3	331.5	330.4	329.2	328.0	326.9	325.7	324.5	323.2	322.0	320.7
110°	376.0	375.2	374.5	373.8	373.1	372.3	371.3	370.1	368.9	367.6	366.4



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	420.3	419.9	419.0	418.0	417.1	416.2	415.3	414.7	414.1	413.5	412.8
115°	487.8	488.1	487.6	487.1	486.6	486.1	485.3	484.3	483.4	482.3	481.4
117.5°	554.4	554.2	553.7	553.3	552.8	552.4	552.0	551.5	551.0	550.6	550.2
120°	599.8	599.8	599.5	599.3	599.0	598.7	598.1	596.8	595.6	594.3	593.1
122.5°	644.2	644.5	643.8	643.2	642.5	641.9	641.3	640.8	640.4	640.0	639.6
125°	709.8	710.3	710.1	709.8	709.6	709.3	708.4	707.0	705.5	704.0	702.5
127.5°	774.4	774.6	774.4	774.0	773.8	773.4	772.9	772.1	771.2	770.3	769.5
130°	817.3	817.5	817.0	816.6	816.1	815.5	814.7	813.5	812.2	811.0	809.7
132.5°	858.4	858.7	858.8	858.8	858.9	859.0	858.1	856.0	854.0	852.0	849.9
135°	921.4	921.4	921.2	920.9	920.7	920.4	919.5	918.1	916.5	915.1	913.6
137.5°	982.7	982.4	981.9	981.3	980.8	980.2	979.2	977.8	976.4	974.9	973.4
140°	1021.3	1020.8	1020.0	1019.3	1018.6	1017.8	1016.8	1015.6	1014.3	1013.1	1011.8
142.5°	1059.5	1059.2	1058.3	1057.3	1056.4	1055.4	1054.5	1053.4	1052.4	1051.4	1050.3
145°	1114.7	1114.7	1113.9	1113.1	1112.4	1111.6	1110.8	1109.7	1108.8	1107.8	1106.8
147.5°	1164.8	1164.2	1163.6	1163.0	1162.4	1161.8	1161.2	1160.7	1160.2	1159.6	1159.1
150°	1197.3	1197.3	1196.3	1195.3	1194.3	1193.3	1192.9	1193.2	1193.4	1193.7	1193.9
152.5°	1226.5	1225.9	1225.5	1225.0	1224.7	1224.3	1223.9	1223.6	1223.2	1222.9	1222.5
155°	1268.6	1267.7	1267.4	1267.1	1266.9	1266.6	1266.5	1266.5	1266.5	1266.5	1266.5
157.5°	1305.4	1304.5	1304.2	1304.0	1303.7	1303.5	1303.6	1304.2	1304.8	1305.3	1305.8
160°	1327.8	1326.8	1326.5	1326.4	1326.1	1325.9	1326.1	1326.8	1327.6	1328.4	1329.0
162.5°	1348.6	1347.4	1347.3	1347.3	1347.2	1347.2	1347.5	1348.0	1348.5	1349.1	1349.6
165°	1377.0	1376.0	1375.7	1375.4	1375.2	1375.0	1375.1	1375.6	1376.1	1376.6	1377.1
167.5°	1397.3	1395.9	1395.9	1395.9	1395.9	1395.9	1396.4	1397.3	1398.4	1399.3	1400.3
170°	1409.9	1408.3	1408.3	1408.3	1408.3	1408.3	1408.9	1409.9	1410.8	1411.9	1412.8
172.5°	1418.8	1417.3	1417.3	1417.3	1417.3	1417.3	1417.8	1418.8	1419.8	1420.7	1421.8
175°	1428.8	1427.4	1427.4	1427.4	1427.4	1427.4	1427.9	1428.8	1429.9	1430.8	1431.8
177.5°	1433.7	1432.4	1432.7	1432.9	1433.0	1433.3	1433.7	1434.6	1435.4	1436.1	1436.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.7	5.3	6.2	7.4	8.3	9.2	9.9	9.9	9.6	9.4	9.1
90°	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.9	19.1	20.3
92.5°	28.4	29.8	31.2	32.5	34.4	36.5	38.7	40.7	42.9	44.5	46.1
95°	73.1	73.6	74.0	74.6	76.1	78.5	81.0	83.5	86.0	87.7	89.5
97.5°	120.8	121.1	121.2	121.4	123.2	126.7	130.1	133.5	136.9	138.5	140.2
100°	156.4	156.4	156.4	156.4	158.0	161.2	164.5	167.6	170.9	173.1	175.4
102.5°	195.8	196.7	197.8	198.7	200.1	201.7	203.4	205.0	206.6	209.1	211.5
105°	255.9	257.1	258.4	259.6	261.0	262.4	264.0	265.4	266.9	268.5	269.9
107.5°	322.0	323.2	324.5	325.7	326.9	328.0	329.2	330.4	331.5	332.3	332.9
110°	367.6	368.9	370.1	371.3	372.3	373.1	373.8	374.5	375.2	376.0	376.8



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	413.5	414.1	414.7	415.3	416.2	417.1	418.0	419.0	419.9	420.3	420.6
115°	482.3	483.4	484.3	485.3	486.1	486.6	487.1	487.6	488.1	487.8	487.6
117.5°	550.6	551.0	551.5	552.0	552.4	552.8	553.3	553.7	554.2	554.4	554.6
120°	594.3	595.6	596.8	598.1	598.7	599.0	599.3	599.5	599.8	599.8	599.8
122.5°	640.0	640.4	640.8	641.3	641.9	642.5	643.2	643.8	644.5	644.2	644.0
125°	704.0	705.5	707.0	708.4	709.3	709.6	709.8	710.1	710.3	709.8	709.3
127.5°	770.3	771.2	772.1	772.9	773.4	773.8	774.0	774.4	774.6	774.4	774.1
130°	811.0	812.2	813.5	814.7	815.5	816.1	816.6	817.0	817.5	817.3	817.0
132.5°	852.0	854.0	856.0	858.1	859.0	858.9	858.8	858.8	858.7	858.4	858.2
135°	915.1	916.5	918.1	919.5	920.4	920.7	920.9	921.2	921.4	921.4	921.4
137.5°	974.9	976.4	977.8	979.2	980.2	980.8	981.3	981.9	982.4	982.7	983.0
140°	1013.1	1014.3	1015.6	1016.8	1017.8	1018.6	1019.3	1020.0	1020.8	1021.3	1021.8
142.5°	1051.4	1052.4	1053.4	1054.5	1055.4	1056.4	1057.3	1058.3	1059.2	1059.5	1059.8
145°	1107.8	1108.8	1109.7	1110.8	1111.6	1112.4	1113.1	1113.9	1114.7	1114.7	1114.7
147.5°	1159.6	1160.2	1160.7	1161.2	1161.8	1162.4	1163.0	1163.6	1164.2	1164.8	1165.4
150°	1193.7	1193.4	1193.2	1192.9	1193.3	1194.3	1195.3	1196.3	1197.3	1197.3	1197.3
152.5°	1222.9	1223.2	1223.6	1223.9	1224.3	1224.7	1225.0	1225.5	1225.9	1226.5	1227.0
155°	1266.5	1266.5	1266.5	1266.5	1266.6	1266.9	1267.1	1267.4	1267.7	1268.6	1269.6
157.5°	1305.3	1304.8	1304.2	1303.6	1303.5	1303.7	1304.0	1304.2	1304.5	1305.4	1306.5
160°	1328.4	1327.6	1326.8	1326.1	1325.9	1326.1	1326.4	1326.5	1326.8	1327.8	1328.8
162.5°	1349.1	1348.5	1348.0	1347.5	1347.2	1347.2	1347.3	1347.3	1347.4	1348.6	1349.8
165°	1376.6	1376.1	1375.6	1375.1	1375.0	1375.2	1375.4	1375.7	1376.0	1377.0	1377.9
167.5°	1399.3	1398.4	1397.3	1396.4	1395.9	1395.9	1395.9	1395.9	1395.9	1397.3	1398.9
170°	1411.9	1410.8	1409.9	1408.9	1408.3	1408.3	1408.3	1408.3	1408.3	1409.9	1411.4
172.5°	1420.7	1419.8	1418.8	1417.8	1417.3	1417.3	1417.3	1417.3	1417.3	1418.8	1420.3
175°	1430.8	1429.9	1428.8	1427.9	1427.4	1427.4	1427.4	1427.4	1427.4	1428.8	1430.3
177.5°	1436.1	1435.4	1434.6	1433.7	1433.3	1433.0	1432.9	1432.7	1432.4	1433.7	1434.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	9.4	9.0	9.2	9.2	9.4	9.4	9.2
90°	21.6	22.8	23.8	24.5	25.3	26.1	26.8
92.5°	47.8	49.4	50.5	51.1	51.7	52.2	52.7
95°	91.2	93.0	94.0	94.5	95.1	95.6	96.1
97.5°	141.8	143.4	144.5	144.7	145.1	145.3	145.7
100°	177.5	179.8	181.2	181.7	182.2	182.7	183.1
102.5°	213.9	216.4	217.9	218.6	219.3	220.0	220.7
105°	271.4	272.9	274.0	274.7	275.5	276.2	277.0
107.5°	333.7	334.5	334.8	334.8	334.7	334.7	334.6
110°	377.5	378.2	378.5	378.2	378.0	377.7	377.5



TEST NUMBER: P333359-935

CATALOG NUMBER: S125DIW-S375D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	420.9	421.3	421.3	420.9	420.4	419.9	419.5
115°	487.3	487.1	486.8	486.6	486.3	486.1	485.9
117.5°	554.7	555.0	554.6	553.6	552.6	551.6	550.6
120°	599.8	599.8	599.3	598.2	597.3	596.2	595.3
122.5°	643.9	643.6	643.2	642.3	641.5	640.8	640.0
125°	708.9	708.3	708.0	707.7	707.5	707.2	707.0
127.5°	773.9	773.7	773.3	772.8	772.3	771.8	771.3
130°	816.8	816.6	816.1	815.7	815.2	814.7	814.2
132.5°	857.9	857.6	857.2	856.5	855.7	855.1	854.4
135°	921.4	921.4	920.9	919.9	918.9	917.9	917.0
137.5°	983.3	983.6	983.1	981.9	980.6	979.4	978.2
140°	1022.3	1022.8	1022.4	1021.1	1019.9	1018.7	1017.4
142.5°	1060.1	1060.4	1060.0	1058.7	1057.5	1056.2	1055.0
145°	1114.7	1114.7	1114.2	1113.5	1112.8	1112.0	1111.3
147.5°	1166.0	1166.6	1166.1	1164.3	1162.7	1161.0	1159.3
150°	1197.3	1197.3	1197.0	1196.5	1196.0	1195.5	1195.1
152.5°	1227.6	1228.2	1228.1	1227.2	1226.3	1225.4	1224.5
155°	1270.6	1271.6	1271.4	1270.2	1269.0	1267.7	1266.5
157.5°	1307.4	1308.5	1308.1	1306.5	1304.8	1303.2	1301.6
160°	1329.8	1330.8	1330.7	1329.5	1328.2	1327.0	1325.7
162.5°	1350.9	1352.1	1352.0	1350.6	1349.1	1347.7	1346.3
165°	1379.0	1379.9	1379.7	1378.2	1376.7	1375.2	1373.7
167.5°	1400.3	1401.8	1401.8	1400.2	1398.7	1397.1	1395.6
170°	1412.8	1414.3	1414.2	1412.5	1410.7	1408.9	1407.2
172.5°	1421.8	1423.2	1423.2	1421.7	1420.1	1418.6	1417.0
175°	1431.8	1433.3	1433.1	1431.4	1429.7	1428.0	1426.2
177.5°	1436.1	1437.3	1437.2	1435.7	1434.3	1433.0	1431.6
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2

(END OF REPORT)