

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333448-940

Luminaire Tested: **S125DIW-S1090D1340U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333448-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1340U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8787.3 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	64	59	74	66	60	55	55	51	47	46	42	39	36	34	32	28
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	43	62	52	45	40	44	39	35	37	33	29	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.6
10°-20°	406.4	4.6
20°-30°	660.0	7.5
30°-40°	805.0	9.2
40°-50°	732.3	8.3
50°-60°	583.3	6.6
60°-70°	406.3	4.6
70°-80°	216.7	2.5
80°-90°	57.9	0.7
90°-100°	56.6	0.6
100°-110°	348.8	4.0
110°-120°	632.6	7.2
120°-130°	811.9	9.2
130°-140°	873.3	9.9
140°-150°	819.7	9.3
150°-160°	663.1	7.5
160°-170°	428.8	4.9
170°-180°	147.9	1.7
0°-30°	1202.9	13.7
0°-40°	2008.0	22.9
0°-60°	3323.6	37.8
0°-90°	4004.5	45.6
90°-120°	1038.1	11.8
90°-150°	3542.9	40.3
90°-180°	4783.0	54.4
0°-180°	8787.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	47
90°	28	1	28	1	28	13
95°	24	66	24	66	24	20
105°	343	340	343	340	343	310
115°	633	637	633	637	633	628
125°	906	906	906	906	906	806
135°	1126	1130	1126	1130	1126	869
145°	1307	1310	1307	1310	1307	816
155°	1433	1443	1433	1443	1433	660
165°	1515	1523	1515	1523	1515	427
175°	1550	1558	1550	1558	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	17.1	17.9	18.2	18.1	18.4	18.2	19.9	19.6	20.8	22.0	23.5
90°	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0	19.8	18.5	16.7
92.5°	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0	19.8	18.5	16.9
95°	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0	19.8	18.5	28.2
97.5°	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4	49.6	56.8	76.1
100°	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4	162.6	200.9	199.8
102.5°	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8	249.1	256.3	255.7
105°	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6	435.5	435.5	435.0
110°	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9	495.7	496.4	496.0



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6	554.6	555.5	555.3
115°	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2	643.2	644.3	644.0
117.5°	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7	729.1	730.4	729.4
120°	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9	783.5	783.9	783.2
122.5°	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5	836.1	836.6	836.2
125°	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3	913.4	914.4	914.4
127.5°	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6	983.1	983.6	983.8
130°	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3	1029.1	1029.8	1029.6
132.5°	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1	1071.3	1071.4	1072.0
135°	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9	1134.4	1134.9	1135.4
137.5°	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4	1192.3	1192.2	1192.7
140°	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3	1227.8	1227.3	1227.5
142.5°	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5	1263.4	1263.3	1262.9
145°	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2	1313.0	1312.7	1312.7
147.5°	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8	1355.5	1355.2	1354.9
150°	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0	1382.5	1382.0	1381.4
152.5°	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0	1406.5	1406.0	1405.5
155°	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1	1439.3	1438.6	1438.1
157.5°	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5	1466.6	1465.8	1465.8
160°	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5	1483.5	1482.5	1482.2
162.5°	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0	1498.6	1497.2	1496.9
165°	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1	1518.6	1517.1	1516.8
167.5°	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3	1533.5	1531.6	1531.3
170°	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1	1541.1	1539.0	1538.7
172.5°	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2	1547.3	1545.4	1545.0
175°	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8	1553.7	1551.7	1551.5
177.5°	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5	1557.1	1555.6	1555.4
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	24.2	22.8	20.6	18.7	15.9	14.1	13.2	13.2	12.2	12.1	13.0
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7	16.3	14.9	13.5
95°	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8	65.0	64.3	63.5
97.5°	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4	138.8	140.2	141.5
100°	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8	193.6	194.3	195.1
102.5°	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1	250.1	251.1	252.1
105°	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5	340.5	341.5	342.5
107.5°	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2	433.2	433.2	433.2
110°	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4	552.1	552.7	553.2
115°	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3	638.6	639.9	641.1
117.5°	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2	726.1	726.1	726.0
120°	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6	781.4	781.1	780.9
122.5°	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5	831.5	832.5	833.5
125°	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3	908.1	909.9	911.7
127.5°	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6	979.9	981.1	982.4
130°	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9	1024.2	1025.5	1026.8
132.5°	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3	1068.7	1070.2	1071.7
135°	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3	1131.8	1133.4	1134.9
137.5°	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3	1189.5	1190.9	1192.2
140°	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1	1226.6	1227.2	1227.6
142.5°	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3	1260.6	1260.9	1261.2
145°	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4	1310.9	1311.4	1312.0
147.5°	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2	1354.2	1354.1	1354.0
150°	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1381.4	1381.0	1380.5
152.5°	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7	1407.7	1406.5	1405.4
155°	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1	1441.6	1440.1	1438.6
157.5°	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7	1468.8	1467.8	1467.0
160°	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2	1486.7	1485.1	1483.5
162.5°	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0	1501.5	1499.9	1498.3
165°	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9	1521.3	1519.7	1518.2
167.5°	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6	1536.1	1534.5	1532.9
170°	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0	1544.2	1542.3	1540.5
172.5°	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5	1549.7	1547.9	1546.0
175°	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5	1555.9	1554.4	1552.8
177.5°	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2	1559.0	1557.8	1556.6
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	13.9	15.2	15.2	16.0	16.3	17.7	17.4	19.6	20.9	22.0	21.8
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.3	23.6	24.6
92.5°	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0	22.3	23.6	24.4
95°	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0	22.3	23.6	24.3
97.5°	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4	35.1	27.8	24.3
100°	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4	86.2	48.0	28.4
102.5°	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8	234.6	227.4	215.0
105°	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	343.9
107.5°	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6	435.7	435.7	435.3
110°	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9	494.2	493.4	493.1



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6	552.7	551.7	551.0
115°	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2	641.1	640.2	638.8
117.5°	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7	726.4	725.1	724.0
120°	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9	782.4	781.9	781.0
122.5°	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5	835.0	834.6	833.5
125°	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3	911.3	910.3	909.4
127.5°	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6	982.0	981.4	980.2
130°	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3	1027.5	1026.8	1025.7
132.5°	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1	1070.9	1070.8	1070.1
135°	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9	1133.4	1132.8	1131.8
137.5°	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4	1192.5	1192.6	1191.9
140°	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3	1228.8	1229.3	1228.8
142.5°	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5	1263.6	1263.7	1263.0
145°	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2	1313.5	1313.8	1313.1
147.5°	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8	1356.1	1356.5	1355.7
150°	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0	1383.5	1384.0	1383.2
152.5°	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0	1407.6	1408.0	1407.4
155°	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1	1440.8	1441.6	1441.0
157.5°	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5	1468.3	1469.1	1468.5
160°	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5	1485.5	1486.6	1486.0
162.5°	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0	1501.6	1503.0	1502.5
165°	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1	1521.7	1523.2	1523.0
167.5°	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3	1537.1	1539.0	1538.7
170°	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1	1545.2	1547.2	1547.1
172.5°	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2	1551.0	1552.8	1552.6
175°	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8	1557.8	1559.9	1559.8
177.5°	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5	1560.0	1561.4	1561.3
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	22.9	22.6	22.7	23.8	22.7	22.6	22.9	21.8	22.0	20.9	19.6
90°	25.4	26.1	26.9	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0
92.5°	24.8	25.1	25.5	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0
95°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0
97.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4
100°	27.3	26.3	25.2	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4
102.5°	197.6	180.1	162.6	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8
105°	343.7	343.4	343.1	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0
107.5°	434.5	433.8	433.0	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6
110°	493.4	493.7	493.9	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	550.6	550.3	549.9	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6
115°	637.3	635.8	634.2	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2
117.5°	723.4	722.7	722.0	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7
120°	779.7	778.4	777.1	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9
122.5°	832.1	830.5	829.0	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5
125°	908.7	907.9	907.0	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3
127.5°	978.3	976.4	974.5	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6
130°	1024.5	1023.1	1021.9	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3
132.5°	1068.8	1067.6	1066.2	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1
135°	1130.3	1128.7	1127.2	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9
137.5°	1190.6	1189.3	1187.9	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4
140°	1227.3	1225.7	1224.2	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3
142.5°	1261.4	1259.9	1258.4	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5
145°	1311.5	1310.0	1308.5	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2
147.5°	1353.8	1351.9	1350.1	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8
150°	1381.2	1379.1	1377.1	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0
152.5°	1405.5	1403.7	1401.9	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0
155°	1439.0	1436.9	1434.9	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1
157.5°	1466.4	1464.4	1462.3	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5
160°	1484.0	1481.9	1479.9	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5
162.5°	1500.3	1498.0	1495.8	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0
165°	1520.9	1518.9	1516.8	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1
167.5°	1536.4	1534.2	1531.9	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3
170°	1544.8	1542.5	1540.2	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1
172.5°	1550.3	1548.0	1545.7	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2
175°	1557.5	1555.1	1552.8	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8
177.5°	1559.6	1558.0	1556.3	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	17.4	17.7	16.3	16.0	15.2	15.2	13.9	13.0	12.1	12.2	13.2
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	19.8	18.5	16.9	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7
95°	19.8	18.5	28.2	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8
97.5°	49.6	56.8	76.1	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4
100°	162.6	200.9	199.8	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8
102.5°	249.1	256.3	255.7	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1
105°	344.0	344.0	344.0	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5
107.5°	435.5	435.5	435.0	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2
110°	495.7	496.4	496.0	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	554.6	555.5	555.3	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4
115°	643.2	644.3	644.0	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3
117.5°	729.1	730.4	729.4	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2
120°	783.5	783.9	783.2	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6
122.5°	836.1	836.6	836.2	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5
125°	913.4	914.4	914.4	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3
127.5°	983.1	983.6	983.8	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6
130°	1029.1	1029.8	1029.6	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9
132.5°	1071.3	1071.4	1072.0	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3
135°	1134.4	1134.9	1135.4	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3
137.5°	1192.3	1192.2	1192.7	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3
140°	1227.8	1227.3	1227.5	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1
142.5°	1263.4	1263.3	1262.9	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3
145°	1313.0	1312.7	1312.7	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4
147.5°	1355.5	1355.2	1354.9	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2
150°	1382.5	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0
152.5°	1406.5	1406.0	1405.5	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7
155°	1439.3	1438.6	1438.1	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1
157.5°	1466.6	1465.8	1465.8	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7
160°	1483.5	1482.5	1482.2	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2
162.5°	1498.6	1497.2	1496.9	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0
165°	1518.6	1517.1	1516.8	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9
167.5°	1533.5	1531.6	1531.3	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6
170°	1541.1	1539.0	1538.7	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0
172.5°	1547.3	1545.4	1545.0	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5
175°	1553.7	1551.7	1551.5	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5
177.5°	1557.1	1555.6	1555.4	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	13.2	14.1	15.9	18.7	20.6	22.8	24.2	23.5	22.0	20.8	19.6
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0
95°	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0
97.5°	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4
100°	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4
102.5°	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8
105°	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6
110°	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6
115°	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2
117.5°	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7
120°	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9
122.5°	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5
125°	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3
127.5°	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6
130°	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3
132.5°	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1
135°	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9
137.5°	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4
140°	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3
142.5°	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5
145°	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2
147.5°	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8
150°	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0
152.5°	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0
155°	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1
157.5°	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5
160°	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5
162.5°	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0
165°	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1
167.5°	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3
170°	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1
172.5°	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2
175°	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8
177.5°	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	19.9	18.2	18.4	18.1	18.2	17.9	17.1
90°	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333448-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)