

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333454-940

Luminaire Tested: **S125DIW-S1090D1560U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333454-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1560U940-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9565.8 lumens  
Efficiency: N/A  
Efficacy: 124.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																												
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36																												
2	88	80	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30																												
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26																												
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22																												
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19																												
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17																												
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																												
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.5	1.4
10°-20°	406.4	4.2
20°-30°	660.0	6.9
30°-40°	805.0	8.4
40°-50°	732.3	7.7
50°-60°	583.3	6.1
60°-70°	406.3	4.2
70°-80°	216.7	2.3
80°-90°	58.4	0.6
90°-100°	65.8	0.7
100°-110°	405.6	4.2
110°-120°	735.5	7.7
120°-130°	944.0	9.9
130°-140°	1015.3	10.6
140°-150°	953.0	10.0
150°-160°	770.9	8.1
160°-170°	498.6	5.2
170°-180°	172.0	1.8
0°-30°	1202.9	12.6
0°-40°	2008.0	21.0
0°-60°	3323.6	34.7
0°-90°	4005.0	41.9
90°-120°	1206.9	12.6
90°-150°	4119.2	43.1
90°-180°	5561.0	58.1
0°-180°	9565.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	47
90°	32	1	32	1	32	15
95°	28	76	28	76	28	23
105°	399	395	399	395	399	360
115°	736	741	736	741	736	730
125°	1054	1054	1054	1054	1054	937
135°	1309	1314	1309	1314	1309	1010
145°	1520	1524	1520	1524	1520	949
155°	1666	1678	1666	1678	1666	768
165°	1761	1771	1761	1771	1761	497
175°	1803	1811	1803	1811	1803	172
180°	1811	1811	1811	1811	1811	



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	18.0	18.8	19.1	18.9	19.2	19.0	20.6	20.3	21.5	22.6	24.1
90°	32.2	31.3	30.4	29.5	28.6	27.5	25.9	24.4	23.0	21.5	19.4
92.5°	30.1	29.7	29.2	28.8	28.4	27.5	25.9	24.4	23.0	21.5	19.6
95°	28.2	28.2	28.2	28.2	28.2	27.5	25.9	24.4	23.0	21.5	32.8
97.5°	28.2	28.2	28.2	28.2	28.2	32.4	40.8	49.2	57.6	66.1	88.5
100°	28.2	29.4	30.6	31.7	33.0	55.8	100.2	144.6	189.1	233.5	232.4
102.5°	168.9	189.1	209.5	229.7	250.0	264.4	272.8	281.2	289.6	298.0	297.3
105°	398.7	399.0	399.3	399.6	399.8	400.0	400.0	400.0	400.0	400.0	400.0
107.5°	502.6	503.5	504.4	505.2	506.1	506.6	506.5	506.5	506.4	506.3	505.8
110°	574.5	574.3	573.9	573.6	573.4	573.6	574.5	575.4	576.3	577.2	576.6



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	638.9	639.4	639.8	640.2	640.6	641.4	642.6	643.6	644.8	646.0	645.6
115°	735.6	737.4	739.1	741.0	742.8	744.2	745.5	746.6	747.8	749.0	748.8
117.5°	838.7	839.5	840.3	841.1	841.8	842.9	844.5	846.1	847.6	849.2	848.0
120°	902.1	903.6	905.0	906.5	908.0	909.1	909.6	910.3	910.9	911.4	910.5
122.5°	962.2	963.9	965.6	967.4	969.1	970.3	970.9	971.4	972.1	972.7	972.2
125°	1053.7	1054.6	1055.5	1056.4	1057.3	1058.4	1059.5	1060.8	1061.9	1063.1	1063.1
127.5°	1130.8	1133.0	1135.2	1137.4	1139.6	1141.0	1141.7	1142.4	1143.0	1143.7	1143.9
130°	1186.6	1188.1	1189.6	1191.1	1192.6	1193.8	1194.7	1195.6	1196.5	1197.4	1197.0
132.5°	1238.1	1239.7	1241.2	1242.7	1244.1	1245.0	1245.2	1245.4	1245.5	1245.7	1246.3
135°	1308.8	1310.5	1312.3	1314.1	1315.9	1317.1	1317.8	1318.3	1318.9	1319.6	1320.1
137.5°	1379.7	1381.2	1382.8	1384.3	1385.9	1386.6	1386.4	1386.3	1386.3	1386.1	1386.6
140°	1421.6	1423.3	1425.1	1426.9	1428.7	1429.3	1428.7	1428.1	1427.5	1426.9	1427.2
142.5°	1461.2	1463.0	1464.8	1466.6	1468.5	1469.3	1469.2	1469.0	1468.9	1468.8	1468.4
145°	1519.6	1521.3	1523.1	1524.9	1526.7	1527.4	1527.1	1526.9	1526.5	1526.3	1526.3
147.5°	1567.6	1569.8	1571.9	1574.0	1576.2	1577.1	1576.7	1576.4	1576.0	1575.7	1575.3
150°	1598.7	1601.2	1603.5	1605.9	1608.3	1609.2	1608.6	1607.9	1607.4	1606.8	1606.1
152.5°	1627.7	1629.9	1632.0	1634.1	1636.3	1637.1	1636.5	1635.9	1635.3	1634.7	1634.1
155°	1665.8	1668.2	1670.6	1673.0	1675.3	1676.1	1675.3	1674.4	1673.5	1672.6	1672.0
157.5°	1697.8	1700.1	1702.5	1705.0	1707.4	1708.1	1707.1	1706.1	1705.2	1704.2	1704.1
160°	1718.2	1720.6	1723.0	1725.4	1727.8	1728.3	1727.2	1725.9	1724.7	1723.6	1723.2
162.5°	1736.4	1739.1	1741.7	1744.4	1747.0	1747.4	1745.8	1744.1	1742.4	1740.7	1740.4
165°	1761.1	1763.5	1765.9	1768.4	1770.7	1771.0	1769.2	1767.4	1765.6	1763.8	1763.5
167.5°	1778.3	1781.0	1783.7	1786.4	1789.0	1789.3	1787.2	1785.0	1782.9	1780.7	1780.5
170°	1788.0	1790.6	1793.4	1796.1	1798.8	1798.8	1796.5	1794.1	1791.7	1789.3	1789.0
172.5°	1794.5	1797.2	1799.8	1802.5	1805.2	1805.4	1803.3	1801.2	1799.0	1796.9	1796.4
175°	1802.8	1805.4	1808.1	1810.8	1813.5	1813.7	1811.2	1808.8	1806.5	1804.1	1803.8
177.5°	1807.6	1809.5	1811.4	1813.3	1815.3	1815.3	1813.7	1812.0	1810.4	1808.7	1808.4
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	24.6	23.3	21.0	19.0	16.1	14.3	13.3	13.3	12.3	12.3	13.3
90°	17.3	15.2	13.1	10.9	8.5	6.2	3.7	1.3	3.7	6.2	8.5
92.5°	17.7	16.0	14.1	14.0	15.7	17.3	19.0	20.7	19.0	17.3	15.7
95°	44.1	55.5	66.8	72.9	73.8	74.7	75.6	76.5	75.6	74.7	73.8
97.5°	110.9	133.3	155.8	166.2	164.6	162.9	161.3	159.7	161.3	162.9	164.6
100°	231.2	230.0	228.8	227.7	226.9	226.0	225.1	224.2	225.1	226.0	226.9
102.5°	296.6	295.9	295.2	294.2	293.1	291.9	290.8	289.7	290.8	291.9	293.1
105°	400.0	400.0	400.0	399.4	398.2	397.1	395.8	394.7	395.8	397.1	398.2
107.5°	505.2	504.5	503.9	503.6	503.6	503.6	503.6	503.6	503.6	503.6	503.6
110°	576.0	575.4	574.8	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5





TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	645.2	644.9	644.5	644.0	643.3	642.6	641.9	641.1	641.9	642.6	643.3
115°	748.4	748.1	747.8	746.9	745.5	744.0	742.4	741.0	742.4	744.0	745.5
117.5°	846.9	845.8	844.6	844.1	844.2	844.2	844.3	844.4	844.3	844.2	844.2
120°	909.6	908.7	907.9	907.6	907.9	908.2	908.5	908.7	908.5	908.2	907.9
122.5°	971.8	971.4	971.0	970.2	969.1	968.0	966.8	965.7	966.8	968.0	969.1
125°	1063.1	1063.1	1063.1	1062.1	1060.0	1057.9	1055.8	1053.7	1055.8	1057.9	1060.0
127.5°	1144.1	1144.2	1144.4	1143.7	1142.3	1140.8	1139.2	1137.7	1139.2	1140.8	1142.3
130°	1196.8	1196.5	1196.1	1195.2	1193.8	1192.3	1190.8	1189.3	1190.8	1192.3	1193.8
132.5°	1247.0	1247.7	1248.3	1247.8	1246.1	1244.3	1242.6	1240.8	1242.6	1244.3	1246.1
135°	1320.7	1321.3	1321.9	1321.3	1319.6	1317.8	1315.9	1314.1	1315.9	1317.8	1319.6
137.5°	1387.1	1387.7	1388.2	1387.8	1386.2	1384.6	1383.0	1381.5	1383.0	1384.6	1386.2
140°	1427.5	1427.8	1428.1	1428.0	1427.4	1426.7	1426.2	1425.6	1426.2	1426.7	1427.4
142.5°	1467.9	1467.6	1467.1	1466.7	1466.3	1466.0	1465.6	1465.3	1465.6	1466.0	1466.3
145°	1526.3	1526.3	1526.3	1526.0	1525.4	1524.7	1524.1	1523.6	1524.1	1524.7	1525.4
147.5°	1574.9	1574.6	1574.2	1574.0	1574.2	1574.3	1574.4	1574.6	1574.4	1574.3	1574.2
150°	1605.6	1605.0	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8	1606.1	1605.6	1605.0
152.5°	1633.5	1632.9	1632.3	1632.6	1634.0	1635.3	1636.6	1637.9	1636.6	1635.3	1634.0
155°	1671.3	1670.8	1670.2	1670.8	1672.6	1674.4	1676.1	1677.9	1676.1	1674.4	1672.6
157.5°	1704.1	1704.1	1704.0	1704.5	1705.6	1706.6	1707.7	1708.8	1707.7	1706.6	1705.6
160°	1723.0	1722.7	1722.3	1723.1	1724.9	1726.7	1728.5	1730.3	1728.5	1726.7	1724.9
162.5°	1740.2	1739.8	1739.5	1740.3	1742.0	1743.9	1745.7	1747.5	1745.7	1743.9	1742.0
165°	1763.3	1762.9	1762.6	1763.4	1765.1	1766.9	1768.8	1770.6	1768.8	1766.9	1765.1
167.5°	1780.1	1779.9	1779.6	1780.3	1782.2	1784.0	1785.9	1787.7	1785.9	1784.0	1782.2
170°	1788.8	1788.4	1788.1	1789.0	1791.1	1793.2	1795.3	1797.4	1795.3	1793.2	1791.1
172.5°	1795.8	1795.3	1794.7	1795.5	1797.6	1799.7	1801.8	1803.8	1801.8	1799.7	1797.6
175°	1803.5	1803.2	1803.0	1803.7	1805.4	1807.2	1809.0	1810.8	1809.0	1807.2	1805.4
177.5°	1808.2	1807.9	1807.7	1808.3	1809.7	1811.2	1812.6	1814.0	1812.6	1811.2	1809.7
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	14.2	15.6	15.6	16.5	16.9	18.3	18.1	20.3	21.6	22.8	22.6
90°	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.4	25.9	27.5	28.6
92.5°	14.0	14.1	16.0	17.7	19.6	21.5	23.0	24.4	25.9	27.5	28.4
95°	72.9	66.8	55.5	44.1	32.8	21.5	23.0	24.4	25.9	27.5	28.2
97.5°	166.2	155.8	133.3	110.9	88.5	66.1	57.6	49.2	40.8	32.4	28.2
100°	227.7	228.8	230.0	231.2	232.4	233.5	189.1	144.6	100.2	55.8	33.0
102.5°	294.2	295.2	295.9	296.6	297.3	298.0	289.6	281.2	272.8	264.4	250.0
105°	399.4	400.0	400.0	400.0	400.0	400.0	400.0	400.0	400.0	400.0	399.8
107.5°	503.6	503.9	504.5	505.2	505.8	506.3	506.4	506.5	506.5	506.6	506.1
110°	574.5	574.8	575.4	576.0	576.6	577.2	576.3	575.4	574.5	573.6	573.4



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	644.0	644.5	644.9	645.2	645.6	646.0	644.8	643.6	642.6	641.4	640.6
115°	746.9	747.8	748.1	748.4	748.8	749.0	747.8	746.6	745.5	744.2	742.8
117.5°	844.1	844.6	845.8	846.9	848.0	849.2	847.6	846.1	844.5	842.9	841.8
120°	907.6	907.9	908.7	909.6	910.5	911.4	910.9	910.3	909.6	909.1	908.0
122.5°	970.2	971.0	971.4	971.8	972.2	972.7	972.1	971.4	970.9	970.3	969.1
125°	1062.1	1063.1	1063.1	1063.1	1063.1	1063.1	1061.9	1060.8	1059.5	1058.4	1057.3
127.5°	1143.7	1144.4	1144.2	1144.1	1143.9	1143.7	1143.0	1142.4	1141.7	1141.0	1139.6
130°	1195.2	1196.1	1196.5	1196.8	1197.0	1197.4	1196.5	1195.6	1194.7	1193.8	1192.6
132.5°	1247.8	1248.3	1247.7	1247.0	1246.3	1245.7	1245.5	1245.4	1245.2	1245.0	1244.1
135°	1321.3	1321.9	1321.3	1320.7	1320.1	1319.6	1318.9	1318.3	1317.8	1317.1	1315.9
137.5°	1387.8	1388.2	1387.7	1387.1	1386.6	1386.1	1386.3	1386.3	1386.4	1386.6	1385.9
140°	1428.0	1428.1	1427.8	1427.5	1427.2	1426.9	1427.5	1428.1	1428.7	1429.3	1428.7
142.5°	1466.7	1467.1	1467.6	1467.9	1468.4	1468.8	1468.9	1469.0	1469.2	1469.3	1468.5
145°	1526.0	1526.3	1526.3	1526.3	1526.3	1526.3	1526.5	1526.9	1527.1	1527.4	1526.7
147.5°	1574.0	1574.2	1574.6	1574.9	1575.3	1575.7	1576.0	1576.4	1576.7	1577.1	1576.2
150°	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8	1607.4	1607.9	1608.6	1609.2	1608.3
152.5°	1632.6	1632.3	1632.9	1633.5	1634.1	1634.7	1635.3	1635.9	1636.5	1637.1	1636.3
155°	1670.8	1670.2	1670.8	1671.3	1672.0	1672.6	1673.5	1674.4	1675.3	1676.1	1675.3
157.5°	1704.5	1704.0	1704.1	1704.1	1704.1	1704.2	1705.2	1706.1	1707.1	1708.1	1707.4
160°	1723.1	1722.3	1722.7	1723.0	1723.2	1723.6	1724.7	1725.9	1727.2	1728.3	1727.8
162.5°	1740.3	1739.5	1739.8	1740.2	1740.4	1740.7	1742.4	1744.1	1745.8	1747.4	1747.0
165°	1763.4	1762.6	1762.9	1763.3	1763.5	1763.8	1765.6	1767.4	1769.2	1771.0	1770.7
167.5°	1780.3	1779.6	1779.9	1780.1	1780.5	1780.7	1782.9	1785.0	1787.2	1789.3	1789.0
170°	1789.0	1788.1	1788.4	1788.8	1789.0	1789.3	1791.7	1794.1	1796.5	1798.8	1798.8
172.5°	1795.5	1794.7	1795.3	1795.8	1796.4	1796.9	1799.0	1801.2	1803.3	1805.4	1805.2
175°	1803.7	1803.0	1803.2	1803.5	1803.8	1804.1	1806.5	1808.8	1811.2	1813.7	1813.5
177.5°	1808.3	1807.7	1807.9	1808.2	1808.4	1808.7	1810.4	1812.0	1813.7	1815.3	1815.3
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	23.7	23.5	23.6	24.7	23.6	23.5	23.7	22.6	22.8	21.6	20.3
90°	29.5	30.4	31.3	32.2	31.3	30.4	29.5	28.6	27.5	25.9	24.4
92.5°	28.8	29.2	29.7	30.1	29.7	29.2	28.8	28.4	27.5	25.9	24.4
95°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	27.5	25.9	24.4
97.5°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	32.4	40.8	49.2
100°	31.7	30.6	29.4	28.2	29.4	30.6	31.7	33.0	55.8	100.2	144.6
102.5°	229.7	209.5	189.1	168.9	189.1	209.5	229.7	250.0	264.4	272.8	281.2
105°	399.6	399.3	399.0	398.7	399.0	399.3	399.6	399.8	400.0	400.0	400.0
107.5°	505.2	504.4	503.5	502.6	503.5	504.4	505.2	506.1	506.6	506.5	506.5
110°	573.6	573.9	574.3	574.5	574.3	573.9	573.6	573.4	573.6	574.5	575.4



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	640.2	639.8	639.4	638.9	639.4	639.8	640.2	640.6	641.4	642.6	643.6
115°	741.0	739.1	737.4	735.6	737.4	739.1	741.0	742.8	744.2	745.5	746.6
117.5°	841.1	840.3	839.5	838.7	839.5	840.3	841.1	841.8	842.9	844.5	846.1
120°	906.5	905.0	903.6	902.1	903.6	905.0	906.5	908.0	909.1	909.6	910.3
122.5°	967.4	965.6	963.9	962.2	963.9	965.6	967.4	969.1	970.3	970.9	971.4
125°	1056.4	1055.5	1054.6	1053.7	1054.6	1055.5	1056.4	1057.3	1058.4	1059.5	1060.8
127.5°	1137.4	1135.2	1133.0	1130.8	1133.0	1135.2	1137.4	1139.6	1141.0	1141.7	1142.4
130°	1191.1	1189.6	1188.1	1186.6	1188.1	1189.6	1191.1	1192.6	1193.8	1194.7	1195.6
132.5°	1242.7	1241.2	1239.7	1238.1	1239.7	1241.2	1242.7	1244.1	1245.0	1245.2	1245.4
135°	1314.1	1312.3	1310.5	1308.8	1310.5	1312.3	1314.1	1315.9	1317.1	1317.8	1318.3
137.5°	1384.3	1382.8	1381.2	1379.7	1381.2	1382.8	1384.3	1385.9	1386.6	1386.4	1386.3
140°	1426.9	1425.1	1423.3	1421.6	1423.3	1425.1	1426.9	1428.7	1429.3	1428.7	1428.1
142.5°	1466.6	1464.8	1463.0	1461.2	1463.0	1464.8	1466.6	1468.5	1469.3	1469.2	1469.0
145°	1524.9	1523.1	1521.3	1519.6	1521.3	1523.1	1524.9	1526.7	1527.4	1527.1	1526.9
147.5°	1574.0	1571.9	1569.8	1567.6	1569.8	1571.9	1574.0	1576.2	1577.1	1576.7	1576.4
150°	1605.9	1603.5	1601.2	1598.7	1601.2	1603.5	1605.9	1608.3	1609.2	1608.6	1607.9
152.5°	1634.1	1632.0	1629.9	1627.7	1629.9	1632.0	1634.1	1636.3	1637.1	1636.5	1635.9
155°	1673.0	1670.6	1668.2	1665.8	1668.2	1670.6	1673.0	1675.3	1676.1	1675.3	1674.4
157.5°	1705.0	1702.5	1700.1	1697.8	1700.1	1702.5	1705.0	1707.4	1708.1	1707.1	1706.1
160°	1725.4	1723.0	1720.6	1718.2	1720.6	1723.0	1725.4	1727.8	1728.3	1727.2	1725.9
162.5°	1744.4	1741.7	1739.1	1736.4	1739.1	1741.7	1744.4	1747.0	1747.4	1745.8	1744.1
165°	1768.4	1765.9	1763.5	1761.1	1763.5	1765.9	1768.4	1770.7	1771.0	1769.2	1767.4
167.5°	1786.4	1783.7	1781.0	1778.3	1781.0	1783.7	1786.4	1789.0	1789.3	1787.2	1785.0
170°	1796.1	1793.4	1790.6	1788.0	1790.6	1793.4	1796.1	1798.8	1798.8	1796.5	1794.1
172.5°	1802.5	1799.8	1797.2	1794.5	1797.2	1799.8	1802.5	1805.2	1805.4	1803.3	1801.2
175°	1810.8	1808.1	1805.4	1802.8	1805.4	1808.1	1810.8	1813.5	1813.7	1811.2	1808.8
177.5°	1813.3	1811.4	1809.5	1807.6	1809.5	1811.4	1813.3	1815.3	1815.3	1813.7	1812.0
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	18.1	18.3	16.9	16.5	15.6	15.6	14.2	13.3	12.3	12.3	13.3
90°	23.0	21.5	19.4	17.3	15.2	13.1	10.9	8.5	6.2	3.7	1.3
92.5°	23.0	21.5	19.6	17.7	16.0	14.1	14.0	15.7	17.3	19.0	20.7
95°	23.0	21.5	32.8	44.1	55.5	66.8	72.9	73.8	74.7	75.6	76.5
97.5°	57.6	66.1	88.5	110.9	133.3	155.8	166.2	164.6	162.9	161.3	159.7
100°	189.1	233.5	232.4	231.2	230.0	228.8	227.7	226.9	226.0	225.1	224.2
102.5°	289.6	298.0	297.3	296.6	295.9	295.2	294.2	293.1	291.9	290.8	289.7
105°	400.0	400.0	400.0	400.0	400.0	400.0	399.4	398.2	397.1	395.8	394.7
107.5°	506.4	506.3	505.8	505.2	504.5	503.9	503.6	503.6	503.6	503.6	503.6
110°	576.3	577.2	576.6	576.0	575.4	574.8	574.5	574.5	574.5	574.5	574.5



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	644.8	646.0	645.6	645.2	644.9	644.5	644.0	643.3	642.6	641.9	641.1
115°	747.8	749.0	748.8	748.4	748.1	747.8	746.9	745.5	744.0	742.4	741.0
117.5°	847.6	849.2	848.0	846.9	845.8	844.6	844.1	844.2	844.2	844.3	844.4
120°	910.9	911.4	910.5	909.6	908.7	907.9	907.6	907.9	908.2	908.5	908.7
122.5°	972.1	972.7	972.2	971.8	971.4	971.0	970.2	969.1	968.0	966.8	965.7
125°	1061.9	1063.1	1063.1	1063.1	1063.1	1063.1	1062.1	1060.0	1057.9	1055.8	1053.7
127.5°	1143.0	1143.7	1143.9	1144.1	1144.2	1144.4	1143.7	1142.3	1140.8	1139.2	1137.7
130°	1196.5	1197.4	1197.0	1196.8	1196.5	1196.1	1195.2	1193.8	1192.3	1190.8	1189.3
132.5°	1245.5	1245.7	1246.3	1247.0	1247.7	1248.3	1247.8	1246.1	1244.3	1242.6	1240.8
135°	1318.9	1319.6	1320.1	1320.7	1321.3	1321.9	1321.3	1319.6	1317.8	1315.9	1314.1
137.5°	1386.3	1386.1	1386.6	1387.1	1387.7	1388.2	1387.8	1386.2	1384.6	1383.0	1381.5
140°	1427.5	1426.9	1427.2	1427.5	1427.8	1428.1	1428.0	1427.4	1426.7	1426.2	1425.6
142.5°	1468.9	1468.8	1468.4	1467.9	1467.6	1467.1	1466.7	1466.3	1466.0	1465.6	1465.3
145°	1526.5	1526.3	1526.3	1526.3	1526.3	1526.3	1526.0	1525.4	1524.7	1524.1	1523.6
147.5°	1576.0	1575.7	1575.3	1574.9	1574.6	1574.2	1574.0	1574.2	1574.3	1574.4	1574.6
150°	1607.4	1606.8	1606.1	1605.6	1605.0	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8
152.5°	1635.3	1634.7	1634.1	1633.5	1632.9	1632.3	1632.6	1634.0	1635.3	1636.6	1637.9
155°	1673.5	1672.6	1672.0	1671.3	1670.8	1670.2	1670.8	1672.6	1674.4	1676.1	1677.9
157.5°	1705.2	1704.2	1704.1	1704.1	1704.1	1704.0	1704.5	1705.6	1706.6	1707.7	1708.8
160°	1724.7	1723.6	1723.2	1723.0	1722.7	1722.3	1723.1	1724.9	1726.7	1728.5	1730.3
162.5°	1742.4	1740.7	1740.4	1740.2	1739.8	1739.5	1740.3	1742.0	1743.9	1745.7	1747.5
165°	1765.6	1763.8	1763.5	1763.3	1762.9	1762.6	1763.4	1765.1	1766.9	1768.8	1770.6
167.5°	1782.9	1780.7	1780.5	1780.1	1779.9	1779.6	1780.3	1782.2	1784.0	1785.9	1787.7
170°	1791.7	1789.3	1789.0	1788.8	1788.4	1788.1	1789.0	1791.1	1793.2	1795.3	1797.4
172.5°	1799.0	1796.9	1796.4	1795.8	1795.3	1794.7	1795.5	1797.6	1799.7	1801.8	1803.8
175°	1806.5	1804.1	1803.8	1803.5	1803.2	1803.0	1803.7	1805.4	1807.2	1809.0	1810.8
177.5°	1810.4	1808.7	1808.4	1808.2	1807.9	1807.7	1808.3	1809.7	1811.2	1812.6	1814.0
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	13.3	14.3	16.1	19.0	21.0	23.3	24.6	24.1	22.6	21.5	20.3
90°	3.7	6.2	8.5	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.4
92.5°	19.0	17.3	15.7	14.0	14.1	16.0	17.7	19.6	21.5	23.0	24.4
95°	75.6	74.7	73.8	72.9	66.8	55.5	44.1	32.8	21.5	23.0	24.4
97.5°	161.3	162.9	164.6	166.2	155.8	133.3	110.9	88.5	66.1	57.6	49.2
100°	225.1	226.0	226.9	227.7	228.8	230.0	231.2	232.4	233.5	189.1	144.6
102.5°	290.8	291.9	293.1	294.2	295.2	295.9	296.6	297.3	298.0	289.6	281.2
105°	395.8	397.1	398.2	399.4	400.0	400.0	400.0	400.0	400.0	400.0	400.0
107.5°	503.6	503.6	503.6	503.6	503.9	504.5	505.2	505.8	506.3	506.4	506.5
110°	574.5	574.5	574.5	574.5	574.8	575.4	576.0	576.6	577.2	576.3	575.4





TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	641.9	642.6	643.3	644.0	644.5	644.9	645.2	645.6	646.0	644.8	643.6
115°	742.4	744.0	745.5	746.9	747.8	748.1	748.4	748.8	749.0	747.8	746.6
117.5°	844.3	844.2	844.2	844.1	844.6	845.8	846.9	848.0	849.2	847.6	846.1
120°	908.5	908.2	907.9	907.6	907.9	908.7	909.6	910.5	911.4	910.9	910.3
122.5°	966.8	968.0	969.1	970.2	971.0	971.4	971.8	972.2	972.7	972.1	971.4
125°	1055.8	1057.9	1060.0	1062.1	1063.1	1063.1	1063.1	1063.1	1063.1	1061.9	1060.8
127.5°	1139.2	1140.8	1142.3	1143.7	1144.4	1144.2	1144.1	1143.9	1143.7	1143.0	1142.4
130°	1190.8	1192.3	1193.8	1195.2	1196.1	1196.5	1196.8	1197.0	1197.4	1196.5	1195.6
132.5°	1242.6	1244.3	1246.1	1247.8	1248.3	1247.7	1247.0	1246.3	1245.7	1245.5	1245.4
135°	1315.9	1317.8	1319.6	1321.3	1321.9	1321.3	1320.7	1320.1	1319.6	1318.9	1318.3
137.5°	1383.0	1384.6	1386.2	1387.8	1388.2	1387.7	1387.1	1386.6	1386.1	1386.3	1386.3
140°	1426.2	1426.7	1427.4	1428.0	1428.1	1427.8	1427.5	1427.2	1426.9	1427.5	1428.1
142.5°	1465.6	1466.0	1466.3	1466.7	1467.1	1467.6	1467.9	1468.4	1468.8	1468.9	1469.0
145°	1524.1	1524.7	1525.4	1526.0	1526.3	1526.3	1526.3	1526.3	1526.3	1526.5	1526.9
147.5°	1574.4	1574.3	1574.2	1574.0	1574.2	1574.6	1574.9	1575.3	1575.7	1576.0	1576.4
150°	1606.1	1605.6	1605.0	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8	1607.4	1607.9
152.5°	1636.6	1635.3	1634.0	1632.6	1632.3	1632.9	1633.5	1634.1	1634.7	1635.3	1635.9
155°	1676.1	1674.4	1672.6	1670.8	1670.2	1670.8	1671.3	1672.0	1672.6	1673.5	1674.4
157.5°	1707.7	1706.6	1705.6	1704.5	1704.0	1704.1	1704.1	1704.1	1704.2	1705.2	1706.1
160°	1728.5	1726.7	1724.9	1723.1	1722.3	1722.7	1723.0	1723.2	1723.6	1724.7	1725.9
162.5°	1745.7	1743.9	1742.0	1740.3	1739.5	1739.8	1740.2	1740.4	1740.7	1742.4	1744.1
165°	1768.8	1766.9	1765.1	1763.4	1762.6	1762.9	1763.3	1763.5	1763.8	1765.6	1767.4
167.5°	1785.9	1784.0	1782.2	1780.3	1779.6	1779.9	1780.1	1780.5	1780.7	1782.9	1785.0
170°	1795.3	1793.2	1791.1	1789.0	1788.1	1788.4	1788.8	1789.0	1789.3	1791.7	1794.1
172.5°	1801.8	1799.7	1797.6	1795.5	1794.7	1795.3	1795.8	1796.4	1796.9	1799.0	1801.2
175°	1809.0	1807.2	1805.4	1803.7	1803.0	1803.2	1803.5	1803.8	1804.1	1806.5	1808.8
177.5°	1812.6	1811.2	1809.7	1808.3	1807.7	1807.9	1808.2	1808.4	1808.7	1810.4	1812.0
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	20.6	19.0	19.2	18.9	19.1	18.8	18.0
90°	25.9	27.5	28.6	29.5	30.4	31.3	32.2
92.5°	25.9	27.5	28.4	28.8	29.2	29.7	30.1
95°	25.9	27.5	28.2	28.2	28.2	28.2	28.2
97.5°	40.8	32.4	28.2	28.2	28.2	28.2	28.2
100°	100.2	55.8	33.0	31.7	30.6	29.4	28.2
102.5°	272.8	264.4	250.0	229.7	209.5	189.1	168.9
105°	400.0	400.0	399.8	399.6	399.3	399.0	398.7
107.5°	506.5	506.6	506.1	505.2	504.4	503.5	502.6
110°	574.5	573.6	573.4	573.6	573.9	574.3	574.5



TEST NUMBER: P333454-940

CATALOG NUMBER: S125DIW-S1090D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	642.6	641.4	640.6	640.2	639.8	639.4	638.9
115°	745.5	744.2	742.8	741.0	739.1	737.4	735.6
117.5°	844.5	842.9	841.8	841.1	840.3	839.5	838.7
120°	909.6	909.1	908.0	906.5	905.0	903.6	902.1
122.5°	970.9	970.3	969.1	967.4	965.6	963.9	962.2
125°	1059.5	1058.4	1057.3	1056.4	1055.5	1054.6	1053.7
127.5°	1141.7	1141.0	1139.6	1137.4	1135.2	1133.0	1130.8
130°	1194.7	1193.8	1192.6	1191.1	1189.6	1188.1	1186.6
132.5°	1245.2	1245.0	1244.1	1242.7	1241.2	1239.7	1238.1
135°	1317.8	1317.1	1315.9	1314.1	1312.3	1310.5	1308.8
137.5°	1386.4	1386.6	1385.9	1384.3	1382.8	1381.2	1379.7
140°	1428.7	1429.3	1428.7	1426.9	1425.1	1423.3	1421.6
142.5°	1469.2	1469.3	1468.5	1466.6	1464.8	1463.0	1461.2
145°	1527.1	1527.4	1526.7	1524.9	1523.1	1521.3	1519.6
147.5°	1576.7	1577.1	1576.2	1574.0	1571.9	1569.8	1567.6
150°	1608.6	1609.2	1608.3	1605.9	1603.5	1601.2	1598.7
152.5°	1636.5	1637.1	1636.3	1634.1	1632.0	1629.9	1627.7
155°	1675.3	1676.1	1675.3	1673.0	1670.6	1668.2	1665.8
157.5°	1707.1	1708.1	1707.4	1705.0	1702.5	1700.1	1697.8
160°	1727.2	1728.3	1727.8	1725.4	1723.0	1720.6	1718.2
162.5°	1745.8	1747.4	1747.0	1744.4	1741.7	1739.1	1736.4
165°	1769.2	1771.0	1770.7	1768.4	1765.9	1763.5	1761.1
167.5°	1787.2	1789.3	1789.0	1786.4	1783.7	1781.0	1778.3
170°	1796.5	1798.8	1798.8	1796.1	1793.4	1790.6	1788.0
172.5°	1803.3	1805.4	1805.2	1802.5	1799.8	1797.2	1794.5
175°	1811.2	1813.7	1813.5	1810.8	1808.1	1805.4	1802.8
177.5°	1813.7	1815.3	1815.3	1813.3	1811.4	1809.5	1807.6
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8

(END OF REPORT)