

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333393-935

Luminaire Tested: **S125DIW-S610D1340U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333393-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6159.5 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.3
10°-20°	220.2	3.6
20°-30°	325.2	5.3
30°-40°	379.4	6.2
40°-50°	381.1	6.2
50°-60°	334.5	5.4
60°-70°	249.3	4.0
70°-80°	142.5	2.3
80°-90°	44.6	0.7
90°-100°	96.1	1.6
100°-110°	283.9	4.6
110°-120°	480.8	7.8
120°-130°	632.7	10.3
130°-140°	709.0	11.5
140°-150°	694.9	11.3
150°-160°	583.6	9.5
160°-170°	388.0	6.3
170°-180°	135.8	2.2
0°-30°	623.4	10.1
0°-40°	1002.8	16.3
0°-60°	1718.4	27.9
0°-90°	2154.8	35.0
90°-120°	860.8	14.0
90°-150°	2897.4	47.0
90°-180°	4005.0	65.0
0°-180°	6159.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	10	18	23	27	6
95°	73	75	86	94	96	77
105°	255	260	267	273	277	272
115°	481	486	488	487	486	476
125°	702	709	710	708	707	629
135°	914	920	921	921	917	704
145°	1107	1111	1115	1114	1111	692
155°	1266	1267	1268	1272	1266	583
165°	1377	1375	1376	1380	1374	388
175°	1432	1428	1427	1433	1426	136
180°	1435	1435	1435	1435	1435	



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.4	14.7	15.2	15.6	15.9	16.3	16.4	16.7	17.0	17.2	17.4
90°	1.1	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.9	19.1
92.5°	27.0	28.4	29.8	31.2	32.5	34.4	36.5	38.7	40.7	42.9	44.5
95°	72.6	73.1	73.6	74.0	74.6	76.1	78.5	81.0	83.5	86.0	87.7
97.5°	120.6	120.8	121.1	121.2	121.4	123.2	126.7	130.1	133.5	136.9	138.5
100°	156.4	156.4	156.4	156.4	156.4	158.0	161.2	164.5	167.6	170.9	173.1
102.5°	194.8	195.8	196.7	197.8	198.7	200.1	201.7	203.4	205.0	206.6	209.1
105°	254.7	255.9	257.1	258.4	259.6	261.0	262.4	264.0	265.4	266.9	268.5
107.5°	320.7	322.0	323.2	324.5	325.7	326.9	328.0	329.2	330.4	331.5	332.3
110°	366.4	367.6	368.9	370.1	371.3	372.3	373.1	373.8	374.5	375.2	376.0



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	412.8	413.5	414.1	414.7	415.3	416.2	417.1	418.0	419.0	419.9	420.3
115°	481.4	482.3	483.4	484.3	485.3	486.1	486.6	487.1	487.6	488.1	487.8
117.5°	550.2	550.6	551.0	551.5	552.0	552.4	552.8	553.3	553.7	554.2	554.4
120°	593.1	594.3	595.6	596.8	598.1	598.7	599.0	599.3	599.5	599.8	599.8
122.5°	639.6	640.0	640.4	640.8	641.3	641.9	642.5	643.2	643.8	644.5	644.2
125°	702.5	704.0	705.5	707.0	708.4	709.3	709.6	709.8	710.1	710.3	709.8
127.5°	769.5	770.3	771.2	772.1	772.9	773.4	773.8	774.0	774.4	774.6	774.4
130°	809.7	811.0	812.2	813.5	814.7	815.5	816.1	816.6	817.0	817.5	817.3
132.5°	849.9	852.0	854.0	856.0	858.1	859.0	858.9	858.8	858.8	858.7	858.4
135°	913.6	915.1	916.5	918.1	919.5	920.4	920.7	920.9	921.2	921.4	921.4
137.5°	973.4	974.9	976.4	977.8	979.2	980.2	980.8	981.3	981.9	982.4	982.7
140°	1011.8	1013.1	1014.3	1015.6	1016.8	1017.8	1018.6	1019.3	1020.0	1020.8	1021.3
142.5°	1050.3	1051.4	1052.4	1053.4	1054.5	1055.4	1056.4	1057.3	1058.3	1059.2	1059.5
145°	1106.8	1107.8	1108.8	1109.7	1110.8	1111.6	1112.4	1113.1	1113.9	1114.7	1114.7
147.5°	1159.1	1159.6	1160.2	1160.7	1161.2	1161.8	1162.4	1163.0	1163.6	1164.2	1164.8
150°	1193.9	1193.7	1193.4	1193.2	1192.9	1193.3	1194.3	1195.3	1196.3	1197.3	1197.3
152.5°	1222.5	1222.9	1223.2	1223.6	1223.9	1224.3	1224.7	1225.0	1225.5	1225.9	1226.5
155°	1266.5	1266.5	1266.5	1266.5	1266.5	1266.6	1266.9	1267.1	1267.4	1267.7	1268.6
157.5°	1305.8	1305.3	1304.8	1304.2	1303.6	1303.5	1303.7	1304.0	1304.2	1304.5	1305.4
160°	1329.0	1328.4	1327.6	1326.8	1326.1	1325.9	1326.1	1326.4	1326.5	1326.8	1327.8
162.5°	1349.6	1349.1	1348.5	1348.0	1347.5	1347.2	1347.2	1347.3	1347.3	1347.4	1348.6
165°	1377.1	1376.6	1376.1	1375.6	1375.1	1375.0	1375.2	1375.4	1375.7	1376.0	1377.0
167.5°	1400.3	1399.3	1398.4	1397.3	1396.4	1395.9	1395.9	1395.9	1395.9	1395.9	1397.3
170°	1412.8	1411.9	1410.8	1409.9	1408.9	1408.3	1408.3	1408.3	1408.3	1408.3	1409.9
172.5°	1421.8	1420.7	1419.8	1418.8	1417.8	1417.3	1417.3	1417.3	1417.3	1417.3	1418.8
175°	1431.8	1430.8	1429.9	1428.8	1427.9	1427.4	1427.4	1427.4	1427.4	1427.4	1428.8
177.5°	1436.9	1436.1	1435.4	1434.6	1433.7	1433.3	1433.0	1432.9	1432.7	1432.4	1433.7
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	17.7	17.9	18.2	18.3	18.2	18.1	18.0	17.9
90°	20.3	21.6	22.8	23.8	24.5	25.3	26.1	26.8
92.5°	46.1	47.8	49.4	50.5	51.1	51.7	52.2	52.7
95°	89.5	91.2	93.0	94.0	94.5	95.1	95.6	96.1
97.5°	140.2	141.8	143.4	144.5	144.7	145.1	145.3	145.7
100°	175.4	177.5	179.8	181.2	181.7	182.2	182.7	183.1
102.5°	211.5	213.9	216.4	217.9	218.6	219.3	220.0	220.7
105°	269.9	271.4	272.9	274.0	274.7	275.5	276.2	277.0
107.5°	332.9	333.7	334.5	334.8	334.8	334.7	334.7	334.6
110°	376.8	377.5	378.2	378.5	378.2	378.0	377.7	377.5



TEST NUMBER: P333393-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	420.6	420.9	421.3	421.3	420.9	420.4	419.9	419.5
115°	487.6	487.3	487.1	486.8	486.6	486.3	486.1	485.9
117.5°	554.6	554.7	555.0	554.6	553.6	552.6	551.6	550.6
120°	599.8	599.8	599.8	599.3	598.2	597.3	596.2	595.3
122.5°	644.0	643.9	643.6	643.2	642.3	641.5	640.8	640.0
125°	709.3	708.9	708.3	708.0	707.7	707.5	707.2	707.0
127.5°	774.1	773.9	773.7	773.3	772.8	772.3	771.8	771.3
130°	817.0	816.8	816.6	816.1	815.7	815.2	814.7	814.2
132.5°	858.2	857.9	857.6	857.2	856.5	855.7	855.1	854.4
135°	921.4	921.4	921.4	920.9	919.9	918.9	917.9	917.0
137.5°	983.0	983.3	983.6	983.1	981.9	980.6	979.4	978.2
140°	1021.8	1022.3	1022.8	1022.4	1021.1	1019.9	1018.7	1017.4
142.5°	1059.8	1060.1	1060.4	1060.0	1058.7	1057.5	1056.2	1055.0
145°	1114.7	1114.7	1114.7	1114.2	1113.5	1112.8	1112.0	1111.3
147.5°	1165.4	1166.0	1166.6	1166.1	1164.3	1162.7	1161.0	1159.3
150°	1197.3	1197.3	1197.3	1197.0	1196.5	1196.0	1195.5	1195.1
152.5°	1227.0	1227.6	1228.2	1228.1	1227.2	1226.3	1225.4	1224.5
155°	1269.6	1270.6	1271.6	1271.4	1270.2	1269.0	1267.7	1266.5
157.5°	1306.5	1307.4	1308.5	1308.1	1306.5	1304.8	1303.2	1301.6
160°	1328.8	1329.8	1330.8	1330.7	1329.5	1328.2	1327.0	1325.7
162.5°	1349.8	1350.9	1352.1	1352.0	1350.6	1349.1	1347.7	1346.3
165°	1377.9	1379.0	1379.9	1379.7	1378.2	1376.7	1375.2	1373.7
167.5°	1398.9	1400.3	1401.8	1401.8	1400.2	1398.7	1397.1	1395.6
170°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.7	1408.9	1407.2
172.5°	1420.3	1421.8	1423.2	1423.2	1421.7	1420.1	1418.6	1417.0
175°	1430.3	1431.8	1433.3	1433.1	1431.4	1429.7	1428.0	1426.2
177.5°	1434.9	1436.1	1437.3	1437.2	1435.7	1434.3	1433.0	1431.6
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2

(END OF REPORT)