

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333437-940

Luminaire Tested: **S125DIW-S1090D770U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333437-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6376.7 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	39
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	39	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	2.1
10°-20°	406.4	6.4
20°-30°	660.0	10.3
30°-40°	805.0	12.6
40°-50°	732.3	11.5
50°-60°	583.3	9.1
60°-70°	406.3	6.4
70°-80°	216.7	3.4
80°-90°	56.5	0.9
90°-100°	57.0	0.9
100°-110°	168.2	2.6
110°-120°	285.0	4.5
120°-130°	375.0	5.9
130°-140°	420.2	6.6
140°-150°	411.8	6.5
150°-160°	345.9	5.4
160°-170°	229.9	3.6
170°-180°	80.5	1.3
0°-30°	1202.9	18.9
0°-40°	2008.0	31.5
0°-60°	3323.6	52.1
0°-90°	4003.1	62.8
90°-120°	510.2	8.0
90°-150°	1717.2	26.9
90°-180°	2374.0	37.2
0°-180°	6376.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	46
90°	16	1	16	1	16	11
95°	57	43	57	43	57	58
105°	164	151	164	151	164	174
115°	288	285	288	285	288	285
125°	419	416	419	416	419	374
135°	544	541	544	541	544	419
145°	659	656	659	656	659	411
155°	751	751	751	751	751	345
165°	814	816	814	816	814	230
175°	845	849	845	849	845	80
180°	851	851	851	851	851	



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	14.7	15.6	16.0	15.9	16.3	16.2	17.9	17.8	19.1	20.4	22.1
90°	15.9	15.4	15.0	14.5	14.1	13.6	12.8	12.0	11.3	10.6	9.5
92.5°	31.2	30.9	30.6	30.3	30.0	29.3	28.4	27.4	26.4	25.4	24.2
95°	56.9	56.6	56.4	56.1	55.7	55.1	54.0	53.1	52.0	51.0	49.5
97.5°	86.3	86.1	86.0	85.8	85.6	85.1	84.1	83.1	82.1	81.1	79.1
100°	108.5	108.3	108.0	107.7	107.4	106.6	105.2	103.9	102.6	101.3	99.3
102.5°	130.8	130.4	130.0	129.6	129.1	128.2	126.8	125.4	123.9	122.4	121.5
105°	164.2	163.7	163.3	162.8	162.4	161.8	160.9	160.0	159.1	158.2	157.3
107.5°	198.3	198.3	198.4	198.4	198.4	198.2	197.8	197.3	196.9	196.4	195.8
110°	223.7	223.9	224.0	224.2	224.4	224.2	223.7	223.3	222.8	222.4	221.9



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	248.6	248.9	249.1	249.4	249.7	249.7	249.5	249.3	249.1	248.9	248.3
115°	287.9	288.1	288.3	288.4	288.6	288.6	288.8	289.0	289.1	289.3	289.0
117.5°	326.4	326.9	327.5	328.1	328.7	329.0	328.8	328.7	328.6	328.5	328.2
120°	352.8	353.4	354.0	354.6	355.2	355.4	355.4	355.4	355.4	355.4	355.3
122.5°	379.3	379.8	380.2	380.7	381.2	381.5	381.6	381.7	381.8	381.9	381.6
125°	419.0	419.2	419.3	419.5	419.6	419.8	420.1	420.4	420.7	421.0	420.9
127.5°	457.2	457.4	457.7	458.1	458.3	458.5	458.7	458.9	459.0	459.1	459.0
130°	482.6	482.9	483.1	483.5	483.8	483.9	484.1	484.3	484.4	484.6	484.3
132.5°	506.4	506.8	507.2	507.7	508.0	508.4	508.5	508.6	508.8	508.9	509.0
135°	543.5	544.0	544.7	545.2	545.8	546.1	546.1	546.1	546.1	546.1	546.0
137.5°	579.7	580.5	581.2	581.9	582.6	583.0	582.8	582.6	582.5	582.3	581.9
140°	603.1	603.8	604.5	605.3	606.0	606.2	605.9	605.6	605.3	605.0	604.6
142.5°	625.3	626.0	626.8	627.5	628.2	628.5	628.3	628.1	627.9	627.8	627.2
145°	658.6	659.1	659.5	660.0	660.4	660.7	660.7	660.7	660.7	660.7	660.2
147.5°	687.2	688.1	689.1	690.1	691.1	691.4	691.1	690.7	690.4	690.0	689.6
150°	708.3	708.6	708.9	709.2	709.4	709.6	709.6	709.6	709.6	709.6	709.0
152.5°	725.8	726.3	726.8	727.4	727.9	728.0	727.6	727.3	726.9	726.6	726.3
155°	750.6	751.4	752.2	752.9	753.6	753.7	753.0	752.5	751.9	751.4	751.2
157.5°	771.4	772.4	773.4	774.4	775.3	775.5	774.9	774.4	773.7	773.2	773.0
160°	785.8	786.5	787.2	787.9	788.7	788.7	788.2	787.6	787.0	786.4	786.2
162.5°	797.9	798.8	799.6	800.5	801.4	801.4	800.7	800.0	799.3	798.6	798.5
165°	814.2	815.1	816.0	816.9	817.7	817.9	817.3	816.7	816.1	815.6	815.4
167.5°	827.2	828.1	829.0	829.9	830.8	830.8	830.0	829.1	828.2	827.3	827.3
170°	834.1	835.1	836.2	837.1	838.2	838.3	837.4	836.5	835.6	834.7	834.7
172.5°	839.9	840.8	841.7	842.7	843.6	843.6	842.7	841.8	840.9	840.0	840.0
175°	845.3	846.3	847.4	848.4	849.4	849.5	848.6	847.7	846.9	846.0	846.0
177.5°	848.5	849.4	850.2	851.0	851.8	851.9	851.1	850.4	849.7	849.0	849.2
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	22.9	21.8	19.6	17.9	15.2	13.6	12.9	13.1	11.9	11.7	12.4
90°	8.6	7.5	6.5	5.4	4.2	3.0	1.9	0.6	1.9	3.0	4.2
92.5°	22.9	21.7	20.3	19.4	18.5	17.7	16.9	16.1	16.9	17.7	18.5
95°	48.1	46.5	45.1	44.2	43.9	43.6	43.3	43.1	43.3	43.6	43.9
97.5°	77.1	75.1	73.0	72.0	71.9	71.7	71.6	71.5	71.6	71.7	71.9
100°	97.5	95.5	93.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6
102.5°	120.6	119.6	118.6	117.8	117.2	116.6	116.0	115.5	116.0	116.6	117.2
105°	156.4	155.6	154.7	153.9	153.1	152.4	151.7	151.0	151.7	152.4	153.1
107.5°	195.1	194.5	193.8	193.1	192.3	191.6	190.8	190.1	190.8	191.6	192.3
110°	221.5	221.1	220.6	220.1	219.4	218.6	217.8	217.1	217.8	218.6	219.4



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.8	247.2	246.6	246.2	245.8	245.4	245.0	244.7	245.0	245.4	245.8
115°	288.6	288.4	288.1	287.7	287.0	286.5	285.9	285.3	285.9	286.5	287.0
117.5°	328.0	327.7	327.4	327.2	326.9	326.6	326.4	326.1	326.4	326.6	326.9
120°	355.2	355.0	354.9	354.5	353.7	352.9	352.2	351.5	352.2	352.9	353.7
122.5°	381.2	380.8	380.4	380.1	379.9	379.6	379.3	379.1	379.3	379.6	379.9
125°	420.7	420.5	420.4	419.9	419.0	418.1	417.2	416.3	417.2	418.1	419.0
127.5°	458.8	458.6	458.4	458.1	457.6	457.1	456.6	456.1	456.6	457.1	457.6
130°	483.9	483.7	483.4	482.9	482.1	481.4	480.6	479.9	480.6	481.4	482.1
132.5°	509.0	509.1	509.2	508.5	507.4	506.1	505.0	503.7	505.0	506.1	507.4
135°	545.8	545.6	545.5	545.0	544.1	543.2	542.3	541.4	542.3	543.2	544.1
137.5°	581.6	581.3	580.9	580.4	579.5	578.6	577.8	576.9	577.8	578.6	579.5
140°	604.1	603.7	603.2	602.7	601.9	601.2	600.5	599.8	600.5	601.2	601.9
142.5°	626.7	626.2	625.5	625.0	624.4	623.8	623.1	622.5	623.1	623.8	624.4
145°	659.8	659.3	658.9	658.4	657.7	657.2	656.6	656.0	656.6	657.2	657.7
147.5°	689.3	688.9	688.6	688.3	688.0	687.6	687.3	687.0	687.3	687.6	688.0
150°	708.5	707.8	707.3	707.0	707.2	707.3	707.5	707.7	707.5	707.3	707.2
152.5°	726.1	725.9	725.6	725.4	725.2	725.0	724.8	724.6	724.8	725.0	725.2
155°	751.0	750.9	750.7	750.6	750.6	750.6	750.6	750.6	750.6	750.6	750.6
157.5°	772.8	772.8	772.6	772.7	773.0	773.3	773.6	774.0	773.6	773.3	773.0
160°	786.1	786.0	785.8	786.0	786.4	786.8	787.3	787.7	787.3	786.8	786.4
162.5°	798.5	798.5	798.4	798.6	799.0	799.2	799.6	800.0	799.6	799.2	799.0
165°	815.2	815.1	814.9	815.0	815.3	815.6	815.9	816.2	815.9	815.6	815.3
167.5°	827.3	827.3	827.3	827.6	828.2	828.8	829.4	830.0	829.4	828.8	828.2
170°	834.7	834.7	834.7	835.0	835.6	836.2	836.8	837.4	836.8	836.2	835.6
172.5°	840.0	840.0	840.0	840.3	840.9	841.5	842.0	842.7	842.0	841.5	840.9
175°	846.0	846.0	846.0	846.2	846.9	847.5	848.0	848.6	848.0	847.5	846.9
177.5°	849.3	849.4	849.5	849.8	850.2	850.7	851.2	851.7	851.2	850.7	850.2
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	13.1	14.3	14.0	14.7	14.9	16.1	15.8	17.8	18.9	20.1	19.7
90°	5.4	6.5	7.5	8.6	9.5	10.6	11.3	12.0	12.8	13.6	14.1
92.5°	19.4	20.3	21.7	22.9	24.2	25.4	26.4	27.4	28.4	29.3	30.0
95°	44.2	45.1	46.5	48.1	49.5	51.0	52.0	53.1	54.0	55.1	55.7
97.5°	72.0	73.0	75.1	77.1	79.1	81.1	82.1	83.1	84.1	85.1	85.6
100°	92.6	93.6	95.5	97.5	99.3	101.3	102.6	103.9	105.2	106.6	107.4
102.5°	117.8	118.6	119.6	120.6	121.5	122.4	123.9	125.4	126.8	128.2	129.1
105°	153.9	154.7	155.6	156.4	157.3	158.2	159.1	160.0	160.9	161.8	162.4
107.5°	193.1	193.8	194.5	195.1	195.8	196.4	196.9	197.3	197.8	198.2	198.4
110°	220.1	220.6	221.1	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.4



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	246.2	246.6	247.2	247.8	248.3	248.9	249.1	249.3	249.5	249.7	249.7
115°	287.7	288.1	288.4	288.6	289.0	289.3	289.1	289.0	288.8	288.6	288.6
117.5°	327.2	327.4	327.7	328.0	328.2	328.5	328.6	328.7	328.8	329.0	328.7
120°	354.5	354.9	355.0	355.2	355.3	355.4	355.4	355.4	355.4	355.4	355.2
122.5°	380.1	380.4	380.8	381.2	381.6	381.9	381.8	381.7	381.6	381.5	381.2
125°	419.9	420.4	420.5	420.7	420.9	421.0	420.7	420.4	420.1	419.8	419.6
127.5°	458.1	458.4	458.6	458.8	459.0	459.1	459.0	458.9	458.7	458.5	458.3
130°	482.9	483.4	483.7	483.9	484.3	484.6	484.4	484.3	484.1	483.9	483.8
132.5°	508.5	509.2	509.1	509.0	509.0	508.9	508.8	508.6	508.5	508.4	508.0
135°	545.0	545.5	545.6	545.8	546.0	546.1	546.1	546.1	546.1	546.1	545.8
137.5°	580.4	580.9	581.3	581.6	581.9	582.3	582.5	582.6	582.8	583.0	582.6
140°	602.7	603.2	603.7	604.1	604.6	605.0	605.3	605.6	605.9	606.2	606.0
142.5°	625.0	625.5	626.2	626.7	627.2	627.8	627.9	628.1	628.3	628.5	628.2
145°	658.4	658.9	659.3	659.8	660.2	660.7	660.7	660.7	660.7	660.7	660.4
147.5°	688.3	688.6	688.9	689.3	689.6	690.0	690.4	690.7	691.1	691.4	691.1
150°	707.0	707.3	707.8	708.5	709.0	709.6	709.6	709.6	709.6	709.6	709.4
152.5°	725.4	725.6	725.9	726.1	726.3	726.6	726.9	727.3	727.6	728.0	727.9
155°	750.6	750.7	750.9	751.0	751.2	751.4	751.9	752.5	753.0	753.7	753.6
157.5°	772.7	772.6	772.8	772.8	773.0	773.2	773.7	774.4	774.9	775.5	775.3
160°	786.0	785.8	786.0	786.1	786.2	786.4	787.0	787.6	788.2	788.7	788.7
162.5°	798.6	798.4	798.5	798.5	798.5	798.6	799.3	800.0	800.7	801.4	801.4
165°	815.0	814.9	815.1	815.2	815.4	815.6	816.1	816.7	817.3	817.9	817.7
167.5°	827.6	827.3	827.3	827.3	827.3	827.3	828.2	829.1	830.0	830.8	830.8
170°	835.0	834.7	834.7	834.7	834.7	834.7	835.6	836.5	837.4	838.3	838.2
172.5°	840.3	840.0	840.0	840.0	840.0	840.0	840.9	841.8	842.7	843.6	843.6
175°	846.2	846.0	846.0	846.0	846.0	846.0	846.9	847.7	848.6	849.5	849.4
177.5°	849.8	849.5	849.4	849.3	849.2	849.0	849.7	850.4	851.1	851.9	851.8
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	20.7	20.3	20.4	21.5	20.4	20.3	20.7	19.7	20.1	18.9	17.8
90°	14.5	15.0	15.4	15.9	15.4	15.0	14.5	14.1	13.6	12.8	12.0
92.5°	30.3	30.6	30.9	31.2	30.9	30.6	30.3	30.0	29.3	28.4	27.4
95°	56.1	56.4	56.6	56.9	56.6	56.4	56.1	55.7	55.1	54.0	53.1
97.5°	85.8	86.0	86.1	86.3	86.1	86.0	85.8	85.6	85.1	84.1	83.1
100°	107.7	108.0	108.3	108.5	108.3	108.0	107.7	107.4	106.6	105.2	103.9
102.5°	129.6	130.0	130.4	130.8	130.4	130.0	129.6	129.1	128.2	126.8	125.4
105°	162.8	163.3	163.7	164.2	163.7	163.3	162.8	162.4	161.8	160.9	160.0
107.5°	198.4	198.4	198.3	198.3	198.3	198.4	198.4	198.4	198.2	197.8	197.3
110°	224.2	224.0	223.9	223.7	223.9	224.0	224.2	224.4	224.2	223.7	223.3



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	249.4	249.1	248.9	248.6	248.9	249.1	249.4	249.7	249.7	249.5	249.3
115°	288.4	288.3	288.1	287.9	288.1	288.3	288.4	288.6	288.6	288.8	289.0
117.5°	328.1	327.5	326.9	326.4	326.9	327.5	328.1	328.7	329.0	328.8	328.7
120°	354.6	354.0	353.4	352.8	353.4	354.0	354.6	355.2	355.4	355.4	355.4
122.5°	380.7	380.2	379.8	379.3	379.8	380.2	380.7	381.2	381.5	381.6	381.7
125°	419.5	419.3	419.2	419.0	419.2	419.3	419.5	419.6	419.8	420.1	420.4
127.5°	458.1	457.7	457.4	457.2	457.4	457.7	458.1	458.3	458.5	458.7	458.9
130°	483.5	483.1	482.9	482.6	482.9	483.1	483.5	483.8	483.9	484.1	484.3
132.5°	507.7	507.2	506.8	506.4	506.8	507.2	507.7	508.0	508.4	508.5	508.6
135°	545.2	544.7	544.0	543.5	544.0	544.7	545.2	545.8	546.1	546.1	546.1
137.5°	581.9	581.2	580.5	579.7	580.5	581.2	581.9	582.6	583.0	582.8	582.6
140°	605.3	604.5	603.8	603.1	603.8	604.5	605.3	606.0	606.2	605.9	605.6
142.5°	627.5	626.8	626.0	625.3	626.0	626.8	627.5	628.2	628.5	628.3	628.1
145°	660.0	659.5	659.1	658.6	659.1	659.5	660.0	660.4	660.7	660.7	660.7
147.5°	690.1	689.1	688.1	687.2	688.1	689.1	690.1	691.1	691.4	691.1	690.7
150°	709.2	708.9	708.6	708.3	708.6	708.9	709.2	709.4	709.6	709.6	709.6
152.5°	727.4	726.8	726.3	725.8	726.3	726.8	727.4	727.9	728.0	727.6	727.3
155°	752.9	752.2	751.4	750.6	751.4	752.2	752.9	753.6	753.7	753.0	752.5
157.5°	774.4	773.4	772.4	771.4	772.4	773.4	774.4	775.3	775.5	774.9	774.4
160°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.7	788.7	788.2	787.6
162.5°	800.5	799.6	798.8	797.9	798.8	799.6	800.5	801.4	801.4	800.7	800.0
165°	816.9	816.0	815.1	814.2	815.1	816.0	816.9	817.7	817.9	817.3	816.7
167.5°	829.9	829.0	828.1	827.2	828.1	829.0	829.9	830.8	830.8	830.0	829.1
170°	837.1	836.2	835.1	834.1	835.1	836.2	837.1	838.2	838.3	837.4	836.5
172.5°	842.7	841.7	840.8	839.9	840.8	841.7	842.7	843.6	843.6	842.7	841.8
175°	848.4	847.4	846.3	845.3	846.3	847.4	848.4	849.4	849.5	848.6	847.7
177.5°	851.0	850.2	849.4	848.5	849.4	850.2	851.0	851.8	851.9	851.1	850.4
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	15.8	16.1	14.9	14.7	14.0	14.3	13.1	12.4	11.7	11.9	13.1
90°	11.3	10.6	9.5	8.6	7.5	6.5	5.4	4.2	3.0	1.9	0.6
92.5°	26.4	25.4	24.2	22.9	21.7	20.3	19.4	18.5	17.7	16.9	16.1
95°	52.0	51.0	49.5	48.1	46.5	45.1	44.2	43.9	43.6	43.3	43.1
97.5°	82.1	81.1	79.1	77.1	75.1	73.0	72.0	71.9	71.7	71.6	71.5
100°	102.6	101.3	99.3	97.5	95.5	93.6	92.6	92.6	92.6	92.6	92.6
102.5°	123.9	122.4	121.5	120.6	119.6	118.6	117.8	117.2	116.6	116.0	115.5
105°	159.1	158.2	157.3	156.4	155.6	154.7	153.9	153.1	152.4	151.7	151.0
107.5°	196.9	196.4	195.8	195.1	194.5	193.8	193.1	192.3	191.6	190.8	190.1
110°	222.8	222.4	221.9	221.5	221.1	220.6	220.1	219.4	218.6	217.8	217.1



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	249.1	248.9	248.3	247.8	247.2	246.6	246.2	245.8	245.4	245.0	244.7
115°	289.1	289.3	289.0	288.6	288.4	288.1	287.7	287.0	286.5	285.9	285.3
117.5°	328.6	328.5	328.2	328.0	327.7	327.4	327.2	326.9	326.6	326.4	326.1
120°	355.4	355.4	355.3	355.2	355.0	354.9	354.5	353.7	352.9	352.2	351.5
122.5°	381.8	381.9	381.6	381.2	380.8	380.4	380.1	379.9	379.6	379.3	379.1
125°	420.7	421.0	420.9	420.7	420.5	420.4	419.9	419.0	418.1	417.2	416.3
127.5°	459.0	459.1	459.0	458.8	458.6	458.4	458.1	457.6	457.1	456.6	456.1
130°	484.4	484.6	484.3	483.9	483.7	483.4	482.9	482.1	481.4	480.6	479.9
132.5°	508.8	508.9	509.0	509.0	509.1	509.2	508.5	507.4	506.1	505.0	503.7
135°	546.1	546.1	546.0	545.8	545.6	545.5	545.0	544.1	543.2	542.3	541.4
137.5°	582.5	582.3	581.9	581.6	581.3	580.9	580.4	579.5	578.6	577.8	576.9
140°	605.3	605.0	604.6	604.1	603.7	603.2	602.7	601.9	601.2	600.5	599.8
142.5°	627.9	627.8	627.2	626.7	626.2	625.5	625.0	624.4	623.8	623.1	622.5
145°	660.7	660.7	660.2	659.8	659.3	658.9	658.4	657.7	657.2	656.6	656.0
147.5°	690.4	690.0	689.6	689.3	688.9	688.6	688.3	688.0	687.6	687.3	687.0
150°	709.6	709.6	709.0	708.5	707.8	707.3	707.0	707.2	707.3	707.5	707.7
152.5°	726.9	726.6	726.3	726.1	725.9	725.6	725.4	725.2	725.0	724.8	724.6
155°	751.9	751.4	751.2	751.0	750.9	750.7	750.6	750.6	750.6	750.6	750.6
157.5°	773.7	773.2	773.0	772.8	772.8	772.6	772.7	773.0	773.3	773.6	774.0
160°	787.0	786.4	786.2	786.1	786.0	785.8	786.0	786.4	786.8	787.3	787.7
162.5°	799.3	798.6	798.5	798.5	798.5	798.4	798.6	799.0	799.2	799.6	800.0
165°	816.1	815.6	815.4	815.2	815.1	814.9	815.0	815.3	815.6	815.9	816.2
167.5°	828.2	827.3	827.3	827.3	827.3	827.3	827.6	828.2	828.8	829.4	830.0
170°	835.6	834.7	834.7	834.7	834.7	834.7	835.0	835.6	836.2	836.8	837.4
172.5°	840.9	840.0	840.0	840.0	840.0	840.0	840.3	840.9	841.5	842.0	842.7
175°	846.9	846.0	846.0	846.0	846.0	846.0	846.2	846.9	847.5	848.0	848.6
177.5°	849.7	849.0	849.2	849.3	849.4	849.5	849.8	850.2	850.7	851.2	851.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	12.9	13.6	15.2	17.9	19.6	21.8	22.9	22.1	20.4	19.1	17.8
90°	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3	12.0
92.5°	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4	27.4
95°	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0	53.1
97.5°	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1	83.1
100°	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6	103.9
102.5°	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9	125.4
105°	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1	160.0
107.5°	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9	197.3
110°	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8	223.3



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1	249.3
115°	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1	289.0
117.5°	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6	328.7
120°	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4	355.4
122.5°	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8	381.7
125°	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7	420.4
127.5°	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0	458.9
130°	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4	484.3
132.5°	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8	508.6
135°	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1	546.1
137.5°	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5	582.6
140°	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3	605.6
142.5°	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9	628.1
145°	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7	660.7
147.5°	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4	690.7
150°	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6	709.6
152.5°	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9	727.3
155°	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9	752.5
157.5°	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7	774.4
160°	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0	787.6
162.5°	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3	800.0
165°	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1	816.7
167.5°	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2	829.1
170°	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6	836.5
172.5°	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9	841.8
175°	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9	847.7
177.5°	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7	850.4
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	17.9	16.2	16.3	15.9	16.0	15.6	14.7
90°	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.7	224.2	224.4	224.2	224.0	223.9	223.7



TEST NUMBER: P333437-940

CATALOG NUMBER: S125DIW-S1090D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)