

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333399-935

Luminaire Tested: **S125DIW-S610D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333399-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6811.5 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19
4	71	60	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.1
10°-20°	220.2	3.2
20°-30°	325.2	4.8
30°-40°	379.4	5.6
40°-50°	381.1	5.6
50°-60°	334.5	4.9
60°-70°	249.3	3.7
70°-80°	142.5	2.1
80°-90°	45.1	0.7
90°-100°	111.8	1.6
100°-110°	330.0	4.8
110°-120°	559.0	8.2
120°-130°	735.7	10.8
130°-140°	824.3	12.1
140°-150°	807.9	11.9
150°-160°	678.6	10.0
160°-170°	451.1	6.6
170°-180°	157.9	2.3
0°-30°	623.4	9.2
0°-40°	1002.8	14.7
0°-60°	1718.4	25.2
0°-90°	2155.3	31.6
90°-120°	1000.8	14.7
90°-150°	3368.6	49.5
90°-180°	4656.0	68.4
0°-180°	6811.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	12	21	27	31	7
95°	84	88	100	109	112	90
105°	296	303	310	318	322	316
115°	560	565	568	566	565	553
125°	817	824	826	823	822	731
135°	1062	1070	1071	1071	1066	818
145°	1287	1292	1296	1296	1292	804
155°	1473	1473	1474	1478	1473	678
165°	1601	1599	1600	1604	1597	451
175°	1665	1660	1660	1666	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.4	14.8	15.3	15.8	16.3	16.6	16.9	17.2	17.5	17.7	18.1
90°	1.3	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2
92.5°	31.4	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7
95°	84.4	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0
97.5°	140.3	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1
100°	181.8	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3
102.5°	226.4	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1
105°	296.1	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1
107.5°	372.9	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2
110°	425.9	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.9	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6
115°	559.6	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1
117.5°	639.6	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5
120°	689.5	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3
122.5°	743.6	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0
125°	816.7	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3
127.5°	894.7	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3
130°	941.4	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2
132.5°	988.2	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0
135°	1062.2	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3
137.5°	1131.8	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5
140°	1176.5	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4
142.5°	1221.2	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8
145°	1286.9	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9
147.5°	1347.6	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3
150°	1388.1	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1
152.5°	1421.3	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0
155°	1472.6	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0
157.5°	1518.2	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9
160°	1545.2	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8
162.5°	1569.2	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0
165°	1601.1	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9
167.5°	1628.1	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6
170°	1642.6	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2
172.5°	1653.0	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6
175°	1664.7	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2
177.5°	1670.7	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	18.3	18.6	18.9	19.0	18.9	18.9	18.9	18.8
90°	23.7	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	53.6	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	104.0	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	163.0	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	203.9	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	245.9	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	313.8	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	387.1	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.1	438.9	439.8	440.1	439.8	439.5	439.2	438.9



TEST NUMBER: P333399-935

CATALOG NUMBER: S125DIW-S610D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.0	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.9	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	644.8	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.8	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.8	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	900.1	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.9	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.7	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1142.9	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.0	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.2	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.0	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1426.7	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1476.1	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1519.0	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1545.0	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1569.3	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1602.1	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1626.3	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1640.9	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1651.3	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1663.0	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1668.3	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)