

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333381-935

Luminaire Tested: **S125DIW-S610D770U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333381-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D770U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4445.3 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	39	44	39	34	37	33	30	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.8
10°-20°	220.2	5.0
20°-30°	325.2	7.3
30°-40°	379.4	8.5
40°-50°	381.1	8.6
50°-60°	334.5	7.5
60°-70°	249.3	5.6
70°-80°	142.5	3.2
80°-90°	43.3	1.0
90°-100°	55.0	1.2
100°-110°	162.4	3.7
110°-120°	275.1	6.2
120°-130°	362.1	8.1
130°-140°	405.7	9.1
140°-150°	397.7	8.9
150°-160°	334.0	7.5
160°-170°	222.0	5.0
170°-180°	77.7	1.7
0°-30°	623.4	14.0
0°-40°	1002.8	22.6
0°-60°	1718.4	38.7
0°-90°	2153.5	48.4
90°-120°	492.6	11.1
90°-150°	1658.1	37.3
90°-180°	2292.0	51.6
0°-180°	4445.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	6	10	13	15	4
95°	42	43	49	54	55	44
105°	146	149	153	156	158	156
115°	276	278	279	279	278	272
125°	402	406	406	405	405	360
135°	523	526	527	527	525	403
145°	633	636	638	638	636	396
155°	725	725	726	728	725	334
165°	788	787	788	790	786	222
175°	819	817	817	820	816	78
180°	821	821	821	821	821	



TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.3	14.5	14.7	15.0	15.2	15.3	15.4	15.5	15.6	15.7	15.8
90°	0.6	1.8	2.9	4.0	5.2	6.3	7.2	8.3	9.2	10.2	10.9
92.5°	15.5	16.3	17.0	17.8	18.7	19.6	20.9	22.1	23.3	24.5	25.5
95°	41.6	41.8	42.1	42.4	42.7	43.6	44.9	46.4	47.8	49.2	50.2
97.5°	69.1	69.1	69.2	69.4	69.5	70.5	72.5	74.5	76.4	78.4	79.3
100°	89.5	89.5	89.5	89.5	89.5	90.4	92.2	94.1	95.9	97.8	99.1
102.5°	111.5	112.0	112.6	113.1	113.7	114.5	115.5	116.4	117.3	118.2	119.7
105°	145.8	146.5	147.1	147.8	148.6	149.4	150.2	151.0	151.9	152.7	153.6
107.5°	183.6	184.3	185.0	185.7	186.4	187.1	187.8	188.4	189.1	189.7	190.1
110°	209.7	210.3	211.0	211.8	212.5	213.0	213.4	213.9	214.3	214.7	215.2



TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	236.3	236.6	236.9	237.4	237.7	238.2	238.7	239.3	239.8	240.3	240.6
115°	275.5	276.0	276.6	277.2	277.8	278.2	278.4	278.7	279.1	279.3	279.1
117.5°	314.9	315.1	315.4	315.6	315.9	316.2	316.4	316.7	316.9	317.2	317.3
120°	339.4	340.1	340.8	341.6	342.2	342.7	342.8	342.9	343.1	343.2	343.2
122.5°	366.0	366.3	366.5	366.8	367.0	367.3	367.6	368.1	368.4	368.8	368.7
125°	402.0	402.9	403.7	404.6	405.4	406.0	406.0	406.2	406.4	406.5	406.2
127.5°	440.4	440.8	441.3	441.9	442.3	442.6	442.8	443.0	443.2	443.3	443.2
130°	463.4	464.1	464.9	465.5	466.2	466.7	467.0	467.3	467.6	467.9	467.7
132.5°	486.4	487.6	488.7	489.9	491.0	491.6	491.5	491.5	491.5	491.4	491.3
135°	522.8	523.7	524.5	525.4	526.2	526.8	526.8	527.0	527.2	527.3	527.3
137.5°	557.1	557.9	558.7	559.6	560.4	560.9	561.3	561.5	561.9	562.2	562.4
140°	579.1	579.8	580.5	581.2	581.9	582.5	582.9	583.3	583.8	584.2	584.4
142.5°	601.1	601.7	602.3	602.9	603.5	604.0	604.6	605.1	605.6	606.1	606.3
145°	633.4	634.0	634.6	635.1	635.7	636.2	636.6	637.1	637.5	637.9	637.9
147.5°	663.3	663.7	663.9	664.3	664.6	664.9	665.2	665.6	665.9	666.2	666.6
150°	683.3	683.1	682.9	682.9	682.7	682.9	683.5	684.1	684.6	685.2	685.2
152.5°	699.6	699.8	700.0	700.3	700.4	700.6	700.9	701.1	701.3	701.5	701.9
155°	724.8	724.8	724.8	724.8	724.8	724.9	725.0	725.1	725.3	725.5	726.0
157.5°	747.3	747.0	746.7	746.4	746.1	746.0	746.1	746.2	746.4	746.6	747.1
160°	760.6	760.2	759.7	759.3	758.9	758.7	758.9	759.1	759.1	759.3	759.9
162.5°	772.4	772.1	771.7	771.5	771.1	770.9	771.0	771.0	771.0	771.1	771.8
165°	788.1	787.8	787.6	787.2	787.0	786.9	787.0	787.1	787.3	787.5	788.0
167.5°	801.4	800.8	800.2	799.7	799.1	798.8	798.8	798.8	798.8	798.8	799.7
170°	808.6	808.0	807.4	806.8	806.2	806.0	806.0	806.0	806.0	806.0	806.8
172.5°	813.6	813.0	812.5	811.9	811.4	811.1	811.1	811.1	811.1	811.1	811.9
175°	819.4	818.8	818.3	817.7	817.1	816.8	816.8	816.8	816.8	816.8	817.7
177.5°	822.3	821.9	821.4	821.0	820.5	820.3	820.1	820.0	819.9	819.8	820.4
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	15.9	16.1	16.2	16.2	16.1	15.9	15.8	15.7
90°	11.6	12.4	13.1	13.6	14.0	14.5	14.9	15.3
92.5°	26.4	27.4	28.3	28.9	29.3	29.5	29.9	30.1
95°	51.2	52.2	53.2	53.8	54.2	54.4	54.7	54.9
97.5°	80.2	81.2	82.1	82.7	82.8	83.0	83.2	83.3
100°	100.3	101.6	102.9	103.7	104.0	104.3	104.5	104.8
102.5°	121.1	122.4	123.8	124.7	125.1	125.5	125.9	126.3
105°	154.5	155.3	156.2	156.8	157.2	157.6	158.1	158.5
107.5°	190.5	191.0	191.4	191.6	191.6	191.6	191.5	191.5
110°	215.6	216.0	216.5	216.6	216.5	216.3	216.2	216.0





TEST NUMBER: P333381-935

CATALOG NUMBER: S125DIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.7	240.9	241.1	241.1	240.8	240.6	240.3	240.0
115°	279.1	278.9	278.7	278.6	278.4	278.4	278.2	278.0
117.5°	317.4	317.5	317.6	317.4	316.8	316.2	315.6	315.1
120°	343.2	343.2	343.2	342.9	342.4	341.8	341.2	340.7
122.5°	368.6	368.4	368.3	368.1	367.6	367.1	366.7	366.3
125°	406.0	405.6	405.4	405.2	405.0	404.8	404.8	404.6
127.5°	443.1	442.9	442.7	442.6	442.3	442.0	441.7	441.4
130°	467.6	467.4	467.3	467.1	466.8	466.5	466.2	466.0
132.5°	491.1	490.9	490.9	490.5	490.2	489.7	489.4	489.0
135°	527.3	527.3	527.3	527.0	526.4	525.9	525.3	524.8
137.5°	562.6	562.7	562.9	562.6	561.9	561.2	560.5	559.7
140°	584.8	585.0	585.3	585.1	584.4	583.7	583.0	582.3
142.5°	606.5	606.7	606.8	606.6	605.9	605.2	604.4	603.7
145°	637.9	637.9	637.9	637.7	637.2	636.8	636.4	635.9
147.5°	666.9	667.3	667.6	667.3	666.3	665.4	664.4	663.5
150°	685.2	685.2	685.2	685.0	684.8	684.5	684.2	683.9
152.5°	702.2	702.6	702.9	702.8	702.3	701.8	701.3	700.8
155°	726.6	727.1	727.7	727.6	726.9	726.3	725.5	724.8
157.5°	747.7	748.2	748.8	748.6	747.7	746.7	745.8	744.9
160°	760.4	761.0	761.6	761.6	760.8	760.1	759.4	758.7
162.5°	772.5	773.1	773.8	773.8	772.9	772.1	771.3	770.4
165°	788.6	789.2	789.7	789.5	788.8	787.9	787.0	786.2
167.5°	800.6	801.4	802.2	802.2	801.3	800.5	799.6	798.7
170°	807.7	808.6	809.4	809.3	808.3	807.4	806.3	805.4
172.5°	812.8	813.6	814.5	814.5	813.6	812.7	811.8	811.0
175°	818.6	819.4	820.3	820.2	819.2	818.2	817.2	816.2
177.5°	821.1	821.8	822.5	822.4	821.7	820.9	820.1	819.2
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3

(END OF REPORT)