

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333485-940

Luminaire Tested: **S125DIW-S1270D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333485-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9447.2 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42				42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35				35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26				26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10577	10577	10577	10577
5°	12248	10613	9292	10613
10°	14250	10558	8141	10558
15°	15774	10480	7511	10480
20°	17657	10357	7003	10357
25°	20685	10219	6757	10219
30°	22342	10082	6542	10082
35°	18370	9826	6401	9826
40°	13057	9470	6247	9470
45°	10030	8990	6158	8990
50°	8562	8395	6146	8395
55°	7624	7812	6199	7812
60°	6877	7174	6356	7174
65°	6353	6533	6522	6533
70°	5776	5867	6617	5867
75°	5100	5168	6558	5168
80°	4292	4214	5995	4214
85°	3394	3038	4846	3038



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.7
10°-20°	469.4	5.0
20°-30°	762.2	8.1
30°-40°	929.8	9.8
40°-50°	845.8	9.0
50°-60°	673.7	7.1
60°-70°	469.3	5.0
70°-80°	250.2	2.6
80°-90°	66.9	0.7
90°-100°	115.7	1.2
100°-110°	341.8	3.6
110°-120°	578.9	6.1
120°-130°	761.9	8.1
130°-140°	853.7	9.0
140°-150°	836.7	8.9
150°-160°	702.8	7.4
160°-170°	467.2	4.9
170°-180°	163.5	1.7
0°-30°	1389.3	14.7
0°-40°	2319.0	24.5
0°-60°	3838.6	40.6
0°-90°	4625.0	49.0
90°-120°	1036.5	11.0
90°-150°	3488.8	36.9
90°-180°	4822.0	51.0
0°-180°	9447.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1638	1638	1638	1638	1638	
5°	1889	1637	1433	1637	1889	190
15°	2359	1567	1123	1567	2359	675
25°	2903	1434	948	1434	2903	1326
35°	2330	1246	812	1246	2330	1426
45°	1098	984	674	984	1098	879
55°	677	694	550	694	677	610
65°	416	428	427	428	416	413
75°	204	207	263	207	204	220
85°	46	41	65	41	46	54
90°	32	1	32	1	32	20
95°	116	87	116	87	116	118
105°	334	307	334	307	334	353
115°	585	580	585	580	585	579
125°	851	846	851	846	851	760
135°	1104	1100	1104	1100	1104	852
145°	1338	1333	1338	1333	1338	835
155°	1525	1525	1525	1525	1525	702
165°	1654	1658	1654	1658	1654	466
175°	1717	1724	1717	1724	1717	163
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1732.2	1730.0	1727.8	1723.3	1726.6	1717.2	1712.7	1705.0	1695.5	1692.2	1688.3
5°	1889.3	1892.7	1896.2	1881.7	1883.0	1873.3	1851.1	1833.0	1818.4	1799.7	1786.5
7.5°	2078.4	2070.2	2069.5	2060.0	2043.8	2030.7	2007.3	1977.5	1948.8	1916.0	1888.9
10°	2172.9	2173.6	2167.4	2156.2	2138.9	2126.4	2095.8	2066.5	2031.1	1989.4	1959.5
12.5°	2244.1	2247.0	2239.1	2224.1	2215.5	2187.5	2163.6	2128.9	2086.7	2053.3	2007.9
15°	2359.2	2351.5	2346.0	2327.2	2312.7	2283.4	2245.2	2209.0	2163.2	2120.8	2078.4
17.5°	2470.1	2476.3	2465.8	2448.7	2403.4	2369.4	2318.1	2268.5	2211.4	2154.6	2104.0
20°	2569.1	2574.7	2558.7	2528.8	2474.6	2440.5	2373.1	2309.2	2243.1	2170.2	2114.5
22.5°	2692.6	2688.2	2666.6	2621.1	2574.1	2511.1	2438.2	2360.3	2277.6	2195.1	2121.2
25°	2902.8	2873.5	2860.3	2804.1	2742.2	2649.7	2549.7	2435.6	2332.8	2223.7	2129.1
27.5°	3019.2	3010.1	2995.3	2956.2	2891.1	2792.2	2674.2	2535.3	2390.2	2252.5	2128.7
30°	2995.9	2997.3	2998.7	2986.2	2944.5	2870.1	2752.6	2603.2	2430.8	2275.8	2132.6
32.5°	2789.1	2814.3	2838.6	2867.2	2878.9	2864.5	2791.0	2656.0	2478.6	2302.5	2130.4
35°	2330.0	2337.6	2416.2	2494.0	2599.7	2681.7	2736.7	2676.8	2527.4	2325.1	2127.7
37.5°	1816.8	1854.3	1908.6	1996.6	2149.1	2285.6	2461.2	2542.0	2493.8	2332.5	2122.9
40°	1548.7	1583.5	1618.9	1708.6	1837.2	2002.6	2202.1	2372.4	2412.0	2309.2	2106.2
42.5°	1341.8	1369.4	1408.7	1476.1	1583.6	1730.1	1920.7	2143.3	2280.2	2241.3	2071.2
45°	1098.2	1115.6	1146.2	1199.8	1277.6	1392.3	1560.5	1803.8	2015.8	2086.0	1988.0
47.5°	940.0	940.0	963.7	1000.7	1056.9	1154.3	1278.7	1469.4	1695.8	1863.3	1855.6
50°	852.2	848.7	867.5	899.5	944.0	1008.6	1127.5	1279.7	1497.3	1687.0	1739.8
52.5°	776.6	776.9	788.5	812.2	849.4	904.6	993.5	1130.7	1316.5	1511.3	1610.9
55°	677.1	674.2	687.4	703.5	730.6	766.7	830.6	935.6	1086.5	1278.3	1407.6
57.5°	585.9	593.5	598.8	609.9	632.4	656.6	710.5	787.6	907.2	1071.8	1208.5
60°	532.4	540.1	544.3	555.4	573.5	594.3	636.1	698.6	799.4	941.2	1076.7
62.5°	484.6	490.6	492.0	502.0	516.7	537.1	569.9	622.4	702.0	826.1	958.9
65°	415.7	415.7	418.5	428.9	435.9	453.9	478.9	517.2	581.1	677.7	791.0
67.5°	349.2	352.6	351.9	356.4	362.8	376.9	394.8	426.4	473.8	544.3	634.9
70°	305.9	308.6	307.9	311.4	318.3	327.4	342.0	371.8	405.9	466.5	544.3
72.5°	266.9	268.0	266.3	270.8	275.0	282.9	299.2	315.1	347.0	398.1	462.0
75°	204.4	205.7	207.1	209.9	214.1	218.3	226.6	242.6	263.4	301.7	342.7
77.5°	153.2	150.5	153.9	153.5	155.9	159.1	166.4	174.9	192.0	216.2	247.9
80°	115.4	116.1	116.1	116.8	120.3	122.3	128.6	134.8	148.0	166.1	188.4
82.5°	84.3	86.1	85.0	86.2	89.1	90.6	94.1	99.2	106.9	121.1	137.2
85°	45.8	42.4	43.8	45.2	45.2	45.8	48.7	50.7	54.9	60.5	66.7
87.5°	19.8	20.8	21.1	21.0	21.3	21.0	23.0	22.7	24.1	25.4	27.2
90°	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5	23.0	21.5	19.4
92.5°	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6	53.6	51.6	49.0
95°	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7	105.7	103.5	100.6
97.5°	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8	166.8	164.9	160.8
100°	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2	208.5	205.7	201.9
102.5°	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7	251.7	248.8	246.8
105°	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0	323.2	321.5	319.6
107.5°	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9	400.0	399.1	397.8
110°	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7	452.7	451.8	450.9



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5	506.0	505.7	504.5
115°	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1	587.4	587.7	587.1
117.5°	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8	667.5	667.4	666.7
120°	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2	722.2	722.2	721.8
122.5°	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5	775.7	776.0	775.2
125°	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2	854.7	855.3	855.1
127.5°	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2	932.5	932.8	932.5
130°	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8	984.1	984.4	983.8
132.5°	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3	1033.6	1033.9	1034.0
135°	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5	1109.5	1109.5	1109.2
137.5°	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7	1183.3	1182.9	1182.2
140°	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4	1229.8	1229.2	1228.3
142.5°	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1	1275.8	1275.4	1274.3
145°	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1	1342.1	1342.1	1341.2
147.5°	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3	1402.6	1401.9	1401.1
150°	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7	1441.7	1441.7	1440.5
152.5°	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6	1476.9	1476.1	1475.6
155°	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7	1527.6	1526.4	1526.1
157.5°	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2	1572.0	1570.7	1570.5
160°	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1	1598.8	1597.7	1597.4
162.5°	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3	1623.9	1622.4	1622.4
165°	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2	1658.0	1656.9	1656.5
167.5°	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4	1682.6	1680.8	1680.8
170°	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4	1697.6	1695.9	1695.9
172.5°	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2	1708.4	1706.6	1706.6
175°	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3	1720.5	1718.7	1718.7
177.5°	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8	1726.4	1724.9	1725.1
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1685.0	1681.1	1676.6	1668.8	1659.4	1654.4	1646.5	1641.6	1631.6	1623.2	1614.4
5°	1770.4	1752.4	1735.7	1714.1	1690.5	1675.2	1657.2	1637.0	1616.1	1594.6	1570.9
7.5°	1859.0	1827.0	1792.2	1754.9	1718.3	1684.6	1652.5	1621.0	1591.5	1555.9	1525.8
10°	1918.5	1878.2	1835.1	1784.3	1735.0	1691.9	1648.1	1609.9	1570.9	1529.2	1492.4
12.5°	1978.0	1924.3	1863.4	1807.7	1748.4	1696.3	1644.8	1596.0	1547.0	1500.8	1457.9
15°	2020.0	1972.7	1916.4	1837.2	1770.4	1698.9	1630.8	1567.4	1508.4	1457.0	1402.8
17.5°	2047.6	1986.7	1926.3	1850.2	1762.8	1682.7	1605.5	1533.1	1466.5	1401.3	1349.1
20°	2052.6	1990.1	1926.8	1852.4	1762.8	1671.1	1593.8	1507.0	1435.4	1368.0	1304.0
22.5°	2051.0	1980.0	1911.3	1834.7	1747.2	1662.7	1569.4	1480.9	1403.1	1336.9	1270.1
25°	2035.2	1959.5	1873.3	1796.2	1709.9	1620.3	1525.8	1434.0	1354.8	1279.0	1213.0
27.5°	2022.2	1924.0	1826.3	1736.3	1653.1	1570.9	1480.4	1386.4	1298.6	1221.8	1159.6
30°	2006.1	1898.4	1788.5	1694.7	1609.2	1529.2	1443.8	1352.0	1260.3	1185.2	1118.5
32.5°	1991.6	1866.1	1750.2	1648.0	1557.5	1479.7	1400.9	1313.6	1223.5	1147.4	1080.6
35°	1963.7	1818.4	1685.6	1570.2	1473.6	1393.7	1327.7	1246.3	1163.6	1089.9	1026.0
37.5°	1928.2	1755.9	1613.4	1492.4	1386.4	1302.3	1240.7	1178.3	1098.9	1028.0	970.1
40°	1900.4	1711.4	1560.5	1436.8	1327.0	1239.4	1182.4	1123.3	1057.3	991.2	930.1
42.5°	1865.4	1671.3	1507.2	1373.9	1265.2	1179.9	1120.1	1069.9	1011.6	950.1	893.3
45°	1801.0	1598.7	1420.8	1277.6	1167.8	1083.7	1021.8	984.3	940.5	882.1	834.1
47.5°	1706.4	1511.5	1327.5	1179.7	1066.4	988.5	930.5	894.5	863.6	820.2	776.7
50°	1622.4	1446.5	1260.3	1113.6	1000.2	921.7	868.2	835.5	809.1	775.7	738.9
52.5°	1528.4	1364.8	1194.1	1049.1	936.8	859.4	807.0	778.3	756.3	732.4	696.1
55°	1379.1	1240.1	1081.6	944.0	840.3	764.6	718.7	693.8	675.6	657.5	635.3
57.5°	1214.6	1105.9	965.5	839.7	744.3	675.4	632.6	608.2	594.1	584.9	571.8
60°	1098.9	1005.8	884.8	770.2	677.1	615.9	574.2	555.4	543.6	535.9	526.2
62.5°	991.7	915.2	803.2	698.5	617.0	559.1	521.9	503.6	492.4	488.7	480.6
65°	833.4	774.4	681.9	595.0	525.5	476.2	444.9	427.5	420.5	416.3	417.1
67.5°	677.6	641.6	567.3	493.2	437.7	396.4	371.3	358.0	354.5	348.9	348.8
70°	582.5	555.4	492.8	428.2	378.8	346.9	324.6	310.7	307.2	304.4	303.8
72.5°	498.6	474.7	420.5	368.7	324.3	296.2	277.9	269.6	263.9	262.2	262.1
75°	374.7	361.5	318.3	277.3	246.7	227.3	214.8	207.1	203.0	202.2	203.0
77.5°	266.4	254.9	227.5	198.4	179.1	164.3	153.7	151.1	146.4	146.5	145.8
80°	200.2	192.5	175.1	152.2	136.3	123.8	118.2	113.3	111.9	109.9	111.9
82.5°	145.2	137.0	125.1	110.5	97.3	89.8	84.3	82.8	81.9	80.9	81.3
85°	71.6	72.3	65.4	54.2	48.7	44.5	41.0	41.0	40.3	39.6	40.3
87.5°	27.9	26.4	23.7	21.7	18.4	16.2	15.2	15.2	14.1	14.0	15.1
90°	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3	3.7	6.2	8.6
92.5°	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5	34.2	35.9	37.5
95°	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4	88.0	88.6	89.2
97.5°	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3	145.4	145.7	146.0
100°	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2
102.5°	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5	235.8	236.9	238.1
105°	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7	308.1	309.6	311.1
107.5°	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2	387.7	389.2	390.7
110°	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1	442.6	444.1	445.6



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0	497.8	498.6	499.4
115°	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6	580.9	582.0	583.2
117.5°	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5	663.0	663.5	664.1
120°	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1	715.6	717.1	718.6
122.5°	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1	770.6	771.2	771.7
125°	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9	847.7	849.5	851.3
127.5°	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6	927.6	928.6	929.6
130°	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0	976.5	978.0	979.5
132.5°	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4	1025.9	1028.3	1030.8
135°	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1	1101.9	1103.7	1105.5
137.5°	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2	1173.9	1175.6	1177.3
140°	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4	1219.9	1221.4	1222.9
142.5°	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7	1266.0	1267.2	1268.5
145°	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8	1333.9	1335.2	1336.3
147.5°	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7	1396.3	1397.0	1397.7
150°	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6	1437.3	1437.1	1436.7
152.5°	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0	1472.5	1472.9	1473.3
155°	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4	1571.7	1571.1	1570.4
160°	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4	1599.5	1598.6	1597.7
162.5°	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1	1624.4	1623.8	1623.2
165°	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2	1657.6	1657.0	1656.4
167.5°	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1	1685.0	1683.8	1682.6
170°	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2	1700.0	1698.8	1697.6
172.5°	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0	1710.8	1709.6	1708.4
175°	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1	1722.9	1721.7	1720.5
177.5°	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3	1729.3	1728.4	1727.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1609.3	1603.2	1598.2	1587.1	1580.9	1572.6	1565.9	1573.2	1565.4	1568.7	1563.7
5°	1559.2	1539.6	1525.8	1505.6	1488.3	1472.2	1460.4	1458.3	1452.8	1450.0	1441.6
7.5°	1498.8	1474.4	1450.5	1424.2	1401.9	1379.2	1364.8	1352.8	1344.9	1334.4	1327.4
10°	1463.2	1430.6	1402.8	1370.7	1342.9	1318.7	1299.1	1289.4	1280.4	1267.2	1262.3
12.5°	1419.2	1385.5	1351.6	1317.4	1290.7	1263.6	1246.9	1232.2	1225.9	1211.0	1209.5
15°	1366.5	1315.8	1282.5	1247.7	1210.9	1188.7	1174.7	1158.8	1151.8	1141.4	1133.7
17.5°	1303.8	1258.4	1216.7	1180.7	1149.1	1130.4	1113.1	1102.2	1090.2	1083.4	1070.9
20°	1258.1	1215.0	1173.3	1135.1	1110.8	1089.2	1075.3	1064.9	1052.4	1048.9	1036.4
22.5°	1219.8	1172.2	1132.2	1100.1	1073.5	1049.2	1034.2	1027.1	1018.5	1007.8	1005.2
25°	1157.4	1108.0	1074.0	1042.0	1018.3	996.1	985.7	976.6	968.3	960.6	957.9
27.5°	1103.4	1059.4	1018.9	990.0	969.4	949.1	940.0	929.0	922.8	916.7	909.2
30°	1065.6	1020.4	985.0	957.2	935.0	916.9	907.1	899.5	893.9	888.3	884.2
32.5°	1026.7	984.8	950.5	923.3	901.0	887.3	878.8	873.3	867.2	860.5	855.2
35°	975.3	929.3	896.0	872.4	855.0	844.5	834.8	829.9	823.0	823.0	817.4
37.5°	917.3	877.6	848.2	826.6	811.0	801.7	791.2	787.8	783.4	780.4	778.6
40°	882.8	846.0	818.1	796.6	779.9	772.2	763.9	758.4	755.5	752.1	750.7
42.5°	847.2	812.0	785.3	765.4	751.0	744.5	736.6	732.8	727.2	722.6	721.8
45°	793.1	759.0	734.8	718.7	706.2	698.6	693.8	685.4	682.6	677.1	676.4
47.5°	741.8	709.2	685.3	672.2	661.2	655.0	647.3	638.9	635.8	632.9	632.7
50°	703.5	673.6	651.3	638.8	628.4	619.4	611.7	606.1	604.0	604.0	605.5
52.5°	664.5	639.1	620.2	604.8	595.0	585.4	578.4	575.0	571.8	575.2	577.7
55°	607.5	581.8	567.9	553.3	543.6	532.4	529.0	527.6	525.5	531.1	533.9
57.5°	547.2	529.1	512.8	498.4	489.6	483.2	478.5	477.7	481.6	484.2	493.2
60°	508.8	487.9	473.4	462.3	451.8	447.6	446.3	444.9	447.6	455.3	467.1
62.5°	466.5	449.6	433.9	425.5	417.9	411.0	410.6	411.5	417.1	425.8	437.7
65°	404.6	389.9	379.5	369.8	363.6	359.4	360.8	363.6	369.8	381.7	394.8
67.5°	341.6	331.5	322.3	314.3	308.4	308.4	309.8	313.9	321.3	334.9	347.0
70°	301.0	289.9	282.2	278.7	273.8	271.1	275.3	282.2	288.5	301.0	311.4
72.5°	260.4	250.9	245.0	242.6	240.5	238.3	239.7	247.2	255.7	268.1	280.3
75°	200.2	196.7	192.5	189.8	187.7	189.0	190.5	197.4	204.4	217.6	231.5
77.5°	146.2	142.5	140.0	139.3	138.2	138.8	142.8	147.9	154.7	164.3	174.9
80°	110.5	109.1	107.7	107.0	107.0	107.7	113.3	116.8	123.1	132.1	140.4
82.5°	80.5	79.6	79.4	79.3	79.8	79.9	83.3	87.8	93.0	99.8	107.0
85°	42.4	41.0	43.1	43.8	42.4	44.5	45.8	48.7	50.7	54.2	57.7
87.5°	16.1	17.7	17.5	18.5	18.9	20.4	20.2	22.7	24.1	25.5	25.2
90°	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5	26.0	27.5	28.7
92.5°	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6	57.5	59.6	60.8
95°	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7	109.9	111.9	113.2
97.5°	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8	170.8	172.7	174.0
100°	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2	213.8	216.5	218.2
102.5°	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7	257.6	260.5	262.4
105°	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0	326.8	328.6	329.9
107.5°	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9	401.8	402.7	403.1
110°	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7	454.6	455.5	455.8



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5	506.9	507.3	507.3
115°	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1	586.8	586.5	586.2
117.5°	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8	668.1	668.2	667.8
120°	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2	722.2	722.2	721.6
122.5°	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5	775.3	775.0	774.5
125°	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2	853.5	852.9	852.5
127.5°	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2	931.9	931.6	931.1
130°	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8	983.6	983.2	982.8
132.5°	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3	1033.0	1032.7	1032.2
135°	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5	1109.5	1109.5	1108.9
137.5°	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7	1184.0	1184.4	1183.8
140°	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4	1231.0	1231.5	1231.1
142.5°	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1	1276.5	1276.9	1276.3
145°	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1	1342.1	1342.1	1341.7
147.5°	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3	1404.0	1404.7	1404.1
150°	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7	1441.7	1441.7	1441.4
152.5°	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6	1478.3	1479.0	1478.8
155°	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7	1530.0	1531.2	1531.1
157.5°	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2	1574.4	1575.6	1575.2
160°	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1	1601.2	1602.5	1602.3
162.5°	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3	1626.7	1628.2	1628.0
165°	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2	1660.5	1661.6	1661.3
167.5°	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4	1686.1	1687.9	1687.9
170°	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4	1701.2	1703.0	1702.9
172.5°	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2	1712.0	1713.8	1713.8
175°	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3	1724.1	1725.9	1725.7
177.5°	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8	1729.2	1730.6	1730.5
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1560.4	1564.2	1560.9	1565.4	1560.9	1564.2	1560.4	1563.7	1568.7	1565.4	1573.2
5°	1438.2	1431.9	1436.1	1433.3	1436.1	1431.9	1438.2	1441.6	1450.0	1452.8	1458.3
7.5°	1325.3	1319.3	1312.5	1309.3	1312.5	1319.3	1325.3	1327.4	1334.4	1344.9	1352.8
10°	1254.6	1247.1	1246.3	1241.4	1246.3	1247.1	1254.6	1262.3	1267.2	1280.4	1289.4
12.5°	1202.9	1195.9	1187.9	1185.9	1187.9	1195.9	1202.9	1209.5	1211.0	1225.9	1232.2
15°	1129.5	1124.0	1119.1	1123.3	1119.1	1124.0	1129.5	1133.7	1141.4	1151.8	1158.8
17.5°	1068.5	1063.9	1063.1	1057.9	1063.1	1063.9	1068.5	1070.9	1083.4	1090.2	1102.2
20°	1030.2	1026.7	1028.1	1019.0	1028.1	1026.7	1030.2	1036.4	1048.9	1052.4	1064.9
22.5°	999.6	992.7	991.9	990.2	991.9	992.7	999.6	1005.2	1007.8	1018.5	1027.1
25°	951.6	948.2	944.7	948.2	944.7	948.2	951.6	957.9	960.6	968.3	976.6
27.5°	909.7	905.6	904.6	905.0	904.6	905.6	909.7	909.2	916.7	922.8	929.0
30°	884.2	877.3	877.9	877.3	877.9	877.3	884.2	884.2	888.3	893.9	899.5
32.5°	856.4	851.7	850.7	849.4	850.7	851.7	856.4	855.2	860.5	867.2	873.3
35°	815.4	815.4	811.9	811.9	811.9	815.4	815.4	817.4	823.0	823.0	829.9
37.5°	776.9	776.1	774.1	774.4	774.1	776.1	776.9	778.6	780.4	783.4	787.8
40°	748.0	747.3	745.1	741.0	745.1	747.3	748.0	750.7	752.1	755.5	758.4
42.5°	720.1	717.7	716.8	715.4	716.8	717.7	720.1	721.8	722.6	727.2	732.8
45°	676.4	676.4	674.9	674.2	674.9	676.4	676.4	676.4	677.1	682.6	685.4
47.5°	633.8	635.1	637.7	637.3	637.7	635.1	633.8	632.7	632.9	635.8	638.9
50°	608.2	608.9	611.0	611.7	611.0	608.9	608.2	605.5	604.0	604.0	606.1
52.5°	579.9	583.9	586.6	586.1	586.6	583.9	579.9	577.7	575.2	571.8	575.0
55°	540.1	544.9	549.8	550.5	549.8	544.9	540.1	533.9	531.1	525.5	527.6
57.5°	500.8	507.6	512.7	514.3	512.7	507.6	500.8	493.2	484.2	481.6	477.7
60°	474.0	483.1	489.4	492.1	489.4	483.1	474.0	467.1	455.3	447.6	444.9
62.5°	448.4	458.6	464.8	465.5	464.8	458.6	448.4	437.7	425.8	417.1	411.5
65°	406.6	417.1	422.6	426.8	422.6	417.1	406.6	394.8	381.7	369.8	363.6
67.5°	361.6	372.0	378.2	381.5	378.2	372.0	361.6	347.0	334.9	321.3	313.9
70°	328.8	339.2	347.6	350.4	347.6	339.2	328.8	311.4	301.0	288.5	282.2
72.5°	296.5	305.9	312.5	315.8	312.5	305.9	296.5	280.3	268.1	255.7	247.2
75°	240.5	253.0	259.3	262.8	259.3	253.0	240.5	231.5	217.6	204.4	197.4
77.5°	185.5	196.9	200.6	202.4	200.6	196.9	185.5	174.9	164.3	154.7	147.9
80°	148.7	155.7	160.6	161.2	160.6	155.7	148.7	140.4	132.1	123.1	116.8
82.5°	114.3	120.1	121.6	123.4	121.6	120.1	114.3	107.0	99.8	93.0	87.8
85°	62.6	65.4	66.1	65.4	66.1	65.4	62.6	57.7	54.2	50.7	48.7
87.5°	26.5	26.1	26.3	27.6	26.3	26.1	26.5	25.2	25.5	24.1	22.7
90°	29.6	30.5	31.4	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5
92.5°	61.5	62.2	62.8	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6
95°	113.9	114.5	115.0	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7
97.5°	174.3	174.7	175.0	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8
100°	218.7	219.4	220.0	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2
102.5°	263.2	264.0	264.9	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7
105°	330.8	331.7	332.6	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0
107.5°	403.1	403.1	403.0	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9
110°	455.5	455.1	454.9	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	506.8	506.2	505.7	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5
115°	585.9	585.6	585.3	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1
117.5°	666.6	665.4	664.2	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8
120°	720.4	719.2	718.0	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2
122.5°	773.5	772.5	771.5	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5
125°	852.2	851.9	851.6	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2
127.5°	930.5	930.0	929.3	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2
130°	982.2	981.6	981.0	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8
132.5°	1031.4	1030.5	1029.7	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3
135°	1107.7	1106.5	1105.3	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5
137.5°	1182.3	1180.8	1179.3	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7
140°	1229.7	1228.2	1226.6	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4
142.5°	1274.8	1273.4	1271.8	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1
145°	1340.8	1339.9	1339.0	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1
147.5°	1402.0	1400.0	1398.0	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3
150°	1440.7	1440.2	1439.6	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7
152.5°	1477.7	1476.7	1475.6	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6
155°	1529.6	1528.0	1526.5	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7
157.5°	1573.2	1571.2	1569.2	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2
160°	1600.8	1599.3	1597.9	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1
162.5°	1626.3	1624.5	1622.8	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3
165°	1659.6	1657.8	1656.0	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2
167.5°	1686.0	1684.3	1682.4	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4
170°	1700.8	1698.7	1696.6	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4
172.5°	1711.9	1710.0	1708.2	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2
175°	1723.7	1721.5	1719.5	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3
177.5°	1728.8	1727.2	1725.5	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1565.9	1572.6	1580.9	1587.1	1598.2	1603.2	1609.3	1614.4	1623.2	1631.6	1641.6
5°	1460.4	1472.2	1488.3	1505.6	1525.8	1539.6	1559.2	1570.9	1594.6	1616.1	1637.0
7.5°	1364.8	1379.2	1401.9	1424.2	1450.5	1474.4	1498.8	1525.8	1555.9	1591.5	1621.0
10°	1299.1	1318.7	1342.9	1370.7	1402.8	1430.6	1463.2	1492.4	1529.2	1570.9	1609.9
12.5°	1246.9	1263.6	1290.7	1317.4	1351.6	1385.5	1419.2	1457.9	1500.8	1547.0	1596.0
15°	1174.7	1188.7	1210.9	1247.7	1282.5	1315.8	1366.5	1402.8	1457.0	1508.4	1567.4
17.5°	1113.1	1130.4	1149.1	1180.7	1216.7	1258.4	1303.8	1349.1	1401.3	1466.5	1533.1
20°	1075.3	1089.2	1110.8	1135.1	1173.3	1215.0	1258.1	1304.0	1368.0	1435.4	1507.0
22.5°	1034.2	1049.2	1073.5	1100.1	1132.2	1172.2	1219.8	1270.1	1336.9	1403.1	1480.9
25°	985.7	996.1	1018.3	1042.0	1074.0	1108.0	1157.4	1213.0	1279.0	1354.8	1434.0
27.5°	940.0	949.1	969.4	990.0	1018.9	1059.4	1103.4	1159.6	1221.8	1298.6	1386.4
30°	907.1	916.9	935.0	957.2	985.0	1020.4	1065.6	1118.5	1185.2	1260.3	1352.0
32.5°	878.8	887.3	901.0	923.3	950.5	984.8	1026.7	1080.6	1147.4	1223.5	1313.6
35°	834.8	844.5	855.0	872.4	896.0	929.3	975.3	1026.0	1089.9	1163.6	1246.3
37.5°	791.2	801.7	811.0	826.6	848.2	877.6	917.3	970.1	1028.0	1098.9	1178.3
40°	763.9	772.2	779.9	796.6	818.1	846.0	882.8	930.1	991.2	1057.3	1123.3
42.5°	736.6	744.5	751.0	765.4	785.3	812.0	847.2	893.3	950.1	1011.6	1069.9
45°	693.8	698.6	706.2	718.7	734.8	759.0	793.1	834.1	882.1	940.5	984.3
47.5°	647.3	655.0	661.2	672.2	685.3	709.2	741.8	776.7	820.2	863.6	894.5
50°	611.7	619.4	628.4	638.8	651.3	673.6	703.5	738.9	775.7	809.1	835.5
52.5°	578.4	585.4	595.0	604.8	620.2	639.1	664.5	696.1	732.4	756.3	778.3
55°	529.0	532.4	543.6	553.3	567.9	581.8	607.5	635.3	657.5	675.6	693.8
57.5°	478.5	483.2	489.6	498.4	512.8	529.1	547.2	571.8	584.9	594.1	608.2
60°	446.3	447.6	451.8	462.3	473.4	487.9	508.8	526.2	535.9	543.6	555.4
62.5°	410.6	411.0	417.9	425.5	433.9	449.6	466.5	480.6	488.7	492.4	503.6
65°	360.8	359.4	363.6	369.8	379.5	389.9	404.6	417.1	416.3	420.5	427.5
67.5°	309.8	308.4	308.4	314.3	322.3	331.5	341.6	348.8	348.9	354.5	358.0
70°	275.3	271.1	273.8	278.7	282.2	289.9	301.0	303.8	304.4	307.2	310.7
72.5°	239.7	238.3	240.5	242.6	245.0	250.9	260.4	262.1	262.2	263.9	269.6
75°	190.5	189.0	187.7	189.8	192.5	196.7	200.2	203.0	202.2	203.0	207.1
77.5°	142.8	138.8	138.2	139.3	140.0	142.5	146.2	145.8	146.5	146.4	151.1
80°	113.3	107.7	107.0	107.0	107.7	109.1	110.5	111.9	109.9	111.9	113.3
82.5°	83.3	79.9	79.8	79.3	79.4	79.6	80.5	81.3	80.9	81.9	82.8
85°	45.8	44.5	42.4	43.8	43.1	41.0	42.4	40.3	39.6	40.3	41.0
87.5°	20.2	20.4	18.9	18.5	17.5	17.7	16.1	15.1	14.0	14.1	15.2
90°	23.0	21.5	19.4	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3
92.5°	53.6	51.6	49.0	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5
95°	105.7	103.5	100.6	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4
97.5°	166.8	164.9	160.8	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3
100°	208.5	205.7	201.9	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2
102.5°	251.7	248.8	246.8	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5
105°	323.2	321.5	319.6	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7
107.5°	400.0	399.1	397.8	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2
110°	452.7	451.8	450.9	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	506.0	505.7	504.5	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0
115°	587.4	587.7	587.1	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6
117.5°	667.5	667.4	666.7	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5
120°	722.2	722.2	721.8	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1
122.5°	775.7	776.0	775.2	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1
125°	854.7	855.3	855.1	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9
127.5°	932.5	932.8	932.5	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6
130°	984.1	984.4	983.8	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0
132.5°	1033.6	1033.9	1034.0	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4
135°	1109.5	1109.5	1109.2	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1
137.5°	1183.3	1182.9	1182.2	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2
140°	1229.8	1229.2	1228.3	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4
142.5°	1275.8	1275.4	1274.3	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7
145°	1342.1	1342.1	1341.2	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8
147.5°	1402.6	1401.9	1401.1	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7
150°	1441.7	1441.7	1440.5	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6
152.5°	1476.9	1476.1	1475.6	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0
155°	1527.6	1526.4	1526.1	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1572.0	1570.7	1570.5	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4
160°	1598.8	1597.7	1597.4	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4
162.5°	1623.9	1622.4	1622.4	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1
165°	1658.0	1656.9	1656.5	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2
167.5°	1682.6	1680.8	1680.8	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1
170°	1697.6	1695.9	1695.9	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2
172.5°	1708.4	1706.6	1706.6	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0
175°	1720.5	1718.7	1718.7	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1
177.5°	1726.4	1724.9	1725.1	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1646.5	1654.4	1659.4	1668.8	1676.6	1681.1	1685.0	1688.3	1692.2	1695.5	1705.0
5°	1657.2	1675.2	1690.5	1714.1	1735.7	1752.4	1770.4	1786.5	1799.7	1818.4	1833.0
7.5°	1652.5	1684.6	1718.3	1754.9	1792.2	1827.0	1859.0	1888.9	1916.0	1948.8	1977.5
10°	1648.1	1691.9	1735.0	1784.3	1835.1	1878.2	1918.5	1959.5	1989.4	2031.1	2066.5
12.5°	1644.8	1696.3	1748.4	1807.7	1863.4	1924.3	1978.0	2007.9	2053.3	2086.7	2128.9
15°	1630.8	1698.9	1770.4	1837.2	1916.4	1972.7	2020.0	2078.4	2120.8	2163.2	2209.0
17.5°	1605.5	1682.7	1762.8	1850.2	1926.3	1986.7	2047.6	2104.0	2154.6	2211.4	2268.5
20°	1593.8	1671.1	1762.8	1852.4	1926.8	1990.1	2052.6	2114.5	2170.2	2243.1	2309.2
22.5°	1569.4	1662.7	1747.2	1834.7	1911.3	1980.0	2051.0	2121.2	2195.1	2277.6	2360.3
25°	1525.8	1620.3	1709.9	1796.2	1873.3	1959.5	2035.2	2129.1	2223.7	2332.8	2435.6
27.5°	1480.4	1570.9	1653.1	1736.3	1826.3	1924.0	2022.2	2128.7	2252.5	2390.2	2535.3
30°	1443.8	1529.2	1609.2	1694.7	1788.5	1898.4	2006.1	2132.6	2275.8	2430.8	2603.2
32.5°	1400.9	1479.7	1557.5	1648.0	1750.2	1866.1	1991.6	2130.4	2302.5	2478.6	2656.0
35°	1327.7	1393.7	1473.6	1570.2	1685.6	1818.4	1963.7	2127.7	2325.1	2527.4	2676.8
37.5°	1240.7	1302.3	1386.4	1492.4	1613.4	1755.9	1928.2	2122.9	2332.5	2493.8	2542.0
40°	1182.4	1239.4	1327.0	1436.8	1560.5	1711.4	1900.4	2106.2	2309.2	2412.0	2372.4
42.5°	1120.1	1179.9	1265.2	1373.9	1507.2	1671.3	1865.4	2071.2	2241.3	2280.2	2143.3
45°	1021.8	1083.7	1167.8	1277.6	1420.8	1598.7	1801.0	1988.0	2086.0	2015.8	1803.8
47.5°	930.5	988.5	1066.4	1179.7	1327.5	1511.5	1706.4	1855.6	1863.3	1695.8	1469.4
50°	868.2	921.7	1000.2	1113.6	1260.3	1446.5	1622.4	1739.8	1687.0	1497.3	1279.7
52.5°	807.0	859.4	936.8	1049.1	1194.1	1364.8	1528.4	1610.9	1511.3	1316.5	1130.7
55°	718.7	764.6	840.3	944.0	1081.6	1240.1	1379.1	1407.6	1278.3	1086.5	935.6
57.5°	632.6	675.4	744.3	839.7	965.5	1105.9	1214.6	1208.5	1071.8	907.2	787.6
60°	574.2	615.9	677.1	770.2	884.8	1005.8	1098.9	1076.7	941.2	799.4	698.6
62.5°	521.9	559.1	617.0	698.5	803.2	915.2	991.7	958.9	826.1	702.0	622.4
65°	444.9	476.2	525.5	595.0	681.9	774.4	833.4	791.0	677.7	581.1	517.2
67.5°	371.3	396.4	437.7	493.2	567.3	641.6	677.6	634.9	544.3	473.8	426.4
70°	324.6	346.9	378.8	428.2	492.8	555.4	582.5	544.3	466.5	405.9	371.8
72.5°	277.9	296.2	324.3	368.7	420.5	474.7	498.6	462.0	398.1	347.0	315.1
75°	214.8	227.3	246.7	277.3	318.3	361.5	374.7	342.7	301.7	263.4	242.6
77.5°	153.7	164.3	179.1	198.4	227.5	254.9	266.4	247.9	216.2	192.0	174.9
80°	118.2	123.8	136.3	152.2	175.1	192.5	200.2	188.4	166.1	148.0	134.8
82.5°	84.3	89.8	97.3	110.5	125.1	137.0	145.2	137.2	121.1	106.9	99.2
85°	41.0	44.5	48.7	54.2	65.4	72.3	71.6	66.7	60.5	54.9	50.7
87.5°	15.2	16.2	18.4	21.7	23.7	26.4	27.9	27.2	25.4	24.1	22.7
90°	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5
92.5°	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6
95°	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7
97.5°	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8
100°	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2
102.5°	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7
105°	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0
107.5°	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9
110°	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5
115°	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1
117.5°	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8
120°	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2
122.5°	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5
125°	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2
127.5°	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2
130°	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8
132.5°	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3
135°	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5
137.5°	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7
140°	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4
142.5°	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1
145°	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1
147.5°	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3
150°	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7
152.5°	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6
155°	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7
157.5°	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2
160°	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1
162.5°	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3
165°	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2
167.5°	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4
170°	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4
172.5°	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2
175°	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3
177.5°	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1712.7	1717.2	1726.6	1723.3	1727.8	1730.0	1732.2
5°	1851.1	1873.3	1883.0	1881.7	1896.2	1892.7	1889.3
7.5°	2007.3	2030.7	2043.8	2060.0	2069.5	2070.2	2078.4
10°	2095.8	2126.4	2138.9	2156.2	2167.4	2173.6	2172.9
12.5°	2163.6	2187.5	2215.5	2224.1	2239.1	2247.0	2244.1
15°	2245.2	2283.4	2312.7	2327.2	2346.0	2351.5	2359.2
17.5°	2318.1	2369.4	2403.4	2448.7	2465.8	2476.3	2470.1
20°	2373.1	2440.5	2474.6	2528.8	2558.7	2574.7	2569.1
22.5°	2438.2	2511.1	2574.1	2621.1	2666.6	2688.2	2692.6
25°	2549.7	2649.7	2742.2	2804.1	2860.3	2873.5	2902.8
27.5°	2674.2	2792.2	2891.1	2956.2	2995.3	3010.1	3019.2
30°	2752.6	2870.1	2944.5	2986.2	2998.7	2997.3	2995.9
32.5°	2791.0	2864.5	2878.9	2867.2	2838.6	2814.3	2789.1
35°	2736.7	2681.7	2599.7	2494.0	2416.2	2337.6	2330.0
37.5°	2461.2	2285.6	2149.1	1996.6	1908.6	1854.3	1816.8
40°	2202.1	2002.6	1837.2	1708.6	1618.9	1583.5	1548.7
42.5°	1920.7	1730.1	1583.6	1476.1	1408.7	1369.4	1341.8
45°	1560.5	1392.3	1277.6	1199.8	1146.2	1115.6	1098.2
47.5°	1278.7	1154.3	1056.9	1000.7	963.7	940.0	940.0
50°	1127.5	1008.6	944.0	899.5	867.5	848.7	852.2
52.5°	993.5	904.6	849.4	812.2	788.5	776.9	776.6
55°	830.6	766.7	730.6	703.5	687.4	674.2	677.1
57.5°	710.5	656.6	632.4	609.9	598.8	593.5	585.9
60°	636.1	594.3	573.5	555.4	544.3	540.1	532.4
62.5°	569.9	537.1	516.7	502.0	492.0	490.6	484.6
65°	478.9	453.9	435.9	428.9	418.5	415.7	415.7
67.5°	394.8	376.9	362.8	356.4	351.9	352.6	349.2
70°	342.0	327.4	318.3	311.4	307.9	308.6	305.9
72.5°	299.2	282.9	275.0	270.8	266.3	268.0	266.9
75°	226.6	218.3	214.1	209.9	207.1	205.7	204.4
77.5°	166.4	159.1	155.9	153.5	153.9	150.5	153.2
80°	128.6	122.3	120.3	116.8	116.1	116.1	115.4
82.5°	94.1	90.6	89.1	86.2	85.0	86.1	84.3
85°	48.7	45.8	45.2	45.2	43.8	42.4	45.8
87.5°	23.0	21.0	21.3	21.0	21.1	20.8	19.8
90°	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333485-940

CATALOG NUMBER: S125DIW-S1270D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)