

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333413-935

Luminaire Tested: **S125DIW-S850D1050U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333413-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6103.0 lumens  
Efficiency: N/A  
Efficacy: 116.0 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42				
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	41	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.4	1.7
10°-20°	301.9	4.9
20°-30°	490.2	8.0
30°-40°	598.0	9.8
40°-50°	544.0	8.9
50°-60°	433.3	7.1
60°-70°	301.8	4.9
70°-80°	160.9	2.6
80°-90°	43.1	0.7
90°-100°	75.1	1.2
100°-110°	221.7	3.6
110°-120°	375.6	6.2
120°-130°	494.3	8.1
130°-140°	553.8	9.1
140°-150°	542.8	8.9
150°-160°	455.9	7.5
160°-170°	303.0	5.0
170°-180°	106.1	1.7
0°-30°	893.6	14.6
0°-40°	1491.6	24.4
0°-60°	2468.9	40.5
0°-90°	2974.7	48.7
90°-120°	672.4	11.0
90°-150°	2263.2	37.1
90°-180°	3128.0	51.3
0°-180°	6103.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	35
90°	21	1	21	1	21	13
95°	75	57	75	57	75	76
105°	216	199	216	199	216	229
115°	380	376	380	376	380	375
125°	552	549	552	549	552	493
135°	716	714	716	714	716	553
145°	868	864	868	864	868	542
155°	989	989	989	989	989	455
165°	1073	1076	1073	1076	1073	302
175°	1114	1118	1114	1118	1114	106
180°	1121	1121	1121	1121	1121	



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	12.7	13.3	13.6	13.5	13.8	13.6	14.8	14.6	15.5	16.4	17.6
90°	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9	14.9	13.9	12.6
92.5°	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1	34.8	33.5	31.9
95°	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9	68.5	67.2	65.3
97.5°	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5	108.2	106.9	104.3
100°	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0	135.3	133.5	131.0
102.5°	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2	163.3	161.4	160.1
105°	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9	209.7	208.5	207.3
107.5°	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1	259.5	258.9	258.0
110°	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3	293.7	293.2	292.6



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6	328.3	328.0	327.3
115°	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8	381.1	381.3	380.8
117.5°	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2	433.1	432.9	432.6
120°	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5	468.5	468.5	468.3
122.5°	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1	503.3	503.4	502.9
125°	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1	554.5	554.8	554.7
127.5°	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7	604.9	605.1	604.9
130°	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3	638.4	638.6	638.3
132.5°	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3	670.5	670.7	670.8
135°	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7	719.7	719.7	719.5
137.5°	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8	767.6	767.4	767.0
140°	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1	797.8	797.4	796.8
142.5°	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9	827.6	827.4	826.6
145°	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6	870.6	870.6	870.1
147.5°	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3	909.9	909.4	909.0
150°	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2	935.2	935.2	934.4
152.5°	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5	958.0	957.6	957.3
155°	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8	991.0	990.2	990.0
157.5°	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5	1019.8	1019.0	1018.8
160°	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0	1037.2	1036.5	1036.2
162.5°	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4	1053.4	1052.5	1052.5
165°	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3	1075.6	1074.8	1074.6
167.5°	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7	1091.5	1090.4	1090.4
170°	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4	1101.3	1100.1	1100.1
172.5°	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4	1108.3	1107.1	1107.1
175°	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2	1116.1	1114.9	1114.9
177.5°	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8	1119.9	1119.0	1119.1
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	18.0	17.0	15.3	13.9	11.8	10.4	9.8	9.8	9.0	9.0	9.7
90°	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9	2.4	4.0	5.5
92.5°	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1	22.2	23.2	24.4
95°	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7	57.1	57.5	57.9
97.5°	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2	94.4	94.5	94.7
100°	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2	122.2	122.2	122.2
102.5°	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1	152.9	153.7	154.5
105°	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9	199.8	200.9	201.8
107.5°	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6	251.5	252.5	253.5
110°	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1	287.1	288.1	289.0





TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4	323.0	323.5	324.0
115°	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0	376.8	377.5	378.3
117.5°	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7	430.1	430.4	430.8
120°	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2	464.3	465.2	466.1
122.5°	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6	499.9	500.2	500.6
125°	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7	549.9	551.0	552.2
127.5°	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1	601.8	602.4	603.0
130°	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5	633.4	634.5	635.4
132.5°	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9	665.5	667.1	668.7
135°	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6	714.8	715.9	717.1
137.5°	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4	761.6	762.7	763.8
140°	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4	791.3	792.4	793.3
142.5°	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4	821.2	822.1	822.9
145°	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5	865.3	866.1	866.9
147.5°	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4	905.9	906.3	906.6
150°	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6	932.5	932.2	932.0
152.5°	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9	955.2	955.5	955.8
155°	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3	989.3	989.3	989.3
157.5°	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0	1019.6	1019.2	1018.7
160°	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2	1037.6	1037.0	1036.5
162.5°	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2	1053.8	1053.3	1052.9
165°	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7	1075.3	1074.9	1074.5
167.5°	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8	1093.0	1092.3	1091.5
170°	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6	1102.9	1102.1	1101.3
172.5°	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6	1109.8	1109.1	1108.3
175°	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4	1117.7	1116.9	1116.1
177.5°	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5	1121.8	1121.2	1120.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	10.3	11.4	11.3	11.9	12.1	13.2	13.0	14.6	15.5	16.4	16.3
90°	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9	16.9	17.8	18.6
92.5°	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1	37.4	38.7	39.4
95°	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9	71.2	72.6	73.4
97.5°	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5	110.8	112.1	112.8
100°	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0	138.7	140.4	141.5
102.5°	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2	167.1	169.0	170.2
105°	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9	212.0	213.2	214.0
107.5°	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1	260.7	261.2	261.6
110°	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3	294.9	295.5	295.7



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6	328.8	329.1	329.1
115°	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8	380.6	380.5	380.3
117.5°	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2	433.3	433.5	433.2
120°	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5	468.5	468.5	468.1
122.5°	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1	502.9	502.7	502.4
125°	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1	553.7	553.3	553.0
127.5°	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7	604.5	604.3	604.1
130°	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3	638.0	637.8	637.6
132.5°	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3	670.1	669.9	669.6
135°	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7	719.7	719.7	719.4
137.5°	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8	768.1	768.3	767.9
140°	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1	798.6	798.9	798.7
142.5°	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9	828.1	828.4	827.9
145°	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6	870.6	870.6	870.4
147.5°	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3	910.8	911.3	910.9
150°	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2	935.2	935.2	935.0
152.5°	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5	959.0	959.4	959.3
155°	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8	992.6	993.3	993.2
157.5°	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5	1021.3	1022.1	1021.8
160°	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0	1038.8	1039.6	1039.4
162.5°	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4	1055.2	1056.2	1056.1
165°	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3	1077.1	1077.9	1077.7
167.5°	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7	1093.8	1095.0	1095.0
170°	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4	1103.6	1104.7	1104.7
172.5°	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4	1110.6	1111.7	1111.7
175°	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2	1118.4	1119.6	1119.5
177.5°	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8	1121.8	1122.7	1122.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	17.0	16.8	17.0	17.7	17.0	16.8	17.0	16.3	16.4	15.5	14.6
90°	19.2	19.8	20.3	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9
92.5°	39.9	40.3	40.7	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1
95°	73.9	74.2	74.6	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9
97.5°	113.0	113.3	113.6	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5
100°	141.9	142.3	142.7	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0
102.5°	170.7	171.3	171.9	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2
105°	214.6	215.2	215.8	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9
107.5°	261.5	261.5	261.4	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1
110°	295.5	295.2	295.1	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	328.7	328.4	328.0	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6
115°	380.0	379.9	379.7	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8
117.5°	432.4	431.6	430.8	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2
120°	467.4	466.6	465.8	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5
122.5°	501.8	501.1	500.5	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1
125°	552.8	552.6	552.4	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1
127.5°	603.6	603.3	602.9	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7
130°	637.1	636.8	636.4	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3
132.5°	669.0	668.5	668.0	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3
135°	718.6	717.8	717.0	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7
137.5°	767.0	766.0	765.0	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8
140°	797.7	796.7	795.7	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1
142.5°	827.0	826.0	825.1	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9
145°	869.8	869.2	868.7	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6
147.5°	909.6	908.2	906.9	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3
150°	934.6	934.3	933.8	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2
152.5°	958.6	957.9	957.2	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5
155°	992.2	991.3	990.3	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8
157.5°	1020.5	1019.3	1018.0	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5
160°	1038.5	1037.5	1036.6	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0
162.5°	1055.0	1053.9	1052.7	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4
165°	1076.6	1075.4	1074.3	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3
167.5°	1093.8	1092.6	1091.4	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7
170°	1103.3	1102.0	1100.6	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4
172.5°	1110.5	1109.3	1108.1	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4
175°	1118.2	1116.8	1115.4	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2
177.5°	1121.5	1120.4	1119.4	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	13.0	13.2	12.1	11.9	11.3	11.4	10.3	9.7	9.0	9.0	9.8
90°	14.9	13.9	12.6	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9
92.5°	34.8	33.5	31.9	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1
95°	68.5	67.2	65.3	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7
97.5°	108.2	106.9	104.3	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2
100°	135.3	133.5	131.0	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2
102.5°	163.3	161.4	160.1	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1
105°	209.7	208.5	207.3	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9
107.5°	259.5	258.9	258.0	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6
110°	293.7	293.2	292.6	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	328.3	328.0	327.3	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4
115°	381.1	381.3	380.8	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0
117.5°	433.1	432.9	432.6	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7
120°	468.5	468.5	468.3	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2
122.5°	503.3	503.4	502.9	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6
125°	554.5	554.8	554.7	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7
127.5°	604.9	605.1	604.9	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1
130°	638.4	638.6	638.3	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5
132.5°	670.5	670.7	670.8	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9
135°	719.7	719.7	719.5	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6
137.5°	767.6	767.4	767.0	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4
140°	797.8	797.4	796.8	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4
142.5°	827.6	827.4	826.6	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4
145°	870.6	870.6	870.1	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5
147.5°	909.9	909.4	909.0	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4
150°	935.2	935.2	934.4	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6
152.5°	958.0	957.6	957.3	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9
155°	991.0	990.2	990.0	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3
157.5°	1019.8	1019.0	1018.8	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0
160°	1037.2	1036.5	1036.2	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2
162.5°	1053.4	1052.5	1052.5	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2
165°	1075.6	1074.8	1074.6	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7
167.5°	1091.5	1090.4	1090.4	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8
170°	1101.3	1100.1	1100.1	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6
172.5°	1108.3	1107.1	1107.1	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6
175°	1116.1	1114.9	1114.9	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4
177.5°	1119.9	1119.0	1119.1	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	9.8	10.4	11.8	13.9	15.3	17.0	18.0	17.6	16.4	15.5	14.6
90°	2.4	4.0	5.5	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9
92.5°	22.2	23.2	24.4	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1
95°	57.1	57.5	57.9	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9
97.5°	94.4	94.5	94.7	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5
100°	122.2	122.2	122.2	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0
102.5°	152.9	153.7	154.5	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2
105°	199.8	200.9	201.8	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9
107.5°	251.5	252.5	253.5	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1
110°	287.1	288.1	289.0	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3





TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	323.0	323.5	324.0	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6
115°	376.8	377.5	378.3	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8
117.5°	430.1	430.4	430.8	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2
120°	464.3	465.2	466.1	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5
122.5°	499.9	500.2	500.6	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1
125°	549.9	551.0	552.2	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1
127.5°	601.8	602.4	603.0	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7
130°	633.4	634.5	635.4	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3
132.5°	665.5	667.1	668.7	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3
135°	714.8	715.9	717.1	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7
137.5°	761.6	762.7	763.8	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8
140°	791.3	792.4	793.3	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1
142.5°	821.2	822.1	822.9	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9
145°	865.3	866.1	866.9	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6
147.5°	905.9	906.3	906.6	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3
150°	932.5	932.2	932.0	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2
152.5°	955.2	955.5	955.8	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5
155°	989.3	989.3	989.3	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8
157.5°	1019.6	1019.2	1018.7	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5
160°	1037.6	1037.0	1036.5	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0
162.5°	1053.8	1053.3	1052.9	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4
165°	1075.3	1074.9	1074.5	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3
167.5°	1093.0	1092.3	1091.5	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7
170°	1102.9	1102.1	1101.3	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4
172.5°	1109.8	1109.1	1108.3	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4
175°	1117.7	1116.9	1116.1	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2
177.5°	1121.8	1121.2	1120.6	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	14.8	13.6	13.8	13.5	13.6	13.3	12.7
90°	16.9	17.8	18.6	19.2	19.8	20.3	20.9
92.5°	37.4	38.7	39.4	39.9	40.3	40.7	41.2
95°	71.2	72.6	73.4	73.9	74.2	74.6	75.0
97.5°	110.8	112.1	112.8	113.0	113.3	113.6	113.7
100°	138.7	140.4	141.5	141.9	142.3	142.7	143.1
102.5°	167.1	169.0	170.2	170.7	171.3	171.9	172.4
105°	212.0	213.2	214.0	214.6	215.2	215.8	216.4
107.5°	260.7	261.2	261.6	261.5	261.5	261.4	261.4
110°	294.9	295.5	295.7	295.5	295.2	295.1	294.9



TEST NUMBER: P333413-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	328.8	329.1	329.1	328.7	328.4	328.0	327.7
115°	380.6	380.5	380.3	380.0	379.9	379.7	379.5
117.5°	433.3	433.5	433.2	432.4	431.6	430.8	430.1
120°	468.5	468.5	468.1	467.4	466.6	465.8	465.0
122.5°	502.9	502.7	502.4	501.8	501.1	500.5	499.9
125°	553.7	553.3	553.0	552.8	552.6	552.4	552.2
127.5°	604.5	604.3	604.1	603.6	603.3	602.9	602.5
130°	638.0	637.8	637.6	637.1	636.8	636.4	636.0
132.5°	670.1	669.9	669.6	669.0	668.5	668.0	667.4
135°	719.7	719.7	719.4	718.6	717.8	717.0	716.3
137.5°	768.1	768.3	767.9	767.0	766.0	765.0	764.1
140°	798.6	798.9	798.7	797.7	796.7	795.7	794.8
142.5°	828.1	828.4	827.9	827.0	826.0	825.1	824.1
145°	870.6	870.6	870.4	869.8	869.2	868.7	868.1
147.5°	910.8	911.3	910.9	909.6	908.2	906.9	905.6
150°	935.2	935.2	935.0	934.6	934.3	933.8	933.5
152.5°	959.0	959.4	959.3	958.6	957.9	957.2	956.5
155°	992.6	993.3	993.2	992.2	991.3	990.3	989.3
157.5°	1021.3	1022.1	1021.8	1020.5	1019.3	1018.0	1016.8
160°	1038.8	1039.6	1039.4	1038.5	1037.5	1036.6	1035.5
162.5°	1055.2	1056.2	1056.1	1055.0	1053.9	1052.7	1051.6
165°	1077.1	1077.9	1077.7	1076.6	1075.4	1074.3	1073.1
167.5°	1093.8	1095.0	1095.0	1093.8	1092.6	1091.4	1090.2
170°	1103.6	1104.7	1104.7	1103.3	1102.0	1100.6	1099.2
172.5°	1110.6	1111.7	1111.7	1110.5	1109.3	1108.1	1106.9
175°	1118.4	1119.6	1119.5	1118.2	1116.8	1115.4	1114.0
177.5°	1121.8	1122.7	1122.6	1121.5	1120.4	1119.4	1118.3
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0

(END OF REPORT)