

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333425-935

Luminaire Tested: **S125DIW-S850D1560U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333425-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1560U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7632.1 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	26	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.4	1.3
10°-20°	301.9	4.0
20°-30°	490.2	6.4
30°-40°	598.0	7.8
40°-50°	544.0	7.1
50°-60°	433.3	5.7
60°-70°	301.8	4.0
70°-80°	160.9	2.1
80°-90°	44.3	0.6
90°-100°	111.8	1.5
100°-110°	330.0	4.3
110°-120°	559.0	7.3
120°-130°	735.7	9.6
130°-140°	824.3	10.8
140°-150°	807.9	10.6
150°-160°	678.6	8.9
160°-170°	451.1	5.9
170°-180°	157.9	2.1
0°-30°	893.6	11.7
0°-40°	1491.6	19.5
0°-60°	2468.9	32.3
0°-90°	2975.9	39.0
90°-120°	1000.8	13.1
90°-150°	3368.6	44.1
90°-180°	4656.0	61.0
0°-180°	7632.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	35
90°	31	1	31	1	31	19
95°	112	84	112	84	112	114
105°	322	296	322	296	322	341
115°	565	560	565	560	565	559
125°	822	817	822	817	822	734
135°	1066	1062	1066	1062	1066	822
145°	1292	1287	1292	1287	1292	807
155°	1473	1473	1473	1473	1473	678
165°	1597	1601	1597	1601	1597	450
175°	1658	1665	1658	1665	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	14.8	15.3	15.6	15.4	15.6	15.3	16.4	16.2	17.0	17.7	18.8
90°	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7	22.2	20.8	18.8
92.5°	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6	51.7	49.9	47.4
95°	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0	102.0	100.0	97.1
97.5°	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0	161.1	159.2	155.2
100°	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9	201.3	198.6	194.9
102.5°	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9	243.1	240.2	238.3
105°	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8	312.1	310.4	308.6
107.5°	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1	386.2	385.4	384.1
110°	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1	437.1	436.3	435.4



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0	488.6	488.3	487.2
115°	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9	567.1	567.5	566.9
117.5°	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8	644.5	644.4	643.8
120°	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3	697.3	697.3	697.0
122.5°	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8	749.0	749.2	748.5
125°	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8	825.3	825.9	825.6
127.5°	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1	900.3	900.7	900.3
130°	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9	950.2	950.5	949.9
132.5°	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7	998.0	998.3	998.4
135°	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3	1071.3	1071.3	1071.0
137.5°	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9	1142.5	1142.2	1141.5
140°	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0	1187.4	1186.9	1186.0
142.5°	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2	1231.8	1231.5	1230.5
145°	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9	1295.9	1295.9	1295.0
147.5°	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0	1354.3	1353.6	1352.9
150°	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1	1392.1	1392.1	1390.9
152.5°	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7	1426.0	1425.3	1424.8
155°	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1	1475.0	1473.9	1473.5
157.5°	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0	1517.9	1516.7	1516.4
160°	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0	1543.8	1542.7	1542.4
162.5°	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3	1568.0	1566.5	1566.5
165°	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1	1600.9	1599.8	1599.5
167.5°	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3	1624.6	1622.9	1622.9
170°	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9	1639.2	1637.4	1637.4
172.5°	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3	1649.6	1647.9	1647.9
175°	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0	1661.2	1659.5	1659.5
177.5°	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3	1666.9	1665.5	1665.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	19.1	18.0	16.1	14.6	12.4	10.8	10.0	9.9	9.3	9.4	10.2
90°	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3	3.6	5.9	8.3
92.5°	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4	33.1	34.7	36.2
95°	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4	85.0	85.6	86.1
97.5°	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3	140.4	140.7	140.9
100°	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8
102.5°	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4	227.6	228.8	229.9
105°	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1	297.5	298.9	300.4
107.5°	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9	374.4	375.8	377.3
110°	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9	427.4	428.8	430.2





TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9	480.7	481.5	482.2
115°	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6	560.9	562.0	563.1
117.5°	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6	640.2	640.7	641.2
120°	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5	691.0	692.4	693.9
122.5°	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6	744.1	744.6	745.1
125°	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7	818.5	820.3	822.0
127.5°	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7	895.7	896.6	897.6
130°	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4	942.9	944.3	945.7
132.5°	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2	990.6	992.9	995.3
135°	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2	1063.9	1065.7	1067.4
137.5°	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8	1133.5	1135.1	1136.8
140°	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5	1177.9	1179.3	1180.8
142.5°	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2	1222.4	1223.6	1224.8
145°	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9	1288.0	1289.2	1290.3
147.5°	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6	1348.2	1348.8	1349.5
150°	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1	1387.8	1387.6	1387.2
152.5°	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3	1421.8	1422.2	1422.5
155°	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2	1517.6	1517.0	1516.3
160°	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2	1544.4	1543.5	1542.7
162.5°	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2	1568.5	1567.9	1567.3
165°	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1	1600.5	1599.9	1599.4
167.5°	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1	1626.9	1625.8	1624.6
170°	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6	1641.5	1640.3	1639.2
172.5°	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0	1651.9	1650.7	1649.6
175°	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7	1663.5	1662.4	1661.2
177.5°	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7	1669.7	1668.9	1667.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	11.0	12.2	12.2	13.0	13.4	14.6	14.5	16.2	17.2	18.2	18.1
90°	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7	25.1	26.5	27.7
92.5°	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6	55.5	57.5	58.7
95°	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0	106.1	108.1	109.3
97.5°	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0	164.9	166.8	168.0
100°	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9	206.5	209.1	210.7
102.5°	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9	248.7	251.5	253.4
105°	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8	315.6	317.3	318.6
107.5°	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1	388.0	388.8	389.3
110°	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1	438.9	439.8	440.1



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0	489.5	489.8	489.8
115°	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9	566.6	566.3	566.0
117.5°	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8	645.1	645.2	644.8
120°	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3	697.3	697.3	696.7
122.5°	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8	748.6	748.3	747.8
125°	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8	824.1	823.5	823.1
127.5°	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1	899.8	899.5	899.1
130°	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9	949.7	949.3	948.9
132.5°	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7	997.5	997.1	996.6
135°	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3	1071.3	1071.3	1070.7
137.5°	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9	1143.2	1143.6	1143.1
140°	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0	1188.6	1189.1	1188.7
142.5°	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2	1232.5	1233.0	1232.3
145°	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9	1295.9	1295.9	1295.5
147.5°	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0	1355.6	1356.3	1355.7
150°	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1	1392.1	1392.1	1391.7
152.5°	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7	1427.4	1428.1	1427.9
155°	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1	1477.3	1478.4	1478.3
157.5°	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0	1520.2	1521.3	1521.0
160°	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0	1546.1	1547.3	1547.1
162.5°	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3	1570.7	1572.1	1571.9
165°	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1	1603.3	1604.4	1604.1
167.5°	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3	1628.1	1629.8	1629.8
170°	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9	1642.6	1644.3	1644.3
172.5°	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3	1653.0	1654.8	1654.8
175°	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0	1664.7	1666.5	1666.3
177.5°	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3	1669.7	1671.0	1670.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	18.9	18.8	18.9	19.8	18.9	18.8	18.9	18.1	18.2	17.2	16.2
90°	28.6	29.4	30.3	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7
92.5°	59.4	60.0	60.6	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6
95°	109.9	110.6	111.1	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0
97.5°	168.3	168.7	169.0	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0
100°	211.2	211.8	212.4	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9
102.5°	254.2	254.9	255.8	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9
105°	319.4	320.3	321.2	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8
107.5°	389.2	389.2	389.1	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1
110°	439.8	439.5	439.2	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.3	488.8	488.3	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0
115°	565.8	565.4	565.2	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9
117.5°	643.6	642.5	641.4	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8
120°	695.6	694.4	693.3	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3
122.5°	746.8	745.9	744.9	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8
125°	822.9	822.5	822.3	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8
127.5°	898.5	897.9	897.3	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1
130°	948.4	947.8	947.2	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9
132.5°	995.8	995.0	994.2	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7
135°	1069.5	1068.4	1067.2	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3
137.5°	1141.6	1140.1	1138.7	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9
140°	1187.3	1185.9	1184.4	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0
142.5°	1230.9	1229.5	1228.0	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2
145°	1294.6	1293.7	1292.9	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9
147.5°	1353.8	1351.8	1349.9	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0
150°	1391.1	1390.6	1390.0	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1
152.5°	1426.8	1425.8	1424.8	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7
155°	1476.9	1475.4	1473.9	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1
157.5°	1519.0	1517.1	1515.2	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0
160°	1545.7	1544.2	1542.8	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0
162.5°	1570.3	1568.6	1566.9	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3
165°	1602.4	1600.7	1599.0	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1
167.5°	1628.0	1626.3	1624.4	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3
170°	1642.2	1640.2	1638.1	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9
172.5°	1652.9	1651.1	1649.3	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3
175°	1664.3	1662.2	1660.3	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0
177.5°	1669.3	1667.7	1666.0	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	14.5	14.6	13.4	13.0	12.2	12.2	11.0	10.2	9.4	9.3	9.9
90°	22.2	20.8	18.8	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3
92.5°	51.7	49.9	47.4	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4
95°	102.0	100.0	97.1	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4
97.5°	161.1	159.2	155.2	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3
100°	201.3	198.6	194.9	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8
102.5°	243.1	240.2	238.3	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4
105°	312.1	310.4	308.6	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1
107.5°	386.2	385.4	384.1	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9
110°	437.1	436.3	435.4	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	488.6	488.3	487.2	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9
115°	567.1	567.5	566.9	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6
117.5°	644.5	644.4	643.8	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6
120°	697.3	697.3	697.0	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5
122.5°	749.0	749.2	748.5	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6
125°	825.3	825.9	825.6	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7
127.5°	900.3	900.7	900.3	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7
130°	950.2	950.5	949.9	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4
132.5°	998.0	998.3	998.4	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2
135°	1071.3	1071.3	1071.0	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2
137.5°	1142.5	1142.2	1141.5	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8
140°	1187.4	1186.9	1186.0	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5
142.5°	1231.8	1231.5	1230.5	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2
145°	1295.9	1295.9	1295.0	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9
147.5°	1354.3	1353.6	1352.9	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6
150°	1392.1	1392.1	1390.9	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1
152.5°	1426.0	1425.3	1424.8	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3
155°	1475.0	1473.9	1473.5	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1517.9	1516.7	1516.4	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2
160°	1543.8	1542.7	1542.4	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2
162.5°	1568.0	1566.5	1566.5	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2
165°	1600.9	1599.8	1599.5	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1
167.5°	1624.6	1622.9	1622.9	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1
170°	1639.2	1637.4	1637.4	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6
172.5°	1649.6	1647.9	1647.9	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0
175°	1661.2	1659.5	1659.5	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7
177.5°	1666.9	1665.5	1665.7	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	10.0	10.8	12.4	14.6	16.1	18.0	19.1	18.8	17.7	17.0	16.2
90°	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7
92.5°	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6
95°	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0
97.5°	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0
100°	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9
102.5°	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9
105°	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8
107.5°	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1
110°	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1





TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0
115°	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9
117.5°	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8
120°	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3
122.5°	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8
125°	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8
127.5°	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1
130°	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9
132.5°	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7
135°	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3
137.5°	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9
140°	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0
142.5°	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2
145°	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9
147.5°	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0
150°	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1
152.5°	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7
155°	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1
157.5°	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0
160°	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0
162.5°	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3
165°	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1
167.5°	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3
170°	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9
172.5°	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3
175°	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0
177.5°	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	16.4	15.3	15.6	15.4	15.6	15.3	14.8
90°	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.9	439.8	440.1	439.8	439.5	439.2	438.9



TEST NUMBER: P333425-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)