

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333404-935

Luminaire Tested: **S125DIW-S850D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333404-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4555.8 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	92	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	60	78	70	63	58	62	57	52	55	50	47	48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	38	44	39	35	38	35	31	29
6	65	53	44	38	61	50	42	37	44	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.3
10°-20°	301.0	6.6
20°-30°	444.5	9.8
30°-40°	518.7	11.4
40°-50°	520.9	11.4
50°-60°	457.3	10.0
60°-70°	340.7	7.5
70°-80°	194.8	4.3
80°-90°	57.8	1.3
90°-100°	19.1	0.4
100°-110°	117.7	2.6
110°-120°	213.4	4.7
120°-130°	273.9	6.0
130°-140°	294.6	6.5
140°-150°	276.5	6.1
150°-160°	223.7	4.9
160°-170°	144.7	3.2
170°-180°	49.9	1.1
0°-30°	852.1	18.7
0°-40°	1370.8	30.1
0°-60°	2348.9	51.6
0°-90°	2942.2	64.6
90°-120°	350.2	7.7
90°-150°	1195.3	26.2
90°-180°	1614.0	35.4
0°-180°	4555.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	0	4	6	8	9	4
95°	22	20	6	8	8	28
105°	114	116	116	116	116	121
115°	215	217	217	216	213	213
125°	306	308	308	307	306	273
135°	381	384	383	382	380	294
145°	442	443	443	443	441	276
155°	487	485	485	486	483	224
165°	514	512	512	514	511	145
175°	526	523	524	526	523	50
180°	526	526	526	526	526	



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.4	19.5	19.6	19.8	20.0	20.0	20.0	19.9	19.9	19.8	20.0
90°	0.4	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.2	6.6
92.5°	6.0	5.5	5.0	4.6	4.0	4.0	4.6	5.2	5.7	6.2	6.6
95°	22.2	22.0	21.7	21.4	21.2	19.4	16.1	12.8	9.6	6.2	6.6
97.5°	46.3	46.8	47.3	47.8	48.2	45.2	38.7	32.2	25.7	19.2	16.7
100°	65.0	65.3	65.6	65.9	66.1	66.4	66.7	67.1	67.4	67.8	54.8
102.5°	84.0	84.4	84.7	85.1	85.4	85.7	85.8	86.0	86.3	86.4	84.0
105°	114.5	114.9	115.2	115.5	115.9	116.1	116.1	116.1	116.1	116.1	116.1
107.5°	146.1	146.1	146.1	146.1	146.1	146.2	146.4	146.5	146.7	146.9	147.0
110°	166.7	166.7	166.7	166.7	166.7	166.8	166.9	167.1	167.3	167.5	167.2



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	186.2	186.4	186.7	186.8	187.0	187.1	187.3	187.4	187.4	187.1
115°	215.0	215.4	215.9	216.3	216.7	217.0	217.1	217.1	217.2	217.3	217.0
117.5°	245.0	245.0	245.0	245.0	245.0	245.1	245.4	245.7	246.1	246.4	246.0
120°	263.7	263.6	263.6	263.5	263.4	263.5	263.7	264.0	264.2	264.5	264.3
122.5°	280.3	280.5	280.9	281.2	281.5	281.7	281.9	282.0	282.1	282.2	282.1
125°	305.7	306.3	306.9	307.5	308.2	308.5	308.5	308.5	308.5	308.5	308.2
127.5°	330.1	330.6	331.1	331.5	331.9	332.1	332.0	332.0	331.9	331.8	331.7
130°	345.1	345.5	345.9	346.4	346.8	347.1	347.2	347.2	347.3	347.4	347.2
132.5°	360.1	360.6	361.1	361.5	362.1	362.2	362.1	361.9	361.6	361.4	361.4
135°	381.3	381.9	382.4	382.9	383.4	383.6	383.4	383.2	383.1	382.9	382.7
137.5°	400.9	401.3	401.7	402.3	402.7	402.9	402.7	402.5	402.3	402.2	402.3
140°	413.6	413.8	414.0	414.1	414.3	414.4	414.3	414.2	414.1	414.1	414.2
142.5°	425.2	425.3	425.4	425.5	425.6	425.7	425.9	425.9	426.1	426.2	426.2
145°	442.1	442.3	442.5	442.6	442.8	442.9	442.9	442.9	442.9	442.9	443.0
147.5°	456.9	456.8	456.8	456.8	456.8	456.8	456.9	457.0	457.1	457.2	457.3
150°	466.2	466.1	465.9	465.7	465.5	465.5	465.7	465.9	466.1	466.2	466.4
152.5°	475.3	474.9	474.5	474.2	473.7	473.6	473.8	474.0	474.2	474.3	474.5
155°	486.9	486.4	485.9	485.3	484.8	484.7	484.8	485.0	485.2	485.3	485.6
157.5°	495.8	495.5	495.2	494.9	494.6	494.5	494.5	494.5	494.5	494.6	494.8
160°	502.0	501.5	501.0	500.5	500.0	499.8	499.9	500.0	500.1	500.2	500.5
162.5°	507.0	506.5	506.0	505.5	505.0	504.8	504.9	505.0	505.1	505.1	505.6
165°	513.8	513.2	512.7	512.2	511.7	511.4	511.5	511.6	511.7	511.8	512.3
167.5°	518.8	518.2	517.7	517.1	516.6	516.3	516.4	516.5	516.6	516.7	517.4
170°	521.6	521.0	520.3	519.7	519.1	518.8	518.9	519.0	519.1	519.2	519.9
172.5°	523.4	522.8	522.2	521.6	521.0	520.8	520.9	521.1	521.2	521.4	522.0
175°	525.5	525.0	524.4	523.9	523.4	523.1	523.2	523.3	523.4	523.5	524.2
177.5°	526.4	526.0	525.6	525.1	524.7	524.5	524.6	524.7	524.8	524.9	525.3
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	20.1	20.1	20.2	20.1	19.8	19.5	19.3	19.0
90°	7.1	7.5	7.9	8.4	8.6	8.9	9.1	9.4
92.5°	7.1	7.5	7.9	8.3	8.4	8.5	8.6	8.7
95°	7.1	7.5	7.9	8.2	8.2	8.2	8.2	8.2
97.5°	14.3	11.9	9.4	8.2	8.2	8.2	8.2	8.2
100°	42.0	29.1	16.2	9.6	9.2	8.9	8.5	8.2
102.5°	81.6	79.1	76.7	72.6	66.6	60.8	54.8	49.0
105°	116.1	116.1	116.1	116.1	116.0	115.9	115.8	115.7
107.5°	147.0	147.0	147.0	146.9	146.6	146.4	146.1	145.9
110°	166.9	166.7	166.4	166.3	166.4	166.5	166.6	166.7



TEST NUMBER: P333404-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.4	186.1	185.9	185.8	185.6	185.5	185.4
115°	216.6	216.3	215.9	215.5	215.0	214.5	214.0	213.4
117.5°	245.5	245.0	244.6	244.3	244.0	243.8	243.6	243.4
120°	264.2	264.0	263.8	263.5	263.0	262.6	262.2	261.7
122.5°	281.9	281.7	281.5	281.2	280.7	280.2	279.7	279.2
125°	307.8	307.5	307.1	306.8	306.5	306.3	306.0	305.7
127.5°	331.5	331.3	331.1	330.7	330.0	329.4	328.7	328.1
130°	346.9	346.6	346.4	346.0	345.6	345.2	344.7	344.3
132.5°	361.4	361.3	361.3	361.0	360.6	360.2	359.7	359.3
135°	382.5	382.4	382.2	381.9	381.3	380.8	380.3	379.8
137.5°	402.3	402.3	402.3	402.2	401.7	401.2	400.8	400.4
140°	414.4	414.6	414.7	414.6	414.1	413.5	413.0	412.5
142.5°	426.3	426.3	426.4	426.1	425.6	425.1	424.6	424.0
145°	443.1	443.2	443.2	443.0	442.5	442.0	441.4	440.9
147.5°	457.4	457.5	457.6	457.4	456.8	456.2	455.5	454.9
150°	466.6	466.7	466.9	466.7	466.0	465.3	464.6	463.9
152.5°	474.7	474.8	475.0	474.8	474.2	473.6	472.9	472.3
155°	485.9	486.1	486.4	486.1	485.4	484.7	484.1	483.4
157.5°	495.1	495.3	495.6	495.4	494.7	494.0	493.4	492.7
160°	500.8	501.2	501.5	501.4	500.7	500.0	499.3	498.6
162.5°	506.1	506.6	507.0	507.0	506.2	505.4	504.6	503.9
165°	512.9	513.4	513.9	513.8	513.2	512.4	511.7	511.0
167.5°	518.0	518.6	519.2	519.2	518.3	517.5	516.8	516.0
170°	520.6	521.3	522.0	521.9	521.2	520.4	519.6	518.8
172.5°	522.6	523.2	523.9	523.8	523.1	522.3	521.5	520.7
175°	524.9	525.6	526.2	526.2	525.5	524.7	523.9	523.1
177.5°	525.8	526.2	526.8	526.8	526.2	525.6	525.0	524.5
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5

(END OF REPORT)