

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333410-935

Luminaire Tested: **S125DIW-S850D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333410-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D770U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5585.8 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44				
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37				
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35	31				
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16				
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	1.9
10°-20°	301.0	5.4
20°-30°	444.5	8.0
30°-40°	518.7	9.3
40°-50°	520.9	9.3
50°-60°	457.3	8.2
60°-70°	340.7	6.1
70°-80°	194.8	3.5
80°-90°	58.5	1.0
90°-100°	31.3	0.6
100°-110°	192.7	3.5
110°-120°	349.6	6.3
120°-130°	448.6	8.0
130°-140°	482.6	8.6
140°-150°	452.9	8.1
150°-160°	366.4	6.6
160°-170°	237.0	4.2
170°-180°	81.7	1.5
0°-30°	852.1	15.3
0°-40°	1370.8	24.5
0°-60°	2348.9	42.1
0°-90°	2942.9	52.7
90°-120°	573.6	10.3
90°-150°	1957.7	35.0
90°-180°	2643.0	47.3
0°-180°	5585.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	1	6	10	13	15	4
95°	36	33	10	13	13	46
105°	188	190	190	190	190	199
115°	352	355	356	353	350	349
125°	501	505	505	503	501	447
135°	625	628	627	626	622	481
145°	724	725	725	726	722	453
155°	798	794	795	796	792	367
165°	842	838	838	842	837	238
175°	861	857	858	862	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.5	19.6	19.9	20.1	20.3	20.5	20.5	20.6	20.6	20.7	20.8
90°	0.6	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9
92.5°	9.8	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9
95°	36.3	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9
97.5°	75.9	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4
100°	106.5	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9
102.5°	137.7	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7
105°	187.5	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6
110°	273.0	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9



TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.7	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4
115°	352.1	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4
117.5°	401.3	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9
120°	431.9	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9
122.5°	458.9	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0
125°	500.8	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7
127.5°	540.7	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2
130°	565.2	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6
132.5°	589.7	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9
135°	624.6	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8
137.5°	656.6	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8
140°	677.5	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5
142.5°	696.4	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1
145°	724.1	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5
147.5°	748.4	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0
150°	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0
152.5°	778.4	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2
155°	797.5	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3
157.5°	812.1	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5
160°	822.3	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8
162.5°	830.5	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1
165°	841.5	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1
167.5°	849.6	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3
170°	854.3	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5
172.5°	857.3	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0
175°	860.7	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6
177.5°	862.1	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	20.9	21.1	21.2	21.2	20.9	20.7	20.5	20.2
90°	11.6	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	11.6	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	11.6	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	23.4	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	68.8	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	133.6	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.5	273.0	272.6	272.5	272.6	272.8	272.9	273.0





TEST NUMBER: P333410-935

CATALOG NUMBER: S125DIW-S850D770U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	305.9	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.8	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	402.1	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.7	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.7	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	504.1	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.9	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	568.3	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.9	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.5	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	678.7	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.2	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.7	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.2	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.2	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.5	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	795.7	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	810.9	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.3	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	828.9	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.0	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	848.3	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	852.6	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	856.0	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	859.7	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.2	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)