

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333388-940

Luminaire Tested: **S125DIW-S610D1340U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333388-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7038.0 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	78	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	24	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5154	5154	5154	5154
5°	5969	5172	4528	5172
10°	6944	5145	3968	5145
15°	7687	5107	3660	5107
20°	8605	5047	3413	5047
25°	10080	4980	3293	4980
30°	10888	4914	3188	4914
35°	8952	4788	3120	4788
40°	6363	4615	3044	4615
45°	4888	4381	3001	4381
50°	4173	4091	2995	4091
55°	3715	3806	3021	3806
60°	3352	3495	3099	3495
65°	3096	3183	3177	3183
70°	2814	2859	3225	2859
75°	2485	2518	3194	2518
80°	2094	2053	2923	2053
85°	1660	1482	2356	1482



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.1
10°-20°	228.8	3.3
20°-30°	371.4	5.3
30°-40°	453.1	6.4
40°-50°	412.2	5.9
50°-60°	328.3	4.7
60°-70°	228.7	3.2
70°-80°	121.9	1.7
80°-90°	34.0	0.5
90°-100°	56.6	0.8
100°-110°	348.8	5.0
110°-120°	632.6	9.0
120°-130°	811.9	11.5
130°-140°	873.3	12.4
140°-150°	819.7	11.6
150°-160°	663.1	9.4
160°-170°	428.8	6.1
170°-180°	147.9	2.1
0°-30°	677.0	9.6
0°-40°	1130.1	16.1
0°-60°	1870.6	26.6
0°-90°	2255.3	32.0
90°-120°	1038.1	14.7
90°-150°	3542.9	50.3
90°-180°	4783.0	68.0
0°-180°	7038.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	921	798	698	798	921	93
15°	1150	764	547	764	1150	329
25°	1415	699	462	699	1415	646
35°	1135	607	396	607	1135	695
45°	535	480	329	480	535	428
55°	330	338	268	338	330	297
65°	203	208	208	208	203	201
75°	100	101	128	101	100	107
85°	22	20	32	20	22	27
90°	28	1	28	1	28	13
95°	24	66	24	66	24	20
105°	343	340	343	340	343	310
115°	633	637	633	637	633	628
125°	906	906	906	906	906	806
135°	1126	1130	1126	1130	1126	869
145°	1307	1310	1307	1310	1307	816
155°	1433	1443	1433	1443	1433	660
165°	1515	1523	1515	1523	1515	427
175°	1550	1558	1550	1558	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	844.2	843.0	842.0	839.8	841.4	836.8	834.6	830.9	826.3	824.7	822.7
5°	920.7	922.4	924.1	916.9	917.7	912.9	902.1	893.2	886.2	877.0	870.6
7.5°	1012.8	1008.8	1008.5	1003.9	996.0	989.6	978.2	963.7	949.7	933.7	920.5
10°	1058.9	1059.3	1056.2	1050.8	1042.3	1036.2	1021.3	1007.1	989.8	969.5	954.9
12.5°	1093.6	1095.0	1091.2	1083.9	1079.7	1066.0	1054.4	1037.4	1016.9	1000.7	978.5
15°	1149.7	1145.9	1143.3	1134.1	1126.9	1112.8	1094.1	1076.5	1054.2	1033.5	1012.8
17.5°	1203.7	1206.8	1201.7	1193.3	1171.3	1154.6	1129.6	1105.5	1077.6	1050.0	1025.3
20°	1252.0	1254.7	1246.9	1232.3	1205.9	1189.3	1156.5	1125.2	1093.1	1057.6	1030.5
22.5°	1312.2	1310.0	1299.5	1277.3	1254.5	1223.7	1188.2	1150.2	1109.9	1069.7	1033.7
25°	1414.6	1400.3	1393.9	1366.5	1336.3	1291.3	1242.5	1187.0	1136.8	1083.6	1037.6
27.5°	1471.3	1466.9	1459.7	1440.6	1408.9	1360.8	1303.2	1235.6	1164.8	1097.7	1037.3
30°	1460.0	1460.6	1461.3	1455.2	1434.9	1398.6	1341.4	1268.5	1184.5	1109.0	1039.3
32.5°	1359.1	1371.5	1383.3	1397.2	1402.9	1396.0	1360.1	1294.3	1207.9	1122.0	1038.1
35°	1135.4	1139.2	1177.5	1215.4	1266.9	1306.9	1333.6	1304.5	1231.6	1133.1	1036.9
37.5°	885.3	903.7	930.1	973.0	1047.3	1113.8	1199.4	1238.8	1215.2	1136.7	1034.5
40°	754.7	771.7	788.9	832.6	895.3	975.9	1073.1	1156.1	1175.5	1125.2	1026.4
42.5°	653.9	667.4	686.5	719.3	771.7	843.1	936.0	1044.5	1111.2	1092.3	1009.3
45°	535.2	543.7	558.6	584.7	622.6	678.5	760.5	879.0	982.3	1016.6	968.8
47.5°	458.1	458.1	469.7	487.7	515.1	562.5	623.1	716.0	826.3	908.0	904.2
50°	415.3	413.6	422.8	438.4	460.0	491.5	549.5	623.7	729.7	822.2	847.8
52.5°	378.4	378.6	384.2	395.7	413.9	440.9	484.1	551.0	641.6	736.5	785.0
55°	329.9	328.6	335.0	342.8	356.1	373.6	404.8	455.9	529.4	622.9	685.9
57.5°	285.5	289.2	291.8	297.2	308.2	319.9	346.3	383.8	442.1	522.4	589.0
60°	259.5	263.2	265.2	270.6	279.5	289.6	310.0	340.5	389.6	458.7	524.7
62.5°	236.1	239.1	239.8	244.6	251.8	261.7	277.7	303.3	342.1	402.5	467.3
65°	202.6	202.6	203.9	209.0	212.4	221.2	233.4	252.0	283.2	330.3	385.5
67.5°	170.1	171.8	171.5	173.7	176.8	183.7	192.4	207.8	230.9	265.2	309.4
70°	149.0	150.4	150.1	151.8	155.2	159.5	166.7	181.2	197.8	227.3	265.2
72.5°	130.1	130.6	129.7	132.0	134.0	137.9	145.8	153.6	169.1	193.9	225.2
75°	99.6	100.2	100.9	102.3	104.3	106.4	110.4	118.2	128.4	147.0	167.0
77.5°	74.6	73.4	75.0	74.8	76.0	77.5	81.1	85.2	93.5	105.3	120.8
80°	56.3	56.5	56.5	56.9	58.6	59.7	62.7	65.7	72.1	81.0	91.8
82.5°	41.0	41.9	41.4	42.0	43.4	44.1	45.8	48.3	52.1	59.0	66.9
85°	22.4	20.7	21.3	22.0	22.0	22.4	23.7	24.7	26.8	29.4	32.5
87.5°	12.0	12.4	12.6	12.4	12.5	12.3	13.1	12.8	13.5	14.0	14.7
90°	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0	19.8	18.5	16.7
92.5°	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0	19.8	18.5	16.9
95°	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0	19.8	18.5	28.2
97.5°	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4	49.6	56.8	76.1
100°	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4	162.6	200.9	199.8
102.5°	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8	249.1	256.3	255.7
105°	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6	435.5	435.5	435.0
110°	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9	495.7	496.4	496.0



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6	554.6	555.5	555.3
115°	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2	643.2	644.3	644.0
117.5°	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7	729.1	730.4	729.4
120°	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9	783.5	783.9	783.2
122.5°	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5	836.1	836.6	836.2
125°	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3	913.4	914.4	914.4
127.5°	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6	983.1	983.6	983.8
130°	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3	1029.1	1029.8	1029.6
132.5°	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1	1071.3	1071.4	1072.0
135°	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9	1134.4	1134.9	1135.4
137.5°	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4	1192.3	1192.2	1192.7
140°	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3	1227.8	1227.3	1227.5
142.5°	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5	1263.4	1263.3	1262.9
145°	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2	1313.0	1312.7	1312.7
147.5°	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8	1355.5	1355.2	1354.9
150°	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0	1382.5	1382.0	1381.4
152.5°	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0	1406.5	1406.0	1405.5
155°	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1	1439.3	1438.6	1438.1
157.5°	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5	1466.6	1465.8	1465.8
160°	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5	1483.5	1482.5	1482.2
162.5°	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0	1498.6	1497.2	1496.9
165°	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1	1518.6	1517.1	1516.8
167.5°	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3	1533.5	1531.6	1531.3
170°	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1	1541.1	1539.0	1538.7
172.5°	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2	1547.3	1545.4	1545.0
175°	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8	1553.7	1551.7	1551.5
177.5°	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5	1557.1	1555.6	1555.4
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	821.1	819.2	817.1	813.2	808.6	806.2	802.5	800.0	795.0	791.0	786.7
5°	862.7	854.0	845.9	835.4	823.9	816.4	807.5	797.7	787.6	777.0	765.5
7.5°	905.9	890.4	873.4	855.2	837.4	821.0	805.3	790.0	775.6	758.2	743.5
10°	935.0	915.3	894.3	869.5	845.5	824.5	803.2	784.5	765.5	745.2	727.3
12.5°	963.9	937.7	908.1	880.9	852.0	826.7	801.6	777.8	753.9	731.4	710.5
15°	984.4	961.4	933.9	895.3	862.7	827.9	794.7	763.8	735.0	710.0	683.6
17.5°	997.8	968.2	938.7	901.7	859.1	820.0	782.4	747.2	714.7	682.9	657.5
20°	1000.3	969.8	939.0	902.8	859.1	814.3	776.8	734.4	699.5	666.6	635.4
22.5°	999.5	964.9	931.4	894.0	851.5	810.3	764.8	721.7	683.8	651.5	618.9
25°	991.8	954.9	912.9	875.3	833.3	789.6	743.5	698.8	660.2	623.3	591.1
27.5°	985.4	937.5	890.0	846.1	805.6	765.5	721.5	675.6	632.8	595.4	565.1
30°	977.6	925.1	871.6	825.8	784.2	745.2	703.6	658.9	614.1	577.6	545.0
32.5°	970.5	909.4	852.9	803.1	759.0	721.1	682.7	640.2	596.3	559.1	526.6
35°	957.0	886.2	821.4	765.2	718.1	679.2	647.0	607.3	567.0	531.1	500.0
37.5°	939.7	855.7	786.2	727.3	675.6	634.6	604.7	574.3	535.6	501.0	472.8
40°	926.1	834.0	760.5	700.2	646.7	604.0	576.2	547.4	515.2	483.0	453.3
42.5°	909.0	814.5	734.4	669.6	616.6	575.0	545.8	521.4	493.0	463.0	435.3
45°	877.7	779.1	692.4	622.6	569.1	528.1	497.9	479.7	458.3	429.9	406.5
47.5°	831.5	736.6	646.9	574.9	519.7	481.7	453.4	435.9	420.9	399.8	378.5
50°	790.6	704.9	614.1	542.7	487.4	449.2	423.1	407.2	394.3	378.0	360.1
52.5°	744.8	665.0	581.9	511.2	456.6	418.8	393.2	379.2	368.5	356.9	339.2
55°	672.1	604.3	527.1	460.0	409.6	372.6	350.3	338.0	329.2	320.5	309.6
57.5°	591.9	539.0	470.5	409.2	362.7	329.1	308.3	296.4	289.5	285.0	278.7
60°	535.6	490.2	431.2	375.3	329.9	300.1	279.8	270.6	264.9	261.2	256.5
62.5°	483.2	445.9	391.4	340.4	300.7	272.5	254.3	245.5	240.0	238.2	234.2
65°	406.2	377.4	332.3	290.0	256.1	232.0	216.8	208.3	204.9	202.9	203.2
67.5°	330.2	312.6	276.5	240.4	213.3	193.1	180.9	174.4	172.7	170.0	170.0
70°	283.8	270.6	240.1	208.7	184.6	169.1	158.2	151.4	149.7	148.4	148.0
72.5°	242.9	231.4	204.9	179.7	158.1	144.4	135.5	131.3	128.6	127.8	127.7
75°	182.6	176.1	155.2	135.2	120.3	110.8	104.7	100.9	98.9	98.5	98.9
77.5°	129.8	124.2	110.8	96.7	87.3	80.1	74.9	73.7	71.3	71.4	71.1
80°	97.6	93.8	85.3	74.2	66.4	60.3	57.6	55.2	54.6	53.5	54.6
82.5°	70.7	66.7	61.0	53.9	47.4	43.8	41.0	40.3	39.9	39.4	39.6
85°	34.9	35.2	31.8	26.4	23.7	21.7	20.0	20.0	19.6	19.4	19.6
87.5°	14.9	14.0	12.6	11.3	9.6	8.4	7.7	7.6	7.1	7.3	7.9
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7	16.3	14.9	13.5
95°	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8	65.0	64.3	63.5
97.5°	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4	138.8	140.2	141.5
100°	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8	193.6	194.3	195.1
102.5°	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1	250.1	251.1	252.1
105°	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5	340.5	341.5	342.5
107.5°	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2	433.2	433.2	433.2
110°	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4	552.1	552.7	553.2
115°	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3	638.6	639.9	641.1
117.5°	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2	726.1	726.1	726.0
120°	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6	781.4	781.1	780.9
122.5°	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5	831.5	832.5	833.5
125°	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3	908.1	909.9	911.7
127.5°	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6	979.9	981.1	982.4
130°	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9	1024.2	1025.5	1026.8
132.5°	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3	1068.7	1070.2	1071.7
135°	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3	1131.8	1133.4	1134.9
137.5°	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3	1189.5	1190.9	1192.2
140°	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1	1226.6	1227.2	1227.6
142.5°	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3	1260.6	1260.9	1261.2
145°	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4	1310.9	1311.4	1312.0
147.5°	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2	1354.2	1354.1	1354.0
150°	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1381.4	1381.0	1380.5
152.5°	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7	1407.7	1406.5	1405.4
155°	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1	1441.6	1440.1	1438.6
157.5°	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7	1468.8	1467.8	1467.0
160°	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2	1486.7	1485.1	1483.5
162.5°	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0	1501.5	1499.9	1498.3
165°	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9	1521.3	1519.7	1518.2
167.5°	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6	1536.1	1534.5	1532.9
170°	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0	1544.2	1542.3	1540.5
172.5°	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5	1549.7	1547.9	1546.0
175°	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5	1555.9	1554.4	1552.8
177.5°	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2	1559.0	1557.8	1556.6
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	784.3	781.2	778.8	773.4	770.4	766.3	763.1	766.6	762.9	764.5	762.1
5°	759.8	750.3	743.5	733.7	725.2	717.5	711.7	710.7	707.9	706.6	702.6
7.5°	730.4	718.5	706.9	694.0	683.1	672.2	665.0	659.2	655.4	650.3	646.8
10°	713.0	697.1	683.6	668.0	654.4	642.6	633.1	628.4	623.9	617.5	615.2
12.5°	691.6	675.2	658.6	641.9	629.0	615.7	607.6	600.5	597.4	590.1	589.4
15°	665.9	641.2	625.0	608.1	590.0	579.3	572.5	564.7	561.3	556.2	552.5
17.5°	635.3	613.2	592.9	575.4	560.0	550.9	542.4	537.1	531.3	528.0	521.8
20°	613.1	592.1	571.8	553.1	541.3	530.8	524.1	519.0	512.8	511.1	505.1
22.5°	594.4	571.2	551.7	536.1	523.2	511.3	504.0	500.5	496.3	491.1	489.9
25°	564.0	539.9	523.3	507.7	496.2	485.4	480.4	475.9	471.9	468.1	466.8
27.5°	537.7	516.2	496.5	482.4	472.4	462.5	458.1	452.7	449.7	446.7	443.1
30°	519.3	497.3	480.0	466.5	455.6	446.8	442.0	438.4	435.6	432.9	430.9
32.5°	500.3	479.9	463.2	450.0	439.1	432.5	428.2	425.6	422.6	419.4	416.8
35°	475.3	452.9	436.7	425.1	416.6	411.5	406.8	404.5	401.1	401.1	398.3
37.5°	447.0	427.7	413.3	402.8	395.2	390.7	385.6	384.0	381.7	380.3	379.4
40°	430.2	412.2	398.7	388.2	380.0	376.3	372.3	369.5	368.2	366.5	365.9
42.5°	412.9	395.7	382.7	373.0	366.0	362.7	359.0	357.1	354.4	352.1	351.8
45°	386.5	369.9	358.0	350.3	344.2	340.5	338.0	334.0	332.6	329.9	329.6
47.5°	361.5	345.5	333.9	327.5	322.2	319.1	315.4	311.4	309.8	308.4	308.4
50°	342.8	328.2	317.4	311.3	306.2	301.8	298.1	295.4	294.4	294.4	295.1
52.5°	323.9	311.5	302.2	294.8	290.0	285.3	281.9	280.2	278.7	280.3	281.5
55°	296.0	283.6	276.8	269.7	264.9	259.5	257.8	257.1	256.1	258.8	260.1
57.5°	266.6	257.9	249.9	242.9	238.6	235.5	233.2	232.8	234.7	235.9	240.4
60°	248.0	237.8	230.7	225.2	220.2	218.1	217.5	216.8	218.1	221.9	227.7
62.5°	227.4	219.1	211.4	207.4	203.7	200.3	200.1	200.5	203.2	207.5	213.3
65°	197.2	190.0	184.9	180.2	177.2	175.1	175.8	177.2	180.2	186.0	192.4
67.5°	166.5	161.6	157.0	153.2	150.3	150.3	151.0	153.0	156.6	163.2	169.1
70°	146.7	141.2	137.5	135.8	133.5	132.2	134.1	137.5	140.5	146.7	151.8
72.5°	126.9	122.3	119.4	118.2	117.2	116.1	116.8	120.5	124.6	130.7	136.6
75°	97.6	95.9	93.8	92.5	91.5	92.1	92.8	96.2	99.6	106.0	112.8
77.5°	71.2	69.5	68.2	67.9	67.3	67.7	69.6	72.1	75.4	80.1	85.2
80°	53.9	53.1	52.5	52.2	52.2	52.5	55.2	56.9	59.9	64.4	68.4
82.5°	39.2	38.8	38.7	38.6	38.9	39.0	40.6	42.8	45.3	48.7	52.2
85°	20.7	20.0	21.0	21.3	20.7	21.7	22.4	23.7	24.7	26.4	28.1
87.5°	8.6	9.5	9.6	10.3	10.6	11.6	11.5	12.8	13.6	14.4	14.4
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.3	23.6	24.6
92.5°	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0	22.3	23.6	24.4
95°	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0	22.3	23.6	24.3
97.5°	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4	35.1	27.8	24.3
100°	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4	86.2	48.0	28.4
102.5°	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8	234.6	227.4	215.0
105°	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	343.9
107.5°	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6	435.7	435.7	435.3
110°	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9	494.2	493.4	493.1



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6	552.7	551.7	551.0
115°	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2	641.1	640.2	638.8
117.5°	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7	726.4	725.1	724.0
120°	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9	782.4	781.9	781.0
122.5°	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5	835.0	834.6	833.5
125°	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3	911.3	910.3	909.4
127.5°	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6	982.0	981.4	980.2
130°	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3	1027.5	1026.8	1025.7
132.5°	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1	1070.9	1070.8	1070.1
135°	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9	1133.4	1132.8	1131.8
137.5°	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4	1192.5	1192.6	1191.9
140°	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3	1228.8	1229.3	1228.8
142.5°	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5	1263.6	1263.7	1263.0
145°	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2	1313.5	1313.8	1313.1
147.5°	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8	1356.1	1356.5	1355.7
150°	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0	1383.5	1384.0	1383.2
152.5°	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0	1407.6	1408.0	1407.4
155°	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1	1440.8	1441.6	1441.0
157.5°	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5	1468.3	1469.1	1468.5
160°	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5	1485.5	1486.6	1486.0
162.5°	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0	1501.6	1503.0	1502.5
165°	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1	1521.7	1523.2	1523.0
167.5°	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3	1537.1	1539.0	1538.7
170°	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1	1545.2	1547.2	1547.1
172.5°	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2	1551.0	1552.8	1552.6
175°	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8	1557.8	1559.9	1559.8
177.5°	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5	1560.0	1561.4	1561.3
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	760.4	762.3	760.7	762.9	760.7	762.3	760.4	762.1	764.5	762.9	766.6
5°	700.9	697.8	699.8	698.5	699.8	697.8	700.9	702.6	706.6	707.9	710.7
7.5°	645.9	642.9	639.6	638.0	639.6	642.9	645.9	646.8	650.3	655.4	659.2
10°	611.4	607.7	607.3	605.0	607.3	607.7	611.4	615.2	617.5	623.9	628.4
12.5°	586.2	582.7	578.9	577.9	578.9	582.7	586.2	589.4	590.1	597.4	600.5
15°	550.5	547.8	545.4	547.4	545.4	547.8	550.5	552.5	556.2	561.3	564.7
17.5°	520.7	518.4	518.1	515.6	518.1	518.4	520.7	521.8	528.0	531.3	537.1
20°	502.0	500.3	501.0	496.6	501.0	500.3	502.0	505.1	511.1	512.8	519.0
22.5°	487.1	483.8	483.4	482.5	483.4	483.8	487.1	489.9	491.1	496.3	500.5
25°	463.8	462.1	460.4	462.1	460.4	462.1	463.8	466.8	468.1	471.9	475.9
27.5°	443.4	441.3	440.9	441.0	440.9	441.3	443.4	443.1	446.7	449.7	452.7
30°	430.9	427.5	427.8	427.5	427.8	427.5	430.9	430.9	432.9	435.6	438.4
32.5°	417.3	415.0	414.6	413.9	414.6	415.0	417.3	416.8	419.4	422.6	425.6
35°	397.3	397.3	395.7	395.7	395.7	397.3	397.3	398.3	401.1	401.1	404.5
37.5°	378.5	378.3	377.2	377.4	377.2	378.3	378.5	379.4	380.3	381.7	384.0
40°	364.4	364.2	363.1	361.1	363.1	364.2	364.4	365.9	366.5	368.2	369.5
42.5°	351.0	349.8	349.3	348.7	349.3	349.8	351.0	351.8	352.1	354.4	357.1
45°	329.6	329.6	329.0	328.6	329.0	329.6	329.6	329.6	329.9	332.6	334.0
47.5°	308.9	309.5	310.8	310.6	310.8	309.5	308.9	308.4	308.4	309.8	311.4
50°	296.4	296.8	297.7	298.1	297.7	296.8	296.4	295.1	294.4	294.4	295.4
52.5°	282.6	284.5	285.8	285.6	285.8	284.5	282.6	281.5	280.3	278.7	280.2
55°	263.2	265.6	268.0	268.3	268.0	265.6	263.2	260.1	258.8	256.1	257.1
57.5°	244.1	247.4	249.9	250.7	249.9	247.4	244.1	240.4	235.9	234.7	232.8
60°	231.0	235.4	238.4	239.9	238.4	235.4	231.0	227.7	221.9	218.1	216.8
62.5°	218.6	223.5	226.6	226.9	226.6	223.5	218.6	213.3	207.5	203.2	200.5
65°	198.1	203.2	206.0	207.9	206.0	203.2	198.1	192.4	186.0	180.2	177.2
67.5°	176.2	181.3	184.3	185.9	184.3	181.3	176.2	169.1	163.2	156.6	153.0
70°	160.2	165.3	169.3	170.8	169.3	165.3	160.2	151.8	146.7	140.5	137.5
72.5°	144.5	149.0	152.3	153.9	152.3	149.0	144.5	136.6	130.7	124.6	120.5
75°	117.2	123.3	126.4	128.0	126.4	123.3	117.2	112.8	106.0	99.6	96.2
77.5°	90.4	95.9	97.7	98.6	97.7	95.9	90.4	85.2	80.1	75.4	72.1
80°	72.5	75.9	78.3	78.6	78.3	75.9	72.5	68.4	64.4	59.9	56.9
82.5°	55.7	58.5	59.3	60.2	59.3	58.5	55.7	52.2	48.7	45.3	42.8
85°	30.5	31.8	32.2	31.8	32.2	31.8	30.5	28.1	26.4	24.7	23.7
87.5°	15.1	15.0	15.2	15.9	15.2	15.0	15.1	14.4	14.4	13.6	12.8
90°	25.4	26.1	26.9	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0
92.5°	24.8	25.1	25.5	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0
95°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0
97.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4
100°	27.3	26.3	25.2	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4
102.5°	197.6	180.1	162.6	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8
105°	343.7	343.4	343.1	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0
107.5°	434.5	433.8	433.0	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6
110°	493.4	493.7	493.9	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	550.6	550.3	549.9	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6
115°	637.3	635.8	634.2	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2
117.5°	723.4	722.7	722.0	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7
120°	779.7	778.4	777.1	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9
122.5°	832.1	830.5	829.0	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5
125°	908.7	907.9	907.0	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3
127.5°	978.3	976.4	974.5	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6
130°	1024.5	1023.1	1021.9	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3
132.5°	1068.8	1067.6	1066.2	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1
135°	1130.3	1128.7	1127.2	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9
137.5°	1190.6	1189.3	1187.9	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4
140°	1227.3	1225.7	1224.2	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3
142.5°	1261.4	1259.9	1258.4	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5
145°	1311.5	1310.0	1308.5	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2
147.5°	1353.8	1351.9	1350.1	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8
150°	1381.2	1379.1	1377.1	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0
152.5°	1405.5	1403.7	1401.9	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0
155°	1439.0	1436.9	1434.9	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1
157.5°	1466.4	1464.4	1462.3	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5
160°	1484.0	1481.9	1479.9	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5
162.5°	1500.3	1498.0	1495.8	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0
165°	1520.9	1518.9	1516.8	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1
167.5°	1536.4	1534.2	1531.9	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3
170°	1544.8	1542.5	1540.2	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1
172.5°	1550.3	1548.0	1545.7	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2
175°	1557.5	1555.1	1552.8	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8
177.5°	1559.6	1558.0	1556.3	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	763.1	766.3	770.4	773.4	778.8	781.2	784.3	786.7	791.0	795.0	800.0
5°	711.7	717.5	725.2	733.7	743.5	750.3	759.8	765.5	777.0	787.6	797.7
7.5°	665.0	672.2	683.1	694.0	706.9	718.5	730.4	743.5	758.2	775.6	790.0
10°	633.1	642.6	654.4	668.0	683.6	697.1	713.0	727.3	745.2	765.5	784.5
12.5°	607.6	615.7	629.0	641.9	658.6	675.2	691.6	710.5	731.4	753.9	777.8
15°	572.5	579.3	590.0	608.1	625.0	641.2	665.9	683.6	710.0	735.0	763.8
17.5°	542.4	550.9	560.0	575.4	592.9	613.2	635.3	657.5	682.9	714.7	747.2
20°	524.1	530.8	541.3	553.1	571.8	592.1	613.1	635.4	666.6	699.5	734.4
22.5°	504.0	511.3	523.2	536.1	551.7	571.2	594.4	618.9	651.5	683.8	721.7
25°	480.4	485.4	496.2	507.7	523.3	539.9	564.0	591.1	623.3	660.2	698.8
27.5°	458.1	462.5	472.4	482.4	496.5	516.2	537.7	565.1	595.4	632.8	675.6
30°	442.0	446.8	455.6	466.5	480.0	497.3	519.3	545.0	577.6	614.1	658.9
32.5°	428.2	432.5	439.1	450.0	463.2	479.9	500.3	526.6	559.1	596.3	640.2
35°	406.8	411.5	416.6	425.1	436.7	452.9	475.3	500.0	531.1	567.0	607.3
37.5°	385.6	390.7	395.2	402.8	413.3	427.7	447.0	472.8	501.0	535.6	574.3
40°	372.3	376.3	380.0	388.2	398.7	412.2	430.2	453.3	483.0	515.2	547.4
42.5°	359.0	362.7	366.0	373.0	382.7	395.7	412.9	435.3	463.0	493.0	521.4
45°	338.0	340.5	344.2	350.3	358.0	369.9	386.5	406.5	429.9	458.3	479.7
47.5°	315.4	319.1	322.2	327.5	333.9	345.5	361.5	378.5	399.8	420.9	435.9
50°	298.1	301.8	306.2	311.3	317.4	328.2	342.8	360.1	378.0	394.3	407.2
52.5°	281.9	285.3	290.0	294.8	302.2	311.5	323.9	339.2	356.9	368.5	379.2
55°	257.8	259.5	264.9	269.7	276.8	283.6	296.0	309.6	320.5	329.2	338.0
57.5°	233.2	235.5	238.6	242.9	249.9	257.9	266.6	278.7	285.0	289.5	296.4
60°	217.5	218.1	220.2	225.2	230.7	237.8	248.0	256.5	261.2	264.9	270.6
62.5°	200.1	200.3	203.7	207.4	211.4	219.1	227.4	234.2	238.2	240.0	245.5
65°	175.8	175.1	177.2	180.2	184.9	190.0	197.2	203.2	202.9	204.9	208.3
67.5°	151.0	150.3	150.3	153.2	157.0	161.6	166.5	170.0	170.0	172.7	174.4
70°	134.1	132.2	133.5	135.8	137.5	141.2	146.7	148.0	148.4	149.7	151.4
72.5°	116.8	116.1	117.2	118.2	119.4	122.3	126.9	127.7	127.8	128.6	131.3
75°	92.8	92.1	91.5	92.5	93.8	95.9	97.6	98.9	98.5	98.9	100.9
77.5°	69.6	67.7	67.3	67.9	68.2	69.5	71.2	71.1	71.4	71.3	73.7
80°	55.2	52.5	52.2	52.2	52.5	53.1	53.9	54.6	53.5	54.6	55.2
82.5°	40.6	39.0	38.9	38.6	38.7	38.8	39.2	39.6	39.4	39.9	40.3
85°	22.4	21.7	20.7	21.3	21.0	20.0	20.7	19.6	19.4	19.6	20.0
87.5°	11.5	11.6	10.6	10.3	9.6	9.5	8.6	7.9	7.3	7.1	7.6
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	19.8	18.5	16.9	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7
95°	19.8	18.5	28.2	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8
97.5°	49.6	56.8	76.1	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4
100°	162.6	200.9	199.8	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8
102.5°	249.1	256.3	255.7	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1
105°	344.0	344.0	344.0	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5
107.5°	435.5	435.5	435.0	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2
110°	495.7	496.4	496.0	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	554.6	555.5	555.3	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4
115°	643.2	644.3	644.0	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3
117.5°	729.1	730.4	729.4	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2
120°	783.5	783.9	783.2	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6
122.5°	836.1	836.6	836.2	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5
125°	913.4	914.4	914.4	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3
127.5°	983.1	983.6	983.8	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6
130°	1029.1	1029.8	1029.6	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9
132.5°	1071.3	1071.4	1072.0	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3
135°	1134.4	1134.9	1135.4	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3
137.5°	1192.3	1192.2	1192.7	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3
140°	1227.8	1227.3	1227.5	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1
142.5°	1263.4	1263.3	1262.9	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3
145°	1313.0	1312.7	1312.7	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4
147.5°	1355.5	1355.2	1354.9	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2
150°	1382.5	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0
152.5°	1406.5	1406.0	1405.5	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7
155°	1439.3	1438.6	1438.1	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1
157.5°	1466.6	1465.8	1465.8	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7
160°	1483.5	1482.5	1482.2	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2
162.5°	1498.6	1497.2	1496.9	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0
165°	1518.6	1517.1	1516.8	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9
167.5°	1533.5	1531.6	1531.3	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6
170°	1541.1	1539.0	1538.7	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0
172.5°	1547.3	1545.4	1545.0	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5
175°	1553.7	1551.7	1551.5	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5
177.5°	1557.1	1555.6	1555.4	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	802.5	806.2	808.6	813.2	817.1	819.2	821.1	822.7	824.7	826.3	830.9
5°	807.5	816.4	823.9	835.4	845.9	854.0	862.7	870.6	877.0	886.2	893.2
7.5°	805.3	821.0	837.4	855.2	873.4	890.4	905.9	920.5	933.7	949.7	963.7
10°	803.2	824.5	845.5	869.5	894.3	915.3	935.0	954.9	969.5	989.8	1007.1
12.5°	801.6	826.7	852.0	880.9	908.1	937.7	963.9	978.5	1000.7	1016.9	1037.4
15°	794.7	827.9	862.7	895.3	933.9	961.4	984.4	1012.8	1033.5	1054.2	1076.5
17.5°	782.4	820.0	859.1	901.7	938.7	968.2	997.8	1025.3	1050.0	1077.6	1105.5
20°	776.8	814.3	859.1	902.8	939.0	969.8	1000.3	1030.5	1057.6	1093.1	1125.2
22.5°	764.8	810.3	851.5	894.0	931.4	964.9	999.5	1033.7	1069.7	1109.9	1150.2
25°	743.5	789.6	833.3	875.3	912.9	954.9	991.8	1037.6	1083.6	1136.8	1187.0
27.5°	721.5	765.5	805.6	846.1	890.0	937.5	985.4	1037.3	1097.7	1164.8	1235.6
30°	703.6	745.2	784.2	825.8	871.6	925.1	977.6	1039.3	1109.0	1184.5	1268.5
32.5°	682.7	721.1	759.0	803.1	852.9	909.4	970.5	1038.1	1122.0	1207.9	1294.3
35°	647.0	679.2	718.1	765.2	821.4	886.2	957.0	1036.9	1133.1	1231.6	1304.5
37.5°	604.7	634.6	675.6	727.3	786.2	855.7	939.7	1034.5	1136.7	1215.2	1238.8
40°	576.2	604.0	646.7	700.2	760.5	834.0	926.1	1026.4	1125.2	1175.5	1156.1
42.5°	545.8	575.0	616.6	669.6	734.4	814.5	909.0	1009.3	1092.3	1111.2	1044.5
45°	497.9	528.1	569.1	622.6	692.4	779.1	877.7	968.8	1016.6	982.3	879.0
47.5°	453.4	481.7	519.7	574.9	646.9	736.6	831.5	904.2	908.0	826.3	716.0
50°	423.1	449.2	487.4	542.7	614.1	704.9	790.6	847.8	822.2	729.7	623.7
52.5°	393.2	418.8	456.6	511.2	581.9	665.0	744.8	785.0	736.5	641.6	551.0
55°	350.3	372.6	409.6	460.0	527.1	604.3	672.1	685.9	622.9	529.4	455.9
57.5°	308.3	329.1	362.7	409.2	470.5	539.0	591.9	589.0	522.4	442.1	383.8
60°	279.8	300.1	329.9	375.3	431.2	490.2	535.6	524.7	458.7	389.6	340.5
62.5°	254.3	272.5	300.7	340.4	391.4	445.9	483.2	467.3	402.5	342.1	303.3
65°	216.8	232.0	256.1	290.0	332.3	377.4	406.2	385.5	330.3	283.2	252.0
67.5°	180.9	193.1	213.3	240.4	276.5	312.6	330.2	309.4	265.2	230.9	207.8
70°	158.2	169.1	184.6	208.7	240.1	270.6	283.8	265.2	227.3	197.8	181.2
72.5°	135.5	144.4	158.1	179.7	204.9	231.4	242.9	225.2	193.9	169.1	153.6
75°	104.7	110.8	120.3	135.2	155.2	176.1	182.6	167.0	147.0	128.4	118.2
77.5°	74.9	80.1	87.3	96.7	110.8	124.2	129.8	120.8	105.3	93.5	85.2
80°	57.6	60.3	66.4	74.2	85.3	93.8	97.6	91.8	81.0	72.1	65.7
82.5°	41.0	43.8	47.4	53.9	61.0	66.7	70.7	66.9	59.0	52.1	48.3
85°	20.0	21.7	23.7	26.4	31.8	35.2	34.9	32.5	29.4	26.8	24.7
87.5°	7.7	8.4	9.6	11.3	12.6	14.0	14.9	14.7	14.0	13.5	12.8
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0
95°	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0
97.5°	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4
100°	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4
102.5°	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8
105°	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6
110°	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6
115°	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2
117.5°	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7
120°	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9
122.5°	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5
125°	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3
127.5°	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6
130°	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3
132.5°	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1
135°	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9
137.5°	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4
140°	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3
142.5°	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5
145°	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2
147.5°	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8
150°	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0
152.5°	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0
155°	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1
157.5°	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5
160°	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5
162.5°	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0
165°	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1
167.5°	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3
170°	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1
172.5°	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2
175°	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8
177.5°	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	834.6	836.8	841.4	839.8	842.0	843.0	844.2
5°	902.1	912.9	917.7	916.9	924.1	922.4	920.7
7.5°	978.2	989.6	996.0	1003.9	1008.5	1008.8	1012.8
10°	1021.3	1036.2	1042.3	1050.8	1056.2	1059.3	1058.9
12.5°	1054.4	1066.0	1079.7	1083.9	1091.2	1095.0	1093.6
15°	1094.1	1112.8	1126.9	1134.1	1143.3	1145.9	1149.7
17.5°	1129.6	1154.6	1171.3	1193.3	1201.7	1206.8	1203.7
20°	1156.5	1189.3	1205.9	1232.3	1246.9	1254.7	1252.0
22.5°	1188.2	1223.7	1254.5	1277.3	1299.5	1310.0	1312.2
25°	1242.5	1291.3	1336.3	1366.5	1393.9	1400.3	1414.6
27.5°	1303.2	1360.8	1408.9	1440.6	1459.7	1466.9	1471.3
30°	1341.4	1398.6	1434.9	1455.2	1461.3	1460.6	1460.0
32.5°	1360.1	1396.0	1402.9	1397.2	1383.3	1371.5	1359.1
35°	1333.6	1306.9	1266.9	1215.4	1177.5	1139.2	1135.4
37.5°	1199.4	1113.8	1047.3	973.0	930.1	903.7	885.3
40°	1073.1	975.9	895.3	832.6	788.9	771.7	754.7
42.5°	936.0	843.1	771.7	719.3	686.5	667.4	653.9
45°	760.5	678.5	622.6	584.7	558.6	543.7	535.2
47.5°	623.1	562.5	515.1	487.7	469.7	458.1	458.1
50°	549.5	491.5	460.0	438.4	422.8	413.6	415.3
52.5°	484.1	440.9	413.9	395.7	384.2	378.6	378.4
55°	404.8	373.6	356.1	342.8	335.0	328.6	329.9
57.5°	346.3	319.9	308.2	297.2	291.8	289.2	285.5
60°	310.0	289.6	279.5	270.6	265.2	263.2	259.5
62.5°	277.7	261.7	251.8	244.6	239.8	239.1	236.1
65°	233.4	221.2	212.4	209.0	203.9	202.6	202.6
67.5°	192.4	183.7	176.8	173.7	171.5	171.8	170.1
70°	166.7	159.5	155.2	151.8	150.1	150.4	149.0
72.5°	145.8	137.9	134.0	132.0	129.7	130.6	130.1
75°	110.4	106.4	104.3	102.3	100.9	100.2	99.6
77.5°	81.1	77.5	76.0	74.8	75.0	73.4	74.6
80°	62.7	59.7	58.6	56.9	56.5	56.5	56.3
82.5°	45.8	44.1	43.4	42.0	41.4	41.9	41.0
85°	23.7	22.4	22.0	22.0	21.3	20.7	22.4
87.5°	13.1	12.3	12.5	12.4	12.6	12.4	12.0
90°	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333388-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)