

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333380-940

Luminaire Tested: **S125DIW-S610D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333380-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D770U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4967.4 lumens  
Efficiency: N/A  
Efficacy: 132.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	31	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	1.6
10°-20°	228.1	4.6
20°-30°	336.8	6.8
30°-40°	393.0	7.9
40°-50°	394.7	7.9
50°-60°	346.5	7.0
60°-70°	258.2	5.2
70°-80°	147.6	3.0
80°-90°	44.8	0.9
90°-100°	32.4	0.7
100°-110°	199.6	4.0
110°-120°	362.0	7.3
120°-130°	464.6	9.4
130°-140°	499.8	10.1
140°-150°	469.1	9.4
150°-160°	379.5	7.6
160°-170°	245.4	4.9
170°-180°	84.6	1.7
0°-30°	645.6	13.0
0°-40°	1038.6	20.9
0°-60°	1779.7	35.8
0°-90°	2230.3	44.9
90°-120°	594.1	12.0
90°-150°	2027.6	40.8
90°-180°	2737.0	55.1
0°-180°	4967.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	6	11	14	16	4
95°	38	34	11	14	14	48
105°	194	197	197	197	196	206
115°	365	368	369	366	362	361
125°	519	523	523	521	519	463
135°	647	651	650	648	644	498
145°	750	751	751	752	748	469
155°	826	822	823	825	820	380
165°	872	868	868	872	867	246
175°	891	888	888	893	887	85
180°	891	891	891	891	891	



TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.8	15.0	15.2	15.4	15.7	15.9	16.0	16.1	16.1	16.2	16.3
90°	0.6	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3
92.5°	10.2	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3
95°	37.6	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3
97.5°	78.6	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4
100°	110.3	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1
102.5°	142.6	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6
105°	194.2	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2
110°	282.8	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7



TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.6	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4
115°	364.7	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1
117.5°	415.6	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2
120°	447.3	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4
122.5°	475.3	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5
125°	518.7	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7
127.5°	560.0	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6
130°	585.4	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9
132.5°	610.7	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1
135°	646.8	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2
137.5°	680.0	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3
140°	701.7	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7
142.5°	721.2	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0
145°	749.9	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4
147.5°	775.1	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7
150°	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2
152.5°	806.2	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9
155°	825.9	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7
157.5°	841.1	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4
160°	851.7	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0
162.5°	860.1	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6
165°	871.5	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1
167.5°	879.9	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5
170°	884.8	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9
172.5°	887.9	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5
175°	891.4	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2
177.5°	892.9	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	16.5	16.7	16.8	16.8	16.7	16.5	16.3	16.1
90°	12.0	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.0	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.0	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	24.3	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	71.2	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	138.4	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	283.2	282.8	282.3	282.2	282.3	282.5	282.7	282.8





TEST NUMBER: P333380-940

CATALOG NUMBER: S125DIW-S610D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.8	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	367.5	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	416.4	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	448.1	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	478.1	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	522.1	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.3	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.5	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	613.0	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.9	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	702.9	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.1	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.5	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	775.9	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.5	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.2	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.1	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	839.8	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	849.5	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	858.4	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.0	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	878.6	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	883.1	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	886.5	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	890.4	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	891.9	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)