

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333708-935

Luminaire Tested: **S125RDIW-S1090D1050U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333708-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1050U935-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7277.4 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9143	9143	9143	9143
5°	10519	9155	8085	9155
10°	12066	9108	7134	9108
15°	13032	9014	6341	9014
20°	14370	8906	5856	8906
25°	16631	8763	5433	8763
30°	18098	8611	5158	8611
35°	15266	8435	4902	8435
40°	10662	8118	4683	8118
45°	7909	7691	4469	7691
50°	6306	7246	4285	7246
55°	5353	6694	4122	6694
60°	4624	6200	3858	6200
65°	4121	5665	3321	5665
70°	3620	5189	3029	5189
75°	3132	4494	2842	4494
80°	2377	3782	2377	3782
85°	1979	2971	2238	2971



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.8	1.9
10°-20°	397.8	5.5
20°-30°	630.8	8.7
30°-40°	760.7	10.5
40°-50°	679.3	9.3
50°-60°	520.9	7.2
60°-70°	338.5	4.7
70°-80°	164.6	2.3
80°-90°	41.7	0.6
90°-100°	42.7	0.6
100°-110°	263.1	3.6
110°-120°	477.1	6.6
120°-130°	612.4	8.4
130°-140°	658.7	9.1
140°-150°	618.2	8.5
150°-160°	500.1	6.9
160°-170°	323.4	4.4
170°-180°	111.6	1.5
0°-30°	1164.4	16.0
0°-40°	1925.0	26.5
0°-60°	3125.2	42.9
0°-90°	3670.1	50.4
90°-120°	782.9	10.8
90°-150°	2672.2	36.7
90°-180°	3607.0	49.6
0°-180°	7277.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1416	1416	1416	1416	1416	
5°	1622	1412	1247	1412	1622	162
15°	1949	1348	948	1348	1949	559
25°	2334	1230	762	1230	2334	1072
35°	1936	1070	622	1070	1936	1170
45°	866	842	489	842	866	691
55°	475	594	366	594	475	431
65°	270	371	217	371	270	268
75°	126	180	114	180	126	134
85°	27	40	30	40	27	31
90°	21	1	21	1	21	10
95°	18	50	18	50	18	15
105°	259	256	259	256	259	234
115°	477	481	477	481	477	474
125°	684	684	684	684	684	608
135°	849	852	849	852	849	655
145°	986	988	986	988	986	616
155°	1081	1088	1081	1088	1081	498
165°	1142	1149	1142	1149	1142	322
175°	1170	1175	1170	1175	1170	111
180°	1175	1175	1175	1175	1175	



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1489.1	1488.2	1490.0	1484.9	1485.4	1477.5	1477.5	1471.4	1463.5	1457.5	1454.7
5°	1622.5	1623.7	1621.3	1612.7	1606.8	1598.1	1588.2	1570.8	1556.3	1542.3	1531.3
7.5°	1759.9	1760.7	1753.0	1750.3	1735.7	1725.0	1703.1	1679.3	1658.3	1631.6	1611.1
10°	1839.9	1839.3	1831.1	1824.7	1812.0	1795.7	1774.2	1746.3	1720.1	1691.1	1663.2
12.5°	1886.4	1884.8	1882.2	1874.5	1862.6	1848.2	1830.0	1802.5	1770.3	1738.5	1706.0
15°	1949.1	1945.0	1937.5	1927.6	1910.7	1893.9	1873.5	1849.2	1818.3	1782.3	1752.1
17.5°	2026.7	2026.9	2015.3	2001.5	1978.6	1948.9	1917.4	1878.1	1836.3	1796.6	1764.4
20°	2090.9	2089.1	2077.5	2050.8	2024.6	1987.4	1951.5	1903.2	1852.0	1800.4	1760.2
22.5°	2183.0	2178.4	2166.3	2131.2	2090.7	2042.8	1987.7	1928.7	1866.9	1808.2	1755.6
25°	2333.8	2330.3	2306.4	2265.8	2208.9	2135.0	2063.0	1982.2	1893.3	1816.0	1752.1
27.5°	2437.0	2433.2	2415.5	2381.7	2329.2	2251.5	2154.0	2046.0	1935.0	1828.7	1736.6
30°	2426.8	2435.5	2433.2	2417.5	2378.0	2308.3	2218.2	2096.7	1964.8	1839.9	1730.0
32.5°	2280.8	2288.6	2309.0	2339.9	2342.2	2314.3	2247.0	2134.8	1998.3	1856.1	1724.9
35°	1936.3	1946.8	1986.3	2048.5	2129.9	2197.8	2211.7	2151.3	2028.7	1875.9	1717.3
37.5°	1488.6	1545.8	1579.1	1644.5	1767.5	1892.5	2012.8	2057.1	2004.8	1867.8	1704.8
40°	1264.6	1278.5	1337.7	1411.5	1515.0	1645.2	1816.6	1940.3	1944.5	1849.2	1685.2
42.5°	1082.3	1099.9	1140.7	1199.5	1288.1	1418.3	1595.3	1758.6	1834.3	1798.0	1659.7
45°	865.9	879.3	908.9	954.2	1022.2	1129.7	1281.9	1470.8	1620.7	1679.5	1591.1
47.5°	711.3	718.5	744.3	778.9	829.1	907.5	1025.4	1189.3	1369.2	1495.2	1482.8
50°	627.6	635.8	655.5	681.7	724.1	790.3	884.5	1021.1	1206.4	1360.4	1391.2
52.5°	562.5	569.3	581.6	606.3	641.4	692.2	768.3	891.8	1058.6	1222.4	1293.6
55°	475.4	480.0	489.9	503.9	531.8	568.3	634.0	719.5	854.3	1019.3	1123.9
57.5°	403.6	405.9	412.2	425.1	444.4	471.1	518.5	590.9	687.6	836.2	951.7
60°	358.0	360.3	368.4	377.1	392.3	416.6	453.8	504.4	597.4	720.1	836.8
62.5°	321.7	323.1	326.6	335.3	348.5	367.4	396.7	437.9	511.9	619.6	729.9
65°	269.7	270.2	271.4	278.4	286.5	300.4	319.6	348.7	404.5	485.9	583.4
67.5°	219.6	220.5	224.5	227.0	235.5	242.8	254.1	276.3	315.6	370.4	446.3
70°	191.7	191.2	195.3	198.2	201.0	209.8	217.3	235.4	259.8	301.6	365.0
72.5°	165.7	164.2	166.0	167.0	170.8	176.8	184.3	195.4	214.2	243.1	291.5
75°	125.5	126.1	126.1	127.3	130.2	132.5	134.8	140.6	151.1	170.3	196.4
77.5°	88.1	87.1	89.6	90.0	91.7	94.3	96.3	98.6	102.9	110.7	124.2
80°	63.9	63.9	64.5	66.2	65.7	66.8	69.7	72.1	77.3	82.0	86.6
82.5°	49.1	48.6	49.2	49.5	49.4	50.5	51.6	52.1	54.1	56.4	59.6
85°	26.7	26.7	27.3	27.3	27.9	27.9	28.5	28.5	28.5	29.0	29.6
87.5°	14.4	13.9	13.3	13.1	13.5	14.3	13.6	12.9	12.7	12.6	12.7
90°	20.9	20.3	19.7	19.2	18.6	17.8	16.9	15.8	14.9	13.9	12.6
92.5°	19.5	19.2	18.9	18.7	18.4	17.8	16.9	15.8	14.9	13.9	12.7
95°	18.3	18.3	18.3	18.3	18.3	17.8	16.9	15.8	14.9	13.9	21.3
97.5°	18.3	18.3	18.3	18.3	18.3	21.0	26.4	31.9	37.4	42.9	57.4
100°	18.3	19.0	19.8	20.6	21.4	36.2	65.0	93.8	122.7	151.5	150.8
102.5°	109.5	122.7	135.9	149.0	162.2	171.5	176.9	182.4	187.9	193.3	192.9
105°	258.6	258.8	259.0	259.2	259.4	259.5	259.5	259.5	259.5	259.5	259.5
107.5°	326.1	326.6	327.2	327.8	328.4	328.6	328.6	328.6	328.5	328.5	328.0
110°	372.7	372.5	372.3	372.1	372.0	372.1	372.7	373.2	373.8	374.4	374.0



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	414.5	414.7	415.0	415.3	415.6	416.1	416.8	417.6	418.3	419.0	418.8
115°	477.2	478.4	479.5	480.7	481.8	482.8	483.5	484.3	485.1	485.9	485.7
117.5°	544.1	544.6	545.1	545.6	546.0	546.8	547.9	548.9	549.8	550.9	550.1
120°	585.1	586.2	587.1	588.1	589.0	589.7	590.1	590.5	590.9	591.2	590.6
122.5°	624.2	625.3	626.5	627.6	628.7	629.4	629.8	630.2	630.6	630.9	630.7
125°	683.5	684.2	684.8	685.4	685.9	686.6	687.3	688.1	688.9	689.7	689.7
127.5°	733.6	734.9	736.4	737.9	739.3	740.2	740.6	741.1	741.5	741.9	742.0
130°	769.8	770.8	771.7	772.7	773.6	774.4	775.0	775.6	776.2	776.7	776.5
132.5°	803.2	804.2	805.1	806.2	807.1	807.6	807.7	807.9	808.0	808.1	808.5
135°	849.0	850.2	851.4	852.5	853.7	854.5	854.8	855.2	855.6	856.0	856.4
137.5°	895.0	896.0	897.0	898.0	899.1	899.5	899.4	899.3	899.2	899.1	899.5
140°	922.1	923.3	924.5	925.7	926.8	927.2	926.8	926.4	926.0	925.7	925.8
142.5°	948.0	949.1	950.3	951.4	952.6	953.1	953.0	953.0	952.9	952.8	952.5
145°	985.8	986.9	988.1	989.2	990.4	990.8	990.7	990.5	990.3	990.1	990.1
147.5°	1016.9	1018.3	1019.7	1021.1	1022.5	1023.0	1022.9	1022.6	1022.4	1022.1	1021.9
150°	1037.1	1038.6	1040.2	1041.7	1043.3	1043.9	1043.5	1043.1	1042.8	1042.3	1042.0
152.5°	1055.9	1057.3	1058.7	1060.1	1061.5	1062.0	1061.6	1061.2	1060.8	1060.4	1060.1
155°	1080.6	1082.2	1083.7	1085.3	1086.8	1087.4	1086.8	1086.2	1085.5	1085.0	1084.6
157.5°	1101.4	1102.9	1104.5	1106.0	1107.6	1108.0	1107.4	1106.8	1106.2	1105.5	1105.5
160°	1114.7	1116.2	1117.8	1119.3	1120.8	1121.2	1120.4	1119.6	1118.9	1118.1	1117.9
162.5°	1126.4	1128.2	1129.9	1131.5	1133.2	1133.6	1132.5	1131.4	1130.3	1129.2	1129.0
165°	1142.5	1144.0	1145.6	1147.1	1148.7	1148.8	1147.7	1146.5	1145.4	1144.2	1144.0
167.5°	1153.7	1155.4	1157.1	1158.8	1160.6	1160.8	1159.3	1158.0	1156.6	1155.2	1155.0
170°	1159.9	1161.7	1163.4	1165.1	1166.8	1167.0	1165.4	1163.9	1162.4	1160.8	1160.5
172.5°	1164.1	1165.8	1167.5	1169.3	1171.0	1171.2	1169.8	1168.5	1167.0	1165.6	1165.3
175°	1169.5	1171.2	1172.9	1174.7	1176.5	1176.6	1175.0	1173.5	1171.9	1170.4	1170.2
177.5°	1172.6	1173.9	1175.1	1176.3	1177.6	1177.7	1176.6	1175.4	1174.4	1173.3	1173.1
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1454.7	1451.4	1445.4	1439.8	1432.8	1426.8	1422.6	1417.5	1411.0	1403.1	1396.5
5°	1519.1	1506.2	1489.4	1474.9	1456.3	1441.7	1426.7	1412.1	1397.6	1379.0	1362.7
7.5°	1590.4	1564.0	1538.3	1506.1	1476.8	1450.6	1425.5	1400.1	1375.2	1348.8	1323.4
10°	1634.1	1602.1	1566.7	1526.0	1488.8	1453.4	1420.8	1388.9	1355.2	1325.5	1293.6
12.5°	1675.1	1633.7	1593.2	1541.9	1497.2	1453.9	1412.5	1372.6	1336.6	1298.1	1263.9
15°	1712.0	1671.3	1626.0	1563.2	1501.1	1448.7	1399.9	1348.2	1303.5	1260.4	1222.1
17.5°	1726.3	1683.6	1631.0	1570.6	1502.7	1436.9	1374.0	1317.3	1264.6	1214.5	1171.4
20°	1720.7	1679.5	1625.4	1567.9	1495.2	1426.7	1358.7	1295.9	1237.3	1184.3	1138.4
22.5°	1707.2	1664.6	1612.4	1551.6	1482.6	1409.9	1337.3	1270.3	1208.8	1154.1	1104.1
25°	1687.0	1628.9	1575.5	1516.1	1450.5	1378.5	1303.5	1229.7	1164.0	1108.2	1053.6
27.5°	1665.9	1593.5	1525.4	1466.5	1397.1	1332.8	1260.6	1184.9	1115.9	1059.0	1003.0
30°	1646.9	1565.6	1490.6	1423.7	1358.1	1297.1	1228.5	1154.7	1083.8	1025.1	968.2
32.5°	1623.2	1536.7	1454.3	1377.3	1313.9	1253.4	1191.3	1120.8	1051.7	991.2	933.3
35°	1593.5	1483.1	1393.5	1311.6	1241.3	1182.6	1126.8	1069.9	1000.7	938.0	881.6
37.5°	1554.4	1429.1	1325.5	1236.3	1162.1	1103.2	1059.1	1007.1	944.0	883.9	831.6
40°	1530.7	1390.1	1276.7	1188.4	1110.5	1048.4	1007.1	962.9	905.4	849.0	796.7
42.5°	1499.1	1354.3	1227.4	1135.4	1057.0	997.2	955.5	916.9	868.7	815.5	759.5
45°	1437.1	1284.9	1151.8	1053.0	974.0	915.2	876.3	842.1	805.5	756.6	707.8
47.5°	1356.4	1212.5	1073.2	965.4	887.9	833.4	795.7	768.6	742.4	700.9	653.5
50°	1291.8	1153.0	1016.9	912.4	829.8	778.1	742.7	721.2	697.3	659.6	620.1
52.5°	1215.6	1091.6	958.4	851.4	773.6	725.1	691.0	669.6	650.0	619.1	581.4
55°	1095.5	986.8	864.7	767.7	696.2	647.4	614.8	594.5	582.9	556.7	527.1
57.5°	956.7	878.9	771.3	677.7	614.5	566.3	542.4	525.1	512.0	493.5	472.6
60°	860.1	805.5	708.9	620.1	562.0	516.0	494.6	480.0	467.8	452.1	435.8
62.5°	762.0	722.2	638.3	562.0	508.5	470.0	449.9	436.8	422.8	412.2	396.3
65°	630.5	595.0	536.9	477.1	427.7	396.9	382.4	370.7	362.1	350.4	339.4
67.5°	490.5	476.0	435.9	394.7	359.2	331.8	319.3	311.2	300.7	293.7	286.1
70°	404.5	397.5	369.0	341.7	308.6	290.0	278.4	274.8	262.1	255.1	249.9
72.5°	328.2	324.9	308.6	289.6	266.3	250.0	239.3	235.4	227.2	221.6	218.3
75°	224.9	226.1	223.2	210.9	202.2	191.7	182.4	180.1	174.4	169.7	166.8
77.5°	142.2	148.2	148.4	147.8	144.4	137.9	134.1	132.4	126.7	124.9	124.2
80°	97.6	104.0	109.9	109.3	108.1	106.3	103.4	101.7	98.8	97.0	95.9
82.5°	65.1	71.0	75.9	79.0	78.8	77.1	75.1	74.3	73.7	72.4	72.2
85°	30.8	31.9	33.7	37.8	40.6	41.2	40.6	40.1	38.3	38.9	39.5
87.5°	12.9	12.7	12.8	12.6	11.8	13.8	14.9	15.1	14.5	13.8	13.2
90°	11.2	9.9	8.5	7.1	5.5	4.0	2.4	0.9	2.4	4.0	5.5
92.5°	11.5	10.3	9.1	9.0	10.2	11.3	12.3	13.4	12.3	11.3	10.2
95°	28.7	36.0	43.3	47.4	47.9	48.5	49.1	49.6	49.1	48.5	47.9
97.5°	72.0	86.5	101.1	107.8	106.8	105.7	104.7	103.7	104.7	105.7	106.8
100°	150.0	149.2	148.4	147.7	147.1	146.5	146.0	145.4	146.0	146.5	147.1
102.5°	192.3	191.9	191.5	190.9	190.1	189.4	188.6	188.0	188.6	189.4	190.1
105°	259.5	259.5	259.5	259.1	258.3	257.5	256.8	256.0	256.8	257.5	258.3
107.5°	327.7	327.3	326.9	326.7	326.7	326.7	326.7	326.7	326.7	326.7	326.7
110°	373.7	373.2	372.9	372.7	372.7	372.7	372.7	372.7	372.7	372.7	372.7





TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	418.5	418.4	418.1	417.8	417.2	416.8	416.4	415.9	416.4	416.8	417.2
115°	485.5	485.3	485.1	484.6	483.5	482.6	481.6	480.7	481.6	482.6	483.5
117.5°	549.4	548.6	547.9	547.6	547.6	547.7	547.7	547.8	547.7	547.7	547.6
120°	590.1	589.5	588.9	588.8	588.9	589.1	589.4	589.5	589.4	589.1	588.9
122.5°	630.4	630.2	629.9	629.4	628.6	627.9	627.2	626.5	627.2	627.9	628.6
125°	689.7	689.7	689.7	689.0	687.6	686.3	684.9	683.5	684.9	686.3	687.6
127.5°	742.2	742.3	742.4	741.9	741.0	740.0	739.1	738.0	739.1	740.0	741.0
130°	776.4	776.2	775.9	775.4	774.4	773.4	772.5	771.5	772.5	773.4	774.4
132.5°	808.9	809.3	809.8	809.4	808.3	807.2	806.1	804.9	806.1	807.2	808.3
135°	856.8	857.1	857.6	857.1	856.0	854.8	853.7	852.5	853.7	854.8	856.0
137.5°	899.9	900.3	900.6	900.3	899.2	898.2	897.2	896.2	897.2	898.2	899.2
140°	926.0	926.3	926.4	926.3	925.9	925.6	925.1	924.8	925.1	925.6	925.9
142.5°	952.3	952.0	951.7	951.5	951.2	951.1	950.8	950.5	950.8	951.1	951.2
145°	990.1	990.1	990.1	989.9	989.5	989.1	988.8	988.3	988.8	989.1	989.5
147.5°	1021.7	1021.4	1021.2	1021.1	1021.2	1021.3	1021.4	1021.4	1021.4	1021.3	1021.2
150°	1041.6	1041.2	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3	1042.0	1041.6	1041.2
152.5°	1059.7	1059.3	1058.9	1059.1	1060.0	1060.8	1061.7	1062.6	1061.7	1060.8	1060.0
155°	1084.3	1083.8	1083.5	1083.8	1085.0	1086.2	1087.4	1088.5	1087.4	1086.2	1085.0
157.5°	1105.4	1105.4	1105.4	1105.7	1106.5	1107.2	1107.8	1108.5	1107.8	1107.2	1106.5
160°	1117.8	1117.5	1117.3	1117.8	1119.0	1120.2	1121.3	1122.5	1121.3	1120.2	1119.0
162.5°	1128.9	1128.7	1128.4	1128.9	1130.1	1131.3	1132.5	1133.6	1132.5	1131.3	1130.1
165°	1143.8	1143.7	1143.4	1143.9	1145.1	1146.2	1147.5	1148.6	1147.5	1146.2	1145.1
167.5°	1154.8	1154.6	1154.4	1154.9	1156.2	1157.4	1158.6	1159.7	1158.6	1157.4	1156.2
170°	1160.4	1160.2	1160.0	1160.5	1161.9	1163.3	1164.7	1166.0	1164.7	1163.3	1161.9
172.5°	1164.9	1164.6	1164.2	1164.8	1166.1	1167.4	1168.8	1170.2	1168.8	1167.4	1166.1
175°	1169.9	1169.8	1169.6	1170.0	1171.2	1172.3	1173.5	1174.7	1173.5	1172.3	1171.2
177.5°	1173.0	1172.9	1172.7	1173.1	1174.0	1174.9	1175.9	1176.8	1175.9	1174.9	1174.0
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1391.9	1385.4	1380.8	1371.5	1364.9	1362.2	1357.0	1355.6	1360.7	1357.0	1356.6
5°	1350.6	1333.7	1320.3	1306.9	1292.4	1283.1	1269.2	1266.9	1263.3	1258.1	1257.0
7.5°	1300.9	1278.9	1261.7	1239.7	1220.5	1205.1	1187.6	1179.3	1174.8	1168.0	1159.0
10°	1267.4	1241.3	1218.1	1195.9	1172.2	1153.0	1135.5	1122.1	1113.4	1105.3	1101.8
12.5°	1234.4	1207.8	1178.0	1151.3	1124.7	1103.2	1083.9	1075.2	1065.6	1056.0	1047.9
15°	1183.2	1147.7	1115.2	1084.3	1061.7	1038.5	1019.9	1007.1	992.6	988.5	972.8
17.5°	1128.8	1094.0	1055.9	1023.5	997.2	971.6	951.1	936.7	925.7	910.8	903.5
20°	1094.8	1053.6	1016.4	986.8	957.7	927.5	906.5	894.3	883.9	871.7	865.9
22.5°	1058.6	1018.2	980.2	945.4	915.8	886.1	871.2	858.6	846.7	835.4	827.8
25°	1005.3	964.7	924.5	888.6	857.7	836.2	818.8	804.3	797.9	786.9	778.7
27.5°	952.7	909.5	867.9	831.9	807.8	786.5	772.2	760.7	749.2	739.5	732.5
30°	918.8	874.6	829.2	800.8	775.2	754.8	739.2	728.1	719.5	710.8	705.5
32.5°	884.8	839.3	799.0	768.3	744.1	726.5	710.3	699.8	690.6	681.0	674.8
35°	830.4	783.9	751.4	721.2	697.3	681.1	670.0	655.0	647.4	640.4	634.0
37.5°	779.9	736.7	701.5	674.9	654.2	638.1	623.8	615.6	606.3	600.0	594.7
40°	742.7	703.2	671.2	643.3	628.2	610.2	596.8	586.3	579.4	571.3	565.4
42.5°	709.2	672.4	641.4	616.3	597.5	582.3	569.4	559.0	550.1	544.3	539.4
45°	661.9	625.3	595.0	571.8	554.4	539.8	526.5	521.2	509.6	502.7	500.3
47.5°	612.9	580.2	551.0	529.6	511.8	498.0	485.4	474.8	468.4	461.5	457.8
50°	580.0	548.5	521.2	500.3	482.9	467.8	456.2	449.2	440.5	434.1	429.5
52.5°	547.0	517.9	490.6	470.6	455.5	440.4	427.4	420.4	412.2	408.0	404.8
55°	499.8	469.0	445.7	425.9	410.3	396.3	384.1	377.1	372.0	367.8	366.7
57.5°	446.3	421.9	400.3	382.5	366.2	353.1	342.4	335.8	331.1	330.5	327.1
60°	411.5	389.3	369.6	350.4	336.5	324.3	315.0	307.4	302.7	302.2	301.0
62.5°	376.6	355.4	337.1	320.2	307.6	295.9	287.1	278.6	275.8	272.9	270.4
65°	324.9	305.7	290.6	277.2	263.8	253.9	245.2	240.0	233.6	230.1	223.8
67.5°	274.1	259.2	244.7	233.4	222.9	213.5	206.3	198.5	194.2	191.4	186.8
70°	240.6	228.9	214.5	202.2	194.1	186.6	180.7	172.0	169.1	166.8	164.5
72.5°	209.0	198.7	186.6	176.7	168.5	161.4	154.7	150.6	147.7	145.4	144.0
75°	164.5	154.5	144.1	137.2	131.3	125.5	122.0	119.2	118.0	117.4	115.0
77.5°	120.8	115.5	107.2	101.6	97.7	95.4	92.3	90.7	90.7	88.1	87.3
80°	92.4	89.5	82.5	80.2	77.3	75.0	73.2	70.3	67.4	66.2	64.5
82.5°	68.7	65.8	63.0	59.2	56.8	55.4	53.7	52.6	53.0	51.4	50.5
85°	36.6	33.7	32.5	31.9	30.8	31.9	31.3	30.8	30.2	29.6	30.2
87.5°	13.0	13.3	13.2	14.3	13.2	13.9	14.1	13.9	14.0	14.3	13.9
90°	7.1	8.5	9.9	11.2	12.6	13.9	14.9	15.8	16.9	17.8	18.6
92.5°	9.0	9.1	10.3	11.5	12.7	13.9	14.9	15.8	16.9	17.8	18.4
95°	47.4	43.3	36.0	28.7	21.3	13.9	14.9	15.8	16.9	17.8	18.3
97.5°	107.8	101.1	86.5	72.0	57.4	42.9	37.4	31.9	26.4	21.0	18.3
100°	147.7	148.4	149.2	150.0	150.8	151.5	122.7	93.8	65.0	36.2	21.4
102.5°	190.9	191.5	191.9	192.3	192.9	193.3	187.9	182.4	176.9	171.5	162.2
105°	259.1	259.5	259.5	259.5	259.5	259.5	259.5	259.5	259.5	259.5	259.4
107.5°	326.7	326.9	327.3	327.7	328.0	328.5	328.5	328.6	328.6	328.6	328.4
110°	372.7	372.9	373.2	373.7	374.0	374.4	373.8	373.2	372.7	372.1	372.0



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	417.8	418.1	418.4	418.5	418.8	419.0	418.3	417.6	416.8	416.1	415.6
115°	484.6	485.1	485.3	485.5	485.7	485.9	485.1	484.3	483.5	482.8	481.8
117.5°	547.6	547.9	548.6	549.4	550.1	550.9	549.8	548.9	547.9	546.8	546.0
120°	588.8	588.9	589.5	590.1	590.6	591.2	590.9	590.5	590.1	589.7	589.0
122.5°	629.4	629.9	630.2	630.4	630.7	630.9	630.6	630.2	629.8	629.4	628.7
125°	689.0	689.7	689.7	689.7	689.7	689.7	688.9	688.1	687.3	686.6	685.9
127.5°	741.9	742.4	742.3	742.2	742.0	741.9	741.5	741.1	740.6	740.2	739.3
130°	775.4	775.9	776.2	776.4	776.5	776.7	776.2	775.6	775.0	774.4	773.6
132.5°	809.4	809.8	809.3	808.9	808.5	808.1	808.0	807.9	807.7	807.6	807.1
135°	857.1	857.6	857.1	856.8	856.4	856.0	855.6	855.2	854.8	854.5	853.7
137.5°	900.3	900.6	900.3	899.9	899.5	899.1	899.2	899.3	899.4	899.5	899.1
140°	926.3	926.4	926.3	926.0	925.8	925.7	926.0	926.4	926.8	927.2	926.8
142.5°	951.5	951.7	952.0	952.3	952.5	952.8	952.9	953.0	953.0	953.1	952.6
145°	989.9	990.1	990.1	990.1	990.1	990.1	990.3	990.5	990.7	990.8	990.4
147.5°	1021.1	1021.2	1021.4	1021.7	1021.9	1022.1	1022.4	1022.6	1022.9	1023.0	1022.5
150°	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3	1042.8	1043.1	1043.5	1043.9	1043.3
152.5°	1059.1	1058.9	1059.3	1059.7	1060.1	1060.4	1060.8	1061.2	1061.6	1062.0	1061.5
155°	1083.8	1083.5	1083.8	1084.3	1084.6	1085.0	1085.5	1086.2	1086.8	1087.4	1086.8
157.5°	1105.7	1105.4	1105.4	1105.4	1105.5	1105.5	1106.2	1106.8	1107.4	1108.0	1107.6
160°	1117.8	1117.3	1117.5	1117.8	1117.9	1118.1	1118.9	1119.6	1120.4	1121.2	1120.8
162.5°	1128.9	1128.4	1128.7	1128.9	1129.0	1129.2	1130.3	1131.4	1132.5	1133.6	1133.2
165°	1143.9	1143.4	1143.7	1143.8	1144.0	1144.2	1145.4	1146.5	1147.7	1148.8	1148.7
167.5°	1154.9	1154.4	1154.6	1154.8	1155.0	1155.2	1156.6	1158.0	1159.3	1160.8	1160.6
170°	1160.5	1160.0	1160.2	1160.4	1160.5	1160.8	1162.4	1163.9	1165.4	1167.0	1166.8
172.5°	1164.8	1164.2	1164.6	1164.9	1165.3	1165.6	1167.0	1168.5	1169.8	1171.2	1171.0
175°	1170.0	1169.6	1169.8	1169.9	1170.2	1170.4	1171.9	1173.5	1175.0	1176.6	1176.5
177.5°	1173.1	1172.7	1172.9	1173.0	1173.1	1173.3	1174.4	1175.4	1176.6	1177.7	1177.6
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1356.1	1351.0	1349.6	1351.4	1349.6	1351.0	1356.1	1356.6	1357.0	1360.7	1355.6
5°	1251.2	1245.4	1248.3	1247.1	1248.3	1245.4	1251.2	1257.0	1258.1	1263.3	1266.9
7.5°	1158.9	1151.7	1144.0	1146.4	1144.0	1151.7	1158.9	1159.0	1168.0	1174.8	1179.3
10°	1094.2	1088.5	1084.9	1087.9	1084.9	1088.5	1094.2	1101.8	1105.3	1113.4	1122.1
12.5°	1039.8	1036.4	1033.4	1032.1	1033.4	1036.4	1039.8	1047.9	1056.0	1065.6	1075.2
15°	965.9	958.9	956.0	948.4	956.0	958.9	965.9	972.8	988.5	992.6	1007.1
17.5°	897.6	895.3	887.7	884.5	887.7	895.3	897.6	903.5	910.8	925.7	936.7
20°	857.1	854.8	847.3	852.0	847.3	854.8	857.1	865.9	871.7	883.9	894.3
22.5°	823.7	818.6	816.1	814.8	816.1	818.6	823.7	827.8	835.4	846.7	858.6
25°	776.4	768.8	765.9	762.4	765.9	768.8	776.4	778.7	786.9	797.9	804.3
27.5°	729.2	725.1	721.3	720.4	721.3	725.1	729.2	732.5	739.5	749.2	760.7
30°	698.5	694.5	691.6	691.6	691.6	694.5	698.5	705.5	710.8	719.5	728.1
32.5°	671.1	668.0	665.0	664.6	665.0	668.0	671.1	674.8	681.0	690.6	699.8
35°	631.1	626.5	625.3	621.8	625.3	626.5	631.1	634.0	640.4	647.4	655.0
37.5°	589.6	585.7	585.7	585.3	585.7	585.7	589.6	594.7	600.0	606.3	615.6
40°	563.1	560.2	559.6	555.5	559.6	560.2	563.1	565.4	571.3	579.4	586.3
42.5°	534.8	533.2	531.2	529.5	531.2	533.2	534.8	539.4	544.3	550.1	559.0
45°	496.3	492.2	492.2	489.3	492.2	492.2	496.3	500.3	502.7	509.6	521.2
47.5°	456.5	453.4	453.7	450.7	453.7	453.4	456.5	457.8	461.5	468.4	474.8
50°	430.1	428.3	427.7	426.5	427.7	428.3	430.1	429.5	434.1	440.5	449.2
52.5°	403.6	402.7	404.9	402.3	404.9	402.7	403.6	404.8	408.0	412.2	420.4
55°	367.8	366.1	369.6	366.1	369.6	366.1	367.8	366.7	367.8	372.0	377.1
57.5°	326.8	325.2	328.3	326.6	328.3	325.2	326.8	327.1	330.5	331.1	335.8
60°	299.9	296.4	298.1	298.7	298.1	296.4	299.9	301.0	302.2	302.7	307.4
62.5°	267.8	265.7	267.0	264.3	267.0	265.7	267.8	270.4	272.9	275.8	278.6
65°	222.6	220.8	218.5	217.3	218.5	220.8	222.6	223.8	230.1	233.6	240.0
67.5°	187.0	182.8	182.7	183.7	182.7	182.8	187.0	186.8	191.4	194.2	198.5
70°	161.0	161.0	160.4	160.4	160.4	161.0	161.0	164.5	166.8	169.1	172.0
72.5°	142.8	142.4	141.3	140.9	141.3	142.4	142.8	144.0	145.4	147.7	150.6
75°	115.0	115.6	114.5	113.9	114.5	115.6	115.0	115.0	117.4	118.0	119.2
77.5°	85.0	82.5	83.8	82.5	83.8	82.5	85.0	87.3	88.1	90.7	90.7
80°	64.5	63.9	65.7	63.9	65.7	63.9	64.5	64.5	66.2	67.4	70.3
82.5°	51.1	50.5	51.2	49.9	51.2	50.5	51.1	50.5	51.4	53.0	52.6
85°	30.8	30.2	29.6	30.2	29.6	30.2	30.8	30.2	29.6	30.2	30.8
87.5°	14.6	14.2	14.3	14.4	14.3	14.2	14.6	13.9	14.3	14.0	13.9
90°	19.2	19.7	20.3	20.9	20.3	19.7	19.2	18.6	17.8	16.9	15.8
92.5°	18.7	18.9	19.2	19.5	19.2	18.9	18.7	18.4	17.8	16.9	15.8
95°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	17.8	16.9	15.8
97.5°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	21.0	26.4	31.9
100°	20.6	19.8	19.0	18.3	19.0	19.8	20.6	21.4	36.2	65.0	93.8
102.5°	149.0	135.9	122.7	109.5	122.7	135.9	149.0	162.2	171.5	176.9	182.4
105°	259.2	259.0	258.8	258.6	258.8	259.0	259.2	259.4	259.5	259.5	259.5
107.5°	327.8	327.2	326.6	326.1	326.6	327.2	327.8	328.4	328.6	328.6	328.6
110°	372.1	372.3	372.5	372.7	372.5	372.3	372.1	372.0	372.1	372.7	373.2



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	415.3	415.0	414.7	414.5	414.7	415.0	415.3	415.6	416.1	416.8	417.6
115°	480.7	479.5	478.4	477.2	478.4	479.5	480.7	481.8	482.8	483.5	484.3
117.5°	545.6	545.1	544.6	544.1	544.6	545.1	545.6	546.0	546.8	547.9	548.9
120°	588.1	587.1	586.2	585.1	586.2	587.1	588.1	589.0	589.7	590.1	590.5
122.5°	627.6	626.5	625.3	624.2	625.3	626.5	627.6	628.7	629.4	629.8	630.2
125°	685.4	684.8	684.2	683.5	684.2	684.8	685.4	685.9	686.6	687.3	688.1
127.5°	737.9	736.4	734.9	733.6	734.9	736.4	737.9	739.3	740.2	740.6	741.1
130°	772.7	771.7	770.8	769.8	770.8	771.7	772.7	773.6	774.4	775.0	775.6
132.5°	806.2	805.1	804.2	803.2	804.2	805.1	806.2	807.1	807.6	807.7	807.9
135°	852.5	851.4	850.2	849.0	850.2	851.4	852.5	853.7	854.5	854.8	855.2
137.5°	898.0	897.0	896.0	895.0	896.0	897.0	898.0	899.1	899.5	899.4	899.3
140°	925.7	924.5	923.3	922.1	923.3	924.5	925.7	926.8	927.2	926.8	926.4
142.5°	951.4	950.3	949.1	948.0	949.1	950.3	951.4	952.6	953.1	953.0	953.0
145°	989.2	988.1	986.9	985.8	986.9	988.1	989.2	990.4	990.8	990.7	990.5
147.5°	1021.1	1019.7	1018.3	1016.9	1018.3	1019.7	1021.1	1022.5	1023.0	1022.9	1022.6
150°	1041.7	1040.2	1038.6	1037.1	1038.6	1040.2	1041.7	1043.3	1043.9	1043.5	1043.1
152.5°	1060.1	1058.7	1057.3	1055.9	1057.3	1058.7	1060.1	1061.5	1062.0	1061.6	1061.2
155°	1085.3	1083.7	1082.2	1080.6	1082.2	1083.7	1085.3	1086.8	1087.4	1086.8	1086.2
157.5°	1106.0	1104.5	1102.9	1101.4	1102.9	1104.5	1106.0	1107.6	1108.0	1107.4	1106.8
160°	1119.3	1117.8	1116.2	1114.7	1116.2	1117.8	1119.3	1120.8	1121.2	1120.4	1119.6
162.5°	1131.5	1129.9	1128.2	1126.4	1128.2	1129.9	1131.5	1133.2	1133.6	1132.5	1131.4
165°	1147.1	1145.6	1144.0	1142.5	1144.0	1145.6	1147.1	1148.7	1148.8	1147.7	1146.5
167.5°	1158.8	1157.1	1155.4	1153.7	1155.4	1157.1	1158.8	1160.6	1160.8	1159.3	1158.0
170°	1165.1	1163.4	1161.7	1159.9	1161.7	1163.4	1165.1	1166.8	1167.0	1165.4	1163.9
172.5°	1169.3	1167.5	1165.8	1164.1	1165.8	1167.5	1169.3	1171.0	1171.2	1169.8	1168.5
175°	1174.7	1172.9	1171.2	1169.5	1171.2	1172.9	1174.7	1176.5	1176.6	1175.0	1173.5
177.5°	1176.3	1175.1	1173.9	1172.6	1173.9	1175.1	1176.3	1177.6	1177.7	1176.6	1175.4
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1357.0	1362.2	1364.9	1371.5	1380.8	1385.4	1391.9	1396.5	1403.1	1411.0	1417.5
5°	1269.2	1283.1	1292.4	1306.9	1320.3	1333.7	1350.6	1362.7	1379.0	1397.6	1412.1
7.5°	1187.6	1205.1	1220.5	1239.7	1261.7	1278.9	1300.9	1323.4	1348.8	1375.2	1400.1
10°	1135.5	1153.0	1172.2	1195.9	1218.1	1241.3	1267.4	1293.6	1325.5	1355.2	1388.9
12.5°	1083.9	1103.2	1124.7	1151.3	1178.0	1207.8	1234.4	1263.9	1298.1	1336.6	1372.6
15°	1019.9	1038.5	1061.7	1084.3	1115.2	1147.7	1183.2	1222.1	1260.4	1303.5	1348.2
17.5°	951.1	971.6	997.2	1023.5	1055.9	1094.0	1128.8	1171.4	1214.5	1264.6	1317.3
20°	906.5	927.5	957.7	986.8	1016.4	1053.6	1094.8	1138.4	1184.3	1237.3	1295.9
22.5°	871.2	886.1	915.8	945.4	980.2	1018.2	1058.6	1104.1	1154.1	1208.8	1270.3
25°	818.8	836.2	857.7	888.6	924.5	964.7	1005.3	1053.6	1108.2	1164.0	1229.7
27.5°	772.2	786.5	807.8	831.9	867.9	909.5	952.7	1003.0	1059.0	1115.9	1184.9
30°	739.2	754.8	775.2	800.8	829.2	874.6	918.8	968.2	1025.1	1083.8	1154.7
32.5°	710.3	726.5	744.1	768.3	799.0	839.3	884.8	933.3	991.2	1051.7	1120.8
35°	670.0	681.1	697.3	721.2	751.4	783.9	830.4	881.6	938.0	1000.7	1069.9
37.5°	623.8	638.1	654.2	674.9	701.5	736.7	779.9	831.6	883.9	944.0	1007.1
40°	596.8	610.2	628.2	643.3	671.2	703.2	742.7	796.7	849.0	905.4	962.9
42.5°	569.4	582.3	597.5	616.3	641.4	672.4	709.2	759.5	815.5	868.7	916.9
45°	526.5	539.8	554.4	571.8	595.0	625.3	661.9	707.8	756.6	805.5	842.1
47.5°	485.4	498.0	511.8	529.6	551.0	580.2	612.9	653.5	700.9	742.4	768.6
50°	456.2	467.8	482.9	500.3	521.2	548.5	580.0	620.1	659.6	697.3	721.2
52.5°	427.4	440.4	455.5	470.6	490.6	517.9	547.0	581.4	619.1	650.0	669.6
55°	384.1	396.3	410.3	425.9	445.7	469.0	499.8	527.1	556.7	582.9	594.5
57.5°	342.4	353.1	366.2	382.5	400.3	421.9	446.3	472.6	493.5	512.0	525.1
60°	315.0	324.3	336.5	350.4	369.6	389.3	411.5	435.8	452.1	467.8	480.0
62.5°	287.1	295.9	307.6	320.2	337.1	355.4	376.6	396.3	412.2	422.8	436.8
65°	245.2	253.9	263.8	277.2	290.6	305.7	324.9	339.4	350.4	362.1	370.7
67.5°	206.3	213.5	222.9	233.4	244.7	259.2	274.1	286.1	293.7	300.7	311.2
70°	180.7	186.6	194.1	202.2	214.5	228.9	240.6	249.9	255.1	262.1	274.8
72.5°	154.7	161.4	168.5	176.7	186.6	198.7	209.0	218.3	221.6	227.2	235.4
75°	122.0	125.5	131.3	137.2	144.1	154.5	164.5	166.8	169.7	174.4	180.1
77.5°	92.3	95.4	97.7	101.6	107.2	115.5	120.8	124.2	124.9	126.7	132.4
80°	73.2	75.0	77.3	80.2	82.5	89.5	92.4	95.9	97.0	98.8	101.7
82.5°	53.7	55.4	56.8	59.2	63.0	65.8	68.7	72.2	72.4	73.7	74.3
85°	31.3	31.9	30.8	31.9	32.5	33.7	36.6	39.5	38.9	38.3	40.1
87.5°	14.1	13.9	13.2	14.3	13.2	13.3	13.0	13.2	13.8	14.5	15.1
90°	14.9	13.9	12.6	11.2	9.9	8.5	7.1	5.5	4.0	2.4	0.9
92.5°	14.9	13.9	12.7	11.5	10.3	9.1	9.0	10.2	11.3	12.3	13.4
95°	14.9	13.9	21.3	28.7	36.0	43.3	47.4	47.9	48.5	49.1	49.6
97.5°	37.4	42.9	57.4	72.0	86.5	101.1	107.8	106.8	105.7	104.7	103.7
100°	122.7	151.5	150.8	150.0	149.2	148.4	147.7	147.1	146.5	146.0	145.4
102.5°	187.9	193.3	192.9	192.3	191.9	191.5	190.9	190.1	189.4	188.6	188.0
105°	259.5	259.5	259.5	259.5	259.5	259.5	259.1	258.3	257.5	256.8	256.0
107.5°	328.5	328.5	328.0	327.7	327.3	326.9	326.7	326.7	326.7	326.7	326.7
110°	373.8	374.4	374.0	373.7	373.2	372.9	372.7	372.7	372.7	372.7	372.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	418.3	419.0	418.8	418.5	418.4	418.1	417.8	417.2	416.8	416.4	415.9
115°	485.1	485.9	485.7	485.5	485.3	485.1	484.6	483.5	482.6	481.6	480.7
117.5°	549.8	550.9	550.1	549.4	548.6	547.9	547.6	547.6	547.7	547.7	547.8
120°	590.9	591.2	590.6	590.1	589.5	588.9	588.8	588.9	589.1	589.4	589.5
122.5°	630.6	630.9	630.7	630.4	630.2	629.9	629.4	628.6	627.9	627.2	626.5
125°	688.9	689.7	689.7	689.7	689.7	689.7	689.0	687.6	686.3	684.9	683.5
127.5°	741.5	741.9	742.0	742.2	742.3	742.4	741.9	741.0	740.0	739.1	738.0
130°	776.2	776.7	776.5	776.4	776.2	775.9	775.4	774.4	773.4	772.5	771.5
132.5°	808.0	808.1	808.5	808.9	809.3	809.8	809.4	808.3	807.2	806.1	804.9
135°	855.6	856.0	856.4	856.8	857.1	857.6	857.1	856.0	854.8	853.7	852.5
137.5°	899.2	899.1	899.5	899.9	900.3	900.6	900.3	899.2	898.2	897.2	896.2
140°	926.0	925.7	925.8	926.0	926.3	926.4	926.3	925.9	925.6	925.1	924.8
142.5°	952.9	952.8	952.5	952.3	952.0	951.7	951.5	951.2	951.1	950.8	950.5
145°	990.3	990.1	990.1	990.1	990.1	990.1	989.9	989.5	989.1	988.8	988.3
147.5°	1022.4	1022.1	1021.9	1021.7	1021.4	1021.2	1021.1	1021.2	1021.3	1021.4	1021.4
150°	1042.8	1042.3	1042.0	1041.6	1041.2	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3
152.5°	1060.8	1060.4	1060.1	1059.7	1059.3	1058.9	1059.1	1060.0	1060.8	1061.7	1062.6
155°	1085.5	1085.0	1084.6	1084.3	1083.8	1083.5	1083.8	1085.0	1086.2	1087.4	1088.5
157.5°	1106.2	1105.5	1105.5	1105.4	1105.4	1105.4	1105.7	1106.5	1107.2	1107.8	1108.5
160°	1118.9	1118.1	1117.9	1117.8	1117.5	1117.3	1117.8	1119.0	1120.2	1121.3	1122.5
162.5°	1130.3	1129.2	1129.0	1128.9	1128.7	1128.4	1128.9	1130.1	1131.3	1132.5	1133.6
165°	1145.4	1144.2	1144.0	1143.8	1143.7	1143.4	1143.9	1145.1	1146.2	1147.5	1148.6
167.5°	1156.6	1155.2	1155.0	1154.8	1154.6	1154.4	1154.9	1156.2	1157.4	1158.6	1159.7
170°	1162.4	1160.8	1160.5	1160.4	1160.2	1160.0	1160.5	1161.9	1163.3	1164.7	1166.0
172.5°	1167.0	1165.6	1165.3	1164.9	1164.6	1164.2	1164.8	1166.1	1167.4	1168.8	1170.2
175°	1171.9	1170.4	1170.2	1169.9	1169.8	1169.6	1170.0	1171.2	1172.3	1173.5	1174.7
177.5°	1174.4	1173.3	1173.1	1173.0	1172.9	1172.7	1173.1	1174.0	1174.9	1175.9	1176.8
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1422.6	1426.8	1432.8	1439.8	1445.4	1451.4	1454.7	1454.7	1457.5	1463.5	1471.4
5°	1426.7	1441.7	1456.3	1474.9	1489.4	1506.2	1519.1	1531.3	1542.3	1556.3	1570.8
7.5°	1425.5	1450.6	1476.8	1506.1	1538.3	1564.0	1590.4	1611.1	1631.6	1658.3	1679.3
10°	1420.8	1453.4	1488.8	1526.0	1566.7	1602.1	1634.1	1663.2	1691.1	1720.1	1746.3
12.5°	1412.5	1453.9	1497.2	1541.9	1593.2	1633.7	1675.1	1706.0	1738.5	1770.3	1802.5
15°	1399.9	1448.7	1501.1	1563.2	1626.0	1671.3	1712.0	1752.1	1782.3	1818.3	1849.2
17.5°	1374.0	1436.9	1502.7	1570.6	1631.0	1683.6	1726.3	1764.4	1796.6	1836.3	1878.1
20°	1358.7	1426.7	1495.2	1567.9	1625.4	1679.5	1720.7	1760.2	1800.4	1852.0	1903.2
22.5°	1337.3	1409.9	1482.6	1551.6	1612.4	1664.6	1707.2	1755.6	1808.2	1866.9	1928.7
25°	1303.5	1378.5	1450.5	1516.1	1575.5	1628.9	1687.0	1752.1	1816.0	1893.3	1982.2
27.5°	1260.6	1332.8	1397.1	1466.5	1525.4	1593.5	1665.9	1736.6	1828.7	1935.0	2046.0
30°	1228.5	1297.1	1358.1	1423.7	1490.6	1565.6	1646.9	1730.0	1839.9	1964.8	2096.7
32.5°	1191.3	1253.4	1313.9	1377.3	1454.3	1536.7	1623.2	1724.9	1856.1	1998.3	2134.8
35°	1126.8	1182.6	1241.3	1311.6	1393.5	1483.1	1593.5	1717.3	1875.9	2028.7	2151.3
37.5°	1059.1	1103.2	1162.1	1236.3	1325.5	1429.1	1554.4	1704.8	1867.8	2004.8	2057.1
40°	1007.1	1048.4	1110.5	1188.4	1276.7	1390.1	1530.7	1685.2	1849.2	1944.5	1940.3
42.5°	955.5	997.2	1057.0	1135.4	1227.4	1354.3	1499.1	1659.7	1798.0	1834.3	1758.6
45°	876.3	915.2	974.0	1053.0	1151.8	1284.9	1437.1	1591.1	1679.5	1620.7	1470.8
47.5°	795.7	833.4	887.9	965.4	1073.2	1212.5	1356.4	1482.8	1495.2	1369.2	1189.3
50°	742.7	778.1	829.8	912.4	1016.9	1153.0	1291.8	1391.2	1360.4	1206.4	1021.1
52.5°	691.0	725.1	773.6	851.4	958.4	1091.6	1215.6	1293.6	1222.4	1058.6	891.8
55°	614.8	647.4	696.2	767.7	864.7	986.8	1095.5	1123.9	1019.3	854.3	719.5
57.5°	542.4	566.3	614.5	677.7	771.3	878.9	956.7	951.7	836.2	687.6	590.9
60°	494.6	516.0	562.0	620.1	708.9	805.5	860.1	836.8	720.1	597.4	504.4
62.5°	449.9	470.0	508.5	562.0	638.3	722.2	762.0	729.9	619.6	511.9	437.9
65°	382.4	396.9	427.7	477.1	536.9	595.0	630.5	583.4	485.9	404.5	348.7
67.5°	319.3	331.8	359.2	394.7	435.9	476.0	490.5	446.3	370.4	315.6	276.3
70°	278.4	290.0	308.6	341.7	369.0	397.5	404.5	365.0	301.6	259.8	235.4
72.5°	239.3	250.0	266.3	289.6	308.6	324.9	328.2	291.5	243.1	214.2	195.4
75°	182.4	191.7	202.2	210.9	223.2	226.1	224.9	196.4	170.3	151.1	140.6
77.5°	134.1	137.9	144.4	147.8	148.4	148.2	142.2	124.2	110.7	102.9	98.6
80°	103.4	106.3	108.1	109.3	109.9	104.0	97.6	86.6	82.0	77.3	72.1
82.5°	75.1	77.1	78.8	79.0	75.9	71.0	65.1	59.6	56.4	54.1	52.1
85°	40.6	41.2	40.6	37.8	33.7	31.9	30.8	29.6	29.0	28.5	28.5
87.5°	14.9	13.8	11.8	12.6	12.8	12.7	12.9	12.7	12.6	12.7	12.9
90°	2.4	4.0	5.5	7.1	8.5	9.9	11.2	12.6	13.9	14.9	15.8
92.5°	12.3	11.3	10.2	9.0	9.1	10.3	11.5	12.7	13.9	14.9	15.8
95°	49.1	48.5	47.9	47.4	43.3	36.0	28.7	21.3	13.9	14.9	15.8
97.5°	104.7	105.7	106.8	107.8	101.1	86.5	72.0	57.4	42.9	37.4	31.9
100°	146.0	146.5	147.1	147.7	148.4	149.2	150.0	150.8	151.5	122.7	93.8
102.5°	188.6	189.4	190.1	190.9	191.5	191.9	192.3	192.9	193.3	187.9	182.4
105°	256.8	257.5	258.3	259.1	259.5	259.5	259.5	259.5	259.5	259.5	259.5
107.5°	326.7	326.7	326.7	326.7	326.9	327.3	327.7	328.0	328.5	328.5	328.6
110°	372.7	372.7	372.7	372.7	372.9	373.2	373.7	374.0	374.4	373.8	373.2





TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	416.4	416.8	417.2	417.8	418.1	418.4	418.5	418.8	419.0	418.3	417.6
115°	481.6	482.6	483.5	484.6	485.1	485.3	485.5	485.7	485.9	485.1	484.3
117.5°	547.7	547.7	547.6	547.6	547.9	548.6	549.4	550.1	550.9	549.8	548.9
120°	589.4	589.1	588.9	588.8	588.9	589.5	590.1	590.6	591.2	590.9	590.5
122.5°	627.2	627.9	628.6	629.4	629.9	630.2	630.4	630.7	630.9	630.6	630.2
125°	684.9	686.3	687.6	689.0	689.7	689.7	689.7	689.7	689.7	688.9	688.1
127.5°	739.1	740.0	741.0	741.9	742.4	742.3	742.2	742.0	741.9	741.5	741.1
130°	772.5	773.4	774.4	775.4	775.9	776.2	776.4	776.5	776.7	776.2	775.6
132.5°	806.1	807.2	808.3	809.4	809.8	809.3	808.9	808.5	808.1	808.0	807.9
135°	853.7	854.8	856.0	857.1	857.6	857.1	856.8	856.4	856.0	855.6	855.2
137.5°	897.2	898.2	899.2	900.3	900.6	900.3	899.9	899.5	899.1	899.2	899.3
140°	925.1	925.6	925.9	926.3	926.4	926.3	926.0	925.8	925.7	926.0	926.4
142.5°	950.8	951.1	951.2	951.5	951.7	952.0	952.3	952.5	952.8	952.9	953.0
145°	988.8	989.1	989.5	989.9	990.1	990.1	990.1	990.1	990.1	990.3	990.5
147.5°	1021.4	1021.3	1021.2	1021.1	1021.2	1021.4	1021.7	1021.9	1022.1	1022.4	1022.6
150°	1042.0	1041.6	1041.2	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3	1042.8	1043.1
152.5°	1061.7	1060.8	1060.0	1059.1	1058.9	1059.3	1059.7	1060.1	1060.4	1060.8	1061.2
155°	1087.4	1086.2	1085.0	1083.8	1083.5	1083.8	1084.3	1084.6	1085.0	1085.5	1086.2
157.5°	1107.8	1107.2	1106.5	1105.7	1105.4	1105.4	1105.4	1105.5	1105.5	1106.2	1106.8
160°	1121.3	1120.2	1119.0	1117.8	1117.3	1117.5	1117.8	1117.9	1118.1	1118.9	1119.6
162.5°	1132.5	1131.3	1130.1	1128.9	1128.4	1128.7	1128.9	1129.0	1129.2	1130.3	1131.4
165°	1147.5	1146.2	1145.1	1143.9	1143.4	1143.7	1143.8	1144.0	1144.2	1145.4	1146.5
167.5°	1158.6	1157.4	1156.2	1154.9	1154.4	1154.6	1154.8	1155.0	1155.2	1156.6	1158.0
170°	1164.7	1163.3	1161.9	1160.5	1160.0	1160.2	1160.4	1160.5	1160.8	1162.4	1163.9
172.5°	1168.8	1167.4	1166.1	1164.8	1164.2	1164.6	1164.9	1165.3	1165.6	1167.0	1168.5
175°	1173.5	1172.3	1171.2	1170.0	1169.6	1169.8	1169.9	1170.2	1170.4	1171.9	1173.5
177.5°	1175.9	1174.9	1174.0	1173.1	1172.7	1172.9	1173.0	1173.1	1173.3	1174.4	1175.4
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1477.5	1477.5	1485.4	1484.9	1490.0	1488.2	1489.1
5°	1588.2	1598.1	1606.8	1612.7	1621.3	1623.7	1622.5
7.5°	1703.1	1725.0	1735.7	1750.3	1753.0	1760.7	1759.9
10°	1774.2	1795.7	1812.0	1824.7	1831.1	1839.3	1839.9
12.5°	1830.0	1848.2	1862.6	1874.5	1882.2	1884.8	1886.4
15°	1873.5	1893.9	1910.7	1927.6	1937.5	1945.0	1949.1
17.5°	1917.4	1948.9	1978.6	2001.5	2015.3	2026.9	2026.7
20°	1951.5	1987.4	2024.6	2050.8	2077.5	2089.1	2090.9
22.5°	1987.7	2042.8	2090.7	2131.2	2166.3	2178.4	2183.0
25°	2063.0	2135.0	2208.9	2265.8	2306.4	2330.3	2333.8
27.5°	2154.0	2251.5	2329.2	2381.7	2415.5	2433.2	2437.0
30°	2218.2	2308.3	2378.0	2417.5	2433.2	2435.5	2426.8
32.5°	2247.0	2314.3	2342.2	2339.9	2309.0	2288.6	2280.8
35°	2211.7	2197.8	2129.9	2048.5	1986.3	1946.8	1936.3
37.5°	2012.8	1892.5	1767.5	1644.5	1579.1	1545.8	1488.6
40°	1816.6	1645.2	1515.0	1411.5	1337.7	1278.5	1264.6
42.5°	1595.3	1418.3	1288.1	1199.5	1140.7	1099.9	1082.3
45°	1281.9	1129.7	1022.2	954.2	908.9	879.3	865.9
47.5°	1025.4	907.5	829.1	778.9	744.3	718.5	711.3
50°	884.5	790.3	724.1	681.7	655.5	635.8	627.6
52.5°	768.3	692.2	641.4	606.3	581.6	569.3	562.5
55°	634.0	568.3	531.8	503.9	489.9	480.0	475.4
57.5°	518.5	471.1	444.4	425.1	412.2	405.9	403.6
60°	453.8	416.6	392.3	377.1	368.4	360.3	358.0
62.5°	396.7	367.4	348.5	335.3	326.6	323.1	321.7
65°	319.6	300.4	286.5	278.4	271.4	270.2	269.7
67.5°	254.1	242.8	235.5	227.0	224.5	220.5	219.6
70°	217.3	209.8	201.0	198.2	195.3	191.2	191.7
72.5°	184.3	176.8	170.8	167.0	166.0	164.2	165.7
75°	134.8	132.5	130.2	127.3	126.1	126.1	125.5
77.5°	96.3	94.3	91.7	90.0	89.6	87.1	88.1
80°	69.7	66.8	65.7	66.2	64.5	63.9	63.9
82.5°	51.6	50.5	49.4	49.5	49.2	48.6	49.1
85°	28.5	27.9	27.9	27.3	27.3	26.7	26.7
87.5°	13.6	14.3	13.5	13.1	13.3	13.9	14.4
90°	16.9	17.8	18.6	19.2	19.7	20.3	20.9
92.5°	16.9	17.8	18.4	18.7	18.9	19.2	19.5
95°	16.9	17.8	18.3	18.3	18.3	18.3	18.3
97.5°	26.4	21.0	18.3	18.3	18.3	18.3	18.3
100°	65.0	36.2	21.4	20.6	19.8	19.0	18.3
102.5°	176.9	171.5	162.2	149.0	135.9	122.7	109.5
105°	259.5	259.5	259.4	259.2	259.0	258.8	258.6
107.5°	328.6	328.6	328.4	327.8	327.2	326.6	326.1
110°	372.7	372.1	372.0	372.1	372.3	372.5	372.7



TEST NUMBER: P333708-935

CATALOG NUMBER: S125RDIW-S1090D1050U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	416.8	416.1	415.6	415.3	415.0	414.7	414.5
115°	483.5	482.8	481.8	480.7	479.5	478.4	477.2
117.5°	547.9	546.8	546.0	545.6	545.1	544.6	544.1
120°	590.1	589.7	589.0	588.1	587.1	586.2	585.1
122.5°	629.8	629.4	628.7	627.6	626.5	625.3	624.2
125°	687.3	686.6	685.9	685.4	684.8	684.2	683.5
127.5°	740.6	740.2	739.3	737.9	736.4	734.9	733.6
130°	775.0	774.4	773.6	772.7	771.7	770.8	769.8
132.5°	807.7	807.6	807.1	806.2	805.1	804.2	803.2
135°	854.8	854.5	853.7	852.5	851.4	850.2	849.0
137.5°	899.4	899.5	899.1	898.0	897.0	896.0	895.0
140°	926.8	927.2	926.8	925.7	924.5	923.3	922.1
142.5°	953.0	953.1	952.6	951.4	950.3	949.1	948.0
145°	990.7	990.8	990.4	989.2	988.1	986.9	985.8
147.5°	1022.9	1023.0	1022.5	1021.1	1019.7	1018.3	1016.9
150°	1043.5	1043.9	1043.3	1041.7	1040.2	1038.6	1037.1
152.5°	1061.6	1062.0	1061.5	1060.1	1058.7	1057.3	1055.9
155°	1086.8	1087.4	1086.8	1085.3	1083.7	1082.2	1080.6
157.5°	1107.4	1108.0	1107.6	1106.0	1104.5	1102.9	1101.4
160°	1120.4	1121.2	1120.8	1119.3	1117.8	1116.2	1114.7
162.5°	1132.5	1133.6	1133.2	1131.5	1129.9	1128.2	1126.4
165°	1147.7	1148.8	1148.7	1147.1	1145.6	1144.0	1142.5
167.5°	1159.3	1160.8	1160.6	1158.8	1157.1	1155.4	1153.7
170°	1165.4	1167.0	1166.8	1165.1	1163.4	1161.7	1159.9
172.5°	1169.8	1171.2	1171.0	1169.3	1167.5	1165.8	1164.1
175°	1175.0	1176.6	1176.5	1174.7	1172.9	1171.2	1169.5
177.5°	1176.6	1177.7	1177.6	1176.3	1175.1	1173.9	1172.6
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7

(END OF REPORT)