

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333416-940

Luminaire Tested: **S125DIW-S850D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333416-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1050U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6784.6 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	1.6
10°-20°	311.8	4.6
20°-30°	460.3	6.8
30°-40°	537.2	7.9
40°-50°	539.5	8.0
50°-60°	473.6	7.0
60°-70°	352.9	5.2
70°-80°	201.8	3.0
80°-90°	61.2	0.9
90°-100°	44.2	0.7
100°-110°	272.5	4.0
110°-120°	494.2	7.3
120°-130°	634.2	9.3
130°-140°	682.1	10.1
140°-150°	640.3	9.4
150°-160°	517.9	7.6
160°-170°	335.0	4.9
170°-180°	115.5	1.7
0°-30°	882.5	13.0
0°-40°	1419.6	20.9
0°-60°	2432.7	35.9
0°-90°	3048.6	44.9
90°-120°	810.9	12.0
90°-150°	2767.5	40.8
90°-180°	3736.0	55.1
0°-180°	6784.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	1	8	14	19	22	5
95°	51	47	14	19	19	66
105°	265	269	269	269	268	281
115°	498	502	503	500	494	493
125°	708	714	714	711	708	632
135°	883	888	886	884	879	680
145°	1024	1025	1025	1026	1021	640
155°	1127	1122	1124	1126	1119	519
165°	1190	1184	1185	1190	1183	336
175°	1217	1212	1212	1218	1211	116
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.2	20.5	20.9	21.1	21.5	21.7	21.8	21.9	22.0	22.1	22.4
90°	0.9	2.5	4.1	5.7	7.3	8.8	10.3	11.6	13.0	14.4	15.4
92.5°	13.9	12.8	11.7	10.5	9.4	9.5	10.7	11.9	13.2	14.4	15.4
95°	51.4	50.8	50.2	49.6	49.0	44.9	37.3	29.7	22.0	14.4	15.4
97.5°	107.4	108.4	109.5	110.6	111.6	104.7	89.6	74.5	59.5	44.4	38.7
100°	150.6	151.2	151.8	152.4	153.0	153.7	154.5	155.3	156.1	156.9	127.1
102.5°	194.7	195.4	196.2	196.9	197.7	198.3	198.8	199.2	199.7	200.2	194.6
105°	265.1	265.9	266.7	267.5	268.3	268.8	268.8	268.8	268.8	268.8	268.8
107.5°	338.4	338.4	338.4	338.4	338.4	338.6	338.9	339.4	339.7	340.2	340.2
110°	386.0	386.0	386.0	386.0	386.0	386.2	386.6	387.0	387.4	387.8	387.2



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.7	431.2	431.7	432.1	432.7	433.0	433.3	433.5	433.7	434.0	433.2
115°	497.8	498.8	499.8	500.8	501.9	502.4	502.7	502.8	503.0	503.2	502.4
117.5°	567.3	567.2	567.2	567.1	567.1	567.5	568.2	569.0	569.7	570.5	569.4
120°	610.6	610.4	610.1	609.9	609.8	609.9	610.6	611.2	611.7	612.3	612.0
122.5°	648.8	649.5	650.3	651.0	651.8	652.4	652.6	652.9	653.2	653.4	653.1
125°	707.9	709.4	710.8	712.1	713.5	714.3	714.3	714.3	714.3	714.3	713.5
127.5°	764.4	765.4	766.4	767.4	768.4	768.8	768.7	768.7	768.5	768.4	767.9
130°	799.1	800.0	801.0	802.0	803.1	803.6	803.9	804.1	804.2	804.4	803.9
132.5°	833.7	834.8	836.0	837.1	838.3	838.7	838.2	837.8	837.3	837.0	836.8
135°	882.9	884.1	885.3	886.5	887.7	888.1	887.7	887.3	886.9	886.5	886.1
137.5°	928.2	929.3	930.2	931.3	932.4	932.7	932.4	932.0	931.6	931.2	931.3
140°	957.8	958.1	958.6	958.9	959.4	959.5	959.3	959.0	958.9	958.7	959.0
142.5°	984.4	984.7	985.0	985.2	985.4	985.7	986.0	986.2	986.5	986.8	986.9
145°	1023.6	1024.0	1024.4	1024.8	1025.2	1025.4	1025.4	1025.4	1025.4	1025.4	1025.6
147.5°	1057.8	1057.8	1057.7	1057.7	1057.6	1057.7	1057.8	1058.1	1058.4	1058.5	1058.8
150°	1079.5	1079.1	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1080.0
152.5°	1100.5	1099.6	1098.7	1097.8	1096.9	1096.7	1097.1	1097.5	1097.9	1098.2	1098.7
155°	1127.3	1126.1	1124.9	1123.7	1122.5	1122.1	1122.5	1122.9	1123.3	1123.7	1124.3
157.5°	1148.1	1147.4	1146.7	1145.9	1145.1	1144.9	1144.9	1144.9	1145.0	1145.0	1145.7
160°	1162.5	1161.3	1160.1	1158.9	1157.7	1157.2	1157.4	1157.6	1157.8	1158.0	1158.8
162.5°	1174.0	1172.9	1171.6	1170.5	1169.2	1168.7	1168.9	1169.1	1169.3	1169.5	1170.6
165°	1189.5	1188.4	1187.1	1186.0	1184.7	1184.2	1184.5	1184.6	1184.8	1185.0	1186.2
167.5°	1201.0	1199.9	1198.6	1197.4	1196.1	1195.6	1195.8	1196.0	1196.2	1196.4	1197.8
170°	1207.6	1206.2	1204.8	1203.4	1201.9	1201.4	1201.6	1201.8	1201.9	1202.2	1203.8
172.5°	1211.9	1210.5	1209.1	1207.7	1206.3	1205.8	1206.1	1206.5	1206.8	1207.2	1208.6
175°	1216.6	1215.4	1214.2	1213.0	1211.7	1211.3	1211.5	1211.7	1211.9	1212.1	1213.7
177.5°	1218.8	1217.8	1216.8	1215.8	1215.0	1214.5	1214.7	1214.9	1215.0	1215.1	1216.3
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	22.6	22.7	22.9	22.9	22.7	22.6	22.3	22.1
90°	16.4	17.5	18.5	19.3	19.9	20.4	21.0	21.7
92.5°	16.4	17.5	18.5	19.1	19.4	19.6	19.9	20.2
95°	16.4	17.5	18.5	18.9	18.9	18.9	18.9	18.9
97.5°	33.1	27.4	21.8	18.9	18.9	18.9	18.9	18.9
100°	97.2	67.3	37.5	22.1	21.3	20.5	19.7	18.9
102.5°	188.9	183.2	177.6	168.0	154.4	140.7	127.1	113.4
105°	268.8	268.8	268.8	268.7	268.5	268.2	268.0	267.9
107.5°	340.3	340.3	340.4	340.1	339.5	338.9	338.2	337.7
110°	386.6	386.0	385.4	385.2	385.4	385.6	385.8	386.0



TEST NUMBER: P333416-940

CATALOG NUMBER: S125DIW-S850D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.5	431.7	431.0	430.4	430.2	429.8	429.5	429.3
115°	501.6	500.8	500.0	499.0	497.8	496.6	495.4	494.2
117.5°	568.5	567.4	566.3	565.5	565.1	564.5	564.0	563.5
120°	611.5	611.2	610.7	610.0	609.0	608.1	607.1	606.0
122.5°	652.6	652.3	651.8	651.1	650.0	648.8	647.6	646.5
125°	712.7	711.9	711.1	710.3	709.8	709.2	708.6	707.9
127.5°	767.5	767.0	766.6	765.6	764.2	762.7	761.2	759.7
130°	803.3	802.6	802.0	801.2	800.2	799.2	798.3	797.3
132.5°	836.7	836.5	836.4	835.9	834.9	833.8	832.9	831.9
135°	885.7	885.3	884.9	884.1	882.9	881.7	880.5	879.3
137.5°	931.4	931.5	931.6	931.1	930.1	929.0	928.0	926.9
140°	959.5	959.8	960.3	959.8	958.7	957.4	956.3	955.0
142.5°	986.9	987.0	987.1	986.6	985.3	984.2	982.9	981.8
145°	1025.8	1026.0	1026.2	1025.7	1024.5	1023.3	1022.1	1020.9
147.5°	1059.1	1059.4	1059.5	1059.0	1057.5	1056.1	1054.6	1053.2
150°	1080.3	1080.8	1081.1	1080.5	1078.9	1077.3	1075.7	1074.1
152.5°	1099.0	1099.5	1099.8	1099.4	1097.9	1096.4	1095.0	1093.6
155°	1124.9	1125.5	1126.1	1125.6	1124.0	1122.4	1120.8	1119.2
157.5°	1146.3	1146.9	1147.5	1147.1	1145.5	1143.9	1142.3	1140.7
160°	1159.6	1160.4	1161.2	1160.7	1159.2	1157.6	1156.0	1154.4
162.5°	1171.8	1172.9	1174.0	1173.7	1171.9	1170.2	1168.4	1166.6
165°	1187.4	1188.7	1189.8	1189.6	1188.0	1186.4	1184.8	1183.2
167.5°	1199.3	1200.7	1202.2	1202.0	1200.2	1198.4	1196.6	1194.8
170°	1205.4	1207.0	1208.6	1208.4	1206.7	1204.9	1203.1	1201.2
172.5°	1210.1	1211.6	1213.0	1212.8	1211.0	1209.2	1207.4	1205.6
175°	1215.3	1216.9	1218.5	1218.4	1216.6	1214.8	1213.0	1211.2
177.5°	1217.4	1218.5	1219.7	1219.6	1218.3	1217.0	1215.8	1214.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6

(END OF REPORT)