

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333712-935

Luminaire Tested: **S125RDIW-S1090D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333712-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1340U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8288.8 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	71	81	75	70	65	62	59	56	51	49	46	41	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24				
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	29	27	24	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9143	9143	9143	9143
5°	10519	9155	8085	9155
10°	12066	9108	7134	9108
15°	13032	9014	6341	9014
20°	14370	8906	5856	8906
25°	16631	8763	5433	8763
30°	18098	8611	5158	8611
35°	15266	8435	4902	8435
40°	10662	8118	4683	8118
45°	7909	7691	4469	7691
50°	6306	7246	4285	7246
55°	5353	6694	4122	6694
60°	4624	6200	3858	6200
65°	4121	5665	3321	5665
70°	3620	5189	3029	5189
75°	3132	4494	2842	4494
80°	2377	3782	2377	3782
85°	1979	2971	2238	2971



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	1.6
10°-20°	397.8	4.8
20°-30°	630.8	7.6
30°-40°	760.7	9.2
40°-50°	679.3	8.2
50°-60°	520.9	6.3
60°-70°	338.5	4.1
70°-80°	164.6	2.0
80°-90°	42.4	0.5
90°-100°	54.6	0.7
100°-110°	336.8	4.1
110°-120°	610.9	7.4
120°-130°	783.9	9.5
130°-140°	843.2	10.2
140°-150°	791.5	9.5
150°-160°	640.2	7.7
160°-170°	414.1	5.0
170°-180°	142.8	1.7
0°-30°	1164.4	14.0
0°-40°	1925.0	23.2
0°-60°	3125.2	37.7
0°-90°	3670.8	44.3
90°-120°	1002.3	12.1
90°-150°	3420.9	41.3
90°-180°	4618.0	55.7
0°-180°	8288.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1416	1416	1416	1416	1416	
5°	1622	1412	1247	1412	1622	162
15°	1949	1348	948	1348	1949	559
25°	2334	1230	762	1230	2334	1072
35°	1936	1070	622	1070	1936	1170
45°	866	842	489	842	866	691
55°	475	594	366	594	475	431
65°	270	371	217	371	270	268
75°	126	180	114	180	126	134
85°	27	40	30	40	27	31
90°	27	1	27	1	27	13
95°	23	64	23	64	23	19
105°	331	328	331	328	331	299
115°	611	615	611	615	611	606
125°	875	875	875	875	875	779
135°	1087	1091	1087	1091	1087	839
145°	1262	1265	1262	1265	1262	788
155°	1384	1393	1384	1393	1384	638
165°	1463	1470	1463	1470	1463	413
175°	1497	1504	1497	1504	1497	142
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1489.1	1488.2	1490.0	1484.9	1485.4	1477.5	1477.5	1471.4	1463.5	1457.5	1454.7
5°	1622.5	1623.7	1621.3	1612.7	1606.8	1598.1	1588.2	1570.8	1556.3	1542.3	1531.3
7.5°	1759.9	1760.7	1753.0	1750.3	1735.7	1725.0	1703.1	1679.3	1658.3	1631.6	1611.1
10°	1839.9	1839.3	1831.1	1824.7	1812.0	1795.7	1774.2	1746.3	1720.1	1691.1	1663.2
12.5°	1886.4	1884.8	1882.2	1874.5	1862.6	1848.2	1830.0	1802.5	1770.3	1738.5	1706.0
15°	1949.1	1945.0	1937.5	1927.6	1910.7	1893.9	1873.5	1849.2	1818.3	1782.3	1752.1
17.5°	2026.7	2026.9	2015.3	2001.5	1978.6	1948.9	1917.4	1878.1	1836.3	1796.6	1764.4
20°	2090.9	2089.1	2077.5	2050.8	2024.6	1987.4	1951.5	1903.2	1852.0	1800.4	1760.2
22.5°	2183.0	2178.4	2166.3	2131.2	2090.7	2042.8	1987.7	1928.7	1866.9	1808.2	1755.6
25°	2333.8	2330.3	2306.4	2265.8	2208.9	2135.0	2063.0	1982.2	1893.3	1816.0	1752.1
27.5°	2437.0	2433.2	2415.5	2381.7	2329.2	2251.5	2154.0	2046.0	1935.0	1828.7	1736.6
30°	2426.8	2435.5	2433.2	2417.5	2378.0	2308.3	2218.2	2096.7	1964.8	1839.9	1730.0
32.5°	2280.8	2288.6	2309.0	2339.9	2342.2	2314.3	2247.0	2134.8	1998.3	1856.1	1724.9
35°	1936.3	1946.8	1986.3	2048.5	2129.9	2197.8	2211.7	2151.3	2028.7	1875.9	1717.3
37.5°	1488.6	1545.8	1579.1	1644.5	1767.5	1892.5	2012.8	2057.1	2004.8	1867.8	1704.8
40°	1264.6	1278.5	1337.7	1411.5	1515.0	1645.2	1816.6	1940.3	1944.5	1849.2	1685.2
42.5°	1082.3	1099.9	1140.7	1199.5	1288.1	1418.3	1595.3	1758.6	1834.3	1798.0	1659.7
45°	865.9	879.3	908.9	954.2	1022.2	1129.7	1281.9	1470.8	1620.7	1679.5	1591.1
47.5°	711.3	718.5	744.3	778.9	829.1	907.5	1025.4	1189.3	1369.2	1495.2	1482.8
50°	627.6	635.8	655.5	681.7	724.1	790.3	884.5	1021.1	1206.4	1360.4	1391.2
52.5°	562.5	569.3	581.6	606.3	641.4	692.2	768.3	891.8	1058.6	1222.4	1293.6
55°	475.4	480.0	489.9	503.9	531.8	568.3	634.0	719.5	854.3	1019.3	1123.9
57.5°	403.6	405.9	412.2	425.1	444.4	471.1	518.5	590.9	687.6	836.2	951.7
60°	358.0	360.3	368.4	377.1	392.3	416.6	453.8	504.4	597.4	720.1	836.8
62.5°	321.7	323.1	326.6	335.3	348.5	367.4	396.7	437.9	511.9	619.6	729.9
65°	269.7	270.2	271.4	278.4	286.5	300.4	319.6	348.7	404.5	485.9	583.4
67.5°	219.6	220.5	224.5	227.0	235.5	242.8	254.1	276.3	315.6	370.4	446.3
70°	191.7	191.2	195.3	198.2	201.0	209.8	217.3	235.4	259.8	301.6	365.0
72.5°	165.7	164.2	166.0	167.0	170.8	176.8	184.3	195.4	214.2	243.1	291.5
75°	125.5	126.1	126.1	127.3	130.2	132.5	134.8	140.6	151.1	170.3	196.4
77.5°	88.1	87.1	89.6	90.0	91.7	94.3	96.3	98.6	102.9	110.7	124.2
80°	63.9	63.9	64.5	66.2	65.7	66.8	69.7	72.1	77.3	82.0	86.6
82.5°	49.1	48.6	49.2	49.5	49.4	50.5	51.6	52.1	54.1	56.4	59.6
85°	26.7	26.7	27.3	27.3	27.9	27.9	28.5	28.5	28.5	29.0	29.6
87.5°	15.6	15.0	14.4	14.2	14.6	15.2	14.6	13.9	13.6	13.3	13.4
90°	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3	19.1	17.8	16.1
92.5°	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3	19.1	17.8	16.3
95°	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3	19.1	17.8	27.2
97.5°	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9	47.9	54.8	73.4
100°	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1	157.0	194.0	193.0
102.5°	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5	240.5	247.5	246.8
105°	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6	420.5	420.5	420.0
110°	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9	478.6	479.3	478.9



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5	535.5	536.4	536.1
115°	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1	621.0	622.1	621.8
117.5°	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7	704.0	705.2	704.3
120°	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0	756.5	756.9	756.2
122.5°	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8	807.3	807.8	807.4
125°	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9	881.9	882.9	882.9
127.5°	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7	949.3	949.8	949.9
130°	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9	993.7	994.4	994.1
132.5°	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2	1034.4	1034.5	1035.1
135°	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8	1095.4	1095.8	1096.3
137.5°	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3	1151.2	1151.2	1151.6
140°	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0	1185.5	1185.0	1185.3
142.5°	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0	1219.9	1219.8	1219.4
145°	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0	1267.7	1267.5	1267.5
147.5°	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2	1308.8	1308.5	1308.2
150°	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4	1334.9	1334.4	1333.9
152.5°	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6	1358.1	1357.5	1357.1
155°	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5	1389.7	1389.1	1388.5
157.5°	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9	1416.1	1415.3	1415.3
160°	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4	1432.4	1431.4	1431.2
162.5°	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4	1447.0	1445.6	1445.4
165°	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7	1466.3	1464.8	1464.6
167.5°	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5	1480.7	1478.9	1478.6
170°	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0	1488.0	1486.0	1485.7
172.5°	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8	1494.0	1492.2	1491.8
175°	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2	1500.2	1498.2	1498.1
177.5°	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9	1503.5	1502.0	1501.8
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1454.7	1451.4	1445.4	1439.8	1432.8	1426.8	1422.6	1417.5	1411.0	1403.1	1396.5
5°	1519.1	1506.2	1489.4	1474.9	1456.3	1441.7	1426.7	1412.1	1397.6	1379.0	1362.7
7.5°	1590.4	1564.0	1538.3	1506.1	1476.8	1450.6	1425.5	1400.1	1375.2	1348.8	1323.4
10°	1634.1	1602.1	1566.7	1526.0	1488.8	1453.4	1420.8	1388.9	1355.2	1325.5	1293.6
12.5°	1675.1	1633.7	1593.2	1541.9	1497.2	1453.9	1412.5	1372.6	1336.6	1298.1	1263.9
15°	1712.0	1671.3	1626.0	1563.2	1501.1	1448.7	1399.9	1348.2	1303.5	1260.4	1222.1
17.5°	1726.3	1683.6	1631.0	1570.6	1502.7	1436.9	1374.0	1317.3	1264.6	1214.5	1171.4
20°	1720.7	1679.5	1625.4	1567.9	1495.2	1426.7	1358.7	1295.9	1237.3	1184.3	1138.4
22.5°	1707.2	1664.6	1612.4	1551.6	1482.6	1409.9	1337.3	1270.3	1208.8	1154.1	1104.1
25°	1687.0	1628.9	1575.5	1516.1	1450.5	1378.5	1303.5	1229.7	1164.0	1108.2	1053.6
27.5°	1665.9	1593.5	1525.4	1466.5	1397.1	1332.8	1260.6	1184.9	1115.9	1059.0	1003.0
30°	1646.9	1565.6	1490.6	1423.7	1358.1	1297.1	1228.5	1154.7	1083.8	1025.1	968.2
32.5°	1623.2	1536.7	1454.3	1377.3	1313.9	1253.4	1191.3	1120.8	1051.7	991.2	933.3
35°	1593.5	1483.1	1393.5	1311.6	1241.3	1182.6	1126.8	1069.9	1000.7	938.0	881.6
37.5°	1554.4	1429.1	1325.5	1236.3	1162.1	1103.2	1059.1	1007.1	944.0	883.9	831.6
40°	1530.7	1390.1	1276.7	1188.4	1110.5	1048.4	1007.1	962.9	905.4	849.0	796.7
42.5°	1499.1	1354.3	1227.4	1135.4	1057.0	997.2	955.5	916.9	868.7	815.5	759.5
45°	1437.1	1284.9	1151.8	1053.0	974.0	915.2	876.3	842.1	805.5	756.6	707.8
47.5°	1356.4	1212.5	1073.2	965.4	887.9	833.4	795.7	768.6	742.4	700.9	653.5
50°	1291.8	1153.0	1016.9	912.4	829.8	778.1	742.7	721.2	697.3	659.6	620.1
52.5°	1215.6	1091.6	958.4	851.4	773.6	725.1	691.0	669.6	650.0	619.1	581.4
55°	1095.5	986.8	864.7	767.7	696.2	647.4	614.8	594.5	582.9	556.7	527.1
57.5°	956.7	878.9	771.3	677.7	614.5	566.3	542.4	525.1	512.0	493.5	472.6
60°	860.1	805.5	708.9	620.1	562.0	516.0	494.6	480.0	467.8	452.1	435.8
62.5°	762.0	722.2	638.3	562.0	508.5	470.0	449.9	436.8	422.8	412.2	396.3
65°	630.5	595.0	536.9	477.1	427.7	396.9	382.4	370.7	362.1	350.4	339.4
67.5°	490.5	476.0	435.9	394.7	359.2	331.8	319.3	311.2	300.7	293.7	286.1
70°	404.5	397.5	369.0	341.7	308.6	290.0	278.4	274.8	262.1	255.1	249.9
72.5°	328.2	324.9	308.6	289.6	266.3	250.0	239.3	235.4	227.2	221.6	218.3
75°	224.9	226.1	223.2	210.9	202.2	191.7	182.4	180.1	174.4	169.7	166.8
77.5°	142.2	148.2	148.4	147.8	144.4	137.9	134.1	132.4	126.7	124.9	124.2
80°	97.6	104.0	109.9	109.3	108.1	106.3	103.4	101.7	98.8	97.0	95.9
82.5°	65.1	71.0	75.9	79.0	78.8	77.1	75.1	74.3	73.7	72.4	72.2
85°	30.8	31.9	33.7	37.8	40.6	41.2	40.6	40.1	38.3	38.9	39.5
87.5°	13.6	13.3	13.3	13.0	12.1	14.0	15.1	15.1	14.6	14.0	13.5
90°	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1	15.8	14.4	13.0
95°	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5	62.8	62.1	61.3
97.5°	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7	134.0	135.3	136.6
100°	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1	186.9	187.6	188.4
102.5°	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6	241.5	242.5	243.4
105°	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8	328.7	329.8	330.7
107.5°	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3	418.3	418.3	418.3
110°	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4	533.0	533.6	534.2
115°	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4	616.6	617.9	619.1
117.5°	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2	701.1	701.1	701.0
120°	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7	754.5	754.2	754.0
122.5°	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9	802.9	803.8	804.8
125°	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1	876.8	878.6	880.3
127.5°	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9	946.2	947.4	948.6
130°	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7	988.9	990.2	991.4
132.5°	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5	1031.9	1033.4	1034.8
135°	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4	1092.9	1094.3	1095.8
137.5°	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4	1148.6	1149.9	1151.2
140°	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9	1184.4	1184.9	1185.3
142.5°	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9	1217.2	1217.5	1217.8
145°	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2	1265.8	1266.3	1266.8
147.5°	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6	1307.5	1307.4	1307.3
150°	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1333.9	1333.4	1332.9
152.5°	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2	1359.2	1358.1	1357.0
155°	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4	1392.0	1390.5	1389.1
157.5°	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1	1418.2	1417.3	1416.4
160°	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9	1435.5	1434.0	1432.4
162.5°	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2	1449.8	1448.2	1446.7
165°	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4	1468.9	1467.4	1465.9
167.5°	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6	1483.2	1481.6	1480.1
170°	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7	1491.0	1489.2	1487.5
172.5°	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1	1496.3	1494.6	1492.8
175°	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8	1502.4	1500.9	1499.3
177.5°	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5	1505.3	1504.2	1503.0
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1391.9	1385.4	1380.8	1371.5	1364.9	1362.2	1357.0	1355.6	1360.7	1357.0	1356.6
5°	1350.6	1333.7	1320.3	1306.9	1292.4	1283.1	1269.2	1266.9	1263.3	1258.1	1257.0
7.5°	1300.9	1278.9	1261.7	1239.7	1220.5	1205.1	1187.6	1179.3	1174.8	1168.0	1159.0
10°	1267.4	1241.3	1218.1	1195.9	1172.2	1153.0	1135.5	1122.1	1113.4	1105.3	1101.8
12.5°	1234.4	1207.8	1178.0	1151.3	1124.7	1103.2	1083.9	1075.2	1065.6	1056.0	1047.9
15°	1183.2	1147.7	1115.2	1084.3	1061.7	1038.5	1019.9	1007.1	992.6	988.5	972.8
17.5°	1128.8	1094.0	1055.9	1023.5	997.2	971.6	951.1	936.7	925.7	910.8	903.5
20°	1094.8	1053.6	1016.4	986.8	957.7	927.5	906.5	894.3	883.9	871.7	865.9
22.5°	1058.6	1018.2	980.2	945.4	915.8	886.1	871.2	858.6	846.7	835.4	827.8
25°	1005.3	964.7	924.5	888.6	857.7	836.2	818.8	804.3	797.9	786.9	778.7
27.5°	952.7	909.5	867.9	831.9	807.8	786.5	772.2	760.7	749.2	739.5	732.5
30°	918.8	874.6	829.2	800.8	775.2	754.8	739.2	728.1	719.5	710.8	705.5
32.5°	884.8	839.3	799.0	768.3	744.1	726.5	710.3	699.8	690.6	681.0	674.8
35°	830.4	783.9	751.4	721.2	697.3	681.1	670.0	655.0	647.4	640.4	634.0
37.5°	779.9	736.7	701.5	674.9	654.2	638.1	623.8	615.6	606.3	600.0	594.7
40°	742.7	703.2	671.2	643.3	628.2	610.2	596.8	586.3	579.4	571.3	565.4
42.5°	709.2	672.4	641.4	616.3	597.5	582.3	569.4	559.0	550.1	544.3	539.4
45°	661.9	625.3	595.0	571.8	554.4	539.8	526.5	521.2	509.6	502.7	500.3
47.5°	612.9	580.2	551.0	529.6	511.8	498.0	485.4	474.8	468.4	461.5	457.8
50°	580.0	548.5	521.2	500.3	482.9	467.8	456.2	449.2	440.5	434.1	429.5
52.5°	547.0	517.9	490.6	470.6	455.5	440.4	427.4	420.4	412.2	408.0	404.8
55°	499.8	469.0	445.7	425.9	410.3	396.3	384.1	377.1	372.0	367.8	366.7
57.5°	446.3	421.9	400.3	382.5	366.2	353.1	342.4	335.8	331.1	330.5	327.1
60°	411.5	389.3	369.6	350.4	336.5	324.3	315.0	307.4	302.7	302.2	301.0
62.5°	376.6	355.4	337.1	320.2	307.6	295.9	287.1	278.6	275.8	272.9	270.4
65°	324.9	305.7	290.6	277.2	263.8	253.9	245.2	240.0	233.6	230.1	223.8
67.5°	274.1	259.2	244.7	233.4	222.9	213.5	206.3	198.5	194.2	191.4	186.8
70°	240.6	228.9	214.5	202.2	194.1	186.6	180.7	172.0	169.1	166.8	164.5
72.5°	209.0	198.7	186.6	176.7	168.5	161.4	154.7	150.6	147.7	145.4	144.0
75°	164.5	154.5	144.1	137.2	131.3	125.5	122.0	119.2	118.0	117.4	115.0
77.5°	120.8	115.5	107.2	101.6	97.7	95.4	92.3	90.7	90.7	88.1	87.3
80°	92.4	89.5	82.5	80.2	77.3	75.0	73.2	70.3	67.4	66.2	64.5
82.5°	68.7	65.8	63.0	59.2	56.8	55.4	53.7	52.6	53.0	51.4	50.5
85°	36.6	33.7	32.5	31.9	30.8	31.9	31.3	30.8	30.2	29.6	30.2
87.5°	13.4	13.8	13.7	15.0	13.9	14.7	15.0	14.7	15.0	15.2	15.0
90°	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3	21.5	22.8	23.8
92.5°	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3	21.5	22.8	23.6
95°	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3	21.5	22.8	23.4
97.5°	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9	33.9	26.9	23.4
100°	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1	83.3	46.3	27.4
102.5°	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5	226.5	219.6	207.6
105°	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.1
107.5°	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6	420.7	420.7	420.3
110°	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9	477.2	476.4	476.1



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5	533.6	532.7	532.0
115°	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1	619.1	618.1	616.8
117.5°	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7	701.4	700.1	699.0
120°	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0	755.4	754.9	754.1
122.5°	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8	806.2	805.8	804.8
125°	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9	879.9	878.9	878.0
127.5°	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7	948.1	947.6	946.4
130°	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9	992.1	991.4	990.4
132.5°	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2	1034.1	1033.9	1033.2
135°	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8	1094.3	1093.8	1092.9
137.5°	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3	1151.4	1151.5	1150.9
140°	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0	1186.5	1187.0	1186.5
142.5°	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0	1220.1	1220.2	1219.5
145°	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0	1268.3	1268.5	1267.9
147.5°	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2	1309.4	1309.8	1309.0
150°	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4	1335.8	1336.4	1335.6
152.5°	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6	1359.1	1359.5	1358.9
155°	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5	1391.2	1392.0	1391.4
157.5°	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9	1417.7	1418.5	1417.9
160°	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4	1434.3	1435.4	1434.9
162.5°	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4	1449.8	1451.2	1450.8
165°	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7	1469.3	1470.8	1470.5
167.5°	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5	1484.2	1486.0	1485.7
170°	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0	1491.9	1493.9	1493.8
172.5°	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8	1497.6	1499.3	1499.2
175°	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2	1504.2	1506.1	1506.1
177.5°	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9	1506.2	1507.6	1507.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1356.1	1351.0	1349.6	1351.4	1349.6	1351.0	1356.1	1356.6	1357.0	1360.7	1355.6
5°	1251.2	1245.4	1248.3	1247.1	1248.3	1245.4	1251.2	1257.0	1258.1	1263.3	1266.9
7.5°	1158.9	1151.7	1144.0	1146.4	1144.0	1151.7	1158.9	1159.0	1168.0	1174.8	1179.3
10°	1094.2	1088.5	1084.9	1087.9	1084.9	1088.5	1094.2	1101.8	1105.3	1113.4	1122.1
12.5°	1039.8	1036.4	1033.4	1032.1	1033.4	1036.4	1039.8	1047.9	1056.0	1065.6	1075.2
15°	965.9	958.9	956.0	948.4	956.0	958.9	965.9	972.8	988.5	992.6	1007.1
17.5°	897.6	895.3	887.7	884.5	887.7	895.3	897.6	903.5	910.8	925.7	936.7
20°	857.1	854.8	847.3	852.0	847.3	854.8	857.1	865.9	871.7	883.9	894.3
22.5°	823.7	818.6	816.1	814.8	816.1	818.6	823.7	827.8	835.4	846.7	858.6
25°	776.4	768.8	765.9	762.4	765.9	768.8	776.4	778.7	786.9	797.9	804.3
27.5°	729.2	725.1	721.3	720.4	721.3	725.1	729.2	732.5	739.5	749.2	760.7
30°	698.5	694.5	691.6	691.6	691.6	694.5	698.5	705.5	710.8	719.5	728.1
32.5°	671.1	668.0	665.0	664.6	665.0	668.0	671.1	674.8	681.0	690.6	699.8
35°	631.1	626.5	625.3	621.8	625.3	626.5	631.1	634.0	640.4	647.4	655.0
37.5°	589.6	585.7	585.7	585.3	585.7	585.7	589.6	594.7	600.0	606.3	615.6
40°	563.1	560.2	559.6	555.5	559.6	560.2	563.1	565.4	571.3	579.4	586.3
42.5°	534.8	533.2	531.2	529.5	531.2	533.2	534.8	539.4	544.3	550.1	559.0
45°	496.3	492.2	492.2	489.3	492.2	492.2	496.3	500.3	502.7	509.6	521.2
47.5°	456.5	453.4	453.7	450.7	453.7	453.4	456.5	457.8	461.5	468.4	474.8
50°	430.1	428.3	427.7	426.5	427.7	428.3	430.1	429.5	434.1	440.5	449.2
52.5°	403.6	402.7	404.9	402.3	404.9	402.7	403.6	404.8	408.0	412.2	420.4
55°	367.8	366.1	369.6	366.1	369.6	366.1	367.8	366.7	367.8	372.0	377.1
57.5°	326.8	325.2	328.3	326.6	328.3	325.2	326.8	327.1	330.5	331.1	335.8
60°	299.9	296.4	298.1	298.7	298.1	296.4	299.9	301.0	302.2	302.7	307.4
62.5°	267.8	265.7	267.0	264.3	267.0	265.7	267.8	270.4	272.9	275.8	278.6
65°	222.6	220.8	218.5	217.3	218.5	220.8	222.6	223.8	230.1	233.6	240.0
67.5°	187.0	182.8	182.7	183.7	182.7	182.8	187.0	186.8	191.4	194.2	198.5
70°	161.0	161.0	160.4	160.4	160.4	161.0	161.0	164.5	166.8	169.1	172.0
72.5°	142.8	142.4	141.3	140.9	141.3	142.4	142.8	144.0	145.4	147.7	150.6
75°	115.0	115.6	114.5	113.9	114.5	115.6	115.0	115.0	117.4	118.0	119.2
77.5°	85.0	82.5	83.8	82.5	83.8	82.5	85.0	87.3	88.1	90.7	90.7
80°	64.5	63.9	65.7	63.9	65.7	63.9	64.5	64.5	66.2	67.4	70.3
82.5°	51.1	50.5	51.2	49.9	51.2	50.5	51.1	50.5	51.4	53.0	52.6
85°	30.8	30.2	29.6	30.2	29.6	30.2	30.8	30.2	29.6	30.2	30.8
87.5°	15.6	15.2	15.4	15.6	15.4	15.2	15.6	15.0	15.2	15.0	14.7
90°	24.5	25.2	26.0	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3
92.5°	23.9	24.3	24.6	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3
95°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3
97.5°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9
100°	26.3	25.4	24.4	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1
102.5°	190.8	173.9	157.0	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5
105°	331.8	331.6	331.3	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2
107.5°	419.6	418.9	418.1	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6
110°	476.4	476.6	476.9	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	531.7	531.3	531.0	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5
115°	615.4	613.9	612.3	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1
117.5°	698.4	697.8	697.2	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7
120°	752.9	751.6	750.4	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0
122.5°	803.4	801.9	800.5	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8
125°	877.4	876.6	875.8	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9
127.5°	944.6	942.8	940.9	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7
130°	989.2	987.9	986.7	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9
132.5°	1032.0	1030.8	1029.5	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2
135°	1091.4	1089.9	1088.4	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8
137.5°	1149.6	1148.3	1147.0	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3
140°	1185.0	1183.5	1182.1	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0
142.5°	1218.0	1216.5	1215.0	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0
145°	1266.4	1264.9	1263.4	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0
147.5°	1307.2	1305.4	1303.6	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2
150°	1333.6	1331.6	1329.6	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4
152.5°	1357.1	1355.4	1353.6	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6
155°	1389.4	1387.4	1385.4	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5
157.5°	1415.9	1413.9	1412.0	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9
160°	1432.9	1430.9	1428.9	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4
162.5°	1448.6	1446.4	1444.2	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4
165°	1468.5	1466.5	1464.6	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7
167.5°	1483.5	1481.4	1479.1	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5
170°	1491.6	1489.4	1487.1	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0
172.5°	1496.9	1494.7	1492.5	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8
175°	1503.8	1501.6	1499.3	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2
177.5°	1505.9	1504.3	1502.7	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1357.0	1362.2	1364.9	1371.5	1380.8	1385.4	1391.9	1396.5	1403.1	1411.0	1417.5
5°	1269.2	1283.1	1292.4	1306.9	1320.3	1333.7	1350.6	1362.7	1379.0	1397.6	1412.1
7.5°	1187.6	1205.1	1220.5	1239.7	1261.7	1278.9	1300.9	1323.4	1348.8	1375.2	1400.1
10°	1135.5	1153.0	1172.2	1195.9	1218.1	1241.3	1267.4	1293.6	1325.5	1355.2	1388.9
12.5°	1083.9	1103.2	1124.7	1151.3	1178.0	1207.8	1234.4	1263.9	1298.1	1336.6	1372.6
15°	1019.9	1038.5	1061.7	1084.3	1115.2	1147.7	1183.2	1222.1	1260.4	1303.5	1348.2
17.5°	951.1	971.6	997.2	1023.5	1055.9	1094.0	1128.8	1171.4	1214.5	1264.6	1317.3
20°	906.5	927.5	957.7	986.8	1016.4	1053.6	1094.8	1138.4	1184.3	1237.3	1295.9
22.5°	871.2	886.1	915.8	945.4	980.2	1018.2	1058.6	1104.1	1154.1	1208.8	1270.3
25°	818.8	836.2	857.7	888.6	924.5	964.7	1005.3	1053.6	1108.2	1164.0	1229.7
27.5°	772.2	786.5	807.8	831.9	867.9	909.5	952.7	1003.0	1059.0	1115.9	1184.9
30°	739.2	754.8	775.2	800.8	829.2	874.6	918.8	968.2	1025.1	1083.8	1154.7
32.5°	710.3	726.5	744.1	768.3	799.0	839.3	884.8	933.3	991.2	1051.7	1120.8
35°	670.0	681.1	697.3	721.2	751.4	783.9	830.4	881.6	938.0	1000.7	1069.9
37.5°	623.8	638.1	654.2	674.9	701.5	736.7	779.9	831.6	883.9	944.0	1007.1
40°	596.8	610.2	628.2	643.3	671.2	703.2	742.7	796.7	849.0	905.4	962.9
42.5°	569.4	582.3	597.5	616.3	641.4	672.4	709.2	759.5	815.5	868.7	916.9
45°	526.5	539.8	554.4	571.8	595.0	625.3	661.9	707.8	756.6	805.5	842.1
47.5°	485.4	498.0	511.8	529.6	551.0	580.2	612.9	653.5	700.9	742.4	768.6
50°	456.2	467.8	482.9	500.3	521.2	548.5	580.0	620.1	659.6	697.3	721.2
52.5°	427.4	440.4	455.5	470.6	490.6	517.9	547.0	581.4	619.1	650.0	669.6
55°	384.1	396.3	410.3	425.9	445.7	469.0	499.8	527.1	556.7	582.9	594.5
57.5°	342.4	353.1	366.2	382.5	400.3	421.9	446.3	472.6	493.5	512.0	525.1
60°	315.0	324.3	336.5	350.4	369.6	389.3	411.5	435.8	452.1	467.8	480.0
62.5°	287.1	295.9	307.6	320.2	337.1	355.4	376.6	396.3	412.2	422.8	436.8
65°	245.2	253.9	263.8	277.2	290.6	305.7	324.9	339.4	350.4	362.1	370.7
67.5°	206.3	213.5	222.9	233.4	244.7	259.2	274.1	286.1	293.7	300.7	311.2
70°	180.7	186.6	194.1	202.2	214.5	228.9	240.6	249.9	255.1	262.1	274.8
72.5°	154.7	161.4	168.5	176.7	186.6	198.7	209.0	218.3	221.6	227.2	235.4
75°	122.0	125.5	131.3	137.2	144.1	154.5	164.5	166.8	169.7	174.4	180.1
77.5°	92.3	95.4	97.7	101.6	107.2	115.5	120.8	124.2	124.9	126.7	132.4
80°	73.2	75.0	77.3	80.2	82.5	89.5	92.4	95.9	97.0	98.8	101.7
82.5°	53.7	55.4	56.8	59.2	63.0	65.8	68.7	72.2	72.4	73.7	74.3
85°	31.3	31.9	30.8	31.9	32.5	33.7	36.6	39.5	38.9	38.3	40.1
87.5°	15.0	14.7	13.9	15.0	13.7	13.8	13.4	13.5	14.0	14.6	15.1
90°	19.1	17.8	16.1	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1
92.5°	19.1	17.8	16.3	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1
95°	19.1	17.8	27.2	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5
97.5°	47.9	54.8	73.4	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7
100°	157.0	194.0	193.0	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1
102.5°	240.5	247.5	246.8	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6
105°	332.2	332.2	332.2	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8
107.5°	420.5	420.5	420.0	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3
110°	478.6	479.3	478.9	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	535.5	536.4	536.1	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4
115°	621.0	622.1	621.8	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4
117.5°	704.0	705.2	704.3	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2
120°	756.5	756.9	756.2	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7
122.5°	807.3	807.8	807.4	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9
125°	881.9	882.9	882.9	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1
127.5°	949.3	949.8	949.9	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9
130°	993.7	994.4	994.1	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7
132.5°	1034.4	1034.5	1035.1	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5
135°	1095.4	1095.8	1096.3	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4
137.5°	1151.2	1151.2	1151.6	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4
140°	1185.5	1185.0	1185.3	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9
142.5°	1219.9	1219.8	1219.4	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9
145°	1267.7	1267.5	1267.5	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2
147.5°	1308.8	1308.5	1308.2	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6
150°	1334.9	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4
152.5°	1358.1	1357.5	1357.1	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2
155°	1389.7	1389.1	1388.5	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4
157.5°	1416.1	1415.3	1415.3	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1
160°	1432.4	1431.4	1431.2	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9
162.5°	1447.0	1445.6	1445.4	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2
165°	1466.3	1464.8	1464.6	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4
167.5°	1480.7	1478.9	1478.6	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6
170°	1488.0	1486.0	1485.7	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7
172.5°	1494.0	1492.2	1491.8	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1
175°	1500.2	1498.2	1498.1	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8
177.5°	1503.5	1502.0	1501.8	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1422.6	1426.8	1432.8	1439.8	1445.4	1451.4	1454.7	1454.7	1457.5	1463.5	1471.4
5°	1426.7	1441.7	1456.3	1474.9	1489.4	1506.2	1519.1	1531.3	1542.3	1556.3	1570.8
7.5°	1425.5	1450.6	1476.8	1506.1	1538.3	1564.0	1590.4	1611.1	1631.6	1658.3	1679.3
10°	1420.8	1453.4	1488.8	1526.0	1566.7	1602.1	1634.1	1663.2	1691.1	1720.1	1746.3
12.5°	1412.5	1453.9	1497.2	1541.9	1593.2	1633.7	1675.1	1706.0	1738.5	1770.3	1802.5
15°	1399.9	1448.7	1501.1	1563.2	1626.0	1671.3	1712.0	1752.1	1782.3	1818.3	1849.2
17.5°	1374.0	1436.9	1502.7	1570.6	1631.0	1683.6	1726.3	1764.4	1796.6	1836.3	1878.1
20°	1358.7	1426.7	1495.2	1567.9	1625.4	1679.5	1720.7	1760.2	1800.4	1852.0	1903.2
22.5°	1337.3	1409.9	1482.6	1551.6	1612.4	1664.6	1707.2	1755.6	1808.2	1866.9	1928.7
25°	1303.5	1378.5	1450.5	1516.1	1575.5	1628.9	1687.0	1752.1	1816.0	1893.3	1982.2
27.5°	1260.6	1332.8	1397.1	1466.5	1525.4	1593.5	1665.9	1736.6	1828.7	1935.0	2046.0
30°	1228.5	1297.1	1358.1	1423.7	1490.6	1565.6	1646.9	1730.0	1839.9	1964.8	2096.7
32.5°	1191.3	1253.4	1313.9	1377.3	1454.3	1536.7	1623.2	1724.9	1856.1	1998.3	2134.8
35°	1126.8	1182.6	1241.3	1311.6	1393.5	1483.1	1593.5	1717.3	1875.9	2028.7	2151.3
37.5°	1059.1	1103.2	1162.1	1236.3	1325.5	1429.1	1554.4	1704.8	1867.8	2004.8	2057.1
40°	1007.1	1048.4	1110.5	1188.4	1276.7	1390.1	1530.7	1685.2	1849.2	1944.5	1940.3
42.5°	955.5	997.2	1057.0	1135.4	1227.4	1354.3	1499.1	1659.7	1798.0	1834.3	1758.6
45°	876.3	915.2	974.0	1053.0	1151.8	1284.9	1437.1	1591.1	1679.5	1620.7	1470.8
47.5°	795.7	833.4	887.9	965.4	1073.2	1212.5	1356.4	1482.8	1495.2	1369.2	1189.3
50°	742.7	778.1	829.8	912.4	1016.9	1153.0	1291.8	1391.2	1360.4	1206.4	1021.1
52.5°	691.0	725.1	773.6	851.4	958.4	1091.6	1215.6	1293.6	1222.4	1058.6	891.8
55°	614.8	647.4	696.2	767.7	864.7	986.8	1095.5	1123.9	1019.3	854.3	719.5
57.5°	542.4	566.3	614.5	677.7	771.3	878.9	956.7	951.7	836.2	687.6	590.9
60°	494.6	516.0	562.0	620.1	708.9	805.5	860.1	836.8	720.1	597.4	504.4
62.5°	449.9	470.0	508.5	562.0	638.3	722.2	762.0	729.9	619.6	511.9	437.9
65°	382.4	396.9	427.7	477.1	536.9	595.0	630.5	583.4	485.9	404.5	348.7
67.5°	319.3	331.8	359.2	394.7	435.9	476.0	490.5	446.3	370.4	315.6	276.3
70°	278.4	290.0	308.6	341.7	369.0	397.5	404.5	365.0	301.6	259.8	235.4
72.5°	239.3	250.0	266.3	289.6	308.6	324.9	328.2	291.5	243.1	214.2	195.4
75°	182.4	191.7	202.2	210.9	223.2	226.1	224.9	196.4	170.3	151.1	140.6
77.5°	134.1	137.9	144.4	147.8	148.4	148.2	142.2	124.2	110.7	102.9	98.6
80°	103.4	106.3	108.1	109.3	109.9	104.0	97.6	86.6	82.0	77.3	72.1
82.5°	75.1	77.1	78.8	79.0	75.9	71.0	65.1	59.6	56.4	54.1	52.1
85°	40.6	41.2	40.6	37.8	33.7	31.9	30.8	29.6	29.0	28.5	28.5
87.5°	15.1	14.0	12.1	13.0	13.3	13.3	13.6	13.4	13.3	13.6	13.9
90°	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3
92.5°	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3
95°	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3
97.5°	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9
100°	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1
102.5°	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5
105°	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6
110°	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5
115°	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1
117.5°	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7
120°	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0
122.5°	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8
125°	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9
127.5°	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7
130°	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9
132.5°	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2
135°	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8
137.5°	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3
140°	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0
142.5°	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0
145°	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0
147.5°	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2
150°	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4
152.5°	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6
155°	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5
157.5°	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9
160°	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4
162.5°	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4
165°	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7
167.5°	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5
170°	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0
172.5°	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8
175°	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2
177.5°	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1477.5	1477.5	1485.4	1484.9	1490.0	1488.2	1489.1
5°	1588.2	1598.1	1606.8	1612.7	1621.3	1623.7	1622.5
7.5°	1703.1	1725.0	1735.7	1750.3	1753.0	1760.7	1759.9
10°	1774.2	1795.7	1812.0	1824.7	1831.1	1839.3	1839.9
12.5°	1830.0	1848.2	1862.6	1874.5	1882.2	1884.8	1886.4
15°	1873.5	1893.9	1910.7	1927.6	1937.5	1945.0	1949.1
17.5°	1917.4	1948.9	1978.6	2001.5	2015.3	2026.9	2026.7
20°	1951.5	1987.4	2024.6	2050.8	2077.5	2089.1	2090.9
22.5°	1987.7	2042.8	2090.7	2131.2	2166.3	2178.4	2183.0
25°	2063.0	2135.0	2208.9	2265.8	2306.4	2330.3	2333.8
27.5°	2154.0	2251.5	2329.2	2381.7	2415.5	2433.2	2437.0
30°	2218.2	2308.3	2378.0	2417.5	2433.2	2435.5	2426.8
32.5°	2247.0	2314.3	2342.2	2339.9	2309.0	2288.6	2280.8
35°	2211.7	2197.8	2129.9	2048.5	1986.3	1946.8	1936.3
37.5°	2012.8	1892.5	1767.5	1644.5	1579.1	1545.8	1488.6
40°	1816.6	1645.2	1515.0	1411.5	1337.7	1278.5	1264.6
42.5°	1595.3	1418.3	1288.1	1199.5	1140.7	1099.9	1082.3
45°	1281.9	1129.7	1022.2	954.2	908.9	879.3	865.9
47.5°	1025.4	907.5	829.1	778.9	744.3	718.5	711.3
50°	884.5	790.3	724.1	681.7	655.5	635.8	627.6
52.5°	768.3	692.2	641.4	606.3	581.6	569.3	562.5
55°	634.0	568.3	531.8	503.9	489.9	480.0	475.4
57.5°	518.5	471.1	444.4	425.1	412.2	405.9	403.6
60°	453.8	416.6	392.3	377.1	368.4	360.3	358.0
62.5°	396.7	367.4	348.5	335.3	326.6	323.1	321.7
65°	319.6	300.4	286.5	278.4	271.4	270.2	269.7
67.5°	254.1	242.8	235.5	227.0	224.5	220.5	219.6
70°	217.3	209.8	201.0	198.2	195.3	191.2	191.7
72.5°	184.3	176.8	170.8	167.0	166.0	164.2	165.7
75°	134.8	132.5	130.2	127.3	126.1	126.1	125.5
77.5°	96.3	94.3	91.7	90.0	89.6	87.1	88.1
80°	69.7	66.8	65.7	66.2	64.5	63.9	63.9
82.5°	51.6	50.5	49.4	49.5	49.2	48.6	49.1
85°	28.5	27.9	27.9	27.3	27.3	26.7	26.7
87.5°	14.6	15.2	14.6	14.2	14.4	15.0	15.6
90°	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.2	476.4	476.1	476.4	476.6	476.9	477.2



TEST NUMBER: P333712-935

CATALOG NUMBER: S125RDIW-S1090D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)