

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333654-935

Luminaire Tested: **S125RDIW-S375D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333654-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5865.8 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	19	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3402	3402	3402
5°	3411	3371	3392
10°	3385	3341	3341
15°	3344	3273	3245
20°	3293	3178	3140
25°	3233	3085	3017
30°	3157	2976	2882
35°	3080	2864	2730
40°	3010	2748	2580
45°	2922	2617	2417
50°	2834	2475	2247
55°	2733	2339	2066
60°	2631	2174	1870
65°	2512	1984	1647
70°	2374	1743	1420
75°	2186	1470	1183
80°	1923	1153	993
85°	1623	941	889



TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.5	0.8
10°-20°	138.4	2.4
20°-30°	200.8	3.4
30°-40°	228.8	3.9
40°-50°	223.0	3.8
50°-60°	187.7	3.2
60°-70°	131.6	2.2
70°-80°	67.6	1.2
80°-90°	20.2	0.3
90°-100°	54.6	0.9
100°-110°	336.8	5.7
110°-120°	610.9	10.4
120°-130°	783.9	13.4
130°-140°	843.2	14.4
140°-150°	791.5	13.5
150°-160°	640.2	10.9
160°-170°	414.1	7.1
170°-180°	142.8	2.4
0°-30°	388.7	6.6
0°-40°	617.6	10.5
0°-60°	1028.3	17.5
0°-90°	1247.8	21.3
90°-120°	1002.3	17.1
90°-150°	3420.9	58.3
90°-180°	4618.0	78.7
0°-180°	5865.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	523	50
15°	500	498	490	489	485	141
25°	454	447	433	428	423	209
35°	391	381	363	352	346	245
45°	320	308	286	271	265	247
55°	243	230	208	190	184	217
65°	164	150	130	114	108	163
75°	88	75	59	50	47	93
85°	22	15	13	12	12	25
90°	1	10	18	23	27	4
95°	64	58	18	23	23	81
105°	328	332	332	332	331	347
115°	615	621	622	617	611	610
125°	875	882	883	878	875	781
135°	1091	1098	1096	1093	1087	841
145°	1265	1267	1268	1268	1262	791
155°	1393	1387	1389	1392	1384	642
165°	1470	1464	1465	1471	1463	415
175°	1504	1498	1498	1506	1497	143
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	527.8	527.6	527.4	527.2	526.9	526.5	525.8	525.0	524.3	523.7	524.3
5°	526.1	525.7	525.4	525.0	524.6	524.0	523.0	522.0	521.1	520.0	521.0
7.5°	520.9	520.6	520.2	519.9	519.5	518.8	517.6	516.4	515.3	514.1	514.7
10°	516.1	515.8	515.6	515.3	515.1	514.3	513.1	511.8	510.6	509.4	509.6
12.5°	510.7	510.3	510.1	509.7	509.4	508.3	506.7	505.1	503.3	501.7	501.9
15°	500.2	499.6	499.1	498.6	498.1	496.9	495.0	493.2	491.3	489.5	489.4
17.5°	488.4	487.5	486.7	485.9	485.1	483.5	481.1	478.8	476.5	474.2	473.7
20°	479.1	478.2	477.3	476.5	475.5	473.7	470.9	468.0	465.2	462.4	461.9
22.5°	468.9	468.0	467.2	466.2	465.4	463.5	460.5	457.5	454.5	451.6	450.7
25°	453.7	452.3	451.0	449.6	448.3	446.0	442.7	439.5	436.2	432.9	431.8
27.5°	436.1	434.5	432.9	431.3	429.6	427.1	423.6	420.1	416.6	413.1	411.5
30°	423.4	421.7	420.0	418.4	416.6	414.0	410.3	406.6	402.9	399.1	397.1
32.5°	411.0	409.0	407.1	405.1	403.1	400.3	396.5	392.7	388.9	385.1	382.9
35°	390.7	388.7	386.5	384.4	382.3	379.2	375.2	371.3	367.3	363.3	360.8
37.5°	370.9	368.3	365.8	363.2	360.6	357.2	353.2	349.0	345.0	340.9	337.8
40°	357.0	354.3	351.6	349.0	346.3	342.9	338.6	334.4	330.1	325.9	322.5
42.5°	342.2	339.6	336.8	334.2	331.4	327.9	323.5	319.1	314.7	310.3	307.1
45°	319.9	317.4	314.8	312.2	309.7	305.9	301.1	296.3	291.4	286.5	282.9
47.5°	296.8	294.0	291.4	288.6	285.9	282.1	277.2	272.3	267.4	262.5	258.9
50°	282.1	279.2	276.3	273.4	270.4	266.5	261.4	256.4	251.3	246.3	242.6
52.5°	266.2	263.2	260.2	257.3	254.3	250.4	245.6	240.8	236.1	231.4	227.4
55°	242.7	239.9	237.0	234.3	231.4	227.6	222.6	217.6	212.7	207.7	203.7
57.5°	219.0	216.0	212.9	209.9	206.9	203.0	198.2	193.5	188.7	183.9	180.0
60°	203.7	200.6	197.5	194.4	191.3	187.4	182.6	177.9	173.1	168.3	164.5
62.5°	187.5	184.5	181.6	178.7	175.6	171.8	166.9	162.1	157.2	152.4	148.8
65°	164.4	161.4	158.3	155.3	152.3	148.4	143.8	139.1	134.4	129.8	126.2
67.5°	141.4	138.4	135.3	132.3	129.3	125.5	121.1	116.6	112.1	107.6	104.4
70°	125.7	122.8	119.8	116.8	113.7	110.0	105.6	101.2	96.8	92.3	89.5
72.5°	110.5	107.5	104.6	101.7	98.8	95.1	91.0	86.9	82.7	78.6	76.1
75°	87.6	84.9	82.2	79.6	77.0	73.8	70.0	66.3	62.6	58.9	56.9
77.5°	64.7	62.7	60.5	58.4	56.3	53.7	50.8	47.8	44.9	41.8	40.5
80°	51.7	49.6	47.5	45.4	43.2	41.0	38.5	36.0	33.5	31.0	30.2
82.5°	39.0	37.1	35.2	33.2	31.3	29.5	27.9	26.2	24.5	22.7	22.4
85°	21.9	20.3	18.7	17.1	15.5	14.5	14.0	13.6	13.2	12.7	12.7
87.5°	7.6	7.4	7.3	7.2	7.1	7.2	7.5	7.7	8.1	8.4	8.6
90°	1.1	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1
92.5°	17.1	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1
95°	63.5	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1
97.5°	132.7	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9
100°	186.1	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0
102.5°	240.6	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5
105°	327.8	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5
110°	477.2	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6



TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	532.4	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5
115°	615.4	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0
117.5°	701.2	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0
120°	754.7	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5
122.5°	801.9	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3
125°	875.1	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9
127.5°	944.9	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3
130°	987.7	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7
132.5°	1030.5	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4
135°	1091.4	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4
137.5°	1147.4	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2
140°	1183.9	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5
142.5°	1216.9	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9
145°	1265.2	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7
147.5°	1307.6	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8
150°	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9
152.5°	1360.2	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1
155°	1393.4	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7
157.5°	1419.1	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1
160°	1436.9	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4
162.5°	1451.2	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0
165°	1470.4	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3
167.5°	1484.6	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7
170°	1492.7	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0
172.5°	1498.1	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0
175°	1503.8	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2
177.5°	1506.5	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	525.0	525.8	526.5	526.8	526.8	526.7	526.6	526.5
5°	521.9	522.7	523.6	524.0	523.8	523.6	523.4	523.2
7.5°	515.3	516.0	516.6	516.8	516.6	516.4	516.3	516.0
10°	509.9	510.1	510.4	510.4	510.1	509.9	509.6	509.4
12.5°	502.0	502.3	502.5	502.4	502.0	501.5	501.2	500.8
15°	489.2	489.1	489.0	488.6	487.8	487.1	486.3	485.4
17.5°	473.3	472.9	472.4	471.8	471.2	470.5	469.8	469.2
20°	461.5	461.1	460.6	460.0	459.2	458.4	457.6	456.8
22.5°	449.8	448.9	448.1	447.3	446.7	446.0	445.4	444.7
25°	430.7	429.5	428.3	427.3	426.3	425.3	424.4	423.4
27.5°	409.9	408.3	406.7	405.4	404.5	403.6	402.6	401.7
30°	395.0	393.0	391.0	389.6	388.7	388.0	387.2	386.4
32.5°	380.6	378.4	376.1	374.5	373.5	372.5	371.4	370.5
35°	358.2	355.6	353.0	351.1	349.9	348.7	347.4	346.2
37.5°	334.7	331.7	328.6	326.4	325.2	324.0	322.8	321.6
40°	319.2	315.8	312.5	310.2	309.2	308.2	307.0	306.0
42.5°	303.8	300.7	297.4	295.1	293.5	291.9	290.3	288.8
45°	279.4	275.9	272.3	269.9	268.6	267.3	266.0	264.6
47.5°	255.3	251.6	248.0	245.4	243.9	242.5	241.0	239.5
50°	238.8	235.1	231.4	228.9	227.6	226.3	225.0	223.6
52.5°	223.3	219.4	215.3	212.7	211.4	210.1	208.7	207.4
55°	199.8	195.8	191.8	189.1	187.7	186.2	184.9	183.5
57.5°	176.2	172.3	168.3	165.7	164.5	163.2	162.0	160.7
60°	160.6	156.6	152.7	150.2	148.8	147.5	146.2	144.8
62.5°	145.2	141.5	137.9	135.5	134.1	132.9	131.6	130.2
65°	122.6	119.1	115.5	113.1	111.8	110.5	109.2	107.8
67.5°	101.1	97.9	94.6	92.5	91.4	90.4	89.3	88.3
70°	86.9	84.1	81.4	79.5	78.4	77.3	76.3	75.2
72.5°	73.5	71.0	68.5	66.9	66.2	65.5	64.7	64.1
75°	55.0	53.0	51.1	49.9	49.2	48.6	48.0	47.4
77.5°	39.2	37.8	36.4	35.5	35.0	34.6	34.1	33.7
80°	29.4	28.7	27.9	27.4	27.2	27.0	26.9	26.7
82.5°	22.0	21.6	21.3	21.0	20.9	20.8	20.8	20.6
85°	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0
87.5°	8.9	9.1	9.3	9.5	9.6	9.6	9.7	9.8
90°	20.3	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	20.3	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	20.3	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	40.9	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	120.1	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	233.5	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.6	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.9	477.2	476.4	476.1	476.4	476.6	476.9	477.2





TEST NUMBER: P333654-935

CATALOG NUMBER: S125RDIW-S375D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	534.5	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	620.1	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	702.7	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	756.0	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.8	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	880.9	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.7	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.9	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.2	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.8	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.3	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.0	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.0	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.0	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.2	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.4	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1358.6	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1390.5	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1416.9	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1433.4	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1448.4	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1467.7	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1482.5	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1490.0	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1495.8	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1502.2	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1504.9	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)