

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333678-935

Luminaire Tested: **S125RDIW-S610D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333678-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1560U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7419.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30	24
2	85	78	72	67	75	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5607	5543	5577
10°	5564	5491	5491
15°	5498	5380	5336
20°	5413	5225	5161
25°	5315	5072	4960
30°	5190	4894	4737
35°	5065	4709	4487
40°	4947	4517	4242
45°	4804	4302	3974
50°	4660	4068	3693
55°	4494	3845	3396
60°	4326	3574	3077
65°	4129	3260	2709
70°	3903	2866	2334
75°	3593	2415	1941
80°	3165	1901	1629
85°	2668	1549	1452



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.1
10°-20°	227.6	3.1
20°-30°	330.1	4.4
30°-40°	376.2	5.1
40°-50°	366.7	4.9
50°-60°	308.6	4.2
60°-70°	216.4	2.9
70°-80°	111.2	1.5
80°-90°	31.7	0.4
90°-100°	63.5	0.9
100°-110°	391.6	5.3
110°-120°	710.2	9.6
120°-130°	911.5	12.3
130°-140°	980.4	13.2
140°-150°	920.2	12.4
150°-160°	744.4	10.0
160°-170°	481.4	6.5
170°-180°	166.0	2.2
0°-30°	639.1	8.6
0°-40°	1015.3	13.7
0°-60°	1690.5	22.8
0°-90°	2049.8	27.6
90°-120°	1165.3	15.7
90°-150°	3977.4	53.6
90°-180°	5369.0	72.4
0°-180°	7419.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	861	860	82
15°	822	818	805	804	798	232
25°	746	735	712	703	696	343
35°	642	626	597	579	569	402
45°	526	506	471	446	435	406
55°	399	377	342	313	302	357
65°	270	247	213	188	177	268
75°	144	124	97	83	78	152
85°	36	25	21	20	20	40
90°	1	12	21	27	31	5
95°	74	67	21	27	27	94
105°	381	386	386	386	385	404
115°	716	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1269	1276	1274	1271	1264	978
145°	1471	1474	1474	1474	1467	920
155°	1620	1613	1615	1618	1608	746
165°	1710	1702	1703	1710	1700	483
175°	1748	1741	1742	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	867.7	867.4	867.0	866.7	866.3	865.6	864.4	863.2	862.0	860.9	862.0
5°	864.8	864.3	863.7	863.1	862.5	861.4	859.8	858.2	856.6	855.0	856.4
7.5°	856.4	855.7	855.2	854.6	854.1	852.9	850.9	849.0	847.1	845.2	846.2
10°	848.4	848.0	847.6	847.1	846.7	845.5	843.4	841.5	839.4	837.3	837.8
12.5°	839.6	839.0	838.4	837.9	837.3	835.7	833.0	830.3	827.5	824.8	825.1
15°	822.3	821.4	820.5	819.7	818.8	816.8	813.8	810.7	807.7	804.6	804.5
17.5°	802.8	801.5	800.1	798.8	797.5	794.9	791.0	787.2	783.3	779.5	778.8
20°	787.6	786.2	784.7	783.3	781.8	778.8	774.1	769.5	764.8	760.2	759.4
22.5°	770.9	769.4	768.0	766.5	765.1	761.9	757.0	752.2	747.3	742.4	741.0
25°	745.8	743.6	741.4	739.3	737.0	733.2	727.9	722.5	717.1	711.7	709.9
27.5°	717.0	714.4	711.7	709.0	706.4	702.2	696.5	690.7	684.9	679.2	676.5
30°	696.0	693.3	690.5	687.8	685.0	680.5	674.4	668.4	662.3	656.2	652.8
32.5°	675.6	672.4	669.2	666.0	662.7	658.0	651.8	645.6	639.3	633.1	629.4
35°	642.4	638.9	635.4	632.0	628.4	623.5	616.9	610.4	603.8	597.3	593.1
37.5°	609.8	605.5	601.3	597.1	592.9	587.4	580.6	573.9	567.1	560.3	555.3
40°	586.8	582.5	578.1	573.7	569.4	563.7	556.7	549.7	542.8	535.8	530.3
42.5°	562.7	558.3	553.8	549.3	544.8	539.0	531.8	524.5	517.4	510.1	504.8
45°	526.0	521.8	517.5	513.3	509.1	503.0	495.0	487.0	479.0	471.0	465.2
47.5°	487.9	483.5	479.0	474.6	470.1	463.8	455.8	447.7	439.7	431.6	425.7
50°	463.8	459.0	454.2	449.4	444.6	438.1	429.8	421.5	413.2	404.9	398.8
52.5°	437.6	432.7	427.8	422.9	418.0	411.6	403.8	396.0	388.1	380.3	373.8
55°	399.1	394.4	389.8	385.1	380.5	374.0	365.9	357.7	349.7	341.5	334.9
57.5°	360.1	355.1	350.1	345.2	340.2	333.7	325.9	318.1	310.2	302.4	295.9
60°	334.9	329.8	324.8	319.7	314.6	308.2	300.2	292.4	284.6	276.7	270.4
62.5°	308.2	303.4	298.5	293.7	288.9	282.4	274.5	266.5	258.6	250.6	244.6
65°	270.2	265.3	260.3	255.4	250.4	244.1	236.3	228.7	220.9	213.3	207.4
67.5°	232.4	227.4	222.5	217.6	212.6	206.5	199.1	191.7	184.3	176.8	171.6
70°	206.7	201.8	196.8	191.9	186.9	180.8	173.6	166.3	159.0	151.8	147.2
72.5°	181.6	176.8	171.9	167.1	162.3	156.4	149.6	142.8	136.0	129.2	125.1
75°	144.0	139.6	135.2	130.9	126.5	121.2	115.1	109.0	102.9	96.8	93.6
77.5°	106.5	103.0	99.5	96.0	92.6	88.3	83.4	78.6	73.7	68.8	66.6
80°	85.1	81.5	78.1	74.6	71.1	67.3	63.2	59.2	55.1	51.1	49.7
82.5°	64.1	61.0	57.9	54.7	51.6	48.6	45.8	43.0	40.2	37.5	36.9
85°	36.0	33.3	30.7	28.2	25.5	23.8	23.1	22.4	21.7	20.9	20.8
87.5°	12.3	12.0	11.6	11.3	10.8	10.8	11.1	11.5	11.7	12.0	12.3
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2
92.5°	20.0	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2
95°	73.9	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2
97.5°	154.2	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6
100°	216.5	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6
102.5°	279.7	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7
105°	381.1	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0
110°	554.7	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	619.1	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6
115°	715.5	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0
117.5°	815.3	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4
120°	877.4	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5
122.5°	932.5	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6
125°	1017.4	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4
127.5°	1098.5	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6
130°	1148.3	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3
132.5°	1198.1	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6
135°	1268.9	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5
137.5°	1333.9	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5
140°	1376.5	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4
142.5°	1414.8	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3
145°	1471.1	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9
147.5°	1520.4	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7
150°	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0
152.5°	1581.5	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0
155°	1620.1	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8
157.5°	1649.9	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5
160°	1670.7	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3
162.5°	1687.3	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4
165°	1709.6	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8
167.5°	1726.1	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5
170°	1735.5	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0
172.5°	1741.7	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1
175°	1748.4	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3
177.5°	1751.5	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	863.2	864.4	865.6	866.1	866.0	865.8	865.7	865.6
5°	857.9	859.4	860.8	861.4	861.1	860.8	860.6	860.2
7.5°	847.2	848.3	849.3	849.6	849.3	848.9	848.7	848.3
10°	838.2	838.6	839.1	839.1	838.6	838.2	837.8	837.3
12.5°	825.4	825.8	826.0	825.9	825.2	824.6	823.9	823.2
15°	804.3	804.2	804.1	803.3	802.0	800.7	799.4	798.1
17.5°	778.1	777.3	776.6	775.7	774.6	773.5	772.5	771.4
20°	758.7	757.9	757.2	756.2	754.9	753.6	752.3	751.0
22.5°	739.5	738.0	736.7	735.4	734.3	733.2	732.2	731.1
25°	708.0	706.1	704.2	702.4	700.9	699.2	697.7	696.0
27.5°	673.9	671.2	668.6	666.5	665.0	663.4	661.9	660.3
30°	649.5	646.1	642.7	640.4	639.1	637.8	636.5	635.2
32.5°	625.7	622.1	618.4	615.7	614.0	612.3	610.7	609.1
35°	588.8	584.6	580.4	577.3	575.2	573.2	571.2	569.1
37.5°	550.3	545.2	540.1	536.6	534.6	532.7	530.7	528.7
40°	524.7	519.2	513.7	510.1	508.3	506.5	504.8	503.1
42.5°	499.6	494.2	489.0	485.0	482.5	479.9	477.3	474.8
45°	459.3	453.6	447.7	443.8	441.6	439.4	437.2	435.1
47.5°	419.7	413.6	407.7	403.5	401.1	398.6	396.2	393.8
50°	392.7	386.6	380.5	376.3	374.2	372.0	369.8	367.6
52.5°	367.2	360.6	354.0	349.7	347.5	345.3	343.1	341.0
55°	328.4	321.8	315.3	310.9	308.6	306.3	303.9	301.6
57.5°	289.6	283.2	276.8	272.5	270.4	268.4	266.4	264.3
60°	263.9	257.5	251.2	246.8	244.7	242.5	240.3	238.2
62.5°	238.7	232.7	226.8	222.7	220.6	218.4	216.2	214.0
65°	201.6	195.8	190.0	186.0	183.8	181.7	179.4	177.3
67.5°	166.3	160.9	155.6	152.1	150.3	148.6	146.8	145.1
70°	142.8	138.3	133.7	130.6	128.9	127.2	125.4	123.6
72.5°	121.0	116.8	112.6	109.9	108.8	107.6	106.5	105.3
75°	90.4	87.2	84.0	81.9	80.9	79.9	78.9	77.8
77.5°	64.3	62.1	59.8	58.4	57.6	56.8	56.1	55.4
80°	48.4	47.1	45.8	45.0	44.7	44.4	44.1	43.8
82.5°	36.2	35.6	35.0	34.6	34.4	34.3	34.1	33.9
85°	20.7	20.5	20.3	20.2	20.1	19.9	19.8	19.6
87.5°	12.6	12.8	13.2	13.3	13.3	13.4	13.5	13.5
90°	23.6	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	23.6	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	23.6	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	139.7	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	271.5	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	555.6	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333678-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	621.5	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	720.9	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	816.9	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.9	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	938.0	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1024.2	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1103.0	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1154.4	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.5	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.9	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.6	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1378.9	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.4	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.3	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.1	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1552.6	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1579.6	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1616.7	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1647.4	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1666.5	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1684.0	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1706.5	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1723.5	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1732.3	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1739.1	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1746.5	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1749.6	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)