

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333712-940

Luminaire Tested: **S125RDIW-S1090D1340U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333712-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1340U940-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8584.5 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	71	81	75	70	65	62	59	56	51	49	46	41	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.6	1.6
10°-20°	412.0	4.8
20°-30°	653.3	7.6
30°-40°	787.8	9.2
40°-50°	703.5	8.2
50°-60°	539.5	6.3
60°-70°	350.6	4.1
70°-80°	170.5	2.0
80°-90°	43.9	0.5
90°-100°	56.6	0.7
100°-110°	348.8	4.1
110°-120°	632.6	7.4
120°-130°	811.9	9.5
130°-140°	873.3	10.2
140°-150°	819.7	9.5
150°-160°	663.1	7.7
160°-170°	428.8	5.0
170°-180°	147.9	1.7
0°-30°	1205.9	14.0
0°-40°	1993.7	23.2
0°-60°	3236.7	37.7
0°-90°	3801.7	44.3
90°-120°	1038.1	12.1
90°-150°	3542.9	41.3
90°-180°	4783.0	55.7
0°-180°	8584.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	33
90°	28	1	28	1	28	13
95°	24	66	24	66	24	20
105°	343	340	343	340	343	310
115°	633	637	633	637	633	628
125°	906	906	906	906	906	806
135°	1126	1130	1126	1130	1126	869
145°	1307	1310	1307	1310	1307	816
155°	1433	1443	1433	1443	1433	660
165°	1515	1523	1515	1523	1515	427
175°	1550	1558	1550	1558	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	16.1	15.5	14.9	14.7	15.1	15.8	15.1	14.4	14.1	13.8	13.9
90°	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0	19.8	18.5	16.7
92.5°	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0	19.8	18.5	16.9
95°	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0	19.8	18.5	28.2
97.5°	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4	49.6	56.8	76.1
100°	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4	162.6	200.9	199.8
102.5°	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8	249.1	256.3	255.7
105°	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6	435.5	435.5	435.0
110°	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9	495.7	496.4	496.0



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6	554.6	555.5	555.3
115°	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2	643.2	644.3	644.0
117.5°	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7	729.1	730.4	729.4
120°	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9	783.5	783.9	783.2
122.5°	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5	836.1	836.6	836.2
125°	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3	913.4	914.4	914.4
127.5°	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6	983.1	983.6	983.8
130°	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3	1029.1	1029.8	1029.6
132.5°	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1	1071.3	1071.4	1072.0
135°	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9	1134.4	1134.9	1135.4
137.5°	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4	1192.3	1192.2	1192.7
140°	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3	1227.8	1227.3	1227.5
142.5°	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5	1263.4	1263.3	1262.9
145°	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2	1313.0	1312.7	1312.7
147.5°	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8	1355.5	1355.2	1354.9
150°	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0	1382.5	1382.0	1381.4
152.5°	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0	1406.5	1406.0	1405.5
155°	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1	1439.3	1438.6	1438.1
157.5°	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5	1466.6	1465.8	1465.8
160°	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5	1483.5	1482.5	1482.2
162.5°	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0	1498.6	1497.2	1496.9
165°	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1	1518.6	1517.1	1516.8
167.5°	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3	1533.5	1531.6	1531.3
170°	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1	1541.1	1539.0	1538.7
172.5°	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2	1547.3	1545.4	1545.0
175°	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8	1553.7	1551.7	1551.5
177.5°	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5	1557.1	1555.6	1555.4
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	14.1	13.7	13.8	13.5	12.6	14.5	15.6	15.6	15.1	14.5	14.0
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7	16.3	14.9	13.5
95°	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8	65.0	64.3	63.5
97.5°	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4	138.8	140.2	141.5
100°	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8	193.6	194.3	195.1
102.5°	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1	250.1	251.1	252.1
105°	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5	340.5	341.5	342.5
107.5°	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2	433.2	433.2	433.2
110°	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2





TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4	552.1	552.7	553.2
115°	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3	638.6	639.9	641.1
117.5°	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2	726.1	726.1	726.0
120°	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6	781.4	781.1	780.9
122.5°	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5	831.5	832.5	833.5
125°	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3	908.1	909.9	911.7
127.5°	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6	979.9	981.1	982.4
130°	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9	1024.2	1025.5	1026.8
132.5°	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3	1068.7	1070.2	1071.7
135°	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3	1131.8	1133.4	1134.9
137.5°	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3	1189.5	1190.9	1192.2
140°	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1	1226.6	1227.2	1227.6
142.5°	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3	1260.6	1260.9	1261.2
145°	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4	1310.9	1311.4	1312.0
147.5°	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2	1354.2	1354.1	1354.0
150°	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1381.4	1381.0	1380.5
152.5°	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7	1407.7	1406.5	1405.4
155°	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1	1441.6	1440.1	1438.6
157.5°	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7	1468.8	1467.8	1467.0
160°	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2	1486.7	1485.1	1483.5
162.5°	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0	1501.5	1499.9	1498.3
165°	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9	1521.3	1519.7	1518.2
167.5°	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6	1536.1	1534.5	1532.9
170°	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0	1544.2	1542.3	1540.5
172.5°	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5	1549.7	1547.9	1546.0
175°	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5	1555.9	1554.4	1552.8
177.5°	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2	1559.0	1557.8	1556.6
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.9	14.3	14.2	15.5	14.4	15.2	15.5	15.2	15.5	15.8	15.5
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.3	23.6	24.6
92.5°	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0	22.3	23.6	24.4
95°	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0	22.3	23.6	24.3
97.5°	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4	35.1	27.8	24.3
100°	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4	86.2	48.0	28.4
102.5°	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8	234.6	227.4	215.0
105°	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	343.9
107.5°	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6	435.7	435.7	435.3
110°	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9	494.2	493.4	493.1



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6	552.7	551.7	551.0
115°	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2	641.1	640.2	638.8
117.5°	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7	726.4	725.1	724.0
120°	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9	782.4	781.9	781.0
122.5°	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5	835.0	834.6	833.5
125°	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3	911.3	910.3	909.4
127.5°	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6	982.0	981.4	980.2
130°	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3	1027.5	1026.8	1025.7
132.5°	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1	1070.9	1070.8	1070.1
135°	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9	1133.4	1132.8	1131.8
137.5°	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4	1192.5	1192.6	1191.9
140°	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3	1228.8	1229.3	1228.8
142.5°	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5	1263.6	1263.7	1263.0
145°	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2	1313.5	1313.8	1313.1
147.5°	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8	1356.1	1356.5	1355.7
150°	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0	1383.5	1384.0	1383.2
152.5°	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0	1407.6	1408.0	1407.4
155°	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1	1440.8	1441.6	1441.0
157.5°	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5	1468.3	1469.1	1468.5
160°	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5	1485.5	1486.6	1486.0
162.5°	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0	1501.6	1503.0	1502.5
165°	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1	1521.7	1523.2	1523.0
167.5°	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3	1537.1	1539.0	1538.7
170°	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1	1545.2	1547.2	1547.1
172.5°	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2	1551.0	1552.8	1552.6
175°	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8	1557.8	1559.9	1559.8
177.5°	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5	1560.0	1561.4	1561.3
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	16.1	15.8	16.0	16.1	16.0	15.8	16.1	15.5	15.8	15.5	15.2
90°	25.4	26.1	26.9	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0
92.5°	24.8	25.1	25.5	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0
95°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0
97.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4
100°	27.3	26.3	25.2	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4
102.5°	197.6	180.1	162.6	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8
105°	343.7	343.4	343.1	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0
107.5°	434.5	433.8	433.0	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6
110°	493.4	493.7	493.9	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	550.6	550.3	549.9	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6
115°	637.3	635.8	634.2	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2
117.5°	723.4	722.7	722.0	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7
120°	779.7	778.4	777.1	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9
122.5°	832.1	830.5	829.0	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5
125°	908.7	907.9	907.0	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3
127.5°	978.3	976.4	974.5	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6
130°	1024.5	1023.1	1021.9	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3
132.5°	1068.8	1067.6	1066.2	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1
135°	1130.3	1128.7	1127.2	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9
137.5°	1190.6	1189.3	1187.9	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4
140°	1227.3	1225.7	1224.2	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3
142.5°	1261.4	1259.9	1258.4	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5
145°	1311.5	1310.0	1308.5	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2
147.5°	1353.8	1351.9	1350.1	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8
150°	1381.2	1379.1	1377.1	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0
152.5°	1405.5	1403.7	1401.9	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0
155°	1439.0	1436.9	1434.9	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1
157.5°	1466.4	1464.4	1462.3	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5
160°	1484.0	1481.9	1479.9	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5
162.5°	1500.3	1498.0	1495.8	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0
165°	1520.9	1518.9	1516.8	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1
167.5°	1536.4	1534.2	1531.9	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3
170°	1544.8	1542.5	1540.2	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1
172.5°	1550.3	1548.0	1545.7	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2
175°	1557.5	1555.1	1552.8	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8
177.5°	1559.6	1558.0	1556.3	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	15.5	15.2	14.4	15.5	14.2	14.3	13.9	14.0	14.5	15.1	15.6
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	19.8	18.5	16.9	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7
95°	19.8	18.5	28.2	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8
97.5°	49.6	56.8	76.1	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4
100°	162.6	200.9	199.8	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8
102.5°	249.1	256.3	255.7	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1
105°	344.0	344.0	344.0	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5
107.5°	435.5	435.5	435.0	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2
110°	495.7	496.4	496.0	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	554.6	555.5	555.3	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4
115°	643.2	644.3	644.0	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3
117.5°	729.1	730.4	729.4	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2
120°	783.5	783.9	783.2	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6
122.5°	836.1	836.6	836.2	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5
125°	913.4	914.4	914.4	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3
127.5°	983.1	983.6	983.8	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6
130°	1029.1	1029.8	1029.6	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9
132.5°	1071.3	1071.4	1072.0	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3
135°	1134.4	1134.9	1135.4	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3
137.5°	1192.3	1192.2	1192.7	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3
140°	1227.8	1227.3	1227.5	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1
142.5°	1263.4	1263.3	1262.9	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3
145°	1313.0	1312.7	1312.7	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4
147.5°	1355.5	1355.2	1354.9	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2
150°	1382.5	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0
152.5°	1406.5	1406.0	1405.5	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7
155°	1439.3	1438.6	1438.1	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1
157.5°	1466.6	1465.8	1465.8	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7
160°	1483.5	1482.5	1482.2	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2
162.5°	1498.6	1497.2	1496.9	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0
165°	1518.6	1517.1	1516.8	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9
167.5°	1533.5	1531.6	1531.3	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6
170°	1541.1	1539.0	1538.7	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0
172.5°	1547.3	1545.4	1545.0	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5
175°	1553.7	1551.7	1551.5	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5
177.5°	1557.1	1555.6	1555.4	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.6	14.5	12.6	13.5	13.8	13.7	14.1	13.9	13.8	14.1	14.4
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0
95°	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0
97.5°	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4
100°	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4
102.5°	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8
105°	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6
110°	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9





TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6
115°	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2
117.5°	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7
120°	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9
122.5°	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5
125°	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3
127.5°	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6
130°	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3
132.5°	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1
135°	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9
137.5°	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4
140°	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3
142.5°	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5
145°	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2
147.5°	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8
150°	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0
152.5°	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0
155°	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1
157.5°	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5
160°	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5
162.5°	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0
165°	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1
167.5°	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3
170°	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1
172.5°	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2
175°	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8
177.5°	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	15.1	15.8	15.1	14.7	14.9	15.5	16.1
90°	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333712-940

CATALOG NUMBER: S125RDIW-S1090D1340U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)