

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333679-935

Luminaire Tested: **S125RDIW-S610D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333679-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1560U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6706.0 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	19	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	12	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5594	5594	5594
5°	5607	5543	5577
10°	5564	5491	5491
15°	5498	5380	5336
20°	5413	5225	5161
25°	5315	5072	4960
30°	5190	4894	4737
35°	5065	4709	4487
40°	4947	4517	4242
45°	4804	4302	3974
50°	4660	4068	3693
55°	4494	3845	3396
60°	4326	3574	3077
65°	4129	3260	2709
70°	3903	2866	2334
75°	3593	2415	1941
80°	3165	1901	1629
85°	2668	1549	1452



TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.4	1.2
10°-20°	227.6	3.4
20°-30°	330.1	4.9
30°-40°	376.2	5.6
40°-50°	366.7	5.5
50°-60°	308.6	4.6
60°-70°	216.4	3.2
70°-80°	111.2	1.7
80°-90°	31.7	0.5
90°-100°	111.8	1.7
100°-110°	330.0	4.9
110°-120°	559.0	8.3
120°-130°	735.7	11.0
130°-140°	824.3	12.3
140°-150°	807.9	12.0
150°-160°	678.6	10.1
160°-170°	451.1	6.7
170°-180°	157.9	2.4
0°-30°	639.1	9.5
0°-40°	1015.3	15.1
0°-60°	1690.5	25.2
0°-90°	2049.8	30.6
90°-120°	1000.8	14.9
90°-150°	3368.6	50.2
90°-180°	4656.0	69.4
0°-180°	6706.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	861	860	82
15°	822	818	805	804	798	232
25°	746	735	712	703	696	343
35°	642	626	597	579	569	402
45°	526	506	471	446	435	406
55°	399	377	342	313	302	357
65°	270	247	213	188	177	268
75°	144	124	97	83	78	152
85°	36	25	21	20	20	40
90°	1	12	21	27	31	6
95°	84	88	100	109	112	90
105°	296	303	310	318	322	316
115°	560	565	568	566	565	553
125°	817	824	826	823	822	731
135°	1062	1070	1071	1071	1066	818
145°	1287	1292	1296	1296	1292	804
155°	1473	1473	1474	1478	1473	678
165°	1601	1599	1600	1604	1597	451
175°	1665	1660	1660	1666	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	867.7	867.4	867.0	866.7	866.3	865.6	864.4	863.2	862.0	860.9	862.0
5°	864.8	864.3	863.7	863.1	862.5	861.4	859.8	858.2	856.6	855.0	856.4
7.5°	856.4	855.7	855.2	854.6	854.1	852.9	850.9	849.0	847.1	845.2	846.2
10°	848.4	848.0	847.6	847.1	846.7	845.5	843.4	841.5	839.4	837.3	837.8
12.5°	839.6	839.0	838.4	837.9	837.3	835.7	833.0	830.3	827.5	824.8	825.1
15°	822.3	821.4	820.5	819.7	818.8	816.8	813.8	810.7	807.7	804.6	804.5
17.5°	802.8	801.5	800.1	798.8	797.5	794.9	791.0	787.2	783.3	779.5	778.8
20°	787.6	786.2	784.7	783.3	781.8	778.8	774.1	769.5	764.8	760.2	759.4
22.5°	770.9	769.4	768.0	766.5	765.1	761.9	757.0	752.2	747.3	742.4	741.0
25°	745.8	743.6	741.4	739.3	737.0	733.2	727.9	722.5	717.1	711.7	709.9
27.5°	717.0	714.4	711.7	709.0	706.4	702.2	696.5	690.7	684.9	679.2	676.5
30°	696.0	693.3	690.5	687.8	685.0	680.5	674.4	668.4	662.3	656.2	652.8
32.5°	675.6	672.4	669.2	666.0	662.7	658.0	651.8	645.6	639.3	633.1	629.4
35°	642.4	638.9	635.4	632.0	628.4	623.5	616.9	610.4	603.8	597.3	593.1
37.5°	609.8	605.5	601.3	597.1	592.9	587.4	580.6	573.9	567.1	560.3	555.3
40°	586.8	582.5	578.1	573.7	569.4	563.7	556.7	549.7	542.8	535.8	530.3
42.5°	562.7	558.3	553.8	549.3	544.8	539.0	531.8	524.5	517.4	510.1	504.8
45°	526.0	521.8	517.5	513.3	509.1	503.0	495.0	487.0	479.0	471.0	465.2
47.5°	487.9	483.5	479.0	474.6	470.1	463.8	455.8	447.7	439.7	431.6	425.7
50°	463.8	459.0	454.2	449.4	444.6	438.1	429.8	421.5	413.2	404.9	398.8
52.5°	437.6	432.7	427.8	422.9	418.0	411.6	403.8	396.0	388.1	380.3	373.8
55°	399.1	394.4	389.8	385.1	380.5	374.0	365.9	357.7	349.7	341.5	334.9
57.5°	360.1	355.1	350.1	345.2	340.2	333.7	325.9	318.1	310.2	302.4	295.9
60°	334.9	329.8	324.8	319.7	314.6	308.2	300.2	292.4	284.6	276.7	270.4
62.5°	308.2	303.4	298.5	293.7	288.9	282.4	274.5	266.5	258.6	250.6	244.6
65°	270.2	265.3	260.3	255.4	250.4	244.1	236.3	228.7	220.9	213.3	207.4
67.5°	232.4	227.4	222.5	217.6	212.6	206.5	199.1	191.7	184.3	176.8	171.6
70°	206.7	201.8	196.8	191.9	186.9	180.8	173.6	166.3	159.0	151.8	147.2
72.5°	181.6	176.8	171.9	167.1	162.3	156.4	149.6	142.8	136.0	129.2	125.1
75°	144.0	139.6	135.2	130.9	126.5	121.2	115.1	109.0	102.9	96.8	93.6
77.5°	106.5	103.0	99.5	96.0	92.6	88.3	83.4	78.6	73.7	68.8	66.6
80°	85.1	81.5	78.1	74.6	71.1	67.3	63.2	59.2	55.1	51.1	49.7
82.5°	64.1	61.0	57.9	54.7	51.6	48.6	45.8	43.0	40.2	37.5	36.9
85°	36.0	33.3	30.7	28.2	25.5	23.8	23.1	22.4	21.7	20.9	20.8
87.5°	12.3	12.0	11.6	11.3	10.8	10.8	11.1	11.5	11.7	12.0	12.3
90°	1.3	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2
92.5°	31.4	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7
95°	84.4	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0
97.5°	140.3	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1
100°	181.8	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3
102.5°	226.4	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1
105°	296.1	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1
107.5°	372.9	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2
110°	425.9	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1



TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.9	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6
115°	559.6	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1
117.5°	639.6	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5
120°	689.5	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3
122.5°	743.6	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0
125°	816.7	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3
127.5°	894.7	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3
130°	941.4	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2
132.5°	988.2	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0
135°	1062.2	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3
137.5°	1131.8	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5
140°	1176.5	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4
142.5°	1221.2	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8
145°	1286.9	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9
147.5°	1347.6	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3
150°	1388.1	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1
152.5°	1421.3	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0
155°	1472.6	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0
157.5°	1518.2	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9
160°	1545.2	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8
162.5°	1569.2	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0
165°	1601.1	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9
167.5°	1628.1	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6
170°	1642.6	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2
172.5°	1653.0	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6
175°	1664.7	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2
177.5°	1670.7	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	863.2	864.4	865.6	866.1	866.0	865.8	865.7	865.6
5°	857.9	859.4	860.8	861.4	861.1	860.8	860.6	860.2
7.5°	847.2	848.3	849.3	849.6	849.3	848.9	848.7	848.3
10°	838.2	838.6	839.1	839.1	838.6	838.2	837.8	837.3
12.5°	825.4	825.8	826.0	825.9	825.2	824.6	823.9	823.2
15°	804.3	804.2	804.1	803.3	802.0	800.7	799.4	798.1
17.5°	778.1	777.3	776.6	775.7	774.6	773.5	772.5	771.4
20°	758.7	757.9	757.2	756.2	754.9	753.6	752.3	751.0
22.5°	739.5	738.0	736.7	735.4	734.3	733.2	732.2	731.1
25°	708.0	706.1	704.2	702.4	700.9	699.2	697.7	696.0
27.5°	673.9	671.2	668.6	666.5	665.0	663.4	661.9	660.3
30°	649.5	646.1	642.7	640.4	639.1	637.8	636.5	635.2
32.5°	625.7	622.1	618.4	615.7	614.0	612.3	610.7	609.1
35°	588.8	584.6	580.4	577.3	575.2	573.2	571.2	569.1
37.5°	550.3	545.2	540.1	536.6	534.6	532.7	530.7	528.7
40°	524.7	519.2	513.7	510.1	508.3	506.5	504.8	503.1
42.5°	499.6	494.2	489.0	485.0	482.5	479.9	477.3	474.8
45°	459.3	453.6	447.7	443.8	441.6	439.4	437.2	435.1
47.5°	419.7	413.6	407.7	403.5	401.1	398.6	396.2	393.8
50°	392.7	386.6	380.5	376.3	374.2	372.0	369.8	367.6
52.5°	367.2	360.6	354.0	349.7	347.5	345.3	343.1	341.0
55°	328.4	321.8	315.3	310.9	308.6	306.3	303.9	301.6
57.5°	289.6	283.2	276.8	272.5	270.4	268.4	266.4	264.3
60°	263.9	257.5	251.2	246.8	244.7	242.5	240.3	238.2
62.5°	238.7	232.7	226.8	222.7	220.6	218.4	216.2	214.0
65°	201.6	195.8	190.0	186.0	183.8	181.7	179.4	177.3
67.5°	166.3	160.9	155.6	152.1	150.3	148.6	146.8	145.1
70°	142.8	138.3	133.7	130.6	128.9	127.2	125.4	123.6
72.5°	121.0	116.8	112.6	109.9	108.8	107.6	106.5	105.3
75°	90.4	87.2	84.0	81.9	80.9	79.9	78.9	77.8
77.5°	64.3	62.1	59.8	58.4	57.6	56.8	56.1	55.4
80°	48.4	47.1	45.8	45.0	44.7	44.4	44.1	43.8
82.5°	36.2	35.6	35.0	34.6	34.4	34.3	34.1	33.9
85°	20.7	20.5	20.3	20.2	20.1	19.9	19.8	19.6
87.5°	12.6	12.8	13.2	13.3	13.4	13.4	13.5	13.5
90°	23.7	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	53.6	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	104.0	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	163.0	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	203.9	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	245.9	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	313.8	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	387.1	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.1	438.9	439.8	440.1	439.8	439.5	439.2	438.9





TEST NUMBER: P333679-935

CATALOG NUMBER: S125RDIW-S610D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.0	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.9	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	644.8	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.8	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.8	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	900.1	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.9	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.7	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1142.9	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.0	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.2	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.0	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1426.7	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1476.1	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1519.0	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1545.0	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1569.3	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1602.1	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1626.3	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1640.9	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1651.3	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1663.0	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1668.3	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)