

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333692-935

Luminaire Tested: **S125RDIW-S850D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333692-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1340U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7442.8 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	45	47	42	38	37	34	31	29	26	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7034	7034	7034	7034
5°	8092	7043	6220	7043
10°	9282	7007	5488	7007
15°	10026	6935	4878	6935
20°	11056	6852	4504	6852
25°	12794	6741	4180	6741
30°	13923	6624	3967	6624
35°	11744	6489	3772	6489
40°	8201	6246	3603	6246
45°	6085	5917	3438	5917
50°	4851	5574	3297	5574
55°	4118	5150	3171	5150
60°	3557	4770	2968	4770
65°	3169	4358	2555	4358
70°	2787	3994	2330	3994
75°	2410	3459	2186	3459
80°	1830	2912	1830	2912
85°	1526	2282	1719	2282



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	1.4
10°-20°	306.1	4.1
20°-30°	485.3	6.5
30°-40°	585.2	7.9
40°-50°	522.6	7.0
50°-60°	400.8	5.4
60°-70°	260.4	3.5
70°-80°	126.6	1.7
80°-90°	33.4	0.4
90°-100°	54.6	0.7
100°-110°	336.8	4.5
110°-120°	610.9	8.2
120°-130°	783.9	10.5
130°-140°	843.2	11.3
140°-150°	791.5	10.6
150°-160°	640.2	8.6
160°-170°	414.1	5.6
170°-180°	142.8	1.9
0°-30°	895.8	12.0
0°-40°	1481.0	19.9
0°-60°	2404.3	32.3
0°-90°	2824.7	38.0
90°-120°	1002.3	13.5
90°-150°	3420.9	46.0
90°-180°	4618.0	62.0
0°-180°	7442.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1089	1089	1089	1089	1089	
5°	1248	1086	959	1086	1248	125
15°	1500	1037	730	1037	1500	430
25°	1795	946	587	946	1795	824
35°	1490	823	478	823	1490	900
45°	666	648	376	648	666	532
55°	366	457	282	457	366	332
65°	207	285	167	285	207	206
75°	97	139	88	139	97	103
85°	21	31	23	31	21	24
90°	27	1	27	1	27	13
95°	23	64	23	64	23	19
105°	331	328	331	328	331	299
115°	611	615	611	615	611	606
125°	875	875	875	875	875	779
135°	1087	1091	1087	1091	1087	839
145°	1262	1265	1262	1265	1262	788
155°	1384	1393	1384	1393	1384	638
165°	1463	1470	1463	1470	1463	413
175°	1497	1504	1497	1504	1497	142
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1145.6	1144.9	1146.3	1142.4	1142.7	1136.6	1136.6	1132.0	1125.9	1121.3	1119.1
5°	1248.2	1249.1	1247.3	1240.6	1236.1	1229.4	1221.8	1208.4	1197.2	1186.5	1178.0
7.5°	1353.9	1354.5	1348.7	1346.6	1335.3	1327.1	1310.2	1291.9	1275.7	1255.2	1239.5
10°	1415.4	1415.0	1408.8	1403.8	1394.0	1381.5	1364.9	1343.4	1323.4	1301.0	1279.5
12.5°	1451.2	1450.0	1448.0	1442.1	1433.0	1421.9	1407.8	1386.7	1361.9	1337.5	1312.4
15°	1499.5	1496.3	1490.6	1482.9	1470.0	1457.0	1441.4	1422.6	1398.9	1371.1	1347.9
17.5°	1559.2	1559.3	1550.4	1539.8	1522.2	1499.3	1475.2	1444.8	1412.6	1382.2	1357.4
20°	1608.6	1607.2	1598.3	1577.7	1557.6	1529.0	1501.2	1464.1	1424.8	1385.0	1354.2
22.5°	1679.4	1675.9	1666.6	1639.6	1608.4	1571.6	1529.1	1483.8	1436.2	1391.1	1350.7
25°	1795.4	1792.8	1774.4	1743.2	1699.4	1642.5	1587.1	1525.0	1456.6	1397.1	1347.9
27.5°	1874.8	1871.9	1858.3	1832.3	1791.9	1732.2	1657.1	1574.1	1488.7	1406.9	1335.9
30°	1867.0	1873.7	1871.9	1859.8	1829.5	1775.8	1706.5	1613.1	1511.6	1415.4	1330.9
32.5°	1754.6	1760.7	1776.4	1800.1	1801.9	1780.5	1728.6	1642.4	1537.3	1428.0	1327.0
35°	1489.6	1497.7	1528.1	1576.0	1638.5	1690.8	1701.6	1655.1	1560.7	1443.1	1321.1
37.5°	1145.2	1189.2	1214.8	1265.2	1359.7	1456.0	1548.5	1582.5	1542.4	1436.9	1311.6
40°	972.8	983.5	1029.2	1086.0	1165.5	1265.7	1397.6	1492.8	1495.9	1422.6	1296.5
42.5°	832.6	846.2	877.5	922.8	991.0	1091.1	1227.3	1353.0	1411.2	1383.3	1276.9
45°	666.2	676.4	699.2	734.1	786.4	869.1	986.3	1131.5	1246.9	1292.0	1224.1
47.5°	547.3	552.8	572.7	599.2	637.9	698.2	788.8	915.0	1053.3	1150.3	1140.7
50°	482.8	489.1	504.3	524.4	557.1	608.0	680.4	785.5	928.2	1046.6	1070.3
52.5°	432.7	438.0	447.5	466.5	493.4	532.5	591.0	686.0	814.4	940.4	995.1
55°	365.7	369.3	376.9	387.6	409.1	437.2	487.8	553.5	657.2	784.2	864.6
57.5°	310.5	312.2	317.1	327.0	341.8	362.4	398.9	454.6	529.0	643.3	732.1
60°	275.4	277.2	283.4	290.2	301.8	320.6	349.1	388.1	459.6	553.9	643.8
62.5°	247.5	248.6	251.2	258.0	268.1	282.7	305.1	336.9	393.8	476.6	561.5
65°	207.4	207.9	208.8	214.1	220.4	231.2	245.9	268.2	311.2	373.8	448.8
67.5°	169.0	169.6	172.7	174.6	181.2	186.8	195.4	212.6	242.8	285.0	343.4
70°	147.6	147.1	150.2	152.5	154.7	161.4	167.2	181.1	199.8	232.0	280.8
72.5°	127.5	126.3	127.7	128.5	131.5	136.0	141.8	150.3	164.8	186.9	224.3
75°	96.6	97.0	97.0	97.9	100.1	101.9	103.8	108.2	116.2	131.0	151.1
77.5°	67.8	67.1	69.0	69.2	70.5	72.5	74.0	75.9	79.1	85.2	95.6
80°	49.2	49.2	49.6	51.0	50.5	51.4	53.6	55.4	59.5	63.0	66.6
82.5°	37.7	37.4	37.8	38.1	38.0	38.9	39.7	40.0	41.6	43.4	45.9
85°	20.6	20.6	21.0	21.0	21.4	21.4	21.9	21.9	21.9	22.4	22.8
87.5°	13.3	12.7	12.2	12.1	12.2	12.7	12.1	11.5	11.4	11.1	11.1
90°	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3	19.1	17.8	16.1
92.5°	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3	19.1	17.8	16.3
95°	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3	19.1	17.8	27.2
97.5°	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9	47.9	54.8	73.4
100°	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1	157.0	194.0	193.0
102.5°	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5	240.5	247.5	246.8
105°	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6	420.5	420.5	420.0
110°	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9	478.6	479.3	478.9



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5	535.5	536.4	536.1
115°	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1	621.0	622.1	621.8
117.5°	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7	704.0	705.2	704.3
120°	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0	756.5	756.9	756.2
122.5°	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8	807.3	807.8	807.4
125°	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9	881.9	882.9	882.9
127.5°	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7	949.3	949.8	949.9
130°	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9	993.7	994.4	994.1
132.5°	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2	1034.4	1034.5	1035.1
135°	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8	1095.4	1095.8	1096.3
137.5°	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3	1151.2	1151.2	1151.6
140°	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0	1185.5	1185.0	1185.3
142.5°	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0	1219.9	1219.8	1219.4
145°	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0	1267.7	1267.5	1267.5
147.5°	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2	1308.8	1308.5	1308.2
150°	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4	1334.9	1334.4	1333.9
152.5°	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6	1358.1	1357.5	1357.1
155°	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5	1389.7	1389.1	1388.5
157.5°	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9	1416.1	1415.3	1415.3
160°	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4	1432.4	1431.4	1431.2
162.5°	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4	1447.0	1445.6	1445.4
165°	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7	1466.3	1464.8	1464.6
167.5°	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5	1480.7	1478.9	1478.6
170°	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0	1488.0	1486.0	1485.7
172.5°	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8	1494.0	1492.2	1491.8
175°	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2	1500.2	1498.2	1498.1
177.5°	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9	1503.5	1502.0	1501.8
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1119.1	1116.6	1112.0	1107.7	1102.3	1097.7	1094.4	1090.5	1085.5	1079.4	1074.4
5°	1168.6	1158.8	1145.8	1134.7	1120.3	1109.2	1097.6	1086.4	1075.2	1060.9	1048.4
7.5°	1223.6	1203.2	1183.5	1158.6	1136.1	1115.9	1096.7	1077.1	1058.0	1037.7	1018.0
10°	1257.1	1232.6	1205.3	1174.0	1145.4	1118.1	1093.1	1068.5	1042.6	1019.8	995.1
12.5°	1288.7	1256.9	1225.7	1186.2	1151.8	1118.5	1086.7	1056.0	1028.3	998.7	972.3
15°	1317.1	1285.8	1250.9	1202.6	1154.8	1114.6	1077.0	1037.2	1002.8	969.7	940.2
17.5°	1328.1	1295.3	1254.7	1208.3	1156.1	1105.4	1057.0	1013.4	972.9	934.4	901.2
20°	1323.8	1292.0	1250.4	1206.2	1150.3	1097.6	1045.3	997.0	951.8	911.1	875.8
22.5°	1313.4	1280.6	1240.4	1193.7	1140.7	1084.7	1028.8	977.3	930.0	887.9	849.4
25°	1297.9	1253.2	1212.0	1166.4	1115.9	1060.5	1002.8	946.0	895.5	852.6	810.5
27.5°	1281.7	1225.9	1173.5	1128.3	1074.9	1025.4	969.8	911.5	858.5	814.8	771.6
30°	1267.0	1204.5	1146.8	1095.4	1044.8	997.9	945.1	888.3	833.8	788.7	744.9
32.5°	1248.8	1182.2	1118.9	1059.5	1010.8	964.2	916.5	862.2	809.1	762.5	718.0
35°	1225.9	1140.9	1072.1	1009.0	954.9	909.8	866.9	823.0	769.8	721.6	678.2
37.5°	1195.8	1099.4	1019.8	951.1	894.1	848.7	814.9	774.8	726.3	680.0	639.7
40°	1177.6	1069.4	982.2	914.3	854.4	806.5	774.8	740.8	696.5	653.2	612.9
42.5°	1153.3	1041.9	944.3	873.5	813.2	767.2	735.0	705.4	668.3	627.4	584.4
45°	1105.6	988.5	886.1	810.1	749.3	704.1	674.2	647.8	619.7	582.1	544.5
47.5°	1043.5	932.8	825.6	742.7	683.1	641.2	612.2	591.3	571.2	539.2	502.7
50°	993.9	887.0	782.4	701.9	638.4	598.7	571.4	554.8	536.5	507.4	477.0
52.5°	935.2	839.8	737.3	655.0	595.1	557.8	531.7	515.1	500.0	476.3	447.4
55°	842.7	759.1	665.2	590.6	535.6	498.0	473.0	457.4	448.4	428.3	405.5
57.5°	736.1	676.1	593.3	521.3	472.8	435.7	417.3	404.0	393.9	379.6	363.6
60°	661.7	619.7	545.4	477.0	432.3	397.0	380.5	369.3	359.9	347.8	335.3
62.5°	586.2	555.6	491.0	432.3	391.2	361.6	346.1	336.0	325.2	317.1	304.9
65°	485.1	457.8	413.1	367.0	329.1	305.3	294.2	285.2	278.5	269.6	261.1
67.5°	377.3	366.3	335.4	303.7	276.4	255.3	245.6	239.4	231.4	225.9	220.2
70°	311.2	305.8	283.9	262.9	237.4	223.1	214.1	211.5	201.6	196.3	192.3
72.5°	252.5	250.0	237.4	222.8	204.8	192.3	184.1	181.1	174.8	170.5	167.9
75°	173.0	173.9	171.7	162.3	155.6	147.6	140.3	138.6	134.1	130.5	128.3
77.5°	109.4	114.0	114.2	113.7	111.1	106.2	103.1	101.9	97.5	96.1	95.6
80°	75.1	80.0	84.5	84.0	83.2	81.8	79.6	78.3	76.0	74.6	73.8
82.5°	50.1	54.7	58.4	60.8	60.6	59.3	57.8	57.2	56.7	55.7	55.5
85°	23.7	24.6	25.9	29.1	31.3	31.8	31.3	30.8	29.5	30.0	30.4
87.5°	11.1	10.8	10.8	10.4	9.6	11.0	11.7	11.7	11.4	11.0	10.7
90°	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1	15.8	14.4	13.0
95°	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5	62.8	62.1	61.3
97.5°	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7	134.0	135.3	136.6
100°	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1	186.9	187.6	188.4
102.5°	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6	241.5	242.5	243.4
105°	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8	328.7	329.8	330.7
107.5°	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3	418.3	418.3	418.3
110°	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4	533.0	533.6	534.2
115°	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4	616.6	617.9	619.1
117.5°	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2	701.1	701.1	701.0
120°	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7	754.5	754.2	754.0
122.5°	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9	802.9	803.8	804.8
125°	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1	876.8	878.6	880.3
127.5°	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9	946.2	947.4	948.6
130°	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7	988.9	990.2	991.4
132.5°	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5	1031.9	1033.4	1034.8
135°	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4	1092.9	1094.3	1095.8
137.5°	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4	1148.6	1149.9	1151.2
140°	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9	1184.4	1184.9	1185.3
142.5°	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9	1217.2	1217.5	1217.8
145°	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2	1265.8	1266.3	1266.8
147.5°	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6	1307.5	1307.4	1307.3
150°	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1333.9	1333.4	1332.9
152.5°	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2	1359.2	1358.1	1357.0
155°	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4	1392.0	1390.5	1389.1
157.5°	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1	1418.2	1417.3	1416.4
160°	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9	1435.5	1434.0	1432.4
162.5°	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2	1449.8	1448.2	1446.7
165°	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4	1468.9	1467.4	1465.9
167.5°	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6	1483.2	1481.6	1480.1
170°	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7	1491.0	1489.2	1487.5
172.5°	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1	1496.3	1494.6	1492.8
175°	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8	1502.4	1500.9	1499.3
177.5°	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5	1505.3	1504.2	1503.0
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1070.8	1065.8	1062.2	1055.1	1050.1	1047.9	1044.0	1042.9	1046.9	1044.0	1043.6
5°	1039.0	1026.1	1015.7	1005.5	994.3	987.1	976.4	974.7	971.9	967.9	967.0
7.5°	1000.8	984.0	970.7	953.7	938.9	927.0	913.6	907.3	903.8	898.6	891.7
10°	975.1	954.9	937.0	920.1	901.7	887.0	873.6	863.3	856.6	850.3	847.7
12.5°	949.7	929.2	906.3	885.7	865.3	848.7	833.9	827.2	819.8	812.4	806.2
15°	910.2	883.0	857.9	834.2	816.8	798.9	784.6	774.8	763.6	760.4	748.4
17.5°	868.4	841.6	812.4	787.4	767.2	747.5	731.8	720.6	712.2	700.7	695.1
20°	842.3	810.5	782.0	759.1	736.8	713.5	697.4	688.0	680.0	670.6	666.2
22.5°	814.4	783.3	754.1	727.3	704.6	681.7	670.3	660.5	651.3	642.7	636.8
25°	773.4	742.2	711.3	683.5	659.9	643.3	629.9	618.7	613.8	605.4	599.1
27.5°	733.0	699.6	667.6	640.1	621.5	605.1	594.1	585.2	576.4	568.9	563.5
30°	706.8	672.9	638.0	616.0	596.4	580.7	568.7	560.2	553.5	546.7	542.8
32.5°	680.7	645.7	614.8	591.0	572.4	559.0	546.5	538.4	531.3	523.9	519.2
35°	638.9	603.1	578.1	554.8	536.5	524.0	515.5	503.9	498.0	492.7	487.8
37.5°	599.9	566.7	539.6	519.3	503.3	490.9	479.9	473.6	466.5	461.7	457.5
40°	571.4	541.0	516.3	494.9	483.3	469.4	459.2	451.1	445.7	439.5	435.0
42.5°	545.6	517.4	493.4	474.2	459.7	448.0	438.1	430.0	423.2	418.7	415.0
45°	509.2	481.0	457.8	439.9	426.5	415.3	405.0	401.1	392.1	386.8	385.0
47.5°	471.6	446.3	424.0	407.4	393.7	383.1	373.5	365.2	360.3	355.1	352.2
50°	446.2	422.1	401.1	385.0	371.5	359.9	350.9	345.6	338.9	334.0	330.4
52.5°	420.8	398.5	377.5	362.1	350.4	338.8	328.8	323.4	317.1	313.9	311.4
55°	384.5	360.8	342.9	327.7	315.6	304.9	295.5	290.2	286.1	283.0	282.1
57.5°	343.4	324.6	308.0	294.3	281.7	271.6	263.4	258.3	254.8	254.3	251.6
60°	316.5	299.5	284.3	269.6	258.8	249.4	242.3	236.5	232.9	232.5	231.6
62.5°	289.7	273.5	259.3	246.3	236.7	227.6	220.8	214.3	212.2	209.9	208.0
65°	249.9	235.1	223.5	213.3	202.9	195.4	188.6	184.6	179.7	177.0	172.1
67.5°	210.9	199.4	188.2	179.5	171.5	164.3	158.7	152.7	149.4	147.2	143.7
70°	185.1	176.2	165.0	155.6	149.3	143.5	139.1	132.3	130.1	128.3	126.5
72.5°	160.7	152.9	143.5	136.0	129.7	124.2	119.0	115.9	113.7	111.8	110.8
75°	126.5	118.9	110.9	105.5	101.1	96.6	93.8	91.6	90.7	90.3	88.5
77.5°	92.9	88.9	82.4	78.2	75.2	73.4	71.0	69.8	69.7	67.8	67.2
80°	71.1	68.9	63.5	61.7	59.5	57.7	56.3	54.1	51.8	51.0	49.6
82.5°	52.9	50.6	48.5	45.6	43.7	42.6	41.3	40.5	40.8	39.5	38.9
85°	28.2	25.9	25.1	24.6	23.7	24.6	24.1	23.7	23.2	22.8	23.2
87.5°	10.8	11.1	11.1	12.1	11.5	12.1	12.4	12.3	12.6	12.7	12.7
90°	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3	21.5	22.8	23.8
92.5°	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3	21.5	22.8	23.6
95°	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3	21.5	22.8	23.4
97.5°	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9	33.9	26.9	23.4
100°	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1	83.3	46.3	27.4
102.5°	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5	226.5	219.6	207.6
105°	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.1
107.5°	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6	420.7	420.7	420.3
110°	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9	477.2	476.4	476.1



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5	533.6	532.7	532.0
115°	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1	619.1	618.1	616.8
117.5°	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7	701.4	700.1	699.0
120°	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0	755.4	754.9	754.1
122.5°	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8	806.2	805.8	804.8
125°	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9	879.9	878.9	878.0
127.5°	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7	948.1	947.6	946.4
130°	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9	992.1	991.4	990.4
132.5°	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2	1034.1	1033.9	1033.2
135°	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8	1094.3	1093.8	1092.9
137.5°	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3	1151.4	1151.5	1150.9
140°	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0	1186.5	1187.0	1186.5
142.5°	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0	1220.1	1220.2	1219.5
145°	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0	1268.3	1268.5	1267.9
147.5°	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2	1309.4	1309.8	1309.0
150°	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4	1335.8	1336.4	1335.6
152.5°	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6	1359.1	1359.5	1358.9
155°	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5	1391.2	1392.0	1391.4
157.5°	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9	1417.7	1418.5	1417.9
160°	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4	1434.3	1435.4	1434.9
162.5°	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4	1449.8	1451.2	1450.8
165°	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7	1469.3	1470.8	1470.5
167.5°	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5	1484.2	1486.0	1485.7
170°	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0	1491.9	1493.9	1493.8
172.5°	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8	1497.6	1499.3	1499.2
175°	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2	1504.2	1506.1	1506.1
177.5°	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9	1506.2	1507.6	1507.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1043.3	1039.4	1038.3	1039.7	1038.3	1039.4	1043.3	1043.6	1044.0	1046.9	1042.9
5°	962.5	958.1	960.3	959.4	960.3	958.1	962.5	967.0	967.9	971.9	974.7
7.5°	891.6	886.0	880.1	882.0	880.1	886.0	891.6	891.7	898.6	903.8	907.3
10°	841.8	837.4	834.7	836.9	834.7	837.4	841.8	847.7	850.3	856.6	863.3
12.5°	800.0	797.3	795.0	794.0	795.0	797.3	800.0	806.2	812.4	819.8	827.2
15°	743.0	737.7	735.5	729.6	735.5	737.7	743.0	748.4	760.4	763.6	774.8
17.5°	690.5	688.8	682.9	680.4	682.9	688.8	690.5	695.1	700.7	712.2	720.6
20°	659.4	657.6	651.9	655.4	651.9	657.6	659.4	666.2	670.6	680.0	688.0
22.5°	633.7	629.7	627.8	626.8	627.8	629.7	633.7	636.8	642.7	651.3	660.5
25°	597.3	591.5	589.3	586.6	589.3	591.5	597.3	599.1	605.4	613.8	618.7
27.5°	561.0	557.8	554.9	554.2	554.9	557.8	561.0	563.5	568.9	576.4	585.2
30°	537.4	534.3	532.0	532.0	532.0	534.3	537.4	542.8	546.7	553.5	560.2
32.5°	516.3	513.8	511.6	511.3	511.6	513.8	516.3	519.2	523.9	531.3	538.4
35°	485.5	482.0	481.0	478.4	481.0	482.0	485.5	487.8	492.7	498.0	503.9
37.5°	453.6	450.6	450.6	450.3	450.6	450.6	453.6	457.5	461.7	466.5	473.6
40°	433.3	431.0	430.5	427.4	430.5	431.0	433.3	435.0	439.5	445.7	451.1
42.5°	411.4	410.3	408.7	407.3	408.7	410.3	411.4	415.0	418.7	423.2	430.0
45°	381.8	378.7	378.7	376.4	378.7	378.7	381.8	385.0	386.8	392.1	401.1
47.5°	351.2	348.8	349.0	346.7	349.0	348.8	351.2	352.2	355.1	360.3	365.2
50°	330.8	329.5	329.1	328.1	329.1	329.5	330.8	330.4	334.0	338.9	345.6
52.5°	310.5	309.8	311.5	309.5	311.5	309.8	310.5	311.4	313.9	317.1	323.4
55°	283.0	281.6	284.3	281.6	284.3	281.6	283.0	282.1	283.0	286.1	290.2
57.5°	251.4	250.2	252.6	251.2	252.6	250.2	251.4	251.6	254.3	254.8	258.3
60°	230.7	228.0	229.4	229.8	229.4	228.0	230.7	231.6	232.5	232.9	236.5
62.5°	206.0	204.4	205.3	203.4	205.3	204.4	206.0	208.0	209.9	212.2	214.3
65°	171.3	169.9	168.1	167.2	168.1	169.9	171.3	172.1	177.0	179.7	184.6
67.5°	143.9	140.7	140.6	141.3	140.6	140.7	143.9	143.7	147.2	149.4	152.7
70°	123.8	123.8	123.4	123.4	123.4	123.8	123.8	126.5	128.3	130.1	132.3
72.5°	109.9	109.5	108.7	108.4	108.7	109.5	109.9	110.8	111.8	113.7	115.9
75°	88.5	88.9	88.1	87.6	88.1	88.9	88.5	88.5	90.3	90.7	91.6
77.5°	65.3	63.5	64.5	63.5	64.5	63.5	65.3	67.2	67.8	69.7	69.8
80°	49.6	49.2	50.5	49.2	50.5	49.2	49.6	49.6	51.0	51.8	54.1
82.5°	39.3	38.8	39.4	38.5	39.4	38.8	39.3	38.9	39.5	40.8	40.5
85°	23.7	23.2	22.8	23.2	22.8	23.2	23.7	23.2	22.8	23.2	23.7
87.5°	13.2	12.9	13.1	13.3	13.1	12.9	13.2	12.7	12.7	12.6	12.3
90°	24.5	25.2	26.0	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3
92.5°	23.9	24.3	24.6	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3
95°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3
97.5°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9
100°	26.3	25.4	24.4	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1
102.5°	190.8	173.9	157.0	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5
105°	331.8	331.6	331.3	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2
107.5°	419.6	418.9	418.1	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6
110°	476.4	476.6	476.9	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	531.7	531.3	531.0	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5
115°	615.4	613.9	612.3	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1
117.5°	698.4	697.8	697.2	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7
120°	752.9	751.6	750.4	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0
122.5°	803.4	801.9	800.5	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8
125°	877.4	876.6	875.8	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9
127.5°	944.6	942.8	940.9	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7
130°	989.2	987.9	986.7	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9
132.5°	1032.0	1030.8	1029.5	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2
135°	1091.4	1089.9	1088.4	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8
137.5°	1149.6	1148.3	1147.0	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3
140°	1185.0	1183.5	1182.1	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0
142.5°	1218.0	1216.5	1215.0	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0
145°	1266.4	1264.9	1263.4	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0
147.5°	1307.2	1305.4	1303.6	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2
150°	1333.6	1331.6	1329.6	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4
152.5°	1357.1	1355.4	1353.6	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6
155°	1389.4	1387.4	1385.4	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5
157.5°	1415.9	1413.9	1412.0	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9
160°	1432.9	1430.9	1428.9	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4
162.5°	1448.6	1446.4	1444.2	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4
165°	1468.5	1466.5	1464.6	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7
167.5°	1483.5	1481.4	1479.1	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5
170°	1491.6	1489.4	1487.1	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0
172.5°	1496.9	1494.7	1492.5	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8
175°	1503.8	1501.6	1499.3	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2
177.5°	1505.9	1504.3	1502.7	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1044.0	1047.9	1050.1	1055.1	1062.2	1065.8	1070.8	1074.4	1079.4	1085.5	1090.5
5°	976.4	987.1	994.3	1005.5	1015.7	1026.1	1039.0	1048.4	1060.9	1075.2	1086.4
7.5°	913.6	927.0	938.9	953.7	970.7	984.0	1000.8	1018.0	1037.7	1058.0	1077.1
10°	873.6	887.0	901.7	920.1	937.0	954.9	975.1	995.1	1019.8	1042.6	1068.5
12.5°	833.9	848.7	865.3	885.7	906.3	929.2	949.7	972.3	998.7	1028.3	1056.0
15°	784.6	798.9	816.8	834.2	857.9	883.0	910.2	940.2	969.7	1002.8	1037.2
17.5°	731.8	747.5	767.2	787.4	812.4	841.6	868.4	901.2	934.4	972.9	1013.4
20°	697.4	713.5	736.8	759.1	782.0	810.5	842.3	875.8	911.1	951.8	997.0
22.5°	670.3	681.7	704.6	727.3	754.1	783.3	814.4	849.4	887.9	930.0	977.3
25°	629.9	643.3	659.9	683.5	711.3	742.2	773.4	810.5	852.6	895.5	946.0
27.5°	594.1	605.1	621.5	640.1	667.6	699.6	733.0	771.6	814.8	858.5	911.5
30°	568.7	580.7	596.4	616.0	638.0	672.9	706.8	744.9	788.7	833.8	888.3
32.5°	546.5	559.0	572.4	591.0	614.8	645.7	680.7	718.0	762.5	809.1	862.2
35°	515.5	524.0	536.5	554.8	578.1	603.1	638.9	678.2	721.6	769.8	823.0
37.5°	479.9	490.9	503.3	519.3	539.6	566.7	599.9	639.7	680.0	726.3	774.8
40°	459.2	469.4	483.3	494.9	516.3	541.0	571.4	612.9	653.2	696.5	740.8
42.5°	438.1	448.0	459.7	474.2	493.4	517.4	545.6	584.4	627.4	668.3	705.4
45°	405.0	415.3	426.5	439.9	457.8	481.0	509.2	544.5	582.1	619.7	647.8
47.5°	373.5	383.1	393.7	407.4	424.0	446.3	471.6	502.7	539.2	571.2	591.3
50°	350.9	359.9	371.5	385.0	401.1	422.1	446.2	477.0	507.4	536.5	554.8
52.5°	328.8	338.8	350.4	362.1	377.5	398.5	420.8	447.4	476.3	500.0	515.1
55°	295.5	304.9	315.6	327.7	342.9	360.8	384.5	405.5	428.3	448.4	457.4
57.5°	263.4	271.6	281.7	294.3	308.0	324.6	343.4	363.6	379.6	393.9	404.0
60°	242.3	249.4	258.8	269.6	284.3	299.5	316.5	335.3	347.8	359.9	369.3
62.5°	220.8	227.6	236.7	246.3	259.3	273.5	289.7	304.9	317.1	325.2	336.0
65°	188.6	195.4	202.9	213.3	223.5	235.1	249.9	261.1	269.6	278.5	285.2
67.5°	158.7	164.3	171.5	179.5	188.2	199.4	210.9	220.2	225.9	231.4	239.4
70°	139.1	143.5	149.3	155.6	165.0	176.2	185.1	192.3	196.3	201.6	211.5
72.5°	119.0	124.2	129.7	136.0	143.5	152.9	160.7	167.9	170.5	174.8	181.1
75°	93.8	96.6	101.1	105.5	110.9	118.9	126.5	128.3	130.5	134.1	138.6
77.5°	71.0	73.4	75.2	78.2	82.4	88.9	92.9	95.6	96.1	97.5	101.9
80°	56.3	57.7	59.5	61.7	63.5	68.9	71.1	73.8	74.6	76.0	78.3
82.5°	41.3	42.6	43.7	45.6	48.5	50.6	52.9	55.5	55.7	56.7	57.2
85°	24.1	24.6	23.7	24.6	25.1	25.9	28.2	30.4	30.0	29.5	30.8
87.5°	12.4	12.1	11.5	12.1	11.1	11.1	10.8	10.7	11.0	11.4	11.7
90°	19.1	17.8	16.1	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1
92.5°	19.1	17.8	16.3	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1
95°	19.1	17.8	27.2	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5
97.5°	47.9	54.8	73.4	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7
100°	157.0	194.0	193.0	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1
102.5°	240.5	247.5	246.8	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6
105°	332.2	332.2	332.2	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8
107.5°	420.5	420.5	420.0	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3
110°	478.6	479.3	478.9	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	535.5	536.4	536.1	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4
115°	621.0	622.1	621.8	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4
117.5°	704.0	705.2	704.3	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2
120°	756.5	756.9	756.2	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7
122.5°	807.3	807.8	807.4	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9
125°	881.9	882.9	882.9	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1
127.5°	949.3	949.8	949.9	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9
130°	993.7	994.4	994.1	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7
132.5°	1034.4	1034.5	1035.1	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5
135°	1095.4	1095.8	1096.3	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4
137.5°	1151.2	1151.2	1151.6	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4
140°	1185.5	1185.0	1185.3	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9
142.5°	1219.9	1219.8	1219.4	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9
145°	1267.7	1267.5	1267.5	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2
147.5°	1308.8	1308.5	1308.2	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6
150°	1334.9	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4
152.5°	1358.1	1357.5	1357.1	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2
155°	1389.7	1389.1	1388.5	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4
157.5°	1416.1	1415.3	1415.3	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1
160°	1432.4	1431.4	1431.2	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9
162.5°	1447.0	1445.6	1445.4	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2
165°	1466.3	1464.8	1464.6	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4
167.5°	1480.7	1478.9	1478.6	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6
170°	1488.0	1486.0	1485.7	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7
172.5°	1494.0	1492.2	1491.8	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1
175°	1500.2	1498.2	1498.1	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8
177.5°	1503.5	1502.0	1501.8	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1094.4	1097.7	1102.3	1107.7	1112.0	1116.6	1119.1	1119.1	1121.3	1125.9	1132.0
5°	1097.6	1109.2	1120.3	1134.7	1145.8	1158.8	1168.6	1178.0	1186.5	1197.2	1208.4
7.5°	1096.7	1115.9	1136.1	1158.6	1183.5	1203.2	1223.6	1239.5	1255.2	1275.7	1291.9
10°	1093.1	1118.1	1145.4	1174.0	1205.3	1232.6	1257.1	1279.5	1301.0	1323.4	1343.4
12.5°	1086.7	1118.5	1151.8	1186.2	1225.7	1256.9	1288.7	1312.4	1337.5	1361.9	1386.7
15°	1077.0	1114.6	1154.8	1202.6	1250.9	1285.8	1317.1	1347.9	1371.1	1398.9	1422.6
17.5°	1057.0	1105.4	1156.1	1208.3	1254.7	1295.3	1328.1	1357.4	1382.2	1412.6	1444.8
20°	1045.3	1097.6	1150.3	1206.2	1250.4	1292.0	1323.8	1354.2	1385.0	1424.8	1464.1
22.5°	1028.8	1084.7	1140.7	1193.7	1240.4	1280.6	1313.4	1350.7	1391.1	1436.2	1483.8
25°	1002.8	1060.5	1115.9	1166.4	1212.0	1253.2	1297.9	1347.9	1397.1	1456.6	1525.0
27.5°	969.8	1025.4	1074.9	1128.3	1173.5	1225.9	1281.7	1335.9	1406.9	1488.7	1574.1
30°	945.1	997.9	1044.8	1095.4	1146.8	1204.5	1267.0	1330.9	1415.4	1511.6	1613.1
32.5°	916.5	964.2	1010.8	1059.5	1118.9	1182.2	1248.8	1327.0	1428.0	1537.3	1642.4
35°	866.9	909.8	954.9	1009.0	1072.1	1140.9	1225.9	1321.1	1443.1	1560.7	1655.1
37.5°	814.9	848.7	894.1	951.1	1019.8	1099.4	1195.8	1311.6	1436.9	1542.4	1582.5
40°	774.8	806.5	854.4	914.3	982.2	1069.4	1177.6	1296.5	1422.6	1495.9	1492.8
42.5°	735.0	767.2	813.2	873.5	944.3	1041.9	1153.3	1276.9	1383.3	1411.2	1353.0
45°	674.2	704.1	749.3	810.1	886.1	988.5	1105.6	1224.1	1292.0	1246.9	1131.5
47.5°	612.2	641.2	683.1	742.7	825.6	932.8	1043.5	1140.7	1150.3	1053.3	915.0
50°	571.4	598.7	638.4	701.9	782.4	887.0	993.9	1070.3	1046.6	928.2	785.5
52.5°	531.7	557.8	595.1	655.0	737.3	839.8	935.2	995.1	940.4	814.4	686.0
55°	473.0	498.0	535.6	590.6	665.2	759.1	842.7	864.6	784.2	657.2	553.5
57.5°	417.3	435.7	472.8	521.3	593.3	676.1	736.1	732.1	643.3	529.0	454.6
60°	380.5	397.0	432.3	477.0	545.4	619.7	661.7	643.8	553.9	459.6	388.1
62.5°	346.1	361.6	391.2	432.3	491.0	555.6	586.2	561.5	476.6	393.8	336.9
65°	294.2	305.3	329.1	367.0	413.1	457.8	485.1	448.8	373.8	311.2	268.2
67.5°	245.6	255.3	276.4	303.7	335.4	366.3	377.3	343.4	285.0	242.8	212.6
70°	214.1	223.1	237.4	262.9	283.9	305.8	311.2	280.8	232.0	199.8	181.1
72.5°	184.1	192.3	204.8	222.8	237.4	250.0	252.5	224.3	186.9	164.8	150.3
75°	140.3	147.6	155.6	162.3	171.7	173.9	173.0	151.1	131.0	116.2	108.2
77.5°	103.1	106.2	111.1	113.7	114.2	114.0	109.4	95.6	85.2	79.1	75.9
80°	79.6	81.8	83.2	84.0	84.5	80.0	75.1	66.6	63.0	59.5	55.4
82.5°	57.8	59.3	60.6	60.8	58.4	54.7	50.1	45.9	43.4	41.6	40.0
85°	31.3	31.8	31.3	29.1	25.9	24.6	23.7	22.8	22.4	21.9	21.9
87.5°	11.7	11.0	9.6	10.4	10.8	10.8	11.1	11.1	11.1	11.4	11.5
90°	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3
92.5°	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3
95°	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3
97.5°	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9
100°	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1
102.5°	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5
105°	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6
110°	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5
115°	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1
117.5°	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7
120°	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0
122.5°	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8
125°	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9
127.5°	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7
130°	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9
132.5°	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2
135°	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8
137.5°	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3
140°	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0
142.5°	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0
145°	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0
147.5°	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2
150°	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4
152.5°	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6
155°	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5
157.5°	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9
160°	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4
162.5°	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4
165°	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7
167.5°	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5
170°	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0
172.5°	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8
175°	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2
177.5°	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1136.6	1136.6	1142.7	1142.4	1146.3	1144.9	1145.6
5°	1221.8	1229.4	1236.1	1240.6	1247.3	1249.1	1248.2
7.5°	1310.2	1327.1	1335.3	1346.6	1348.7	1354.5	1353.9
10°	1364.9	1381.5	1394.0	1403.8	1408.8	1415.0	1415.4
12.5°	1407.8	1421.9	1433.0	1442.1	1448.0	1450.0	1451.2
15°	1441.4	1457.0	1470.0	1482.9	1490.6	1496.3	1499.5
17.5°	1475.2	1499.3	1522.2	1539.8	1550.4	1559.3	1559.2
20°	1501.2	1529.0	1557.6	1577.7	1598.3	1607.2	1608.6
22.5°	1529.1	1571.6	1608.4	1639.6	1666.6	1675.9	1679.4
25°	1587.1	1642.5	1699.4	1743.2	1774.4	1792.8	1795.4
27.5°	1657.1	1732.2	1791.9	1832.3	1858.3	1871.9	1874.8
30°	1706.5	1775.8	1829.5	1859.8	1871.9	1873.7	1867.0
32.5°	1728.6	1780.5	1801.9	1800.1	1776.4	1760.7	1754.6
35°	1701.6	1690.8	1638.5	1576.0	1528.1	1497.7	1489.6
37.5°	1548.5	1456.0	1359.7	1265.2	1214.8	1189.2	1145.2
40°	1397.6	1265.7	1165.5	1086.0	1029.2	983.5	972.8
42.5°	1227.3	1091.1	991.0	922.8	877.5	846.2	832.6
45°	986.3	869.1	786.4	734.1	699.2	676.4	666.2
47.5°	788.8	698.2	637.9	599.2	572.7	552.8	547.3
50°	680.4	608.0	557.1	524.4	504.3	489.1	482.8
52.5°	591.0	532.5	493.4	466.5	447.5	438.0	432.7
55°	487.8	437.2	409.1	387.6	376.9	369.3	365.7
57.5°	398.9	362.4	341.8	327.0	317.1	312.2	310.5
60°	349.1	320.6	301.8	290.2	283.4	277.2	275.4
62.5°	305.1	282.7	268.1	258.0	251.2	248.6	247.5
65°	245.9	231.2	220.4	214.1	208.8	207.9	207.4
67.5°	195.4	186.8	181.2	174.6	172.7	169.6	169.0
70°	167.2	161.4	154.7	152.5	150.2	147.1	147.6
72.5°	141.8	136.0	131.5	128.5	127.7	126.3	127.5
75°	103.8	101.9	100.1	97.9	97.0	97.0	96.6
77.5°	74.0	72.5	70.5	69.2	69.0	67.1	67.8
80°	53.6	51.4	50.5	51.0	49.6	49.2	49.2
82.5°	39.7	38.9	38.0	38.1	37.8	37.4	37.7
85°	21.9	21.4	21.4	21.0	21.0	20.6	20.6
87.5°	12.1	12.7	12.2	12.1	12.2	12.7	13.3
90°	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.2	476.4	476.1	476.4	476.6	476.9	477.2



TEST NUMBER: P333692-935

CATALOG NUMBER: S125RDIW-S850D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)