

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333707-940

Luminaire Tested: **S125RDIW-S1090D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333707-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D770U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6140.7 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	110	110	110	110		103	103	103	103		90	90	90		78	78	78		67	67	67	61	
1	101	96	92	89		94	90	87	84		79	77	74		69	67	65		59	58	57	52	
2	92	84	78	73		86	79	74	69		70	66	62		61	58	55		52	50	48	44	
3	84	74	67	61		78	70	63	58		62	57	52		54	50	47		47	44	41	38	
4	77	66	58	52		72	62	55	50		55	49	45		48	44	40		42	39	36	33	
5	71	59	51	45		66	56	48	43		49	43	39		43	39	35		38	34	31	28	
6	65	53	45	39		61	50	43	37		45	39	34		39	35	31		34	31	28	25	
7	60	48	40	34		57	45	38	33		41	35	30		36	31	27		32	28	25	22	
8	56	44	36	31		53	41	34	29		37	31	27		33	28	25		29	25	22	20	
9	52	40	33	27		49	38	31	26		34	28	24		30	26	22		27	23	20	18	
10	49	37	30	25		46	35	28	24		31	26	22		28	23	20		25	21	18	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.4
10°-20°	418.8	6.8
20°-30°	607.3	9.9
30°-40°	692.2	11.3
40°-50°	674.7	11.0
50°-60°	567.9	9.2
60°-70°	398.1	6.5
70°-80°	204.6	3.3
80°-90°	53.5	0.9
90°-100°	57.0	0.9
100°-110°	168.2	2.7
110°-120°	285.0	4.6
120°-130°	375.0	6.1
130°-140°	420.2	6.8
140°-150°	411.8	6.7
150°-160°	345.9	5.6
160°-170°	229.9	3.7
170°-180°	80.5	1.3
0°-30°	1176.0	19.2
0°-40°	1868.2	30.4
0°-60°	3110.9	50.7
0°-90°	3767.1	61.3
90°-120°	510.2	8.3
90°-150°	1717.2	28.0
90°-180°	2374.0	38.7
0°-180°	6140.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	1	6	11	14	16	5
95°	43	45	51	55	57	46
105°	151	154	158	162	164	161
115°	285	288	289	289	288	282
125°	416	420	421	420	419	373
135°	541	545	546	546	544	417
145°	656	659	661	661	659	410
155°	751	751	751	754	751	346
165°	816	815	816	818	814	230
175°	849	846	846	849	845	81
180°	851	851	851	851	851	



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.3	21.0	19.8	18.5	17.2	16.6	16.6	16.6	16.6	16.6	16.7
90°	0.6	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3
92.5°	16.1	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4
95°	43.1	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0
97.5°	71.5	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1
100°	92.6	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6
102.5°	115.5	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9
105°	151.0	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1
107.5°	190.1	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9
110°	217.1	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	244.7	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1
115°	285.3	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1
117.5°	326.1	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6
120°	351.5	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4
122.5°	379.1	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8
125°	416.3	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7
127.5°	456.1	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0
130°	479.9	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4
132.5°	503.7	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8
135°	541.4	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1
137.5°	576.9	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5
140°	599.8	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3
142.5°	622.5	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9
145°	656.0	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7
147.5°	687.0	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4
150°	707.7	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6
152.5°	724.6	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9
155°	750.6	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9
157.5°	774.0	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7
160°	787.7	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0
162.5°	800.0	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3
165°	816.2	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1
167.5°	830.0	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2
170°	837.4	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6
172.5°	842.7	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9
175°	848.6	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9
177.5°	851.7	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	16.9	17.0	17.1	17.1	17.0	16.9	16.8	16.7
90°	12.0	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	27.4	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	53.1	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	83.1	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	103.9	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	125.4	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.0	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.3	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.3	223.7	224.2	224.4	224.2	224.0	223.9	223.7



TEST NUMBER: P333707-940

CATALOG NUMBER: S125RDIW-S1090D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.3	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	289.0	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.7	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.7	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.4	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.9	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.3	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.6	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.6	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.6	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.1	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	690.7	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.3	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	752.5	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.4	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	787.6	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.0	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	816.7	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	829.1	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	836.5	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	841.8	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	847.7	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	850.4	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)