

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333698-935

Luminaire Tested: **S125RDIW-S850D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333698-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8169.8 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	58	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7647	7647	7647
5°	7664	7577	7623
10°	7606	7506	7506
15°	7515	7353	7294
20°	7399	7142	7056
25°	7264	6933	6780
30°	7095	6689	6475
35°	6923	6437	6133
40°	6762	6175	5798
45°	6566	5881	5431
50°	6370	5561	5050
55°	6141	5255	4641
60°	5913	4885	4204
65°	5644	4455	3703
70°	5336	3916	3191
75°	4908	3301	2655
80°	4322	2592	2228
85°	3646	2119	1993



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	1.4
10°-20°	311.1	3.8
20°-30°	451.2	5.5
30°-40°	514.2	6.3
40°-50°	501.2	6.1
50°-60°	421.9	5.2
60°-70°	295.7	3.6
70°-80°	152.0	1.9
80°-90°	42.0	0.5
90°-100°	63.5	0.8
100°-110°	391.6	4.8
110°-120°	710.2	8.7
120°-130°	911.5	11.2
130°-140°	980.4	12.0
140°-150°	920.2	11.3
150°-160°	744.4	9.1
160°-170°	481.4	5.9
170°-180°	166.0	2.0
0°-30°	873.6	10.7
0°-40°	1387.8	17.0
0°-60°	2310.8	28.3
0°-90°	2800.6	34.3
90°-120°	1165.3	14.3
90°-150°	3977.4	48.7
90°-180°	5369.0	65.7
0°-180°	8169.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1182	1178	1169	1177	1176	112
15°	1124	1118	1100	1099	1091	317
25°	1019	1005	973	961	951	469
35°	878	856	816	791	778	550
45°	719	692	644	609	595	554
55°	545	516	467	428	412	488
65°	369	338	292	257	242	366
75°	197	169	132	113	106	208
85°	49	34	29	28	27	55
90°	1	12	21	27	31	5
95°	74	67	21	27	27	94
105°	381	386	386	386	385	404
115°	716	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1269	1276	1274	1271	1264	978
145°	1471	1474	1474	1474	1467	920
155°	1620	1613	1615	1618	1608	746
165°	1710	1702	1703	1710	1700	483
175°	1748	1741	1742	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1186.0	1185.6	1185.1	1184.6	1184.1	1183.1	1181.6	1179.9	1178.4	1176.7	1178.4
5°	1182.2	1181.4	1180.5	1179.7	1179.0	1177.5	1175.3	1173.1	1170.9	1168.7	1170.7
7.5°	1170.5	1169.8	1169.0	1168.2	1167.5	1165.8	1163.2	1160.5	1158.0	1155.3	1156.7
10°	1159.8	1159.2	1158.6	1158.0	1157.4	1155.7	1153.0	1150.1	1147.4	1144.6	1145.1
12.5°	1147.6	1146.9	1146.1	1145.4	1144.6	1142.4	1138.6	1134.9	1131.2	1127.4	1127.8
15°	1124.0	1122.8	1121.6	1120.4	1119.2	1116.5	1112.4	1108.2	1104.1	1099.8	1099.7
17.5°	1097.3	1095.5	1093.7	1091.9	1090.0	1086.5	1081.2	1076.0	1070.7	1065.5	1064.5
20°	1076.6	1074.6	1072.6	1070.7	1068.7	1064.5	1058.2	1051.8	1045.4	1039.1	1038.1
22.5°	1053.7	1051.7	1049.7	1047.8	1045.8	1041.5	1034.7	1028.1	1021.4	1014.8	1012.8
25°	1019.4	1016.4	1013.4	1010.5	1007.5	1002.3	995.0	987.6	980.2	972.9	970.3
27.5°	980.1	976.5	972.8	969.2	965.6	959.8	952.0	944.1	936.3	928.3	924.7
30°	951.4	947.6	943.9	940.1	936.3	930.2	922.0	913.6	905.3	896.9	892.3
32.5°	923.5	919.1	914.7	910.3	905.9	899.4	891.0	882.4	873.9	865.4	860.4
35°	878.1	873.3	868.6	863.8	859.0	852.1	843.3	834.3	825.4	816.4	810.6
37.5°	833.5	827.8	822.0	816.1	810.4	802.9	793.7	784.4	775.2	765.9	759.1
40°	802.1	796.2	790.1	784.2	778.3	770.5	761.0	751.4	741.9	732.4	724.8
42.5°	769.2	763.1	757.0	750.8	744.7	736.8	726.9	717.0	707.1	697.3	690.1
45°	718.9	713.2	707.4	701.6	695.9	687.5	676.6	665.7	654.8	643.9	635.8
47.5°	666.9	660.8	654.7	648.7	642.6	634.0	623.0	612.0	601.0	590.0	581.8
50°	634.0	627.4	620.9	614.3	607.8	598.8	587.5	576.2	564.8	553.5	545.2
52.5°	598.2	591.5	584.8	578.1	571.4	562.7	552.0	541.3	530.5	519.9	510.9
55°	545.4	539.1	532.8	526.4	520.0	511.3	500.2	489.0	477.9	466.7	457.8
57.5°	492.1	485.3	478.5	471.7	465.0	456.2	445.5	434.7	424.0	413.3	404.6
60°	457.8	450.9	443.9	437.0	430.0	421.2	410.4	399.7	389.0	378.2	369.5
62.5°	421.4	414.7	408.1	401.4	394.8	386.1	375.1	364.3	353.4	342.5	334.4
65°	369.3	362.6	355.8	349.0	342.2	333.6	323.1	312.5	302.0	291.5	283.5
67.5°	317.6	310.8	304.1	297.4	290.6	282.1	272.1	262.0	251.9	241.8	234.5
70°	282.6	275.8	269.1	262.3	255.5	247.2	237.3	227.3	217.4	207.4	201.3
72.5°	248.2	241.6	235.1	228.4	221.9	213.9	204.6	195.3	186.0	176.7	171.0
75°	196.7	190.8	184.8	178.8	172.9	165.7	157.4	149.0	140.7	132.3	127.9
77.5°	145.6	140.8	136.0	131.3	126.5	120.8	114.1	107.5	100.7	94.1	91.0
80°	116.2	111.5	106.7	101.9	97.2	92.0	86.4	80.8	75.3	69.7	67.9
82.5°	87.6	83.3	79.0	74.7	70.4	66.4	62.6	58.8	54.9	51.1	50.3
85°	49.2	45.6	42.0	38.5	34.9	32.5	31.6	30.6	29.6	28.6	28.4
87.5°	16.7	16.1	15.4	14.7	14.1	13.9	14.1	14.4	14.6	14.9	15.2
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2
92.5°	20.0	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2
95°	73.9	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2
97.5°	154.2	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6
100°	216.5	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6
102.5°	279.7	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7
105°	381.1	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0
110°	554.7	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	619.1	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6
115°	715.5	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0
117.5°	815.3	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4
120°	877.4	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5
122.5°	932.5	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6
125°	1017.4	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4
127.5°	1098.5	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6
130°	1148.3	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3
132.5°	1198.1	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6
135°	1268.9	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5
137.5°	1333.9	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5
140°	1376.5	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4
142.5°	1414.8	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3
145°	1471.1	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9
147.5°	1520.4	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7
150°	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0
152.5°	1581.5	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0
155°	1620.1	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8
157.5°	1649.9	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5
160°	1670.7	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3
162.5°	1687.3	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4
165°	1709.6	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8
167.5°	1726.1	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5
170°	1735.5	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0
172.5°	1741.7	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1
175°	1748.4	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3
177.5°	1751.5	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1184.0	1184.0	<i>1184.0</i>	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1179.9	1181.6	<i>1183.1</i>	1183.9	1183.7	1183.5	1183.4	1183.2
5°	1172.7	1174.7	<i>1176.6</i>	1177.5	1177.1	1176.6	1176.3	1175.9
7.5°	1158.1	1159.5	<i>1160.9</i>	1161.3	1160.9	1160.5	1160.0	1159.6
10°	1145.7	1146.3	<i>1146.9</i>	1146.9	1146.3	1145.7	1145.1	1144.6
12.5°	1128.3	1128.7	<i>1129.1</i>	1128.9	1128.0	1127.0	1126.2	1125.2
15°	1099.5	1099.2	<i>1099.1</i>	1098.1	1096.3	1094.5	1092.7	1090.9
17.5°	1063.5	1062.6	<i>1061.5</i>	1060.3	1058.9	1057.4	1055.9	1054.5
20°	1037.1	1036.0	<i>1035.1</i>	1033.7	1031.9	1030.1	1028.3	1026.6
22.5°	1010.8	1008.9	<i>1006.9</i>	1005.2	1003.8	1002.3	1000.8	999.4
25°	967.8	965.2	<i>962.6</i>	960.2	957.9	955.8	953.6	951.4
27.5°	921.1	917.5	<i>913.9</i>	911.0	909.0	906.8	904.7	902.6
30°	887.8	883.2	<i>878.6</i>	875.5	873.7	871.8	870.0	868.2
32.5°	855.3	850.2	<i>845.2</i>	841.5	839.3	837.1	834.7	832.5
35°	804.9	799.1	<i>793.3</i>	789.1	786.3	783.5	780.8	777.9
37.5°	752.2	745.2	<i>738.3</i>	733.5	730.8	728.1	725.4	722.7
40°	717.2	709.7	<i>702.1</i>	697.2	694.8	692.4	690.0	687.7
42.5°	682.9	675.6	<i>668.4</i>	663.0	659.5	656.0	652.5	649.0
45°	627.9	620.0	<i>612.0</i>	606.6	603.6	600.6	597.6	594.6
47.5°	573.6	565.4	<i>557.2</i>	551.5	548.2	544.9	541.6	538.3
50°	536.8	528.5	<i>520.1</i>	514.4	511.5	508.5	505.5	502.6
52.5°	502.0	492.9	<i>484.0</i>	477.9	475.0	472.0	469.1	466.1
55°	448.9	440.0	<i>431.0</i>	424.9	421.8	418.6	415.4	412.2
57.5°	395.8	387.1	<i>378.3</i>	372.6	369.7	366.9	364.1	361.3
60°	360.8	352.0	<i>343.3</i>	337.4	334.4	331.5	328.5	325.5
62.5°	326.2	318.1	<i>310.0</i>	304.5	301.5	298.5	295.6	292.6
65°	275.6	267.7	<i>259.7</i>	254.3	251.2	248.3	245.3	242.3
67.5°	227.2	220.0	<i>212.7</i>	207.8	205.5	203.1	200.7	198.4
70°	195.1	189.0	<i>182.8</i>	178.6	176.2	173.7	171.4	169.0
72.5°	165.3	159.6	<i>153.9</i>	150.3	148.7	147.1	145.6	144.0
75°	123.6	119.2	<i>114.9</i>	112.0	110.6	109.2	107.8	106.4
77.5°	87.9	84.9	<i>81.8</i>	79.8	78.8	77.7	76.7	75.7
80°	66.2	64.4	<i>62.6</i>	61.5	61.1	60.7	60.3	59.9
82.5°	49.5	48.6	<i>47.8</i>	47.3	47.0	46.8	46.6	46.3
85°	28.2	28.0	<i>27.8</i>	27.6	27.4	27.2	27.0	26.9
87.5°	15.4	15.8	<i>16.0</i>	16.2	16.2	16.2	16.2	16.3
90°	23.6	25.1	<i>26.5</i>	27.6	28.5	29.4	30.2	31.1
92.5°	23.6	25.1	<i>26.5</i>	27.4	27.8	28.2	28.7	29.0
95°	23.6	25.1	<i>26.5</i>	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	<i>31.3</i>	27.2	27.2	27.2	27.2	27.2
100°	139.7	96.8	<i>53.9</i>	31.9	30.7	29.5	28.4	27.2
102.5°	271.5	263.4	<i>255.3</i>	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	<i>386.2</i>	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.0	<i>489.1</i>	488.7	487.8	487.0	486.1	485.3
110°	555.6	554.7	<i>553.9</i>	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333698-935

CATALOG NUMBER: S125RDIW-S850D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	621.5	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	720.9	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	816.9	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.9	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	938.0	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1024.2	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1103.0	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1154.4	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.5	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.9	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.6	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1378.9	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.4	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.3	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.1	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1552.6	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1579.6	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1616.7	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1647.4	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1666.5	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1684.0	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1706.5	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1723.5	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1732.3	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1739.1	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1746.5	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1749.6	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)