

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333683-935

Luminaire Tested: **S125RDIW-S850D470U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333683-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D470U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4197.4 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	98	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	75	68	62	80	71	65	59	64	59	54	57	53	49	50	47	44	41
4	78	67	59	53	73	63	56	51	57	51	47	51	46	42	45	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7647	7647	7647
5°	7664	7577	7623
10°	7606	7506	7506
15°	7515	7353	7294
20°	7399	7142	7056
25°	7264	6933	6780
30°	7095	6689	6475
35°	6923	6437	6133
40°	6762	6175	5798
45°	6566	5881	5431
50°	6370	5561	5050
55°	6141	5255	4641
60°	5913	4885	4204
65°	5644	4455	3703
70°	5336	3916	3191
75°	4908	3301	2655
80°	4322	2592	2228
85°	3646	2119	1993



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	2.7
10°-20°	311.1	7.4
20°-30°	451.2	10.7
30°-40°	514.2	12.2
40°-50°	501.2	11.9
50°-60°	421.9	10.1
60°-70°	295.7	7.0
70°-80°	152.0	3.6
80°-90°	39.5	0.9
90°-100°	33.6	0.8
100°-110°	99.2	2.4
110°-120°	168.0	4.0
120°-130°	221.1	5.3
130°-140°	247.7	5.9
140°-150°	242.8	5.8
150°-160°	203.9	4.9
160°-170°	135.6	3.2
170°-180°	47.4	1.1
0°-30°	873.6	20.8
0°-40°	1387.8	33.1
0°-60°	2310.8	55.1
0°-90°	2798.0	66.7
90°-120°	300.8	7.2
90°-150°	1012.4	24.1
90°-180°	1399.0	33.3
0°-180°	4197.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1182	1178	1169	1177	1176	112
15°	1124	1118	1100	1099	1091	317
25°	1019	1005	973	961	951	469
35°	878	856	816	791	778	550
45°	719	692	644	609	595	554
55°	545	516	467	428	412	488
65°	369	338	292	257	242	366
75°	197	169	132	113	106	208
85°	49	34	29	28	27	55
90°	0	4	6	8	9	4
95°	25	26	30	33	34	27
105°	89	91	93	96	97	95
115°	168	170	171	170	170	166
125°	246	248	248	247	247	220
135°	319	321	322	322	320	246
145°	387	388	389	389	388	242
155°	443	443	443	444	443	204
165°	481	480	481	482	480	136
175°	500	499	499	501	498	48
180°	501	501	501	501	501	



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1186.0	1185.6	1185.1	1184.6	1184.1	1183.1	1181.6	1179.9	1178.4	1176.7	1178.4
5°	1182.2	1181.4	1180.5	1179.7	1179.0	1177.5	1175.3	1173.1	1170.9	1168.7	1170.7
7.5°	1170.5	1169.8	1169.0	1168.2	1167.5	1165.8	1163.2	1160.5	1158.0	1155.3	1156.7
10°	1159.8	1159.2	1158.6	1158.0	1157.4	1155.7	1153.0	1150.1	1147.4	1144.6	1145.1
12.5°	1147.6	1146.9	1146.1	1145.4	1144.6	1142.4	1138.6	1134.9	1131.2	1127.4	1127.8
15°	1124.0	1122.8	1121.6	1120.4	1119.2	1116.5	1112.4	1108.2	1104.1	1099.8	1099.7
17.5°	1097.3	1095.5	1093.7	1091.9	1090.0	1086.5	1081.2	1076.0	1070.7	1065.5	1064.5
20°	1076.6	1074.6	1072.6	1070.7	1068.7	1064.5	1058.2	1051.8	1045.4	1039.1	1038.1
22.5°	1053.7	1051.7	1049.7	1047.8	1045.8	1041.5	1034.7	1028.1	1021.4	1014.8	1012.8
25°	1019.4	1016.4	1013.4	1010.5	1007.5	1002.3	995.0	987.6	980.2	972.9	970.3
27.5°	980.1	976.5	972.8	969.2	965.6	959.8	952.0	944.1	936.3	928.3	924.7
30°	951.4	947.6	943.9	940.1	936.3	930.2	922.0	913.6	905.3	896.9	892.3
32.5°	923.5	919.1	914.7	910.3	905.9	899.4	891.0	882.4	873.9	865.4	860.4
35°	878.1	873.3	868.6	863.8	859.0	852.1	843.3	834.3	825.4	816.4	810.6
37.5°	833.5	827.8	822.0	816.1	810.4	802.9	793.7	784.4	775.2	765.9	759.1
40°	802.1	796.2	790.1	784.2	778.3	770.5	761.0	751.4	741.9	732.4	724.8
42.5°	769.2	763.1	757.0	750.8	744.7	736.8	726.9	717.0	707.1	697.3	690.1
45°	718.9	713.2	707.4	701.6	695.9	687.5	676.6	665.7	654.8	643.9	635.8
47.5°	666.9	660.8	654.7	648.7	642.6	634.0	623.0	612.0	601.0	590.0	581.8
50°	634.0	627.4	620.9	614.3	607.8	598.8	587.5	576.2	564.8	553.5	545.2
52.5°	598.2	591.5	584.8	578.1	571.4	562.7	552.0	541.3	530.5	519.9	510.9
55°	545.4	539.1	532.8	526.4	520.0	511.3	500.2	489.0	477.9	466.7	457.8
57.5°	492.1	485.3	478.5	471.7	465.0	456.2	445.5	434.7	424.0	413.3	404.6
60°	457.8	450.9	443.9	437.0	430.0	421.2	410.4	399.7	389.0	378.2	369.5
62.5°	421.4	414.7	408.1	401.4	394.8	386.1	375.1	364.3	353.4	342.5	334.4
65°	369.3	362.6	355.8	349.0	342.2	333.6	323.1	312.5	302.0	291.5	283.5
67.5°	317.6	310.8	304.1	297.4	290.6	282.1	272.1	262.0	251.9	241.8	234.5
70°	282.6	275.8	269.1	262.3	255.5	247.2	237.3	227.3	217.4	207.4	201.3
72.5°	248.2	241.6	235.1	228.4	221.9	213.9	204.6	195.3	186.0	176.7	171.0
75°	196.7	190.8	184.8	178.8	172.9	165.7	157.4	149.0	140.7	132.3	127.9
77.5°	145.6	140.8	136.0	131.3	126.5	120.8	114.1	107.5	100.7	94.1	91.0
80°	116.2	111.5	106.7	101.9	97.2	92.0	86.4	80.8	75.3	69.7	67.9
82.5°	87.6	83.3	79.0	74.7	70.4	66.4	62.6	58.8	54.9	51.1	50.3
85°	49.2	45.6	42.0	38.5	34.9	32.5	31.6	30.6	29.6	28.6	28.4
87.5°	16.5	15.6	14.6	13.6	12.7	12.1	12.1	12.1	12.1	12.0	12.1
90°	0.4	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.3	6.7
92.5°	9.5	9.9	10.4	10.9	11.4	12.0	12.7	13.5	14.2	15.0	15.6
95°	25.4	25.6	25.7	25.9	26.1	26.6	27.5	28.3	29.2	30.0	30.7
97.5°	42.1	42.2	42.3	42.4	42.4	43.0	44.3	45.5	46.7	47.9	48.4
100°	54.7	54.7	54.7	54.7	54.7	55.2	56.3	57.4	58.5	59.7	60.5
102.5°	68.0	68.4	68.8	69.1	69.5	69.9	70.5	71.0	71.6	72.2	73.0
105°	88.9	89.4	89.8	90.2	90.7	91.2	91.7	92.2	92.7	93.2	93.8
107.5°	112.1	112.5	113.0	113.4	113.8	114.3	114.6	115.0	115.5	115.8	116.1
110°	128.0	128.5	128.9	129.3	129.8	130.1	130.4	130.6	130.9	131.1	131.4



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	144.2	144.5	144.6	144.9	145.2	145.4	145.8	146.1	146.4	146.7	146.9
115°	168.2	168.5	168.9	169.3	169.6	169.9	170.0	170.2	170.4	170.6	170.5
117.5°	192.3	192.3	192.5	192.7	192.9	193.0	193.2	193.3	193.5	193.6	193.7
120°	207.2	207.7	208.1	208.5	209.0	209.2	209.3	209.4	209.5	209.6	209.6
122.5°	223.4	223.6	223.8	223.9	224.0	224.3	224.5	224.7	225.0	225.2	225.1
125°	245.5	246.0	246.5	247.0	247.5	247.9	248.0	248.1	248.1	248.2	248.1
127.5°	268.9	269.1	269.5	269.8	270.1	270.3	270.4	270.4	270.5	270.7	270.6
130°	282.9	283.4	283.8	284.2	284.6	285.0	285.2	285.3	285.5	285.7	285.6
132.5°	297.0	297.6	298.4	299.1	299.8	300.1	300.1	300.1	300.1	300.0	299.9
135°	319.2	319.8	320.3	320.8	321.3	321.6	321.7	321.8	321.8	321.9	321.9
137.5°	340.1	340.6	341.1	341.6	342.2	342.5	342.7	342.9	343.0	343.3	343.4
140°	353.5	354.0	354.4	354.8	355.2	355.7	355.9	356.2	356.5	356.7	356.9
142.5°	367.0	367.3	367.7	368.1	368.4	368.8	369.1	369.5	369.8	370.1	370.2
145°	386.8	387.1	387.4	387.8	388.1	388.4	388.7	388.9	389.2	389.4	389.4
147.5°	405.0	405.2	405.4	405.5	405.8	406.0	406.1	406.4	406.6	406.8	407.0
150°	417.2	417.1	417.0	416.9	416.8	417.0	417.3	417.7	418.0	418.4	418.4
152.5°	427.1	427.3	427.4	427.5	427.7	427.7	427.9	428.1	428.2	428.3	428.5
155°	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.7	442.8	442.9	443.2
157.5°	456.2	456.1	455.9	455.7	455.5	455.5	455.6	455.6	455.7	455.8	456.2
160°	464.4	464.2	463.8	463.6	463.3	463.2	463.3	463.4	463.5	463.6	464.0
162.5°	471.6	471.4	471.2	471.0	470.8	470.7	470.7	470.7	470.8	470.8	471.2
165°	481.1	481.0	480.8	480.6	480.4	480.4	480.5	480.6	480.7	480.8	481.1
167.5°	489.3	489.0	488.6	488.3	487.9	487.8	487.8	487.8	487.8	487.8	488.3
170°	493.6	493.3	492.9	492.6	492.2	492.1	492.1	492.1	492.1	492.1	492.6
172.5°	496.8	496.5	496.1	495.8	495.4	495.2	495.2	495.2	495.2	495.2	495.8
175°	500.3	499.9	499.6	499.2	498.9	498.7	498.7	498.7	498.7	498.7	499.2
177.5°	502.0	501.8	501.5	501.3	500.9	500.8	500.8	500.7	500.6	500.5	500.9
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1179.9	1181.6	1183.1	1183.9	1183.7	1183.5	1183.4	1183.2
5°	1172.7	1174.7	1176.6	1177.5	1177.1	1176.6	1176.3	1175.9
7.5°	1158.1	1159.5	1160.9	1161.3	1160.9	1160.5	1160.0	1159.6
10°	1145.7	1146.3	1146.9	1146.9	1146.3	1145.7	1145.1	1144.6
12.5°	1128.3	1128.7	1129.1	1128.9	1128.0	1127.0	1126.2	1125.2
15°	1099.5	1099.2	1099.1	1098.1	1096.3	1094.5	1092.7	1090.9
17.5°	1063.5	1062.6	1061.5	1060.3	1058.9	1057.4	1055.9	1054.5
20°	1037.1	1036.0	1035.1	1033.7	1031.9	1030.1	1028.3	1026.6
22.5°	1010.8	1008.9	1006.9	1005.2	1003.8	1002.3	1000.8	999.4
25°	967.8	965.2	962.6	960.2	957.9	955.8	953.6	951.4
27.5°	921.1	917.5	913.9	911.0	909.0	906.8	904.7	902.6
30°	887.8	883.2	878.6	875.5	873.7	871.8	870.0	868.2
32.5°	855.3	850.2	845.2	841.5	839.3	837.1	834.7	832.5
35°	804.9	799.1	793.3	789.1	786.3	783.5	780.8	777.9
37.5°	752.2	745.2	738.3	733.5	730.8	728.1	725.4	722.7
40°	717.2	709.7	702.1	697.2	694.8	692.4	690.0	687.7
42.5°	682.9	675.6	668.4	663.0	659.5	656.0	652.5	649.0
45°	627.9	620.0	612.0	606.6	603.6	600.6	597.6	594.6
47.5°	573.6	565.4	557.2	551.5	548.2	544.9	541.6	538.3
50°	536.8	528.5	520.1	514.4	511.5	508.5	505.5	502.6
52.5°	502.0	492.9	484.0	477.9	475.0	472.0	469.1	466.1
55°	448.9	440.0	431.0	424.9	421.8	418.6	415.4	412.2
57.5°	395.8	387.1	378.3	372.6	369.7	366.9	364.1	361.3
60°	360.8	352.0	343.3	337.4	334.4	331.5	328.5	325.5
62.5°	326.2	318.1	310.0	304.5	301.5	298.5	295.6	292.6
65°	275.6	267.7	259.7	254.3	251.2	248.3	245.3	242.3
67.5°	227.2	220.0	212.7	207.8	205.5	203.1	200.7	198.4
70°	195.1	189.0	182.8	178.6	176.2	173.7	171.4	169.0
72.5°	165.3	159.6	153.9	150.3	148.7	147.1	145.6	144.0
75°	123.6	119.2	114.9	112.0	110.6	109.2	107.8	106.4
77.5°	87.9	84.9	81.8	79.8	78.8	77.7	76.7	75.7
80°	66.2	64.4	62.6	61.5	61.1	60.7	60.3	59.9
82.5°	49.5	48.6	47.8	47.3	47.0	46.8	46.6	46.3
85°	28.2	28.0	27.8	27.6	27.4	27.2	27.0	26.9
87.5°	12.1	12.2	12.3	12.3	12.2	12.1	12.0	11.9
90°	7.1	7.6	8.0	8.4	8.6	8.9	9.1	9.4
92.5°	16.1	16.7	17.3	17.7	17.8	18.0	18.3	18.4
95°	31.3	31.9	32.5	32.9	33.1	33.2	33.4	33.6
97.5°	49.0	49.6	50.1	50.5	50.5	50.7	50.8	50.9
100°	61.3	62.1	62.9	63.3	63.5	63.6	63.8	64.0
102.5°	73.9	74.7	75.6	76.1	76.4	76.6	76.9	77.1
105°	94.3	94.8	95.3	95.7	96.0	96.3	96.5	96.8
107.5°	116.3	116.6	116.8	117.0	117.0	116.9	116.9	116.9
110°	131.6	131.9	132.2	132.2	132.2	132.1	132.0	131.9



TEST NUMBER: P333683-935

CATALOG NUMBER: S125RDIW-S850D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.0	147.1	147.2	147.2	147.1	146.9	146.7	146.5
115°	170.4	170.3	170.2	170.1	170.0	170.0	169.9	169.8
117.5°	193.8	193.8	193.9	193.8	193.5	193.1	192.7	192.3
120°	209.6	209.6	209.6	209.4	209.1	208.7	208.4	208.0
122.5°	225.1	225.0	224.9	224.7	224.5	224.2	223.9	223.6
125°	247.9	247.7	247.5	247.4	247.3	247.2	247.1	247.0
127.5°	270.5	270.4	270.4	270.2	270.0	269.8	269.7	269.5
130°	285.5	285.4	285.3	285.2	285.0	284.8	284.6	284.5
132.5°	299.8	299.7	299.6	299.5	299.3	299.0	298.8	298.5
135°	321.9	321.9	321.9	321.8	321.4	321.1	320.7	320.4
137.5°	343.5	343.5	343.7	343.5	343.1	342.7	342.2	341.7
140°	357.1	357.2	357.4	357.2	356.8	356.4	355.9	355.5
142.5°	370.3	370.4	370.5	370.3	369.9	369.5	369.0	368.6
145°	389.4	389.4	389.4	389.3	389.1	388.8	388.6	388.3
147.5°	407.2	407.4	407.6	407.4	406.8	406.2	405.6	405.1
150°	418.4	418.4	418.4	418.3	418.1	417.9	417.8	417.6
152.5°	428.8	429.0	429.1	429.1	428.8	428.5	428.2	427.8
155°	443.6	443.9	444.3	444.3	443.8	443.4	443.0	442.6
157.5°	456.5	456.8	457.2	457.1	456.5	455.9	455.4	454.8
160°	464.3	464.7	465.0	464.9	464.5	464.1	463.6	463.2
162.5°	471.7	472.0	472.4	472.4	471.9	471.4	470.9	470.4
165°	481.5	481.8	482.2	482.1	481.6	481.0	480.5	480.0
167.5°	488.8	489.3	489.8	489.8	489.2	488.7	488.2	487.7
170°	493.1	493.6	494.2	494.1	493.5	492.9	492.3	491.7
172.5°	496.3	496.8	497.3	497.3	496.7	496.2	495.7	495.2
175°	499.7	500.3	500.8	500.8	500.2	499.6	498.9	498.3
177.5°	501.4	501.8	502.2	502.1	501.7	501.2	500.7	500.2
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4

(END OF REPORT)