

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333686-935

Luminaire Tested: **S125RDIW-S850D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333686-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D770U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5441.5 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42	37
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	57	49	43	64	54	46	41	46	40	36	39	35	32	33	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7647	7647	7647
5°	7664	7577	7623
10°	7606	7506	7506
15°	7515	7353	7294
20°	7399	7142	7056
25°	7264	6933	6780
30°	7095	6689	6475
35°	6923	6437	6133
40°	6762	6175	5798
45°	6566	5881	5431
50°	6370	5561	5050
55°	6141	5255	4641
60°	5913	4885	4204
65°	5644	4455	3703
70°	5336	3916	3191
75°	4908	3301	2655
80°	4322	2592	2228
85°	3646	2119	1993



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	2.0
10°-20°	311.1	5.7
20°-30°	451.2	8.3
30°-40°	514.2	9.4
40°-50°	501.2	9.2
50°-60°	421.9	7.8
60°-70°	295.7	5.4
70°-80°	152.0	2.8
80°-90°	40.2	0.7
90°-100°	31.3	0.6
100°-110°	192.7	3.5
110°-120°	349.6	6.4
120°-130°	448.6	8.2
130°-140°	482.6	8.9
140°-150°	452.9	8.3
150°-160°	366.4	6.7
160°-170°	237.0	4.4
170°-180°	81.7	1.5
0°-30°	873.6	16.1
0°-40°	1387.8	25.5
0°-60°	2310.8	42.5
0°-90°	2798.7	51.4
90°-120°	573.6	10.5
90°-150°	1957.7	36.0
90°-180°	2643.0	48.6
0°-180°	5441.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1182	1178	1169	1177	1176	112
15°	1124	1118	1100	1099	1091	317
25°	1019	1005	973	961	951	469
35°	878	856	816	791	778	550
45°	719	692	644	609	595	554
55°	545	516	467	428	412	488
65°	369	338	292	257	242	366
75°	197	169	132	113	106	208
85°	49	34	29	28	27	55
90°	1	6	10	13	15	4
95°	36	33	10	13	13	46
105°	188	190	190	190	190	199
115°	352	355	356	353	350	349
125°	501	505	505	503	501	447
135°	625	628	627	626	622	481
145°	724	725	725	726	722	453
155°	798	794	795	796	792	367
165°	842	838	838	842	837	238
175°	861	857	858	862	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1186.0	1185.6	1185.1	1184.6	1184.1	1183.1	1181.6	1179.9	1178.4	1176.7	1178.4
5°	1182.2	1181.4	1180.5	1179.7	1179.0	1177.5	1175.3	1173.1	1170.9	1168.7	1170.7
7.5°	1170.5	1169.8	1169.0	1168.2	1167.5	1165.8	1163.2	1160.5	1158.0	1155.3	1156.7
10°	1159.8	1159.2	1158.6	1158.0	1157.4	1155.7	1153.0	1150.1	1147.4	1144.6	1145.1
12.5°	1147.6	1146.9	1146.1	1145.4	1144.6	1142.4	1138.6	1134.9	1131.2	1127.4	1127.8
15°	1124.0	1122.8	1121.6	1120.4	1119.2	1116.5	1112.4	1108.2	1104.1	1099.8	1099.7
17.5°	1097.3	1095.5	1093.7	1091.9	1090.0	1086.5	1081.2	1076.0	1070.7	1065.5	1064.5
20°	1076.6	1074.6	1072.6	1070.7	1068.7	1064.5	1058.2	1051.8	1045.4	1039.1	1038.1
22.5°	1053.7	1051.7	1049.7	1047.8	1045.8	1041.5	1034.7	1028.1	1021.4	1014.8	1012.8
25°	1019.4	1016.4	1013.4	1010.5	1007.5	1002.3	995.0	987.6	980.2	972.9	970.3
27.5°	980.1	976.5	972.8	969.2	965.6	959.8	952.0	944.1	936.3	928.3	924.7
30°	951.4	947.6	943.9	940.1	936.3	930.2	922.0	913.6	905.3	896.9	892.3
32.5°	923.5	919.1	914.7	910.3	905.9	899.4	891.0	882.4	873.9	865.4	860.4
35°	878.1	873.3	868.6	863.8	859.0	852.1	843.3	834.3	825.4	816.4	810.6
37.5°	833.5	827.8	822.0	816.1	810.4	802.9	793.7	784.4	775.2	765.9	759.1
40°	802.1	796.2	790.1	784.2	778.3	770.5	761.0	751.4	741.9	732.4	724.8
42.5°	769.2	763.1	757.0	750.8	744.7	736.8	726.9	717.0	707.1	697.3	690.1
45°	718.9	713.2	707.4	701.6	695.9	687.5	676.6	665.7	654.8	643.9	635.8
47.5°	666.9	660.8	654.7	648.7	642.6	634.0	623.0	612.0	601.0	590.0	581.8
50°	634.0	627.4	620.9	614.3	607.8	598.8	587.5	576.2	564.8	553.5	545.2
52.5°	598.2	591.5	584.8	578.1	571.4	562.7	552.0	541.3	530.5	519.9	510.9
55°	545.4	539.1	532.8	526.4	520.0	511.3	500.2	489.0	477.9	466.7	457.8
57.5°	492.1	485.3	478.5	471.7	465.0	456.2	445.5	434.7	424.0	413.3	404.6
60°	457.8	450.9	443.9	437.0	430.0	421.2	410.4	399.7	389.0	378.2	369.5
62.5°	421.4	414.7	408.1	401.4	394.8	386.1	375.1	364.3	353.4	342.5	334.4
65°	369.3	362.6	355.8	349.0	342.2	333.6	323.1	312.5	302.0	291.5	283.5
67.5°	317.6	310.8	304.1	297.4	290.6	282.1	272.1	262.0	251.9	241.8	234.5
70°	282.6	275.8	269.1	262.3	255.5	247.2	237.3	227.3	217.4	207.4	201.3
72.5°	248.2	241.6	235.1	228.4	221.9	213.9	204.6	195.3	186.0	176.7	171.0
75°	196.7	190.8	184.8	178.8	172.9	165.7	157.4	149.0	140.7	132.3	127.9
77.5°	145.6	140.8	136.0	131.3	126.5	120.8	114.1	107.5	100.7	94.1	91.0
80°	116.2	111.5	106.7	101.9	97.2	92.0	86.4	80.8	75.3	69.7	67.9
82.5°	87.6	83.3	79.0	74.7	70.4	66.4	62.6	58.8	54.9	51.1	50.3
85°	49.2	45.6	42.0	38.5	34.9	32.5	31.6	30.6	29.6	28.6	28.4
87.5°	16.6	15.7	14.8	13.9	13.0	12.7	12.7	12.7	12.7	12.7	12.9
90°	0.6	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9
92.5°	9.8	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9
95°	36.3	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9
97.5°	75.9	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4
100°	106.5	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9
102.5°	137.7	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7
105°	187.5	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6
110°	273.0	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.7	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4
115°	352.1	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4
117.5°	401.3	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9
120°	431.9	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9
122.5°	458.9	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0
125°	500.8	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7
127.5°	540.7	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2
130°	565.2	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6
132.5°	589.7	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9
135°	624.6	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8
137.5°	656.6	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8
140°	677.5	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5
142.5°	696.4	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1
145°	724.1	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5
147.5°	748.4	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0
150°	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0
152.5°	778.4	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2
155°	797.5	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3
157.5°	812.1	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5
160°	822.3	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8
162.5°	830.5	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1
165°	841.5	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1
167.5°	849.6	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3
170°	854.3	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5
172.5°	857.3	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0
175°	860.7	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6
177.5°	862.1	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1179.9	1181.6	1183.1	1183.9	1183.7	1183.5	1183.4	1183.2
5°	1172.7	1174.7	1176.6	1177.5	1177.1	1176.6	1176.3	1175.9
7.5°	1158.1	1159.5	1160.9	1161.3	1160.9	1160.5	1160.0	1159.6
10°	1145.7	1146.3	1146.9	1146.9	1146.3	1145.7	1145.1	1144.6
12.5°	1128.3	1128.7	1129.1	1128.9	1128.0	1127.0	1126.2	1125.2
15°	1099.5	1099.2	1099.1	1098.1	1096.3	1094.5	1092.7	1090.9
17.5°	1063.5	1062.6	1061.5	1060.3	1058.9	1057.4	1055.9	1054.5
20°	1037.1	1036.0	1035.1	1033.7	1031.9	1030.1	1028.3	1026.6
22.5°	1010.8	1008.9	1006.9	1005.2	1003.8	1002.3	1000.8	999.4
25°	967.8	965.2	962.6	960.2	957.9	955.8	953.6	951.4
27.5°	921.1	917.5	913.9	911.0	909.0	906.8	904.7	902.6
30°	887.8	883.2	878.6	875.5	873.7	871.8	870.0	868.2
32.5°	855.3	850.2	845.2	841.5	839.3	837.1	834.7	832.5
35°	804.9	799.1	793.3	789.1	786.3	783.5	780.8	777.9
37.5°	752.2	745.2	738.3	733.5	730.8	728.1	725.4	722.7
40°	717.2	709.7	702.1	697.2	694.8	692.4	690.0	687.7
42.5°	682.9	675.6	668.4	663.0	659.5	656.0	652.5	649.0
45°	627.9	620.0	612.0	606.6	603.6	600.6	597.6	594.6
47.5°	573.6	565.4	557.2	551.5	548.2	544.9	541.6	538.3
50°	536.8	528.5	520.1	514.4	511.5	508.5	505.5	502.6
52.5°	502.0	492.9	484.0	477.9	475.0	472.0	469.1	466.1
55°	448.9	440.0	431.0	424.9	421.8	418.6	415.4	412.2
57.5°	395.8	387.1	378.3	372.6	369.7	366.9	364.1	361.3
60°	360.8	352.0	343.3	337.4	334.4	331.5	328.5	325.5
62.5°	326.2	318.1	310.0	304.5	301.5	298.5	295.6	292.6
65°	275.6	267.7	259.7	254.3	251.2	248.3	245.3	242.3
67.5°	227.2	220.0	212.7	207.8	205.5	203.1	200.7	198.4
70°	195.1	189.0	182.8	178.6	176.2	173.7	171.4	169.0
72.5°	165.3	159.6	153.9	150.3	148.7	147.1	145.6	144.0
75°	123.6	119.2	114.9	112.0	110.6	109.2	107.8	106.4
77.5°	87.9	84.9	81.8	79.8	78.8	77.7	76.7	75.7
80°	66.2	64.4	62.6	61.5	61.1	60.7	60.3	59.9
82.5°	49.5	48.6	47.8	47.3	47.0	46.8	46.6	46.3
85°	28.2	28.0	27.8	27.6	27.4	27.2	27.0	26.9
87.5°	13.1	13.2	13.3	13.3	13.3	13.3	13.2	13.1
90°	11.6	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	11.6	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	11.6	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	23.4	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	68.8	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	133.6	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.5	273.0	272.6	272.5	272.6	272.8	272.9	273.0



TEST NUMBER: P333686-935

CATALOG NUMBER: S125RDIW-S850D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	305.9	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.8	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	402.1	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.7	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.7	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	504.1	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.9	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	568.3	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.9	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.5	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	678.7	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.2	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.7	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.2	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.2	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.5	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	795.7	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	810.9	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.3	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	828.9	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.0	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	848.3	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	852.6	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	856.0	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	859.7	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.2	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)