

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333734-940

Luminaire Tested: **S125RDIW-S1270D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333734-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1340U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9134.6 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	1.9
10°-20°	483.7	5.3
20°-30°	701.4	7.7
30°-40°	799.4	8.8
40°-50°	779.2	8.5
50°-60°	655.9	7.2
60°-70°	459.8	5.0
70°-80°	236.3	2.6
80°-90°	62.9	0.7
90°-100°	56.6	0.6
100°-110°	348.8	3.8
110°-120°	632.6	6.9
120°-130°	811.9	8.9
130°-140°	873.3	9.6
140°-150°	819.7	9.0
150°-160°	663.1	7.3
160°-170°	428.8	4.7
170°-180°	147.9	1.6
0°-30°	1358.2	14.9
0°-40°	2157.6	23.6
0°-60°	3592.8	39.3
0°-90°	4351.9	47.6
90°-120°	1038.1	11.4
90°-150°	3542.9	38.8
90°-180°	4783.0	52.4
0°-180°	9134.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	10	18	24	28	6
95°	66	60	18	24	24	84
105°	340	344	344	344	343	360
115°	637	643	644	640	633	632
125°	906	914	914	910	906	809
135°	1130	1137	1135	1132	1126	871
145°	1310	1313	1313	1313	1307	819
155°	1443	1437	1439	1441	1433	665
165°	1523	1516	1517	1523	1515	430
175°	1558	1551	1552	1560	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.8	24.5	23.2	21.8	20.5	20.0	20.1	20.2	20.2	20.4	20.6
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	17.7	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8
95°	65.8	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8
97.5°	137.4	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6
100°	192.8	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6
102.5°	249.1	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1
105°	339.5	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5
110°	494.2	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	551.4	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6
115°	637.3	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2
117.5°	726.2	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1
120°	781.6	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5
122.5°	830.5	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1
125°	906.3	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4
127.5°	978.6	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1
130°	1022.9	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1
132.5°	1067.3	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3
135°	1130.3	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4
137.5°	1188.3	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3
140°	1226.1	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8
142.5°	1260.3	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4
145°	1310.4	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0
147.5°	1354.2	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5
150°	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5
152.5°	1408.7	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5
155°	1443.1	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3
157.5°	1469.7	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6
160°	1488.2	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5
162.5°	1503.0	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6
165°	1522.9	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6
167.5°	1537.6	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5
170°	1546.0	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1
172.5°	1551.5	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3
175°	1557.5	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7
177.5°	1560.2	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	20.9	21.1	21.4	21.5	21.4	21.3	21.2	21.1
90°	21.0	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	21.0	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	21.0	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	42.4	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	124.4	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	241.8	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.6	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.9	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333734-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	553.6	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	642.2	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	727.7	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.9	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.5	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	912.3	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.6	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1028.3	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1071.1	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.9	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.4	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.3	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.5	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.2	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1355.8	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.0	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.0	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.1	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1467.5	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1484.5	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1500.0	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1520.1	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1535.3	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1543.1	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1549.2	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1555.8	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1558.5	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)