

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333735-940

Luminaire Tested: **S125RDIW-S1270D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333735-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8499.4 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	57	49	43	64	53	46	41	46	40	36	39	35	31	32	29	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	2.0
10°-20°	483.7	5.7
20°-30°	701.4	8.3
30°-40°	799.4	9.4
40°-50°	779.2	9.2
50°-60°	655.9	7.7
60°-70°	459.8	5.4
70°-80°	236.3	2.8
80°-90°	62.9	0.7
90°-100°	99.5	1.2
100°-110°	294.0	3.5
110°-120°	497.9	5.9
120°-130°	655.3	7.7
130°-140°	734.3	8.6
140°-150°	719.7	8.5
150°-160°	604.5	7.1
160°-170°	401.8	4.7
170°-180°	140.6	1.7
0°-30°	1358.2	16.0
0°-40°	2157.6	25.4
0°-60°	3592.8	42.3
0°-90°	4351.9	51.2
90°-120°	891.4	10.5
90°-150°	3000.7	35.3
90°-180°	4148.0	48.8
0°-180°	8499.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	10	18	24	28	8
95°	75	78	89	97	100	80
105°	264	270	276	283	287	282
115°	499	503	506	504	503	493
125°	728	734	736	733	732	651
135°	946	953	954	954	950	729
145°	1146	1151	1154	1154	1151	716
155°	1312	1312	1313	1317	1312	604
165°	1426	1424	1425	1429	1423	402
175°	1483	1479	1478	1484	1477	141
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.8	24.5	23.2	21.8	20.5	20.0	20.1	20.2	20.2	20.4	20.6
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	28.0	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1
95°	75.2	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9
97.5°	124.9	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5
100°	161.9	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3
102.5°	201.7	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5
105°	263.8	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0
107.5°	332.2	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1
110°	379.4	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	427.5	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2
115°	498.6	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2
117.5°	569.8	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2
120°	614.2	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2
122.5°	662.4	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2
125°	727.5	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1
127.5°	796.9	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0
130°	838.6	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4
132.5°	880.2	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0
135°	946.2	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3
137.5°	1008.2	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7
140°	1047.9	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7
142.5°	1087.8	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3
145°	1146.3	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4
147.5°	1200.4	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4
150°	1236.5	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0
152.5°	1266.1	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2
155°	1311.7	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8
157.5°	1352.4	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0
160°	1376.4	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2
162.5°	1397.8	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7
165°	1426.2	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1
167.5°	1450.3	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2
170°	1463.2	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2
172.5°	1472.5	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4
175°	1482.9	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8
177.5°	1488.2	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	20.9	21.1	21.4	21.5	21.4	21.3	21.2	21.1
90°	21.0	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	47.8	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	92.6	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	145.2	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	181.6	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	219.0	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	279.6	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	344.8	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.2	390.9	391.7	392.0	391.7	391.5	391.2	390.9



TEST NUMBER: P333735-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.6	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	505.0	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.4	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	667.0	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.6	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.7	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.1	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.8	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.1	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.3	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1097.6	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1206.9	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1270.8	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1314.9	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1353.1	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1376.2	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1397.9	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1427.1	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1448.8	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1461.7	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1471.0	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1481.3	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1486.0	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)